Project		Catalog #		Type	
Prepared by		Notes		Date	



Lumière

BOCA 650-1,2,4

LED / Halogen
Ground-Mount
Recessed

Typical Applications

• Hospitality • Commerical Landscape • Outdoor Area/Site • Residential • Architectural

Discontinued 14-05-2026

Interactive Menu

- Order Information page 2
- Product Warranty

Product Certification

IP65


Product Features

wet location

Top Product Features

- Available as a fixed uplight or marker light with 1, 2 or 4 openings
- Corrosion-proof, thermoplastic, recessed housing
- Die-cast aluminum inner housing
- Die-cast aluminum or machined brass, bronze or stainless steel trim
- Three-year warranty

Dimensions



TECHNICAL DATA
8W LED
20W (max.) T3
Low Voltage

Order Information

SAMPLE ORDER NUMBER: **650-2-6LED4012-12-BZ**

Domestic Preferences	Series	Source (for LED, select from each column and combine)			Voltage	Finish	Options
[Blank]=Standard **BAA**=Buy American Act	**650-1**=3 11/16" Dia. Non-Adjustable Boca Inground Single (1) Opening **650-2**=3 11/16" Dia. Non-Adjustable Boca Inground Dual (2) Opening **650-4**=3 11/16" Dia. Non-Adjustable Boca Inground Quadruple (4) Opening	**20MR11**=12V MR11 20W max. GU4 (lamp not included)			**12**=12 Volt - Remote 12V transformer required (not included)	**Painted** **BK**=Black **BZ**=Bronze **CS**=City Silver **VE**=Verde **WT**=White	**LBB**=Less Back Box (order 650-BB recessed housing separately)
		8LED=8W LED	**27**=2700K **30**=3000K **40**=4000K*	**10**=10° Spot			
Notes (1) Only product configurations with this designated prefix are built to be compliant with the Buy American Act of 1933 (BAA). Please refer to DOMESTIC PREFERENCES website for more information. Components shipped separately may be separately analyzed under domestic preference requirements.	**Notes**	**Notes** * Not Title 20 compliant.			**Notes** Remote 12V transformer required (not included). Available from Lumiere as an accessory. See ACCESSORIES & TECHINCAL DATA section of the Lumiere catalog for Low Voltage Cable & Transformers.	**Notes** (2) Consult factory for premium / natural metals material finish.	**Notes**

Discontinued 14-05-2026

Product Specifications

Material
- Recessed housing is constructed from injection molded, outdoor rated engineering thermoplastic
- Trim and inner housing are die cast with corrosion resistant aluminum alloy
- Premium materials are machined from solid stainless steel, copper, bronze* or brass

Finish
- Fixtures are double protected by a ROHS* compliant chemical conversion undercoating and polyester powdercoat paint finish, surpassing the rigorous demands of the outdoor environment.
- A variety of standard colors are available

Gasket
- Inner recessed housing and trim ring are sealed with a high temperature silicone, wrap around gasket to prevent water intrusion

Lens
- Optical glass lens designed for horizontal throw

Hardware
- Stainless steel hardware is standard to provide maximum corrosion-resistance

Socket
- Ceramic socket with 250° C Teflon® coated lead wires and G4 bi-pin base

Electrical
- Remote 12V transformer required (not included)
- Initial power draw on LED equipped fixtures is 12 watts
- When sizing transformer use 12 watts per LED fixture
- Nominal power draw after start up is 8 watts
- LEDs are more voltage sensitive than standard halogen MR16 lamps
- The LED module is designed to operate within the range 12V+/- 1.2V
- Any less or more voltage can cause premature failures.

Lamp
- Halogen Lamp not included. Available from Lumière as an accessory
- LED modules are included and are available in three color temperatures (2700, 3000, and 4000) with a spot distribution
- Color temperature must be specified when ordering - see reverse side for details and catalog logic

Recessed Housing
- Recessed housing is available to ship in advance of complete fixture for rough in purposes
- Specify option -LBB and order separately recessed housing 650-BB

Warranty
- Lumière warrants its fixtures against defects in materials & workmanship for three (3) years
- Auxiliary equipment such as transformers, ballasts and lamps carry the original manufacturer's warranty

* For natural bronze ROHS material consult factory.