



Type "G" Fixture

(Exposed Grid)




G Grid Lay In (Standard)



Integral Grid-Lock Feature (Standard)

A Recessed Luminaire with Narrow Flanges designed to rest on exposed 15/16" or 9/16" wide Inverted Grid Tees.
 • Fixture Example: 2GR8-432-UNV-EB81-U

(Concealed T)



G Concealed T


A Recessed Luminaire with Narrow Flanges designed to rest on 15/16" wide Concealed Inverted Grid Tees

- Fixture Example 2EP3GAX-332S36I
- Optional Aluminum TK Trim Kit Available
 - Available TK Trim Finishes: Natural Anodized Aluminum (N) Standard and Baked White Enamel (W)

TK TRIM KIT

TK-14N-U	1' x 4'
TK-22N-U	2' x 2'
TK-24N-U	2' x 4'

(Slot Grid)




G Slot Grid

A Recessed Luminaire designed to rest on 9/16" Slot T Grid

- Fixture Example: 2GR8-432
- T-Bar Safety Clips Required

Type "F" Fixture

(Flange Trim)



F Flange Trim






For factory installed flange, replace "G" in fixture trim description with "F". Factory installed flange available on GC8 only, field installed kits are available for all other models and are listed below.

A Recessed Luminaire with Horizontal Steel or Aluminum (A) Flanges which conceal the edges of the ceiling opening

- Fixture example 2FC8-332
- Adjustable Swing Gates for mounting
- Optional Flange Kit available
 - Field Convertible, Converts Grid Fixture (G) to Flange Fixture (F)
 - Standard Flange Trim Finish: Baked White Enamel (W)
- Typical fixture ceiling opening requirements: **Single** – (Width) One-quarter Inch (1/4") plus nominal width, (Length) 1/4" plus nominal length.
- **Rows** - fixture quantity times fixture length plus 1/4".
- Plaster Frames available, see options and accessories section

FLANGE KITS (Field Installed)

Fixture	Fixture Size	Flange Kit	Ceiling Opening Size
GR8/GC8/GR5	1' x 4'	FCS-14W-U (Steel)	12-1/4" x 48-1/4"
GR8/GC8/GR5	2' x 2'	FCTKA-22W-U	24-1/4" x 24-1/4"
GR8/GC8/GR5	2' x 4'	FCTKA-24W-U	24-1/4" x 48-1/4"

Type "G" Fixture																																	
<p>(Exposed Grid)</p>  <p>G Grid Lay In (Standard)</p> <p>Integral Grid-Lock Feature (Standard)</p>	<p>A Recessed Luminaire with Narrow Flanges designed to rest on exposed 15/16" or 9/16" wide Inverted Grid Tees.</p> <ul style="list-style-type: none"> • Fixture example: 2EP3GX-332S36l 																																
<p>(Concealed T)</p>  <p>T Concealed T</p>	<p>A Recessed Luminaire with Narrow Flanges designed to rest on 15/16" wide Concealed Inverted Grid Tees</p> <ul style="list-style-type: none"> • Fixture Example 2EP3GX-332S36l • Optional TK Trim Kit available <ul style="list-style-type: none"> – Available TK trim finishes: Natural Anodized Aluminum (N) standard and Baked White Enamel (W) <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th colspan="2" style="text-align: center;">TK TRIM KIT</th> </tr> </thead> <tbody> <tr> <td>TK-14N-U</td> <td style="text-align: center;">1' x 4'</td> </tr> <tr> <td>TK-22N-U</td> <td style="text-align: center;">2' x 2'</td> </tr> <tr> <td>TK-24N-U</td> <td style="text-align: center;">2' x 4'</td> </tr> </tbody> </table>	TK TRIM KIT		TK-14N-U	1' x 4'	TK-22N-U	2' x 2'	TK-24N-U	2' x 4'																								
TK TRIM KIT																																	
TK-14N-U	1' x 4'																																
TK-22N-U	2' x 2'																																
TK-24N-U	2' x 4'																																
<p>(Slot Grid)</p>  <p>G Slot Grid</p>	<p>A Recessed Luminaire designed to rest on 9/16" Slot-T Grid</p> <ul style="list-style-type: none"> • Fixture example: 2EP3GAX-332S36l • T-Bar Safety Clips required • Face of luminaire/door assembly is recessed about 5/16" into ceiling 																																
Type "F" Fixture																																	
<p>(Flange)</p>  <p>F Aluminum Flange Trim with Supporting Swing Gates</p>	<p>A Recessed Luminaire with Horizontal Steel or Mitered Aluminum (M) Flanges which conceal the edges of the ceiling opening</p> <ul style="list-style-type: none"> • Complete fixture / factory installed trim. Fixture example: 2EP3FX-332S36l • Adjustable Swing Gates for mounting • Field installed Flange Kit available <ul style="list-style-type: none"> – Field Convertible, Converts Grid Fixture (G) to Flange Fixture (F) – Standard Flange Trim finish: Baked White Enamel (W) • Typical fixture ceiling opening requirements: Single – (Width) One-quarter Inch (1/4") plus nominal width, (length) 1/4" plus nominal length. • Rows - fixture quantity times fixture length plus 1/4". • Plaster frames available, see options and accessories section <p style="text-align: center;">FLANGE KITS (Steel) (Field Installed)</p> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th>Fixture</th> <th>Fixture Size</th> <th>Flange Kit</th> <th>Ceiling Opening Size</th> </tr> </thead> <tbody> <tr> <td>EP3</td> <td style="text-align: center;">1' x 2'</td> <td style="text-align: center;">F3/4-12W-U (steel)</td> <td style="text-align: center;">12-1/4" x 24-1/4"</td> </tr> <tr> <td>EP3</td> <td style="text-align: center;">1' x 4'</td> <td style="text-align: center;">F3/4M-14W-U</td> <td style="text-align: center;">12-1/4" x 48-1/4"</td> </tr> <tr> <td>EP3</td> <td style="text-align: center;">20" x 24"</td> <td style="text-align: center;">F3/4-2024W-U (steel)</td> <td style="text-align: center;">20-1/4" x 24-1/4"</td> </tr> <tr> <td>P2</td> <td style="text-align: center;">20" x 24"</td> <td style="text-align: center;">F2-2024W-U (steel)</td> <td style="text-align: center;">20-1/4" x 24-1/4"</td> </tr> <tr> <td>EP3</td> <td style="text-align: center;">2' x 2'</td> <td style="text-align: center;">F2/3M-22S-W-U</td> <td style="text-align: center;">24-1/4" x 24-1/4"</td> </tr> <tr> <td>EP3</td> <td style="text-align: center;">20" x 48"</td> <td style="text-align: center;">F3/4-28W-U (steel)</td> <td style="text-align: center;">20-1/4" x 48-1/4"</td> </tr> <tr> <td>EP3</td> <td style="text-align: center;">2' x 4'</td> <td style="text-align: center;">F2/3M-24S-W-U</td> <td style="text-align: center;">24-1/4" x 48-1/4"</td> </tr> </tbody> </table>	Fixture	Fixture Size	Flange Kit	Ceiling Opening Size	EP3	1' x 2'	F3/4-12W-U (steel)	12-1/4" x 24-1/4"	EP3	1' x 4'	F3/4M-14W-U	12-1/4" x 48-1/4"	EP3	20" x 24"	F3/4-2024W-U (steel)	20-1/4" x 24-1/4"	P2	20" x 24"	F2-2024W-U (steel)	20-1/4" x 24-1/4"	EP3	2' x 2'	F2/3M-22S-W-U	24-1/4" x 24-1/4"	EP3	20" x 48"	F3/4-28W-U (steel)	20-1/4" x 48-1/4"	EP3	2' x 4'	F2/3M-24S-W-U	24-1/4" x 48-1/4"
Fixture	Fixture Size	Flange Kit	Ceiling Opening Size																														
EP3	1' x 2'	F3/4-12W-U (steel)	12-1/4" x 24-1/4"																														
EP3	1' x 4'	F3/4M-14W-U	12-1/4" x 48-1/4"																														
EP3	20" x 24"	F3/4-2024W-U (steel)	20-1/4" x 24-1/4"																														
P2	20" x 24"	F2-2024W-U (steel)	20-1/4" x 24-1/4"																														
EP3	2' x 2'	F2/3M-22S-W-U	24-1/4" x 24-1/4"																														
EP3	20" x 48"	F3/4-28W-U (steel)	20-1/4" x 48-1/4"																														
EP3	2' x 4'	F2/3M-24S-W-U	24-1/4" x 48-1/4"																														
Type "MZ" (Fixture) 3" Parabolics																																	
<p>(Modular Trim / Aluminum)</p>  <p>MZ Modular Trim with Supporting Swing Gates</p> <p>Concealed "T" Metal Pan and Concealed "Z" Spline Application</p>	<p>A Recessed Luminaire trimmed to a Modular / Concealed finished dimension</p> <ul style="list-style-type: none"> • Complete fixture / factory installed trim Fixture example: 22EP3MZ-3U15/8-W33P • On complete ordered fixture, Modular MZ Trim matches door frame assembly unless otherwise specified • Adjustable Swing Gates for mounting • Optional Aluminum Modular (MZ) Trim Kit available <ul style="list-style-type: none"> – Field Convertible, Converts Grid Fixture (G) to Modular Fixture (MZ) – Available Aluminum Trim Finishes: Baked White Enamel (W) and Natural Anodized Aluminum (N) • For Concealed "T" and Concealed "Z" the main ceiling carries must be on the sides of the Luminaire. The weight of the luminaire exists on the Swing-Gates and must be supported by main carriers, not cross members. At each end of the luminaire, an Angle Spline must be used, Cross or Main T's cannot be used. <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th colspan="3" style="text-align: center;">MODULAR / MZ TRIM KIT / ALUMINUM</th> </tr> <tr> <th>Fixture</th> <th>Flange Kit</th> <th>Fixture Size</th> </tr> </thead> <tbody> <tr> <td>EP3</td> <td style="text-align: center;">F3/4MZ-14W-U</td> <td style="text-align: center;">1' x 4'</td> </tr> <tr> <td>EP3</td> <td style="text-align: center;">F2/3MZ/E-22W-U</td> <td style="text-align: center;">2' x 2'</td> </tr> <tr> <td>EP3</td> <td style="text-align: center;">F2/3MZ/E-24W-U</td> <td style="text-align: center;">2' x 4'</td> </tr> </tbody> </table>	MODULAR / MZ TRIM KIT / ALUMINUM			Fixture	Flange Kit	Fixture Size	EP3	F3/4MZ-14W-U	1' x 4'	EP3	F2/3MZ/E-22W-U	2' x 2'	EP3	F2/3MZ/E-24W-U	2' x 4'																	
MODULAR / MZ TRIM KIT / ALUMINUM																																	
Fixture	Flange Kit	Fixture Size																															
EP3	F3/4MZ-14W-U	1' x 4'																															
EP3	F2/3MZ/E-22W-U	2' x 2'																															
EP3	F2/3MZ/E-24W-U	2' x 4'																															