Mounting Accessories
Single Point Mount

Mounting Methods

Hook and Safety Hook

F-Bay Mounting

F-Bay Mounting Accessories"

HB HBL 15/18 OHB VHB HBL 15/18 ILED

Designation

FH-1=Fixture

3-3/8

S	(1)					
	Designation	Description				
	- SPM =Galvanized Single Monopoint Hanging Kit with Hub	Suitable for three-quarter inch (3/4") conduit mounting or for use with fixture hook, loop or safety hook. Use chain or cable set to meet NEC requirements for single point mount and to prevent cantilevering and rotation of fixture.				
	- SPM-S =Galvanized Surface Mount Hanging Kit with Hub					
	- SPM =Galvanized Single Monopoint Hanging Kit with Hub					
		Description				
• 	took	Fixture Hook (must be used with -SPM accessory)				
	1-7/8° [48mm]					

	[1-3/16 ⁻] [26mm]	
Loop	FL-1=Fixture Loop[Fixture Loop (must be used with-SPM accessory)
SHK	SHK=Fixture Hook	Fixture Hook (must be used with -SPM accessory)

Notes: (1) Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information.

Fixture Series	AYC	HB/AYC	SPM	SHK	Single Toggle	"Y" Toggle	Loop Hanger	Mounting Hardware Included
HBI/HBL		Х	Х	Х		х		
ILED	х		Х	Х	Х		Х	
CZL	Х			Х	Х	х	Х	
ВМК				х			Х	
LHBS							Х	V-hanger and chain
ОНВ		Х	Х	Х		х		V-hanger
VHB/VHBS		Х		Х		х		V-hanger
SNX	Х				Х	X ⁽²⁾		
SLSTP	Х					X ⁽²⁾		J-box cover plate w/ screws
ST		Х			Х	X ⁽²⁾		
Steeler			Х					hook
UHBS			Х					Hook
VT2 LED						х		
VT3							Х	
VT4/VT4S						х		V-hanger only
APVTS								Surface Mnt Bracket and V-clip

Notes: (2) Continuous row mount only between fixtures.



Metalux

F-Bay Mounting

F-Bay Mounting Accessories[®]



		-varia-
Mounting Methods	Catalog Logic	Description
	HBAYC-CHAIN/SET-U=Hook style V-hanger w/chain set	Two (2) Hook style V-hangers, thirty-six Inch (36") Chain Sets with S-hooks
	AYC-CHAIN/SET-U=V-hanger w/chain set	Standard V-hanger and thirty-six Inch (36") Chain Sets with S-hooks
"Y" Toggle	Y-Toggle-10-2PK=Mounting Toggle and Ten Foot (10') Cable	(2) Y-Toggle #2 Cables at 10FT long
×+	Y-Toggle-30-2PK=Mounting Toggle and Thirty (30') Cable	(2) Y-Toggle #2 Cables at 30FT long
Loop Hanger	Loop-10	Ten Foot (10') Loop Hanger #2 Cable
	Loop-30	Thirty Foot (30') Loop Hanger #2 Cable
Single Toggle	Toggle-10	Ten Foot (10') Single Toggle #2 Cable
	Toggle-30	Thirty Foot (30') Single Toggle #2 Cable

Notes: (1) Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information.



Cooper Lighting Solutions 1121 Highway 74 South Peachtree City, GA 30269 P: 770-486-4800 www.cooperlighting.com

© 2023 Cooper Lighting Solutions All Rights Reserved. Specifications and dimensions subject to change without notice.