




HALO[®]

Canless EZ-Trim
Lamp Based Canless Downlight



Product Features


- Durable metal baffle trim with attached j-box
- No housing required for installation
- Compatible with LED GU10, GU24 or E26 lamps
- Maximum lamp wattage: 15W
- IC rated, for direct contact with insulation
- Spring clips firmly secure fixture in ceiling



Scan Here to
Learn More!

Traditional Housing Features Minus the Housing

- A. Air-Tite** pre-installed gasket
- B. Quick Connect** pre-installed push-in wiring connectors
- C. Slide-N-Side** pre-installed tool-less strain reliefs eliminate need for additional non-metallic cable connectors.



Canless EZ-Trim

The Canless EZ-Trim bridges the gap between traditional downlighting (housing + trim + lamp) and canless LED downlighting. Canless EZ-Trim is available in 4" and 6" apertures and is designed to look like HALO's best-selling trim, the 6125WB. It features a durable metal trim, attached junction box, and white baffles for ultimate visual comfort.

Options for GU10, GU24, and E26 lamp bases make Canless EZ-Trim compatible with most LED lamps on the market. Shallow options are available for all aperture sizes, making this a perfect solution for 2x6 construction. It's Air-Tite, IC rated, and of course, no housings are required for installation.

HALO Canless EZ-Trim is a perfect solution for customers looking for value-priced, canless solutions in single-family and multi-family residential applications.



cut hole

wire fixture

install fixture

install lamp
* lamp not included

Also compatible with HALO mounting frames.

HL4RSMF

4" round and square
mounting frame

MF4RC

4" round mounting frame
with drywall collar



CEZ4125GU10WBICAT
CEZ4125E26WBICAT

HL6RSMF

6" round and square
mounting frame

MF6RC

6" round mounting frame
with drywall collar



CEZ6125GU24WBICAT
CEZ6125E26WBICAT



CEZ6126GU24WBICAT
CEZ6126E26WBICAT



CEZ3125GU10WBICAT

3-inch, shallow
GU10 lamp

CEZ4125GU10WBICAT

4-inch, shallow
GU10 lamp

CEZ6125GU24WBICAT

6-inch
GU24 lamp

CEZ6126GU24WBICAT

6-inch, shallow
GU24 lamp

CEZ4125E26WBICAT

4-inch, shallow
E26 lamp

CEZ6125E26WBICAT

6-inch
E26 lamp

CEZ6126E26WBICAT

6-inch, shallow
E26 lamp

Catalog Number	Description	UPC	Accessories		
			Mounting Frame	Designer Overlays	
CEZ3125GU10WBICAT	3" Canless EZ-Trim, GU10 Lamp Base, White Flange/White Baffle Trim, IC Rated, Air-Tite	080083175512			
CEZ4125GU10WBICAT	4" Canless EZ-Trim, GU10 Lamp Base, White Flange/White Baffle Trim, IC Rated, Air-Tite	080083175536	HL4RSMF 4" round and square mounting frame	MF4RC 4" round mounting frame with drywall collar	
CEZ4125E26WBICAT	4" Canless EZ-Trim, E26 Lamp Base, White Flange/White Baffle Trim, IC Rated, Air-Tite	080083175550			
CEZ6125GU24WBICAT	6" Canless EZ-Trim, GU24 Lamp Base, White Flange/White Baffle Trim, IC Rated, Air-Tite	080083175574	HL6RSMF 6" round and square mounting frame	MF6RC 6" round mounting frame with drywall collar	CEZ6125LTRMWHWB 6" lens overlay, White trim, White baffle
CEZ6126GU24WBICAT	6" Canless EZ-Trim, Shallow, GU24 Lamp Base, White Flange/White Baffle Trim, IC Rated, Air-Tite	080083175598			CEZ6125LTRMWHBB 6" lens overlay, White trim, Black baffle
CEZ6125E26WBICAT	6" Canless EZ-Trim, E26 Lamp Base, White Flange/White Baffle Trim, IC Rated, Air-Tite	080083176212			CEZ6125LTRMBKBB 6" lens overlay, Black trim, Black baffle
CEZ6126E26WBICAT	6" Canless EZ-Trim, Shallow, E26 Lamp Base, White Flange/White Baffle Trim, IC Rated, Air-Tite	080083176236			CEZ6125LTRMSN 6" lens overlay, Satin Nickel
					CEZ6125LTRMTBZ 6" lens overlay, Tuscan Bronze

Designer Overlays (compatible with CEZ6 fixtures only)

Wet location rated lens, perfect for bathrooms and soffits



CEZ6125LTRMWHWB



CEZ6125LTRMWHBB



CEZ6125LTRMBKBB






CEZ6125LTRMSN



CEZ6125LTRMTBZ

Compatible lamps (not included with fixture)

Maximum lamp wattage: **15W**

						
CEZ3125GU10WBICAT	CEZ4125GU10WBICAT	CEZ6125GU24WBICAT	CEZ6126GU24WBICAT	CEZ4125E26WBICAT	CEZ6125E26WBICAT	CEZ6126E26WBICAT
MR16 LED / GU10 PAR16 LED / GU10 MR11 LED / GU10		A19 LED / GU24 PAR38 LED / GU24 BR40 LED / GU24 BR30 LED / GU24 PAR30L LED / GU24 PAR30S LED / GU24 R30 LED / GU24	A19 LED / GU24 BR30 LED / GU24 PAR30L LED / GU24 PAR30S LED / GU24 R30L LED / GU24	MR16 LED / E26 PAR16 LED / E26	A19 LED / E26 PAR38 LED / E26 BR40 LED / E26 BR30 LED / E26 PAR30L LED / E26 PAR30S LED / E26 R30 LED / E26	A19 LED / E26 BR30 LED / E26 PAR30L LED / E26 PAR30S LED / E26 R30L LED / E26

Lighting Brands

Ametrix
AtLite
Corelite
Ephesus
Fail-Safe
HALO
HALO Commercial
Invue
iO
Iris
Lumark
Lumière
McGraw-Edison
Metalux
MWS
Neo-Ray
Portfolio
PrentaLux - 3D Printed Lighting
RSA
Shaper
Streetworks
Sure-Lites
Telensa

Controls Brands

Greengate
Fifth Light
Intelligent Lighting Controls


Connected Lighting Systems and Smart Spaces Platform

WaveLinx



Cooper Lighting Solutions
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.cooperlighting.com

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172



© 2023 Cooper Lighting Solutions
All Rights Reserved
Printed in USA
Publication No. BR51817221
July 7, 2023 5:00 PM

All other trademarks are property
of their respective owners.

Product availability, specifications,
and compliances are subject to
change without notice.