

Description

The Halo H5 series utilizes a 5" aperture designed to accommodate smaller sized PAR20 and PAR30 halogen lamps. The wide variety of trims available allows a number of different lighting effects to be created with one basic housing. The 5" diameter trim size makes the H5RT the right choice for applications where dramatic yet inconspicuous lighting is required in an existing ceiling.

Catalog #		Type
Project		
Comments		Date
Prepared by		

Specification Features

Housing

- Single wall die-stamped CRS with white powder coat finish
- For installation from below finished ceiling
- Integral flange secures fixture against ceiling

Remodel Springs

- Four remodel clips secure housing and accommodate 1/2" and 5/8" ceiling material

Junction Box

- Seven 1/2" trade size conduit knockouts with true pry-out slots
- Four type non-metallic (NM) cable pry-outs simplify installation

"Quick Connect" Connectors

- Three "Quick Connect" connectors eliminate need for separate wire nuts - simply strip supply wires and push in

Socket

- Porcelain socket with nickel plated brass screw shell
- Snaps into trim for consistent lamp positioning
- Overspray protector included

Socket Plate

- Rigid socket plate adjusts and locks without tools for various lamp sizes
- Socket plate and bracket may be removed when using socket supporting trims

Thermal Protector

- Self resetting thermal protector deactivates fixture if overheating occurs due to improper lamping or misapplied insulation

Compliance

- cULus Listed 1598 luminaire
- cULus Listed for damp location
- cULus Listed for wet location, covered ceiling, with select trims
- cULus Listed for feed through
- IP rated (Improper Lamp)
- RoHS compliant




H5RT

5" Non-IC,
Remodel Housing



Dimensions



Ordering Information

Sample Number: H5RT - 5020SC

Order housing, trim and lamp (by others) separately for a complete luminaire.

Domestic Preferences⁽¹⁾

[Blank] = Standard
TAA = Trade Agreements Act

Housing

H5RT = 5" Non-IC, Remodel, 120V

Trims

Reflectors



5020 PAR Reflector

OD: 6-3/8" [162mm]

5020P=White Reflector, White Trim

5020H=Haze Reflector, White Trim

5020SC=Clear Specular Reflector, White Trim

5020BL=Black Specular Reflector, White Trim

5020SN=Satin Nickel Reflector, Satin Nickel Trim

5020TBZ=Tuscan Bronze Reflector,
Tuscan Bronze Trim



5021 Full Reflector

OD: 6-3/8" [162mm]

5021H=Haze Reflector, White Trim

5021SC=Clear Specular Reflector, White Trim

5021SN=Satin Nickel Reflector, Satin Nickel Trim

5021TBZ=Tuscan Bronze Reflector,
Tuscan Bronze Trim



5107 Specular Reflector, Self-flange

OD: 6-5/8" [168mm]

5107SC=Specular Reflector, White Self-flange



5120 Full Cone Reflector, Self-flange

OD: 6-5/8" [168mm]

5120WH=White Reflector, White Self-flange

5120SN=Satin Nickel Reflector,
Satin Nickel Self-flange

5120TBZ=Tuscan Bronze Reflector,
Tuscan Bronze Self-flange

Baffles



5001 PAR Metal Baffle Splay

OD: 6-3/8" [156mm]

5001P=White Baffle, White Trim

5001MB=Black Baffle, White Trim

5001SN=Satin Nickel Baffle, Satin Nickel Trim

5001TBZ=Tuscan Bronze Baffle,
Tuscan Bronze Trim



5010 PAR Metal Step Baffle

OD: 6-3/8" [156mm]

5010W=White Baffle, White Trim

5010=Black Baffle, White Trim




5012 High Coilex® Baffle

OD: 6-3/8" [166mm]

5012W=White Baffle, White Trim

5012P=Black Baffle, White Trim



5016 Coilex® Baffle with Reflector

OD: 6-3/8" [162mm]

5016W=White Baffle, White Trim

5016P=Black Baffle, White Trim



5102 Tapered Metal Baffle, Self-flange

OD: 6-5/8" [168mm]

5102WB=White Baffle, White Self-flange

5102BB=Black Baffle, White Self-flange



5109 Coilex® Tapered Baffle, Self-flange

OD: 6-5/8" [168mm]

5109WB=White Plastic Straight Coilex Baffle,
White Self-flange

5109BB=Black Plastic Straight Coilex Baffle,
White Self-flange

5109BKB=Black Plastic Straight Coilex Baffle,
Black Self-flange



5110 Pertex™ Baffle, Self-flange

OD: 6-5/8" [168mm]

5110WB=White Pertex Baffle,
White Self-flange

5110WB=Black Pertex Baffle,
White Self-flange

5110BKB=Black Pertex Baffle,
Black Self-flange



5125 Full Cone Baffle, Self-flanged

OD: 6-5/8" [168mm]

5125WB=White Baffle, White Self-flange

5125BB=White Baffle, Black Self-flange

5125BKB=Black Baffle, Black Self-flange

Adjustable - Eyeballs & Gimbals



5060 Adjustable Gimbal 20° Tilt, Self-flange

OD: 6-3/8" [162mm]

5060P=White Gimbal, White Trim



5070 Adjustable Eyeball 30° Tilt, Self-flange

OD: 6-3/8" [162mm]

5070P=White Eyeball, White Trim

5070SN=Satin Nickel Eyeball, Satin Nickel Trim

5070TBZ=Tuscan Bronze Eyeball,
Tuscan Bronze Trim



5071 Adjustable Eyeball 30° Tilt, Self-flange

OD: 6-1/2" [165mm]

5071P=White Eyeball, White Trim



5130 Eyeball 35° Tilt, Self-flange

OD: 6-5/8" [168mm]

5130WH=White Eyeball, White Trim



5135 Eyeball 35° Tilt, Self-flange

OD: 6-5/8" [168mm]

5135WH=White Eyeball, White Trim, Self-flanged



5165 Gimbal 35° Tilt, Self-flange

OD: 6-5/8" [168mm]

5165WH=White Gimbal, White Trim

5165BK=Black Gimbal, Black Trim

5165SN=Satin Nickel Gimbal, Satin Nickel Trim

5165TBZ=Tuscan Bronze Gimbal,
Tuscan Bronze Trim



5222 Regressed Angle Cut Adjustable Gimbal 30° Tilt, Self-flange

OD: 6-5/8" [168mm]

5222WB=White Baffle and Gimbal, White Trim

5222BB=Black Baffle and Gimbal, White Trim

5222SC=Specular Clear Reflector
and Gimbal, White Trim

5222H=Haze Reflector and Gimbal, White Trim

Lenses & Wet Location Showerlights



5051 Frosted Glass Lens - Showerlight

OD: 6-7/16" [164mm]

5051PS=Frosted Glass Lens, White Trim



5054 Frosted Glass Dome Lens - Showerlight

OD: 6-3/8" [162mm]

5054PS=Frosted Glass Dome Lens, White Trim

5054SNS=Frosted Glass Dome Lens,
Satin Nickel Trim

5054TBZS=Frosted Glass Dome Lens,
Tuscan Bronze Trim



5150 Low Profile, Frosted Dome Glass Lens, Self-flange - Showerlight

OD: 6-5/8" [168mm]

5150WH=Frost Dome Glass Lens with Reflector,
White Plastic Self-flange

5150SN=Frost Dome Glass Lens with Reflector,
Satin Nickel Plastic Self-flange

5150TBZ=Frost Dome Glass Lens with Reflector,
Tuscan Bronze Plastic Self-flange



5162 Drop Opal Plastic Lens, Self-flange

OD: 6-5/8" [168mm]

5162WH=Drop Opal Plastic Lens with Reflector,
White Plastic Self-flange



5230 Squirrel Frost Glass Lens, Metal Trim, Self-flange - Showerlight

OD: 6-7/8" [174mm]

5230AH=Frost Glass Lens, Aluminum Haze
Squirrel Trim

5230PN=Frost Glass Lens, Polished Nickel
Squirrel Trim

5230SN=Frost Glass Lens, Satin Nickel
Squirrel Trim

5230TBZ=Frost Glass Lens, Tuscan Bronze
Squirrel Trim



5255 Soft Square, Frost Curve Glass Lens, Self-flange - Showerlight

OD: 7-1/4" [183mm]

5255WH=Frost Curve Glass Lens with Reflector,
White Plastic Self-flange

5255SN=Frost Curve Glass Lens with Reflector,
Satin Nickel Plastic Self-flange

5255TBZ=Frost Curve Glass Lens with Reflector,
Tuscan Bronze Plastic Self-flange



5145 Open Wet Location, Shallow Reflector, Self-flange - Showerlight *

OD: 6-5/8" [168mm]

5145WH=White Self-flanged

5145SN=Satin Nickel Self-Flanged

5145TBZ=Tuscan Bronze Self-Flanged

Lamp Gasket= (Included)



5146 Open Wet Location Full Reflector, Self-flange - Showerlight *

OD: 6-5/8" [168mm]

5146WH=White Self-flanged

5146SN=Satin Nickel Self-Flanged

5146TBZ=Tuscan Bronze Self-Flanged

Lamp Gasket= (Included)

continued

Notes: (1) Only product configurations with this designated prefix are built to be compliant with the Trade Agreements Act of 1979 (TAA). Please refer to [DOMESTIC PREFERENCES](#) website for more information. Components shipped separately may be separately analyzed under domestic preference requirements. Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information.

*Outdoor rated lamp only (purchase separately)

Ordering Information

Sample Number: H5RT - 5020SC
 Order housing, trim and lamp (by others) separately for a complete luminaire.

Domestic Preferences ⁽¹⁾	Housing
[Blank] = Standard TAA = Trade Agreements Act	H5RT = 5" Non-IC, Remodel, 120V

Trims

Open, Splay & Wall Wash



5000 PAR Metal Splay, Self-flange
 OD: 6-3/8" [162mm]
5000P=White Splay, White Trim
5000SN=Satin Nickel Splay, Satin Nickel Trim
5000TBZ=Tuscan Bronze Splay,
 Tuscan Bronze Trim



5030 Wall Wash with Baffle
 OD: 6-1/4" [159mm]
5030W=White Eyelid with White Baffle,
 White Trim
5175P=White Eyelid with Black Baffle,
 White Trim



5175 Open, Self-flange
 OD: 6-5/8" [168mm]
5175WH=White Self-flange
5175SN=Satin Nickel Self-flange
5175TBZ=Tuscan Bronze Self-flange



5176 Open, Self-flange
 OD: 6-5/8" [168mm]
5176WH=White Self-flange
5176SN=Satin Nickel Self-flange
5176TBZ=Tuscan Bronze Self-flange



5185 Open Splay, Self-flange
 OD: 6-5/8" [168mm]
5185WH=White Self-flange
5185SN=Satin Nickel Self-flange
5185TBZ=Tuscan Bronze Self-flange



5186 Open Splay, Self-flange
 OD: 6-5/8" [168mm]
5186WH=White Self-flange
5186SN=Satin Nickel Self-flange
5186TBZ=Tuscan Bronze Self-flange

Notes: (1) Only product configurations with this designated prefix are built to be compliant with the Trade Agreements Act of 1979 (TAA). Please refer to [DOMESTIC PREFERENCES](#) website for more information. Components shipped separately may be separately analyzed under domestic preference requirements. Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information.
 *Outdoor rated lamp only (purchase separately)