


Project		Catalog #		Type	
Prepared by		Notes		Date	



Greengate

Screwless wallplates

System accessory for Greengate wall box devices

Typical Applications

Office • Education • Healthcare • Hospitality • Retail • Industrial • Manufacturing


Interactive Menu

- Order Information page 2
- Additional Resources page 3
- Product Warranty


Top Product Features

- The wallplate fits a standard decorator opening or toggle opening and provides a contemporary, sleek design
- Screwless Wallplates clip easily into place with gentle pressure
- Virtually unbreakable polycarbonate construction
- Mid-sized to cover wall imperfections and large wallboard openings
- Available in multi-gang configurations
- Available in a variety of colors
- Meets flammability requirements per UL 94, V2 rated

Dimensional Details




Decorator Wallplates can be used with:
Occupancy and Vacancy sensors, GDS, GMDS,
Automatic Turn-Off switches and 0-10V slide dimmers



Toggle Wallplates can be used with:
Momentary toggle switches,
Automatic Turn-Off switches

Mounting Height



[additional product diagrams](#)

Order Information

This is an accessory for the Greengate Lighting Control System.

Decorator Wallplates

Can be used with: Occupancy and Vacancy sensors, GDS, GMDS, Automatic Turn-Off switches and 0-10V slide dimmers

Catalog Number

Catalog Number	Gang	Color	Description
PJS26W	1-Gang	White	Single Gang, Screwless Decorator Wallplate
PJS26V	1-Gang	Ivory	Single Gang, Screwless Decorator Wallplate
PJS26GY	1-Gang	Gray	Single Gang, Screwless Decorator Wallplate
PJS26BK	1-Gang	Black	Single Gang, Screwless Decorator Wallplate
PJS262W	2-Gang	White	Two Gang, Screwless Decorator Wallplate
PJS262V	2-Gang	Ivory	Two Gang, Screwless Decorator Wallplate
PJS262BK	2-Gang	Black	Two Gang, Screwless Decorator Wallplate
PJS263W	3-Gang	White	Three Gang, Screwless Decorator Wallplate
PJS263V	3-Gang	Ivory	Three Gang, Screwless Decorator Wallplate
PJS263BK	3-Gang	Black	Three Gang, Screwless Decorator Wallplate
PJS264W	4-Gang	White	Four Gang, Screwless Decorator Wallplate
PJS264V	4-Gang	Ivory	Four Gang, Screwless Decorator Wallplate
PJS264BK	4-Gang	Black	Four Gang, Screwless Decorator Wallplate
PJS265W	5-Gang	White	Five Gang, Screwless Decorator Wallplate
PJS265V	5-Gang	Ivory	Five Gang, Screwless Decorator Wallplate
PJS265BK	5-Gang	Black	Five Gang, Screwless Decorator Wallplate
PJS266W	6-Gang	White	Six Gang, Screwless Decorator Wallplate
PJS266V	6-Gang	Ivory	Six Gang, Screwless Decorator Wallplate
PJS266BK	6-Gang	Black	Six Gang, Screwless Decorator Wallplate

Toggle Wallplates

Can be used with: Momentary toggle switches, Automatic Turn-Off switches

Catalog Number

Catalog Number	Gang	Color	Description
PJS1W	1-Gang	White	Single Gang, Screwless Toggle Wallplate
PJS1V	1-Gang	Ivory	Single Gang, Screwless Toggle Wallplate
PJS2W	2-Gang	White	Two Gang, Screwless Toggle Wallplate
PJS2V	2-Gang	Ivory	Two Gang, Screwless Toggle Wallplate
PJS3W	3-Gang	White	Three Gang, Screwless Toggle Wallplate
PJS3V	3-Gang	Ivory	Three Gang, Screwless Toggle Wallplate
PJS4W	4-Gang	White	Four Gang, Screwless Toggle Wallplate
PJS4V	4-Gang	Ivory	Four Gang, Screwless Toggle Wallplate

Product Specifications

Key Features

- Screwless wallplates appear to float freely on the surface of the wall and are designed for easy and fast installation
- Mounting plate attaches to the device and the wallplate is simply pressed into place

Mechanical

Size:

- **Decorator Opening Dimensions:** 2.64"H x 1.31"W (67.1mm x 33.3mm)
- **Toggle Opening Dimensions:** 1"H x 0.5"W (25.4mm x 12.7mm)
- **1-Gang:** 4.88"H x 3.13"W (123.8mm x 79.4mm)
- **2-Gang:** 4.88"H x 4.95"W (123.8mm x 125.4mm)
- **3-Gang:** 4.88"H x 6.76"W (123.8mm x 171.4mm)
- **4-Gang:** 4.88"H x 8.57"W (123.8mm x 217.5mm)
- **5-Gang:** 4.88"H x 10.38"W (123.8mm x 263.5mm)
- **6-Gang:** 4.88"H x 12.19"W (123.8mm x 309.5mm)

Environment:

- **Operating temperature:** -40°F to 149°F (-40°C to 65°C)
- For indoor use only

Mounting: This system accessory will require wall mounting at the site.

Color: White, Ivory, Gray & Black

Housing: Polycarbonate

Standards/Ratings

Flammability:

- Meets UL 94 requirements
- V2 rated

Warranty

Consult website for warranty information



Control Systems

- Greengate