



Save Money



Save Time



Peace of Mind

The SLSTP is a commercial grade LED strip that balances performance, aesthetics, and cost. It is available in 2', 4' or 8' lengths with 3500, 4000 or 5000K selectable CCT options and selectable lumens up to 12,000 lumens of light output. These striplights have quick installation features making them suitable for single or continuous row applications. SLSTP is ideal for warehouse, retail, office or retrofit applications making them the ideal choice for stock and design build opportunities.





Save Money



Save Time



Peace of Mind

	Features	Benefits	Result
Construction	2', 4' and 8' lengths with single continuous lens (all lengths)	Design flexibility for new construction or retrofit applications	\$ ⌚ ✓
	Decorative snap-on injection molded end caps	Provides clean lines and aesthetically pleasing appearance	\$ ⌚ ✓
	Suitable for either single or continuous row application	Add-on length as needed regardless of application or layout	\$ ⌚ ✓
	Impact resistant polycarbonate lens	Reduced maintenance	\$ ⌚ ✓
	Easy access selectable switches on the outside of the fixture	Contractor friendly; simple in field adjustment	\$ ⌚ ✓
Performance	Up to 150 lm/W, selectable lumens up to 1500 lumens per foot, and 3500, 4000 or 5000K selectable CCT options	Multi-application flexibility	\$ ⌚ ✓
	Frosted lens with linear prisms	Uniform light distribution and wide area coverage	\$ ⌚ ✓
	UNV (0-10V) dimming to 10%	Save over 40% energy over existing LFL strips	\$ ⌚ ✓
	DLC®, 5-year warranty, 50K life hours at L70	Eligible for energy rebates; certified and guaranteed performance	\$ ⌚ ✓

Energy and Performance Data by Catalog Number

Catalog #	UPC	Length	CCT (K)	Delivered Lumens	Watts	Efficacy (lm/W)	Dimming (Triac or 0-10V)	Input Current (A)		
								120V	277V	347V
2SLSTPSC-UNV	080083174409	2	3500	2715	21	126	0-10V Dim to 10%	0.18	0.08	-
			4000	2870		137				
			5000	2747		128				
4SLSTPSC-UNV	080083174416	4	3500	2666	18	146	0-10V Dim to 10%	0.15	0.06	-
			4000	2668		152				
			5000	2629		148				
			3500	4366	30	143		0.25	0.11	-
			4000	4481		151				
			5000	4352		144				
			3500	6512	50	135		0.42	0.18	-
			4000	6785		146				
			5000	6492		136				
8SLSTPSC-UNV	080083174423	8	3500	4432	35	131	0-10V Dim to 10%	0.29	0.13	-
			4000	4543		137				
			5000	4509		134				
			3500	8559	68	133		0.57	0.25	-
			4000	8953		143				
			5000	8689		135				
			3500	11211	95	127		0.79	0.34	-
			4000	11921		140				
			5000	11211		127				