



Corelite CL

LED Recessed Slot Linear Series

Elegantly Simple

The CL LED Recessed Slot linear provides clean lines of light with a simple easy-to-use design. Offered in 2" and 4" width linear apertures with trims to fit five different ceiling types, the CL series is ideal for a variety of architectural environments. Offered in 4', 8', and 12' incremental continuous row lengths, the CL series provides uniform illumination while also reducing energy costs. Integrated sensor configuration options allow for even greater energy savings while providing cost-effective code-compliance for both retrofit and new installs. The Corelite CL series is ideal for office, education, hospitality, and healthcare environments.




Save Money



Save Time



Peace of Mind



Frosted Lens



Flush Asymmetric



Corelite CL

LED Recessed Slot Linear Series



Save Money



Save Time



Peace of Mind

Category	Feature	Benefit	Result
Construction	Formed housing with precision cut extruded aluminum trim	Ideal balance of quality and affordability	\$ ✓
	Driver accessible from below	Easy access to electrical components	\$
	Recessed lay-in for T-grid installation or direct into gypsum with ½" flange	Design flexibility	✓
Performance	Up to 122 lumens per watt	Significant energy savings; eligible for rebates	\$
	Projected lumen maintenance based on TM21 testing standards is L94>60,000 hour	Maintenance-free	\$ ✓
	Connected lighting options available - Integrated Wavelinx, LumaWatt Pro, and SVPD	Code compliance, energy savings, IoT value-added applications	\$ ✓ ⌚
	5-year warranty	Guaranteed quality	✓

Performance Data

CL2DR LED Light Level Outputs (3500K, 80 CRI)				
Series	Lumen Package	Delivered Lumens	Wattage	Efficacy LPW
		Per FT	Per FT	
CL2DR	30D	290	2.9	100
	50D	475	4.7	101
	70D	662	6.6	101
	90D	844	8.7	97
	100D	980	10.3	95

CL4DR LED Light Level Outputs (3500K, 80 CRI)				
Series	Lumen Package	Delivered Lumens	Wattage	Efficacy LPW
		Per FT	Per FT	
CL4DR	40D	350	2.9	121
	60D	575	4.7	122
	80D	801	6.6	121
	100D	1021	8.7	117
	120D	1187	10.3	116

LUMEN ADJUSTMENT FACTORS

CCT	80CRI	90CRI
3000K	0.943	0.815
3500K	1.000	0.861
4000K	1.010	0.892

Run Configurations

Standard Length	4ft	8ft	12ft	16ft	20ft	24ft	28ft	32ft	36ft	40ft	44ft	48ft	52ft	56ft	60ft	64ft	68ft	72ft	76ft	80ft	84ft	88ft	92ft	96ft
4ft	1		1		1		1		1		1		1		1		1		1		1		1	
8ft		1	1	2	2	3	3	4	4	5	5	6	6	7	7	8	8	9	9	10	10	11	11	12



Cooper Lighting Solutions
18001 East Colfax Avenue
Aurora, CO 80011
P: 303-393-1522
www.eaton.com/lighting

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2020 Cooper Lighting Solutions
All Rights Reserved
Printed in USA
Publication No. SA519074EN
February 4, 2020 12:56 PM