

Description

The H7 family of recessed housings are the standard in the industry for both commercial and residential applications. The wide variety of trims available allows a number of different lighting effects to be created with one basic housing. The H7RICT is designed for installations where the housing will be in direct contact with insulation.

Catalog #	Type
Project	
Comments	Date
Prepared by	

Specification Features

Housing

- Single wall aluminum housing
- Aluminum construction for greater heat dissipation
- For installation from below the finished ceiling. Integral flange secures fixture against ceiling.

Socket Plate

- Rigid socket plate adjusts and locks without tools for various lamp sizes
- Socket plate and bracket may be removed when using socket supporting trims

Junction Box

- Seven 1/2" trade size conduit knockouts with true pry-out slots are positioned to accommodate straight conduit runs
- Four non-metallic (NM) cable pry-outs included
- Includes:

Quick Connect™

- Three 4-port push-in "Quick Connect" wire nuts included in junction box
- Speed installation and increase reliability
- No additional wire nuts required
- Simply strip and insert supply wires

Remodel Springs

- Four remodel springs secure housing and accommodate 1/2" and 5/8" ceiling material

Socket

- Porcelain socket with nickel plated brass screw shell
- Snap-in springs secure socket to socket plate, and may be detached when using socket supporting trims
- Overspray protector included

Thermal Protector

- Self resetting thermal protector deactivates fixture if overheating occurs due to improper lamping or misapplied insulation

Trims

- Halo Fit-All concept offers multiple trim options in a variety of design styles, and functional beam distributions to control beam angle and lumen delivery in accommodating various lamp types including Halogen, CFL and LED

Compliance

- cULus Listed 1598 luminaire
- cULus Listed damp location
- cULus Listed for wet location, covered ceiling, with select trims
- cULus Listed for feed through
- cULus Listed for direct contact with insulation and combustible material*
- RoHS compliant

*Not to be used in direct contact with spray foam insulation (Consult NEMA LSD57-2013)



H7RICT



6" IC, Remodel , 120V

FOR USE IN INSULATED
CEILINGS

FOR DIRECT CONTACT
WITH INSULATION*



Dimensions



Ordering Information

Sample Number: H7RICT 6110WB

Order housing, trim and lamp (by others) separately for a complete luminaire.

Domestic Preferences⁽¹⁾

[Blank] = Standard

TAA = Trade Agreements Act

Housing

H7RICT = 6" IC, Remodel, 120V

Trims

 Reflectors 30 Reflector, Self-flange OD: 7-1/4" [184mm] 30HAT =Haze Reflector, White Trim 30RGAT =Residential Gold Reflector, White Trim 30CAT =Clear Specular Reflector, White Trim	 353 Metal Baffle OD: 7-1/4" [184mm] 353SN =Satin Nickel Baffle and Trim 353TBZ =Tuscan Bronze Baffle and Trim	 78 BR/PAR30 Eyeball 30° Tilt, Self-flange OD: 8" [203mm] 78P =White Eyeball and Trim 78PAT =White Eyeball and Trim, Air-Tite 78SN =Satin Nickel Eyeball and Trim 78TBZ =Tuscan Bronze Eyeball and Trim
 30SBAT Reflector, Self-flange OD: 7-1/4" [184mm] 30SBAT =Black Specular Reflector, Self-flange	 6100 Tapered Metal Baffle with (2) Trim Rings OD: 7-1/8" [181mm] 6100WB =White Baffle, Narrow and Wide White Trims (included) 6100BB =Black Baffle, Narrow and Wide White Trims (included)	 376 PAR30 Regressed Gimbal 30° Tilt, Self-flange OD: 7-1/4" [184mm] 376W =White Baffle and Trim 376P =Black Baffle and White Trim
 404 Specular Reflector OD: 7-1/4" [184mm] 404C =Clear Specular Reflector, White Trim 404H =Haze Reflector, White Trim 404SN =Satin Nickel Reflector and Trim 404TBZ =Tuscan Bronze Reflector and Trim	 6101 Straight Metal Baffle with (2) Trim Rings OD: 7-1/8" [181mm] 6101WB =White Baffle, Narrow and Wide White Trims (included) 6101BB =Black Baffle, Narrow and Wide White Trims (included)	 378 PAR30 Regressed Gimbal with Splay 25° Tilt, Self-flange OD: 7-1/4" [184mm] 378P =White Splay and Trim 378 =Clear Specular Splay and White Trim
 426 Reflector Cone OD: 7-1/4" [184mm] 426 =Clear Specular Reflector Cone, White Trim 426WB =Black Specular Reflector Cone, White Trim 426H =Haze Reflector Cone, White Trim 426SN =Satin Nickel Reflector Cone and Trim 426TBZ =Tuscan Bronze Reflector Cone and Trim	 6102 Tapered Metal Baffle, Self-flange OD: 7-3/4" [197mm] 6102WB =White Baffle and Trim 6102BB =Black Baffle, White Trim	 420 BR/PAR30 Regressed Eyeball 30° Tilt, Self-flange OD: 7-1/4" [184mm] 420W =White Eyeball, Baffle and Trim 420P =White Eyeball, Black Baffle, White Trim
 429 Dayform White Cone OD: 7-1/4" [184mm] 429P =White Reflector and Trim	 6103 Straight Metal Baffle, Self-flange OD: 7-3/4" [197mm] 6103WB =White Baffle and Trim 6103BB =Black Baffle, White Trim	 478 PAR38 Adjustable Regressed Gimbal with Splay 25° Tilt, Self-flange OD: 7-1/4" [184mm] 478P =White Splay and Trim
 4041 White Reflector, Self-flange OD: 7-1/4" [184mm] 4041P =White Reflector and Trim	 6108 Coilex® Straight Plastic Baffle, Self-flange OD: 7-3/4" [197mm] 6108WB =White Plastic Straight Coilex Baffle, White Trim 6108BB =Black Plastic Straight Coilex Baffle, White Trim 6108BKBB =Black Plastic Straight Coilex Baffle, Black Trim	 6130 BR/PAR30 Eyeball 35° Tilt, Self-flange OD: 7-3/4" [197mm] 6130WH =White Eyeball and Trim
 4261 White Reflector Cone, Self-flange OD: 7-1/4" [184mm] 4261P =White Reflector and Trim	 6109 Coilex® Tapered Baffle, Self-flange OD: 7-3/4" [197mm] 6109WB =White Tapered Coilex Baffle, White Trim 6109BB =Black Tapered Coilex Baffle, White Trim 6109BKBB =Black Tapered Coilex Baffle, Black Trim	 6170 PAR38 Gimbal 25° Tilt, Self-flange OD: 7-3/4" [197mm] 6170WH =White Gimbal and Trim 6170BK =Black Gimbal and Trim 6170SN =Satin Nickel Gimbal and Trim 6170TBZ =Tuscan Bronze Gimbal and Trim
 6106 Straight Reflector Cone, Self-flange OD: 7-3/4" [197mm] 6106SC =Specular Reflector, White Trim	 6110 Pertex Baffle, Self-flange OD: 7-3/4" [197mm] 6110WB =White Pertex Baffle and Trim 6110BB =Black Pertex Baffle, White Trim 6110BKBB =Black Pertex Baffle and Trim	 6215 PAR30 Double Gimbal 35°-50° Tilt, Self-flange OD: 7-3/4" [197mm] 6215WH =White Gimbal and Trim 6215BK =Black Gimbal and Trim 6215SN =Satin Nickel Gimbal and Trim 6215TBZ =Tuscan Bronze Gimbal and Trim
 6107 Tapered Reflector, Self-flange OD: 7-3/4" [197mm] 6107SC =Specular Reflector, White Trim	 6120 Full Cone Reflector, Self-flange OD: 7-3/4" [197mm] 6120WH =White Reflector and Trim 6120SN =Satin Nickel Reflector and Trim 6120TBZ =Tuscan Bronze Reflector and Trim	 6222 Regressed PAR30 Adjustable 45° Tilt, Self-flange OD: 7-3/4" [197mm] 6222WB =White Baffle and Trim 6222BB =Black Baffle and Trim 6222SC =Specular Clear Reflector, White Trim 6222H =Haze Reflector, White Trim
 6121 Shallow Full Cone Reflector, Self-flange OD: 7-3/4" [197mm] 6121WH =White Reflector and Trim	 6125 Full Cone Baffle, Self-flange OD: 7-3/4" [197mm] 6125WB =White Baffle and Trim 6125BB =Black Baffle, White Trim 6125BKBB =Black Baffle and Trim	 Lenses & Wet Location Showerlights 170 Albalite Lens with Reflector OD: 8" [203mm] 170P =Frosted Albalite Glass Lens, White Trim 170PS =Frosted Albalite Glass Lens, White Plastic Trim, Showerlight, Air-Tite
 Baffles 30 Baffle, Self-flange OD: 7-1/4" [184mm] 30WAT =White Baffle, Reflector and Trim 30WATH =White Baffle, Clear Reflector and White Trim 30PAT =Black Baffle, Clear Reflector and White Trim 30SNAT =Satin Nickel Baffle, Reflector and Trim 30TBZAT =Tuscan Bronze Baffle, Reflector and Trim	 6126 Shallow Full Cone Baffle, Self-flange OD: 7-3/4" [197mm] 6126WB =White Baffle and Trim 6126BB =Black Baffle, White Trim	 171 Drop Opal Lens with Reflector OD: 8" [203mm] 171P =Drop Opal Glass Lens, White Trim 171PS =Drop Opal Glass Lens, White Plastic Trim, Showerlight, Air-Tite
 310 Coilex® Baffle OD: 7-1/4" [184mm] 310W =White Coilex Baffle and Trim 310P =Black Coilex Baffle, White Trim 310SN =Black Coilex Baffle, Satin Nickel Trim 310TBZ =Black Coilex Baffle, Tuscan Bronze Trim	 Adjustable - Eyeballs & Gimbals 74 PAR30 Eyeball 30° Tilt, Self-flange OD: 8" [203mm] 74P =White Eyeball and Trim	 172 Dome Lens with Reflector OD: 7-3/4" [197mm] 172PS =Frosted Glass Dome, White Plastic Trim 172SNS =Frosted Glass Dome, Satin Nickel Plastic Trim 172TBZS =Frosted Glass Dome, Tuscan Bronze Plastic Trim
	 76 PAR38 Gimbal 30° Tilt, Self-flange OD: 8" [203mm] 76P =White Gimbal and Trim	

continued

Notes: (1) Only product configurations with this designated prefix are built to be compliant with the Trade Agreements Act of 1979 (TAA). Please refer to [DOMESTIC PREFERENCES](#) website for more information. Components shipped separately may be separately analyzed under domestic preference requirements. Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information.

*Outdoor rated lamp only (purchase separately)

Ordering Information

Sample Number: H7RICT 6110WB

Order housing, trim and lamp (by others) separately for a complete luminaire.

Domestic Preferences⁽¹⁾

[Blank] = Standard

TAA = Trade Agreements Act

Housing

H7RICT = 6" IC, Remodel, 120V

Trims

Lenses & Wet Location Showerlights



173 Fresnel Lens with Reflector

OD: 8" [203mm]

173P=Fresnel Glass Lens, White Trim

173PS=Fresnel Glass Lens, White Plastic Trim, Showerlight, Air-Tite



6145 Open Wet Location, Shallow Reflector, Self-flange - Showerlight*

OD: 7-3/4" [197mm]

6145WH=White Reflector and Trim

6145SN=Satin Nickel Reflector and Trim

6145TBZ=Tuscan Bronze Reflector and Trim



6146 Open Wet Location, Full Reflector, Self-flange - Showerlight*

OD: 7-3/4" [197mm]

6146WH=White Reflector and Trim

6146SN=Satin Nickel Reflector and Trim

6146TBZ=Tuscan Bronze Reflector and Trim



6150 Frost Dome Glass Lens, Self-flange

OD: 7-3/4" [197mm]

6150WH=Frost Dome Glass Lens with Reflector, White Plastic Trim

6150SN=Frost Dome Glass Lens with Reflector, Satin Nickel Plastic Trim

6150TBZ=Frost Dome Glass Lens with Reflector, Tuscan Bronze Plastic Trim



6162 Drop Opal Plastic Lens, Self-flange - Showerlight

OD: 7-3/4" [197mm]

6162WH=Drop Opal Plastic Lens with Reflector, White Plastic Trim



6230 Squirrel Frost Glass Lens, Metal Trim - Showerlight

OD: 7-1/4" [183mm]

6230AH=Frost Glass Lens, Aluminum Haze Squirrel Trim

6230PN=Frost Glass Lens, Polished Nickel Squirrel Trim

6230SN=Frost Glass Lens, Satin Nickel Squirrel Trim

6230TBZ=Frost Glass Lens, Tuscan Bronze Squirrel Trim



6255 Soft Square, Frost Curve Glass Lens, Self-flange - Showerlight

OD: 7-1/4" [183mm]

6255WH=Frost Curve Glass Lens with Reflector, White Plastic Trim

6255SN=Frost Curve Glass Lens with Reflector, Satin Nickel Plastic Trim

6255TBZ=Frost Curve Glass Lens with Reflector, Tuscan Bronze Plastic Trim

Open, Splay & Wall Wash



300 Open Trim with Fixed Socket Bracket, Self-flange

OD: 7-1/4" [183mm]

300P=Self-flange with White Open Trim

300SN=Self-flange with Satin Nickel Open Trim

300TBZ=Self-flange with Tuscan Bronze Open Trim



327 White Splay Trim with Fixed Socket Bracket, Self-flange

OD: 7-3/4" [197mm]

327P=White Splay Trim with Socket Bracket



328 White Splay Trim

OD: 7-3/4" [197mm]

328P=White Splay Trim



430 Wall Wash with Baffle & Full Reflector

OD: 7-1/4" [183mm]

430W=White Baffle, with Upper Reflector, White Trim

430P=Black Baffle, with Upper Reflector, White Trim

Accessories

Designer Finish Trim Rings

TRM6C=Chrome

TRM6SN=Satin Nickel

TRM6TBZ=Tuscan Bronze

TRM6MB=Black Metal

TRM7MB=Black plastic

Metal 7 1/4" OD. Compatible with 310*, 312*, 376, 378, 400, 404, 405, 410, 416, 419, 420, 424, 425, 426*, 429*, 455CG, 455SC, 456P, 456W, 477, 478, 1412, 1416, 1475.

Oversized Trim Rings

OT400P=6" ID x 9-1/4" OD, Oversized white metal trim ring for designated 6" trims.

OT403P=6" ID x 8" OD, Oversized white plastic trim ring for designated 6" trims.

H930 R/PAR Lamp Aiming Accessory

H930=For H7T, H7RT, H7ICT, H7ICAT, H7RICT, H7RICAT housings with 310 and 426 trims. Allows lamp to be aimed up to 30° from vertical and rotated 358°. See housing-trim selection for lamp listings.

*Originally supplied with TRM6P white metal trim rings. All others are supplied with white plastic trim rings.

Notes: (1) Only product configurations with this designated prefix are built to be compliant with the Trade Agreements Act of 1979 (TAA). Please refer to [DOMESTIC PREFERENCES](#) website for more information. Components shipped separately may be separately analyzed under domestic preference requirements. Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information.

*Outdoor rated lamp only (purchase separately)