

PRODUCT SELECTION GUIDE

WIDE RANGE OF PRODUCTS TO FIT YOUR NEED!

Contents





AREA LIGHTS PAGE 6

WALL & CEILING PAGE 8





HALO FLOODLIGHTS

The Floodlight category is a large pool of varieous families designed to cover many possible use case scenarios from security floods to connected floodlighting. Easy to install and with options for mode of controls like Dusk to Dawn, Motion activated and switch activated, the Floodlights are ideal for both residential and commercial areas such as yards, driveways, patios, loading areas and warehouses.




			SECURITY	FLOODS	
	PRODUCT FAMILY			000	
		PWT	MS34	MS185 & MS185R	ESF
	Number of Head	Twin	Twin	Twin	Twin
NOL	Head Shape	_	-	-	Blade
UCT	Lens Finish	-	-	-	Frosted PC
STR	Housing Material	PC	PC	Die-Cast Aluminum	PC
CONSTRUCTION	Color Finish	White & Bronze	White & Bronze	White & Bronze	White & Bronze
	Mounting	Wall/Eave	Wall / Eave	Wall / Eave	Wall / Eave
FEATURES / PERFORMANCE	Light Source	Two 150W PAR Lamps (maximum)	Two 150W PAR Lamps (maximum)	Two 150W PAR Lamps (maximum)	LED Integrated
	Lumens (Max)	-	-	-	1400 & 2400
	Life (L70)	Based on lamp separately	Based on lamp separately	Based on lamp separately	50K Hours
	CRI	80 (min)	80 (min)	80 (min)	80 (min)
/ PE	CCT (K)	-	-	-	4000K
RES	Input Voltage	120V	120V	120V	120V
ATUI	Environment Rating	Wet Location	Wet Location	Wet Location	Wet Location
E	Energy Rating	-	-	-	-
	Warranty	2 Year	2 Year	3 Year	1 Year
	Field Select CCT	_	-	-	-
	Field Select Lumens	-	-	-	-
CONTROL	Mode of Control	Switch Activated or Dusk to Dawn	Motion Activated	Motion Activated	Switch Activated or Dusk to Dawn or Motion Activated
	Motion Detection & Range	-	110° detection 60' range	180° detection 70' range	180° detection 50' range
	Blindspot Sensor	-	-	-	-
0	Standby Dimming	-	-	-	-
	Dusk to Dawn Control	Yes	Yes	Yes	Yes
	Remote Control	_	-	-	-
	Smart Control	-	-	-	-

			SECURIT	Y FLOODS	
	PRODUCT FAMILY				
			TGS5S - HIGH OUTPUT		
_	Number of Head	Single	Twin	Triple	Single
CONSTRUCTION	Head Shape	Square	Round & Square	Round	Square
SUC	Lens Finish	Clear Glass	Clear Glass	Clear Glass	Clear Glass
ISTF	Housing Material		Die-Cast Aluminum		
CON	Color Finish		White & Bronze		
	Mounting		Wall / Eave / Surface*		Wall / Eave / Surface*
	Light Source		LED Integrated		
FEATURES / PERFORMANCE	Lumens (Max)	3000	2500	3000	6100
	Life (L70)		70K hours		
FOR	CRI		80		
PER	CCT (K)		4000K		
ES /	Input Voltage		120V		120-277V
TUR	Environment Rating		Wet Location		Wet Location
FEA'	Energy Rating		Energy Star		Energy Star
	Warranty		5 Year		
	Field Select CCT	-	-	-	-
	Field Select Lumens		Yes - 3 Levles of Brightness		
	Mode of Control	Switch Activ	Switch Activated or Dusk to Dawn or Motion Activated		
FROL	Motion Detection & Range	180° detection180° detection270° detection50' range50' range50' range			180° detection 50' range
CONTRO	Blindspot Sensor		-		
0	Standby Dimming		-		
	Dusk to Dawn Control		Yes		
	Remote Control	-	-		
	Smart Control	-	-	-	-



		SMART LED Wi-Fi SECURITY FLOODS	PRO GRADE FLOODSLIGHTS				
	PRODUCT FAMILY						
		ESF WIZ	ARFL	GFL			
	Number of Head	Twin	Single	Single			
Z O	Head Shape	Blade	Square	Square			
2	Lens Finish	Frosted PC	Clear Glass	PC			
פואר	Housing Material	PC	Die-Cast Aluminum	Die-Cast Aluminum			
CONSTRUCTION	Color Finish	White & Black	Bronze	Bronze			
5	Mounting	Wall / Eave	Knuckle Mount with Wall Plate	Knuckle mount- upto 11000 lumens Slipfitter- above 14000 lumens			
	Light Source	LED Integrated	LED Integrated	LED Integrated			
ц	Lumens (Max)	2200	1500-9600lm	1500-18,000			
IAN	Life (L70)	50K hours	50K hours	50K hours			
0KN 0	CRI	>80	>70	>70			
FEATURES / FERFURMANCE	CCT (K)	RGB & Tunable White 2200K - 6500K	2700K/3000K/3500K 4000K/5000K	3000K/4000K/5000K			
X E V	Input Voltage	120V	120V	120-277V			
	Environment Rating	Wet Location	IP65	IP65			
Ì	Energy Rating	-	Energy Star	DLC			
	Warranty	5 Year	5 Year	5 Year			
	Field Select CCT	Yes	Yes	Yes			
	Field Select Lumens	Wireless Dimming 0-100%	-	-			
	Mode of Control	App Control	Switch Activated Or Dusk to Dawn	Switch Activated Or Dusk to Dawn			
šor	Motion Detection & Range	-	-	-			
CONIKUL	Blindspot Sensor	-	-	-			
5	Standby Dimming	-	-	-			
	Dusk to Dawn Control	Through scheduling	Yes	Yes			
	Remote Control	-	Yes	-			
	Smart Control	Yes	-	-			





Turn Photocell ON/OF



HALO AREA LIGHTS

HALO Outdoor LED area and site solutions provide a uniform lighting experience for improved safety by illuminating walking paths, potential obstacles as well as providing substantial energy savings over traditional sources. These patented designs offer a mix of mounting heights, optical designs, and control options for a variety of applications.



			AREA LIGHTS		PRO GRADE AREA LIGHTS
	PRODUCT FAMILY				
		AL6501LED	ALB	ALS	ALP
N	Housing Material	Die-Cast Aluminum	Die-Cast Aluminum	Die-Cast Aluminum	Die-Cast Aluminum
стіс	Design	Traditional	-	-	-
IRU	Lens Style	Drop Lens	Low Profile	Drop Lens	Low Profile
CONSTRUCTION	Color Finish	Gray	Gray	Gray	Gray
ö	Mounting	Wall / Pole	Wall / Pole	Wall / Pole	Wall / Pole
	Light Source	LED Integrated	LED Integrated	LED Integrated	LED Integrated
UH CH	Lumens (Max)	4000	2000-7000	4000-10,000	4000/6000/9000
MAN	Life (L70)	50K hours	50K hours	70K hours	50K hours
FOR	CRI	80 (min)	70 (min)	70 (min)	70 (min)
PER	CCT (K)	4000K	4000K	4000K	3000K / 4000K / 5000K
ES /	Input Voltage	120V	120V	120V	120-277V
FEATURES / PERFORMANCE	Environment Rating	Wet Location	Wet Location	Wet Location	IP65
FEA	Energy Rating	-	Energy Star	Energy Star	DLC Premium
	Warranty	5 year	1 Year	5 Year	5 Year
	Field Select CCT	-	-	-	Yes
CONTROL	Field Select Lumens	-	-	-	Yes
	Dimming	-	-	-	0-10V
	Photocell	Integrated Button Photocell	Integrated Button Photocell	NEMA 3-Pin Photocell	NEMA 3-Pin Photocell





HALO WALL & CEILING

Wall & Ceiling mounted luminaires can provide unique architectural styling to a building while illuminating the adjacent areas for increased pedestrian safety. These LED products offer a mix of mounting heights, optical distributions, and control options for a variety of lighting applications.



		WALL & CEILING LIGHTS		PRO GR	ADE WALL & CEILING			
	PRODUCT FAMILY							
NO		VT	FE	EWP	MWP	WXP	Basic / Lumen	Photocell
	Product Type	Vapor Proof	Wall Sconce	Entry Wall Pack	Mini Wall Pack	Semi Cut Off Wall pack	Select	Integrated lumen select button built in
	Housing Material	Die-Cast Aluminum	PC	PC	Die-Cast Aluminum	Die-Cast Aluminum		allows for adjusting 3 brightness levels
CONSTRUCTION	Lens Finish	Incandescent - Clear LED - Frosted	Frosted PC	Frosted PC	Prismatic PC	Prismatic Glass		
NST	Size	-	-	-	-	Small & Medium		
ខ	Color Finish	Gray	Bronze / White	Bronze	Bronze	Bronze		100
	Mounting	Wall / Ceiling	Wall	Wall	Wall & Conduit	Wall & Conduit	Glow Ring	A
	Light Source	VT100G - 100W Max VT0840L - LED	LED Integrated	LED integrated	LED Integrated	LED Integrated		
ICE	Lumens (Max)	LED- 800	800-1200	1500	2000-4000	4000-12,000		
FEATURES / PERFORMANCE	Life (L70)	50K hours	50,000 hours (FE12S and FE10A Series) & 25000 hours (FE08 Series)	50K hours	50K hours	50K hours	•	
PER	CRI	>70	80	>70	90 (min)	70 (min)		7
ES /	CCT (K)	4000K	3500K/4000K	3000K/4000K/5000K	3000K/4000K/5000K	3000K/4000K/5000K	SURFACE MOUNTED U	SINC
TUR	Input Voltage	120V	120V	120V	120-277V	120-277V	THE INCLUDED CONDUL	
FEA	Enviroment Rating	Wet Location	Wet Location	Wet Location	Wet Location	IP65		
	Energy Rating	-	-	Energy Star	DLC Standard	DLC Standard		
	Warranty	2 Year	5 Year	5 Year	5 Year	5 Year		
	Field Select CCT	-	-	Yes	Yes	Yes		
	Field Select Lumens	-	Yes	-	-	Yes		
CONTROL	Mode of Control	-	Switch Activated or Dusk to Dawn or Motion Activated	Switch Activated Or Dusk to Dawn	Switch Activated Or Dusk to Dawn	Switch Activated Or Dusk to Dawn	WALL MOUNTED TO A RECESSED JUNCTION	BOX
CON	Motion Detection & Range	-	120 detection 15' range	-	-	-		112
	Dimming	-	-	-	0-10V	0-10V		
	Dusk to Dawn Control	-	Yes	On/Off	On/Off	On/Off		

HALO OUTDOOR LIGHTING SOLAR

Iluminate your outdoor space with ease using our Solar Lights. The integrated LED provides ample brightness. Featuring a robust die-cast housing that is resistant to harsh outdoor elements, these lights will stand the test of time.

		SOLAR			SOLAR WITH 3 MODES OF OPERATION			
	PRODUCT FAMILY				Stall Stall			OFF GRID SOLAR SOLUTION
		MSLED300	SWL	SLFS	SLST	SBL ALL-IN-1	SBL HIGH OUTPUT	NO HARD WIRING NEEDED
	Product Type	Wall Mount	Wall Mount	Security Flood	Area	Area	Area	MODES OF OPERATION / MODES DE FONCTIONNEMENT
NO	Sizes Available	1	2	Single, Twin &Triple	2	3	2	*
JCTI	Lens Finish	Frosted	Frosted	Frosted	Clear	Clear	Clear	MOTION DUSK to DUSK to DAWN + ACTIVATED DAWN MOTION ACTIVATED
CONSTRUCTION	Housing Material		Polycarbonate	Polycarbonate	Polycarbonate	Polycarbonate	Die-Cast Aluminum	ACTIVATED DAWN MOTION ACTIVATED MOUVEMENT DU CRÉPUSCULE DU CRÉPUSCULE à L'AUBE + ACTIVE à L'AUBE MOUVEMENT ACTIVE
ပိ	Color Finish	White/Bronze	White/Bronze	White/Bronze	Bronze	Gray	Gray	INTEGRATED MOTION SENSOR
	Mounting	Wall	Wall	Wall/Eave	Wall/Pole 15ft High	Wall/Pole 15 ft High	Wall/Pole 25ft High	
	Light Source	LED Integrated	LED Integrated	LED Integrated	LED Integrated	LED Integrated	LED Integrated	- 120° DECENT
NCE	Lumens (Max)	300lm	500lm, 800lm	2000lm	4500lm	3000lm	10000lm	
RMA	Lifetime	50,000 hours	50,000 hours	50,000 hours	50,000 hours	50,000 hours	50,000 hours	20'
FEATURES / PERFORMANCE	CCT (K)	5000K	4000K	4000K	5000K	5000K	5000K	20' DETECTION DISTANCE
/ PE	Battery Tech	Li-Ion	Li-Ion	Li-Ion	Li-Ion	Li-Ion	Li-Ion	
RES	Battery Run Time	60 minutes	70 minutes	70 minutes	90 minutes	90 minutes	60 minutes	
ATU	Recharge Time	8 Hours	8 Hours	8 Hours	8 Hours	8 Hours	8 Hours	
ΕE	Enniroment Rating	Wet Location	Wet Location	Wet Location	IP65	Wet Location	Wet Location	
	Warranty	1 Year	1 Year	1 Year	1 Year	1 Year	3 Year	
	Mode of Control	Motion + Dusk to Dawn	Motion + Dusk to Dawn	Motion + Dusk to Dawn	WALL ELE MOUNT			
CONTROL	Modes of operation	Motion	Motion	Motion	Motion Dusk to Dawn Motion + D2D	Motion Dusk to Dawn Motion + D2D	Motion Dusk to Dawn Motion + D2D	HALO
	Motion Detection & Range	120 Degree	120 Degree	180 Degree	120 Degree	120 Degree	180 Degree	CONFIGURE WITH REMOTE
	Auto Time Out	60S	30S, 60S, & 90S	30S, 60S, & 90S	30S, 60S, & 90S	30S, 60S, & 90S	30S, 60S, & 90S	CONTROL
	Remote Control	-	-	_	Yes	Yes	Yes	POLE MOUNT

Lighting Brands Ametrix AtLite Corelite Ephesus Fail-Safe HALO HALO Outdoor HALO Commercial Invue iO Iris Lumark Lumière McGraw-Edison Metalux MWS Neo-Ray Portfolio PrentaLux - 3D Printed Lighting RSA Shaper Streetworks Sure-Lites Telensa

Controls Brands

Greengate Fifth Light Intelligent Lighting Controls

Connected Lighting Systems and Smart Spaces Platform

WaveLinx

Cooper Lighting Solutions

1121 Highway 74 South Peachtree City, GA 30269 P: 770-486-4800 www.cooperlighting.com

Canada Sales 5925 McLaughlin Road Mississauga, Ontario L5R 1B8 P: 905-501-3000 F: 905-501-3172 © 2023 Cooper Lighting Solutions All Rights Reserved Printed in USA Publication No. CA51870323 October 20, 2023 5:55 PM All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.

