



Metalux

COMMERCIAL LED LIGHTING

Metalux Commercial features a wide selection of affordable yet aesthetically pleasing fixtures with an expanded offering of selectable color temperatures and lumen options.

METALUX FLAT PANELS

CGTS | CGT Series FLAT PANEL

- Affordable contractor LED panel with fixed or selectable configurations
- Fits in shallow plenums with room to spare; Thin 2 1/8 - inch height
- Field Selectable CCT and Lumens
- Ideal for office spaces, education, healthcare and retail merchandising
- Optional: Wireless integrated sensors provide standalone operation that meets code compliance with simple set up via the Wavelinx mobile app
- Optional: 8W emergency battery packs installed



MarketPro Essentials Selectable CCT & Lumens

Catalog Number	Description	Replaces	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
ES 14CGTS-L3C3	1'x4' Recessed Panel	2-T8	3500K-5000K	120-277V	2,600-4,800	20/29/34	080083282517	S-3EJHF2
ES 22CGTS-L3C3	2'x2' Recessed Panel	3-T8 17W, 2-U6T8	3500K-5000K	120-277V	2,800-4,700	19/28/32	080083194728	PL74TQBZR6SL
ES 24CGTS-L3C3	2'x4' Recessed Panel	4-T8 32W	3500K-5000K	120-277V	4,200-7,200	29/42/51	080083194704	PL0ULJMKXBCH

MarketPro Essentials Dedicated CCT & Lumens

Catalog Number	Description	Replaces	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
ES 22CGT3540C	2'x2' Recessed Panel	3-T8	4000K	120-277V	3,582	32	080083880027	POYGNM7S
ES 24CGT4540C	2'x4' Recessed Panel	2-T8, 3-T8	4000K	120-277V	4,432	38	080083880102	PLTEVMIJ

CGTS with Wavelinx LITE

Catalog Number	Description	Replaces	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
14CGTS-L3C3-WLS	1'x4' Recessed Panel with WaveLinX LITE	2-T8	3500K-5000K	120-277V	2,600-4,800	20/29/34	080083306015	S-RFBM0G
22CGTS-L3C3-WLS	2'x2' Recessed Panel with WaveLinX LITE	3-T8 17W, 2-U6T8	3500K-5000K	120-277V	2,800-4,700	19/28/32	080083306022	S-KTBZC8
24CGTS-L3C3-WLS	2'x4' Recessed Panel with WaveLinX LITE	4-T8 32W	3500K-5000K	120-277V	4,200-7,200	29/42/51	080083306039	S-6DLPMV

Note: DLC Premium items are noted in bold.

CGTS with Emergency Battery Packs

Catalog Number	Description	Replaces	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
14CGTS-L3C3-EL8W	1X4 CGTS 8W w/Emer. Battery Backup	2-T8	3500K-5000K	120-277V	2,600-4,700	20/29/34	080083306046	S-RFBM0G
22CGTS-L3C3-EL8W	2X2 CGTS 8W w/Emer. Battery Backup	3-T8 17W, 2-U6T8	3500K-5000K	120-277V	2,800-4,600	19/28/32	080083306053	S-KTBZC8
24CGTS-L3C3-EL8W	2X4 CGTS 8W w/Emer. Battery Backup	4-T8 32W	3500K-5000K	120-277V	4,200-7,200	29/42/51	080083306060	S-6DLPMV

FPS Series FLAT PANEL

- Ultra-thin LED flat panel; Less than 2-inches height for shallow plenums
- 3 Color Field-Selectable in 30/35/4000K
- Selectable switch to set color temperature, lumens and watts desired for task
- Refined visual optics, superior acrylic light guide; uniform corner to corner illumination
- Ideal for office spaces, schools, healthcare facilities and retail merchandising areas



Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
14FPSL1SCT3	1'x4' Recessed Panel	2-T8	3000K-4000K	120-277V	2,000-4,100	18/27/36	080083889440	PYJV3ZJZ
22FPSL2SCT3	2'x2' Recessed Panel	3-T8	3000K-4000K	120-277V	1,700-3,500	15/22/31	080083889402	PB32RP9H
24FPSL2SCT3	2'x4' Recessed Panel	2-T8, 3-T8	3000K-4000K	120-277V	3,100-6,300	27/40/56	080083889365	PZFJCMXS

METALUX FLAT PANELS

Multi-Mount Selectable
FLAT PANEL

- Visually comforting panel mounts directly to the ceiling or wall reducing labor and material cost by removing the need for a surface mount kit
- Versatile mounting allows for surface, wall, recessed, or suspended with kit
- Selectable Color Temperatures in 90 CRI Standard:
2x2/2x4/1x4: 35/40/5000K | 4' x 6": 27/30/35/40/5000K
- Selectable Lumens: Low, Medium, High settings
- Ideal choice for commercial office, school, and healthcare spaces




Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
4MMS6-L3C5-UNV	4'x6", Direct Mount Panel	2-T8 32W	2700K-5000K	120-277V	1,680-3,000	19/25/33	080083292028	S-KJX1CZ
22MMS-L3C3-UNV	2'x2", Direct Mount Panel	3-T8 32W	3500K-5000K	120-277V	2,400-4,800	21/28/42	080083292042	S-KJX1CZ
24MMS-L3C3-UNV	2'x4', Direct Mount Panel	4-T8 32W	3500K-5000K	120-277V	3,500-6,200	28/36/48	080083292059	S-V9CG2Y
14MMS-L3C3-UNV	1'x4', Direct Mount Panel	2-T8 32W	3500K-5000K	120-277V	2,620-5,286	18/25/38	080083292035	S-28RRZT

Y-hanger Suspension Cable Kit
FLAT PANEL

Y-hanger suspension cable kit with carabiner, SO cord, connectors and round 4" J-box cover plate

Catalog Number	Description	UPC
FPSUS24	Y-hanger suspension cable kit	080083258895



CGRK Retrofit Kit
FLAT PANEL

- Luminaire panels and mounting rails shipped separately for quick installation
- 3 Color Field-Selectable in 35/40/5000K with three lumen options for various retrofit applications
- Micro-optics for uniform illumination, extruded aluminum frame for performance and aesthetics
- DLC Premium options for maximum energy savings and rebates, including WaveLinx Lite for enhanced savings



Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
14CGRK-L3C3-UNV-MP4	1'x4' Backlit Panel Retrofit Kit (4-Pack)	2-T8	3500K-5000K	120-277V	2,000-4,100	14/22/29	080083312139	S-XP62Y7
22CGRK-L3C3-UNV-MP4	2'x2' Backlit Panel Retrofit Kit (4-Pack)	3-T8 17W, 2-U6T8	3500K-5000K	120-277V	2,000-4,100	15/22/29	080083312146	S-W4YPLT
24CGRK-L3C3-UNV-MP4	2'x4' Backlit Panel Retrofit Kit (4-Pack)	4-T8 32W	3500K-5000K	120-277V	2,800-5,000	20/27/35	080083312153	S-871T6V

Note: DLC Premium items are noted in bold.

METALUX TROFFERS

Surround Frame Selectable
ILLUMINATED FRAME

- Architectural 1.5" illuminated modern frame enhances the look of any space
- Versatile mounting in existing T-grid using ceiling tile as the reflector, suspension also available with kit
- 4 Color Field-Selectable in 30/35/40/5000K
- Selectable Lumens - Low, Medium, High settings
- Ideal choice for commercial office, school, and healthcare spaces



Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
22SFS-L3C4-UNV	2'x2', Surround Frame	3-T8 32W	3000K-5000K	120-277V	1,900-4,600	15/25/36	080083293124	S-6WZN2T
24SFS-L3C4-UNV	2'x4', Surround Frame	4-T8 32W	3000K-5000K	120-277V	3,000-6,000	23/35/47	080083293148	S-TPM2HQ

Cruze Selectable CZS | Cruze ST Recessed
TROFFER

- Architectural center lens troffer with aesthetic appeal
- Latch-less design provides clean architectural look; ribbed, frosted acrylic lens
- 3 Color Field-Selectable in 30/35/4000K and dedicated in 3500K, 4000K
- Ideal choice for commercial, institutional and healthcare facilities



Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
14CZSCT3-UNV	1'x4', Troffer	2-T8	3000K-4000K	120-277V	3,000-4,400	20-30	080083268443	S-5LPE0V
22CZSCT3-UNV	2'x2', Troffer	2-T5, 2-T8	3000K-4000K	120-277V	2,700-4,075	21-31	080083268467	S-QDP2J8
24CZSCT3-UNV	2'x4', Troffer	2-T8, 3-T8	3000K-4000K	120-277V	3,500-6,500	24-47	080083268481	S-MW0TCN

Achieva™ Recessed Selectable
TROFFER

- Ultra slim 1.5" center basket design fits into the shallowest of plenums
- 3 Color Field-Selectable in 30/35/4000K in 80+ CRI
- 3 Selectable lumens in standard or HO options up to 8,150
- Ideal choice for commercial, institutional and healthcare facilities



MarketPro Essentials

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
ES 14ARS-L3C3-UNV	1'x4', Troffer	2-T8	3500K-5000K	120-277V	2,800-4,600	20/26/33	080083282241	S-N7LRJL
ES 22ARS-L3C3-UNV	2'x2', Troffer	2-T8, 2-T5	3500K-5000K	120-277V	2,750-4,300	20/26/33	080083282128	S-N0X10I
ES 24ARS-L3C3-UNV	2'x4', Troffer	2-T8, 3-T8	3500K-5000K	120-277V	3,400-6,250	24/33/46	080083282005	S-EA9S16
ES 24ARS-L3C3-HO-UNV	2'x4', Troffer, High Output	3-T8, 2-T5HO	3500K-5000K	120-277V	6,300-8,150	46/52/58	080083282081	S-SHLC4F
ES 22ARS-L3C3-UNV-MP4	2'x2', Troffer (4-Pack)	2-T5, 2-T8	3500K-5000K	120-277V	2,750-4,300	20/26/33	080083282388	S-N0X10I
ES 24ARS-L3C3-UNV-MP2	2'x4', Troffer (2-Pack)	2-T8, 3-T8	3500K-5000K	120-277V	3,400-6,250	24/33/46	080083282364	S-EA9S16

Note: DLC Premium items are noted in bold.