



High Bays



Vaportites

Metalux

INDUSTRIAL LIGHTING

Metalux Industrial offers a selection of economical and energy-efficient high-bay and vaportite lighting solutions designed for a wide variety of applications.

METALUX HIGH BAYS

UHBS2 High Performance LED HIGH BAY

- Durable, 12", 14", and 20" round die cast aluminum housing
- Field selectable distribution - Narrow, Medium, or Wide
- Up to 60,000 selectable lumens with 5 Color Selectable CCT - 30/35/40/50/6500K
- Sensor ready port for quick plug and play install
- 120-347V input, 0-10V dimming with 6kV surge protection



Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
UHBS2-1218-MV-L8C5-U	Round, White	4-T5HO 54W, 400W MH	3000K-6500K	120-347V	12,000-18,000	79-122W	080083301836	S-DVZ2KB
UHBS2-2436-MV-L8C5-U	Round, White	8-T5HO 54W, 10T8 32W, 750MH	3000K-6500K	120-347V	24,000-36,000	153-239W	080083301843	S-JVQHNC
UHBS2-4860-MV-L8C5-U	Round, White	1000W MH, 400MH	3000K-6500K	120-347V	48,000-60,000	311-388	080083301850	Pending

Note: DLC Premium items are noted in bold.

SPHB Selectable Series HIGH BAY

- 2 Compact, lightweight designs for easy install
- Up to 36,000 selectable lumens and 4000K/5000K selectable CCT
- Sensor Ready port for quick plug and play install
- Great for industrial, manufacturing, gymnasium, and warehouse



Selectable lumen output and color temperature with an easy to access toggle switch.

MarketPro Essentials

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
ES SPHB-1224SE-M-UNV-L84050-CD-SP1-U	Med. Distr	6-T5HO, 8-T8, 400W MH	4000K-5000K	120-277V	12,000-24,000	82/123/166	080083289264	S-01PR4D
ES SPHB-2436SE-M-UNV-L84050-CD-SP1-U	Med. Distr	8-T5HO, 10-T8, 400W MH	4000K-5000K	120-277V	24,000-36,000	162/209/251	080083289288	S-7V2YTC

Catalog Number	Description	UPC
Y-TOGGLE-10-2PK	Mounting Toggle and 10' Cable	080083259557
Y-TOGGLE-30-2PK	Mounting Toggle and 30' Cable	080083259571

Note: DLC Premium items are noted in bold.

PIR Sensor HIGH BAY

- Simple, in-field plug and play installation; Occupancy control with 4 preset modes
- Passive Infra-Red (PIR) and daylight sensor with detection at mounting heights up to 50FT
- Remote control capability using separate accessory (UHBS Sensor Remote Control)



Catalog Number	Description	UPC
UHBS-SENSOR PK*	PIR Sensor 360 Lens 50FT MH Kit	080083257898
UHBS SENSOR REMOTE	UHBS Sensor Remote Control	080083260249

*To meet state and local codes, EBP cannot be used with UHBS with sensor or with UHBS sensor accessory.

WaveLinx Sensor HIGH BAY

- Models suitable for High bay (up to 40ft) applications
- Out of the box functionality: Occupied to Full, Unoccupied to off, daylighting disabled
- Passive Infra-Red (PIR) motion sensor; Integrated photocell for daylight harvesting



Catalog Number	Description	UPC
WLS4-HB2	WaveLinx LITE Industrial Fixture Mount High Bay Sensor, White, 15 - 40ft (4.5 - 12.2m)	080083446315

EZBY Series
HIGH BAY

- Up to 30,000 selectable lumens and 3000/4000/5000K selectable CCT
- Sensor ready port for quick plug and play install
- Mounting ring included for rapid install
- 120-347V input, 0-10V dimming



MarketPro Essentials

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
ES EZBY-1830C3-MV-BLK	Round, Black	8 T8 or 6 T5HO lamps or 400W MH	3000K-5000K	120-347V	18,000-30,000	122-185W	080083305889	S-WK156D

Note: DLC Premium items are noted in bold.

APVT Series
VAPORTITE

- Durable polycarbonate housing with integral metal gear tray
- 4ft and 8ft sizes with CCT and lumen select capability
- UL Wet location, IP65 and operating temp -20C to 40C
- Stainless steel latches, single conduit hub, and mounting included



MarketPro Essentials

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
ES 4APVTLD-SL3C3	4' Selectable Output	3-T8 32W, 2-T5HO 54W	3500K-5000K	120-277V	3,000-6,000	21-46	080083264216	S-M39BJL
ES 8APVTLD-SL3C3	8' Selectable Output	4-T8 32W, 3-T5HO 54W	3500K-5000K	120-277V	8,500-12,000	59-94	080083266333	S-3EH2VC



		MarketPro Essentials	MarketPro Essentials	
		EZBY	SPHB	UHBS2
APPLICABILITY ¹	Big Box Retail	★	★★	★★
	Sports / Recreation	★	★★	★★
	Warehouses	★★★	★★★	★★★
	Manufacturing	★★	★★★	★★★
	Cold Storage	★★	★★★	★★
	Complex Environments	★	★	★★

FEATURES / PERFORMANCE	Lumen Range	18,000 - 28,000	12,000 - 36,000	12,000 to 60,000
	Selectable Lumens	18,000-30,000	12,000 - 24,000 or 24,000 - 36,000	12,000-18,000, 24,000-36,000, and 48,000-60,000
	Efficacy (Max)	150 lm/W	158 lm/W	181 lm/W
	CRI	80	80	80
	Distribution	Medium (100-deg)	M	Selectable Optics (N, M, or W)
	Sizes	13.4	12" x 18" or 12" x 36"	12", 14", 20"
	Housing ²	Diecast	CRS	Diecast
	Lensing	Polycarbonate	Polycarbonate	Polycarbonate
	Uplight	None	None	None
	Life (@ 60K hrs)	L91	L86	L91
	Ambient Range	-20C to 50C	-40C to 45C	-40C to 50C
	Emergency	Remote	Optional	Remote
	Ratings	IP65	Damp, IP5X	IP65, NEMA, 4X, NSF, Wet Location
	DLC	Premium	Premium	Premium

INTEGRATED CONTROLS	Basic Occupancy		✓	
	Stand Alone Daylight / Occupancy	✓	✓	✓
	WaveLinx		✓	✓

Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable
2. CRS=Cold-rolled Steel, Extruded= Extruded Aluminum, Diecast=Diecast Aluminum.