



**LUMARK AP**  
**LUMARK**  
**OUTDOOR LUMINAIRES**

Lumark brands offer a wide selection of high-quality product solutions that provide market-leading ease of installation, superior area safety, and maximum energy savings in commercial and industrial spaces.

## LUMARK AP WALL MOUNTS

### AWP Architectural Wall Pack

#### WALL MOUNT

- Customizable 0–45° rotatable optics for targeted lighting
- Finned or smooth front options available to match any building style
- Flexibility with field-selectable 3-color CCT (3000K/4000K/5000K)
- Wide coverage with field-selectable 2,600–20,500 lumens
- Durable die-cast housing with hinged, removable door for quick installation



AWPS with smooth front



AWPF with finned front

#### Wall Mounts



#### Floodlights



#### Ceiling Mounts



#### Area/Site



#### MarketPro Essentials

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
<b>ES</b> AWPS28S	Architectural Wall Pack Small Smooth	Bronze	70W MHL	3000K-5000K	120-347V	2,600-3,900	20-28W	080083448388	Pending
<b>ES</b> AWPS75S	Architectural Wall Pack Medium Smooth	Bronze	125W MHL	3000K-5000K	120-347V	7,600-10,800	55-75W	080083448401	Pending
<b>ES</b> AWPS150S	Architectural Wall Pack Large Smooth	Bronze	250W MHL	3000K-5000K	120-347V	13,300-20,500	100-50W	080083448425	Pending
<b>ES</b> AWPF28S	Architectural Wall Pack Small Fins	Bronze	70W MHL	3000K-5000K	120-347V	2,600-3,900	20-28W	080083448449	Pending
<b>ES</b> AWPF75S	Architectural Wall Pack Medium Fins	Bronze	125W MHL	3000K-5000K	120-347V	7,600-10,800	55-75W	080083448463	Pending
<b>ES</b> AWPF150S	Architectural Wall Pack Large Fins	Bronze	250W MHL	3000K-5000K	120-347V	13,300-20,500	100-50W	080083448487	Pending

Note: DLC Premium items are noted in bold.

### WP Wall Pack

#### WALL MOUNT

- Three housing sizes for versatile lighting applications
- Flexibility with field-selectable 5-color CCT (3000K/3500K/4000K/5000K/6500K)
- Wide coverage with field-selectable 4,300–21,000 lumens
- Borosilicate glass and die-cast housing to withstand heat, weather, and impacts
- Quick installation and access with hinged, removable door design



#### MarketPro Essentials

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
<b>ES</b> WPSLED15S	Small LED Wall Pack	Bronze	150W HID	3000K-6500K	120-347V	4,300-8,100	30-60W	080083304561	S-G2CQRH
<b>ES</b> WPMLED26S	Medium LED Wall Pack	Bronze	350W HID	3000K-6500K	120-347V	10,000-14,900	70-100W	080083304585	S-G2CQRH
<b>ES</b> WPLLED38S	Large LED Wall Pack	Bronze	500W HID	3000K-6500K	120-347V	17,300-21,000	120-150W	080083304707	S-34RRLO

### CYL Wall Cylinder

#### WALL MOUNT

- Three lighting styles in one - configure as a downlight, uplight, or both
- Flexibility with field-selectable 3-color CCT (3000K/4000K/5000K)
- Wide coverage with field-selectable 1,600–3,600 lumens
- Rugged die-cast housing with sealed lens for weather-resistant performance
- Ideal for walkways, parking lots, and building areas



Also available in Bronze

#### MarketPro Essentials

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
<b>ES</b> CYL-2D-30W-PC-BK	6" Cylinder	Black	70W HID	3000K-5000K	120-347V	1,600-3,600	30W	080083445998	S-MQXYX1
<b>ES</b> CYL-2D-30W-PC-BZ	6" Cylinder	Bronze	70W HID	3000K-5000K	120-347V	1,600-3,600	30W	080083446001	S-MQXYX1

## WPSQ Square Wall Pack

### WALL MOUNT

- Built-in photocontrol for automated security lighting and energy saving
- Flexibility with field-selectable 3-color CCT (3000K/4000K/5000K)
- Wide coverage with field-selectable 10,200-13,700 lumens
- Borosilicate glass and die-cast housing to withstand heat, weather, and impacts
- Ideal for building entrances, vehicle ramps, stairways, loading docks and more



#### MarketPro Essentials

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
ES WPSQ25S-347-PC	Square Wall Mount	250W HID	3000-5000K	120-347V	10,200-13,700	70W-100W	080083307203	S-KXHMTG

## LSF Floodlight

### FLOODLIGHT

- Three housing sizes for versatile lighting applications
- Flexibility with field-selectable 3-color CCT (3000K/4000K/5000K)
- Wide coverage with field-selectable 1,700-20,000 lumens
- Knuckle, slipfitter, trunnion, and yoke mounting options available
- Ideal for walls, polls, brackets, or ground installation



#### MarketPro Essentials

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
ES LSF25-KNYK-PC	Yoke Mount, Photocontrol	Bronze	155W HID	3000K-5000K	120-347V	1,700-4,000	11-25W	080083305230	<b>S-W43YTM</b>
ES LSF65-KNYK-PC	Yoke Mount, Photocontrol	Bronze	375W HID	3000K-5000K	120-347V	5,000-10,000	25-65W	080083305254	<b>S-5HK1XN</b>
ES LSF120-SFTR-PC	Trunnion Mount, Photocontrol	Bronze	450W HID	3000K-5000K	120-347V	9,000-20,000	50-120W	080083305278	<b>S-M4YHAF</b>

Note: DLC Premium items are noted in bold.

## CLCS Canopy

### CEILING MOUNT

- Two housing sizes for versatile lighting applications
- Flexibility with field-selectable 3-color CCT (3000K/4000K/5000K)
- Wide coverage with field-selectable 3,400-17,600 lumens
- Dusk to dawn capability with ON/OFF photocontrol
- Quick installation in new or existing canopies for drive-thrus, gas stations, and walkways



#### MarketPro Essentials

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
ES CLCS15S-PC	Small LED Canopy	Bronze	150-300W HID	3000K-5000K	120-347V	3,400-8,200	24-60W	080083304905	S-GFY8QK
ES CLCS30S-PC	Large LED Canopy	Bronze	150-300W HID	3000K-5000K	120-347V	7,300-17,600	50-120W	080083304929	S-L00Y67

## RPGC Round Canopy

### CEILING MOUNT

- Round drop lens provides uplight to eliminate dark ceilings
- Flexibility with field-selectable 3-color CCT (3000K/4000K/5000K)
- Wide coverage with field-selectable 3,700-7,800 lumens
- Low profile, die cast aluminum housing
- Easy installation with quick-mount bracket for hands-free wiring



Catalog Number	Description	Finish	Replaces	CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
RPGC25S	Round Parking Garage, UNV	White	150-250W HID	4000K	120-277V	3,700-7,800	30-60W	080083911769	P8ZU6PEI
RPGC25S-347	Round Parking Garage, 347V	White	150-250W HID	4000K	120-277V	3,700-7,800	30-60W	080083911783	PDTLEH52
RPGC25-MS/DIM-L08	Round Parking Garage, UNV, 8' Sensor Ht	White	150-250W HID	4000K	120-347V	3,700-7,800	30-60W	080083911806	P8ZU6PEI
RPGC25-MS/DIM-L20	Round Parking Garage, UNV, 20' Sensor Ht	White	150-250W HID	4000K	120-347V	3,700-7,800	30-60W	080083911820	P8ZU6PEI
RPGC25-347-MS/DIM-L08	Round Parking Garage, 347V, 8' Sensor Ht	White	150-250W HID	4000K	120-347V	3,700-7,800	30-60W	080083911844	PDTLEH52
RPGC25-347-MS/DIM-L20	Round Parking Garage, 347V, 20' Sensor Ht	White	150-250W HID	4000K	120-347V	3,700-7,800	30-60W	080083911868	PDTLEH52

## BOL Bollard

### AREA/SITE

- Four head options for versatile lighting design flexibility
- Flexibility with field-selectable 3-color CCT (3000K/4000K/5000K)
- Wide coverage with field-selectable 1,300-3,800 lumens
- Designed with future battery pack capability and IP65 durability
- Ideal for parking lots, pedestrian spaces, walkways and building areas



Catalog Number	Description	Finish	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
BOLD42-25S*	Dome-shaped Bollard	Bronze	3000K-5000K	120-277V	2,300-3,800	15-26W	080083445189	Pending
BOLY42-25S*	Y-Shaped Bollard	Bronze	3000K-5000K	120-277V	1,800-3,300	15-26W	080083445196	Pending
BOLF42-25S	Flat Top Bollard	Bronze	3000K-5000K	120-277V	1,300-2,400	15-26W	080083445189	Pending
BOLR42-25S	Round Top Bollard	Bronze	3000K-5000K	120-277V	1,300-2,400	15-26W	080083445813	Pending

\* DesignLights Consortium® Qualified. Refer to [www.designlights.org](http://www.designlights.org) Qualified Products List under Family Models for details.

## Accessories

Catalog Number	Description	UPC
BOLHKIT	Spare Hardware Kit: Anchor Bolt Carrier (x1), Nut (x12), Spring Washer (x3), Flat Washer (x6), Anchor Bolts (x3), Hex Wrench (x1)	080083445820

## LAS Area and Site Luminaire

### AREA/SITE

- Two housing sizes for versatile lighting applications
- Automatic dusk-to-dawn area lighting with standard twist-lock photocontrol
- Wide coverage with 10 position field-selectable lumens
- Available with pole-mount arm or adjustable slipfitter for quick installation
- Ideal for parking lots, walkways, and building perimeters



### MarketPro Essentials

Catalog Number	Description	Finish	Replaces	CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
<b>ES LAS45S-T3</b>	T3 Distr., Adjustable Slipfitter Arm	Bronze	450W HID	4000K	120-277V	4,900-20,000	30-153W	080083155804	<b>P1T4HG08</b>
<b>ES LAS45P-T3</b>	T3 Distr., Pole Mount Arm	Bronze	450W HID	4000K	120-277V	4,900-20,000	30-153W	080083248360	<b>P1T4HG08</b>
<b>ES LAS45S-T4</b>	T4 Distr., Adjustable Slipfitter Arm	Bronze	450W HID	4000K	120-277V	4,900-20,000	30-153W	080083155828	<b>PJZTZ423</b>
<b>ES LAS45P-T4</b>	T4 Distr., Pole Mount Arm	Bronze	450W HID	4000K	120-277V	4,900-20,000	30-153W	080083248384	<b>PJZTZ423</b>
<b>ES LAS45S-T5</b>	T5 Distr., Adjustable Slipfitter Arm	Bronze	450W HID	4000K	120-277V	4,900-20,000	30-153W	080083155842	<b>PW39PQB3</b>
<b>ES LAS45P-T5</b>	T5 Distr., Pole Mount Arm	Bronze	450W HID	4000K	120-277V	4,900-20,000	30-153W	080083248704	<b>PW39PQB3</b>
<b>ES LAS100S-T3</b>	T3 Distr., Adjustable Slipfitter Arm	Bronze	1,000W HID	4000K	120-277V	8,200-34,000	48-251W	080083155866	<b>PP8AW4F5</b>
<b>ES LAS100P-T3</b>	T3 Distr., Pole Mount Arm	Bronze	1,000W HID	4000K	120-277V	8,200-34,000	48-251W	080083248780	<b>PP8AW4F5</b>
<b>ES LAS100S-T4</b>	T4 Distr., Adjustable Slipfitter Arm	Bronze	1,000W HID	4000K	120-277V	8,200-34,000	48-251W	080083155880	<b>POCHU9AS</b>
<b>ES LAS100P-T4</b>	T4 Distr., Pole Mount Arm	Bronze	1,000W HID	4000K	120-277V	8,200-34,000	48-251W	080083248803	<b>POCHU9AS</b>
<b>ES LAS100S-T5</b>	T5 Distr., Adjustable Slipfitter Arm	Bronze	1,000W HID	4000K	120-277V	8,200-34,000	48-251W	080083155903	<b>PMUFIF4F</b>
<b>ES LAS100P-T5</b>	T5 Distr., Pole Mount Arm	Bronze	1,000W HID	4000K	120-277V	8,200-34,000	48-251W	080083248827	<b>PMUFIF4F</b>

Note: DLC Premium items are noted in bold.



## AXC Axcent Luminaire

### WALL MOUNT

- Full cutoff and refractive LED lens models available in small or large
- Hook-N-Lock mechanism for easy, one-person installation
- Die-cast aluminum construction with energy-efficient illumination
- Fully gasketed optical compartment keeps out contaminants like bugs, water and dust
- Ideal for pathway illumination and floodlighting applications



Catalog Number	Description	Finish	Replaces	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
AXCS1A	Small Full Cutoff	Carbon Bronze	70W HID	4000K	120-277V	1,806	14	080083887965	<b>S-3SJYCL</b>
AXCS2A	Small Full Cutoff	Carbon Bronze	100W HID	4000K	120-277V	2,561	21	080083887989	<b>S-0YO8BE</b>
AXCS3A	Small Full Cutoff	Carbon Bronze	150W HID	4000K	120-277V	3,537	27	080083888009	<b>S-H7120V</b>
AXCS4A	Small Full Cutoff	Carbon Bronze	250W HID	4000K	120-277V	5,520	44	080083888023	<b>PI16J9UO</b>
AXCS4RL	Small Refractive Lens	Carbon Bronze	250W HID	4000K	120-277V	5,858	44	080083888030	<b>PPXSGJ9K, PCFKRFBV</b>
AXCS5A	Small Full Cutoff	Carbon Bronze	320W HID	4000K	120-277V	6,300	52	080083888047	<b>PCPDYSZM</b>
AXCL6A	Large Full Cutoff	Carbon Bronze	320W HID	4000K	120-277V	7,594	56	080083811564	<b>PLXS8Y3B</b>
AXCL6ARL	Large Refractive Lens	Carbon Bronze	320W HID	4000K	120-277V	7,809	56	080083811649	<b>PZXNXUOI</b>
AXCL8A	Large Full Cutoff	Carbon Bronze	400W HID	4000K	120-277V	9,696	72	080083811588	<b>PG4TJNY3</b>
AXCL8ARL	Large Refractive Lens	Carbon Bronze	400W HID	4000K	120-277V	9,970	72	080083811663	<b>PBA84MB6</b>
AXCL10A	Large Full Cutoff	Carbon Bronze	400W HID	4000K	120-277V	13,283	102	080083811601	<b>P5X06GE7</b>
AXCL12A	Large Full Cutoff	Carbon Bronze	450W HID	4000K	120-277V	16,823	123	080083811625	<b>PD1N4D39</b>

Note: DLC Premium items are noted in bold.

## AXC Back Box Accessory

Catalog Number	Description	Finish	UPC
BB/AXC	Back Box	Carbon Bronze	080083160709
BB/AXC-PC	Back Box with Photocontrol	Carbon Bronze	080083160723

### Features

Lumen Select pack allows installer to reduce the light output to 75 or 50%

Integrated photocontrol provides maximum energy savings while leveraging

Four 1/2" NPT conduit entry points for surface mounted conduit

Single die-cast aluminum back box to simultaneously accommodate Axcent small and large housings



## XTOR Crosstour Luminaire

### WALL MOUNT

- Architectural design with low profile and super bright, energy-efficient LEDs
- Rugged and weather-sealed die-cast construction
- Universal back box with sealed and gasketed optical compartment
- Wall, surface, post, bollard, low-level, inverted, floodlight mounting
- Ideal for multi-use facilities, pathway illumination and building entrances



Catalog Number	Description	Finish	Replaces	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
XTOR1B	Small Full Cutoff	Carbon Bronze	70W HID	5000K	120-277V	1,418	12	080083777969	PRVAZAZR
XTOR2B	Small Full Cutoff	Carbon Bronze	100W HID	5000K	120-277V	2,135	18	080083778225	PGP4FYV3
XTOR3B	Small Full Cutoff	Carbon Bronze	150W HID	5000K	120-277V	2,751	26	080083778041	PWFZHYJH
XTOR4B	Medium Full Cutoff	Carbon Bronze	250W HID	5000K	120-277V	4,269	38	080083778003	PUJ1NXGY
XTOR6B	Large Full Cutoff	Carbon Bronze	320W HID	5000K	120-277V	6,129	58	080083774807	S-X7BH39
XTOR6B-PC1	Large Full Cutoff with Photocontrol	Carbon Bronze	320W HID	5000K	120-277V	6,129	58	080083774845	S-X7BH39
XTOR6BRL	Large Refractive Lens	Carbon Bronze	320W HID	5000K	120-277V	6,225	58	080083774821	N/A
XTOR8B	Large Full Cutoff	Carbon Bronze	400W HID	5000K	120-277V	8,502	81	080083774814	P5557CRH
XTOR8B-PC1	Large Full Cutoff with Photocontrol	Carbon Bronze	400W HID	5000K	120-277V	8,502	81	080083774869	P5557CRH
XTOR8BRL	Large Refractive Lens	Carbon Bronze	400W HID	5000K	120-277V	8,635	81	080083774852	N/A

## CTKR Caretaker Series

### AREA/SITE

- Rugged die-cast construction for durability and security applications
- Precision optics provide uniform, widespread illumination for maximized visibility
- Wall/pole-mount bracket and integral slipfitter for versatility in mounting
- Versatile universal mounting plate allows quick and easy installation on poles, walls or barns
- Ideal for rural street lighting, perimeter fences, parking areas, loading docks and more



### MarketPro Essentials

Catalog Number	Description	Finish	Replaces	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
ES CTKRV1C	Nano 30W, 4500lm, UNV, Dimming, Photocontrol	Raw	CTKRV1B	4000K	120-277V	4,500	30	080083470990	Pending
ES CTKRV2C	Nano 50W, 6200lm, UNV, Dimming, Photocontrol	Raw	CTKRV2B	4000K	120-277V	6,200	50	080083470983	Pending
ES CTKRV3B	71W, 9700lm, UNV, Dimming, Photocontrol	Raw	250W HID	4000K	120-277V	9,700	71	080083865413	<b>P3P0FHTML</b>

Note: DLC Premium items are noted in bold.

### Accessories

Catalog Number	Description	Finish	UPC
SR-CARETAKER	Small Acrylic Refractor	Clear	080083777969

## PRV Prevail Luminaire

### AREA/SITE

- Sleek, low-profile architectural design with high-performance LEDs and superior efficacy
- Versatile arm mount fits round or square poles for quick installation
- Multiple optical configurations ensure uniform site coverage and optimal pole spacing for energy savings
- Simple retrofit installation for reduced installation time and labor savings
- Ideal for parking lots, campuses, roadways, and walkways



Catalog Number	Description	Finish	Replaces	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
PRVS-C25-UNV-T3	T3 Distr., STD Arm Mount	Bronze	250W HID	4000K	120-277V	13,183	96	080083897308	<b>S-43K2M0</b>
PRVS-C25-UNV-T4	T4 Distr., STD Arm Mount	Bronze	250W HID	4000K	120-277V	13,140	96	080083897322	<b>S-CXYVFA</b>
PRVS-C40-UNV-T3	T3 Distr., STD Arm Mount	Bronze	400W HID	4000K	120-277V	17,144	131	080083897346	<b>S-YEWL3K</b>
PRVS-C40-UNV-T4	T4 Distr., STD Arm Mount	Bronze	400W HID	4000K	120-277V	17,087	131	080083897360	<b>S-L5W8VA</b>
PRVS-C60-UNV-T3	T3 Distr., STD Arm Mount	Bronze	450W HID	4000K	120-277V	20,050	153	080083897384	<b>S-NS9Z4</b>
PRVS-C60-UNV-T4	T4 Distr., STD Arm Mount	Bronze	450W HID	4000K	120-277V	19,984	153	080083897421	<b>S-RAGPH4</b>

Note: DLC Premium items are noted in bold.

## NFFLD Night Falcon Luminaire

### FLOODLIGHT

- Cost-effective LED floodlight available in medium or large sizes
- Wide 6x6 NEMA beam pattern ensures even illumination with fewer fixtures
- Precision engineered and high-efficiency optics delivers superior uniformity
- Rugged, die-cast aluminum housing for reliable, weatherproof operation
- Ideal for building façades, wall signs, and yard perimeters



Catalog Number	Description	Finish	Replaces	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
NFFLD-S-C15-T-UNV	Small, Trunnion	Carbon Bronze	150W HID	4000K	120-277V	5,797	51	080083760275	P07DFEUO
NFFLD-S-C15-KNC-UNV	Small, Knuckle	Carbon Bronze	150W HID	4000K	120-277V	5,797	51	080083760268	P07DFEUO
NFFLD-C25-S	Medium, Slipfitter	Carbon Bronze	250W HID	4000K	120-277V	10,530	85	080083801244	P5JBKNFS
NFFLD-C25-T	Medium, Trunnion	Carbon Bronze	250W HID	4000K	120-277V	10,530	85	080083801220	P5JBKNFS
NFFLD-C40-S	Medium, Slipfitter	Carbon Bronze	400W HID	4000K	120-277V	16,932	128	080083801206	<b>PCHB15F8</b>
NFFLD-C40-T	Medium, Trunnion	Carbon Bronze	400W HID	4000K	120-277V	16,932	128	080083801183	<b>PCHB15F8</b>
NFFLD-L-C100-S	Large, Slipfitter	Carbon Bronze	1,000W HID	4000K	120-277V	33,941	252	080083800889	P53SWTBG
NFFLD-L-C100-T	Large, Trunnion	Carbon Bronze	1,000W HID	4000K	120-277V	33,941	252	080083800902	<b>P53SWTBG</b>

Note: DLC Premium items are noted in bold.

## NHR Night Harrier Luminaire

### FLOODLIGHT

- NEMA 3-Pin photocontrol (large) & button-type photocontrol (medium)
- Flexibility with field-selectable 3-color CCT (3000K/4000K/5000K)
- Wide coverage with field-selectable 5,500-43,000 lumens
- Available with slipfitter and trunnion mountings for pole, wall, or ground installations
- Ideal for façades, wall-washing, large signage, and other large areas




Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
NHRS50UT	500W Trunnion Mount	Bronze	70W to 500W HID	3000K-5000K	120-277V	5,500-22,000	40-155W	080083283903	Pending
NHRS50US	500W Slipfitter Mount	Bronze	70W to 500W HID	3000K-5000K	120-277V	5,500-22,000	40-155W	080083283910	Pending
NHRS50HT	500W Trunnion Mount	Bronze	70W to 500W HID	3000K-5000K	347-480V	5,500-22,000	40-155W	080083283927	Pending
NHRS50HS	500W Slipfitter Mount	Bronze	70W to 500W HID	3000K-5000K	347-480V	5,500-22,000	40-155W	080083283934	Pending
NHRS50UT-BPC	500W Trunnion Mount, Photocontrol	Bronze	70W to 500W HID	3000K-5000K	120-277V	5,500-22,000	40-155W	080083283941	Pending
NHRS50US-BPC	500W Slipfitter Mount, Photocontrol	Bronze	70W to 500W HID	3000K-5000K	120-277V	5,500-22,000	40-155W	080083283958	Pending
NHRS100UT	1000W Trunnion Mount	Bronze	500W-1000W HID	3000K-5000K	120-277V	23,000-43,000	40-155W	080083296965	Pending
NHRS100US	1000W Slipfitter Mount	Bronze	500W-1000W HID	3000K-5000K	120-277V	23,000-43,000	40-155W	080083296972	Pending
NHRS100HT	1000W Trunnion Mount	Bronze	500W-1000W HID	3000K-5000K	347-480V	23,000-43,000	40-155W	080083296989	Pending
NHRS100HS	1000W Slipfitter Mount	Bronze	500W-1000W HID	3000K-5000K	347-480V	23,000-43,000	40-155W	080083296996	Pending



## Resource Center


[Cooperlighting.com](https://Cooperlighting.com) > Resources

Visit Cooperlighting.com and click on the Resources tab. The Resource Center is a central location of supportive product selection tools, inspirational images and downloadable digital resources.



**Product Resources**

- Brochures & guides
- Spec sheets
- Installation sheets and guides
- Product Selection Guide




**Inspiration**

- Application photography
- Product photography & videos
- Case studies
- Logos



**Tools**

- PRISM Portal
- Energy Incentive Finder
- Photometric IES
- Revit models
- Calculators & audit tools



**Programs**

- MarketPro™
- Quick Spec
- Overstock



**Education**

- Instructor-led classes
- Free online courses
- Continuing education

## Learn. Grow. Visualize.

Explore our one-stop-shop for Cooper Lighting Solutions digital tools.

## Explore Our Video Library!

Visit Cooper Lighting Solutions' YouTube page to explore our ever-expanding product video library! Everything you need to know about our innovative product offering can be found here. Get the facts on newly introduced solutions, discover product benefits and watch videos on how to install them. Explore our curated playlists to easily find informative videos by industry-leading brand, market and product category.

[youtube.com/cooperlightingsolutions](https://youtube.com/cooperlightingsolutions)



# HALO Outdoor



Security and utility lighting for residential and commercial applications offering a wide range of features including motion sense, color temperature choices, lumen options, dawn-to-dusk, and more.

## HALO OUTDOOR FLOODLIGHTS

### TGS Series – Twin Head

#### SECURITY FLOODLIGHT

- Three different brightness levels using Lumen Select Technology
- Durable die-cast aluminum square head with UV resistant lens
- Easy install to wall or eave mounting, with integrated easy connector
- Switch activated, Dusk-to-Dawn, and motion activated models available
- Ideal for security lighting in residential and commercial applications



Catalog Number	Description	Finish	Replaces	CCT	Voltage	Selectable Lumens	Watts	UPC
TGS2S402FRRB	Twin Head Round	Bronze	180W INC	4000K	120V	1,500-2,500	22	080083913053
TGS2S402FRRW	Twin Head Round	White	180W INC	4000K	120V	1,500-2,500	22	080083913374
TGS2S402DRRB	Twin Head Round, D2D	Bronze	180W INC	4000K	120V	1,500-2,500	22	080083913435
TGS2S402DRRW	Twin Head Round, D2D	White	180W INC	4000K	120V	1,500-2,500	22	080083913459
TGS2S402MRRB	Twin Head Round, Motion	Bronze	180W INC	4000K	120V	1,500-2,500	22	080083913510
TGS2S402MRRW	Twin Head Round, Motion	White	180W INC	4000K	120V	1,500-2,500	22	080083913534

### TGS Series – Triple Head

#### SECURITY FLOODLIGHT

- Three different brightness levels using Lumen Select Technology
- Durable die-cast aluminum square head with UV resistant lens
- Easy install to wall or eave mounting, with integrated easy connector
- Switch activated, Dusk-to-Dawn, and motion activated models available
- Ideal for security lighting in residential and commercial applications



Catalog Number	Description	Finish	Replaces	CCT	Voltage	Selectable Lumens	Watts	UPC
TGS3S403FRRW	Triple Head Round	White	270W INC	4000K	120V	2,000-3,000	27	080083913619
TGS3S403DRRB	Triple Head Round, D2D	Bronze	270W INC	4000K	120V	2,000-3,000	27	080083913671
TGS3S403DRRW	Triple Head Round, D2D	White	270W INC	4000K	120V	2,000-3,000	27	080083913695

### TGS Series – Single Head High Output

#### SECURITY FLOODLIGHT

- Three different brightness levels using Lumen Select Technology
- Durable die-cast aluminum square head with UV resistant lens
- Easy install to wall or eave mounting, with integrated easy connector
- Switch activated, Dusk-to-Dawn, and motion activated models available
- Ideal for security lighting in residential and commercial applications



Catalog Number	Description	Finish	Replaces	CCT	Voltage	Selectable Lumens	Watts	UPC
TGS5S401DSCB	Single Head High Output Square, D2D	Bronze	175W HID	4000K	120-277V	2,700-5,800	50	080083256013
TGS5S401MSCW	Single Head High Output Square, Motion	White	175W HID	4000K	120-277V	2,700-5,800	50	080083260065

# HALO OUTDOOR FLOODLIGHTS

## ESF Series

### SECURITY FLOODLIGHT

- Sleek wrap-around lens design – enhanced aesthetics and low glare
- Two lumen packages available; 1400 and 2400 lumens in 2 color finishes
- Switch activated, Dusk-to-Dawn, and motion activated models available
- 50,000 hour lifespan, Wet Location rated and non-corrosive polycarbonate housing



Catalog Number	Description	Finish	Replaces	CCT	Voltage	Lumens	Watts	UPC
ESF1A4FB	Twin Head Floodlight	Bronze	90W INC	4000K	120V	1,400	15	080083146000
ESF1A4FW	Twin Head Floodlight	White	90W INC	4000K	120V	1,400	15	080083146024
ESF1A4DB	Twin Head Floodlight	Bronze	90W INC	4000K	120V	1,400	15	080083146048
ESF1A4MB	Twin Head Floodlight, Motion	Bronze	90W INC	4000K	120V	1,400	15	080083146086
ESF1A4MW	Twin Head Floodlight, Motion	White	90W INC	4000K	120V	1,400	15	080083146109
ESF2A4FB	Twin Head Floodlight	Bronze	180W INC	4000K	120V	2,300	24	080083146123
ESF2A4FW	Twin Head Floodlight	White	180W INC	4000K	120V	2,300	24	080083146147
ESF2A4DB	Twin Head Floodlight	Bronze	180W INC	4000K	120V	2,300	24	080083146161
ESF2A4DW	Twin Head Floodlight, D2D,	White	180W INC	4000K	120V	2,300	24	080083146185
ESF2A4MB	Twin Head Floodlight, Motion	Bronze	180W INC	4000K	120V	2,300	24	080083146208
ESF2A4MW	Twin Head Floodlight, Motion	White	180W INC	4000K	120V	2,300	24	080083146222

## FGS SECURITY FLOODLIGHT

- Flexibility with field-selectable 5-color CCT (3000K/3500K/4000K/5000K/6500K)
- 2,000 to 6,000 selectable lumens range with low, medium, and high outputs
- Dusk to Dawn Photocell and motion with standby options available
- Glare-free UV, & impact resistant PC prismatic lens
- Ideal for residential applications like backyards, barns, garages, etc



Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC
FGS30CLD2DB	Single Head High Output Square, D2D	Bronze	180W HID	3000K-6500K	120V	2,000-3,000	12-27	080083292936
FGS30CLD2DW	Single Head High Output Square, D2D	White	180W HID	3000K-6500K	120V	2,000-3,000	12-27	080083292943
FGS60CLMTNB	Single Head High Output Square, Motion	Bronze	270W HID	3000K-6500K	120-277V	2,000-6,000	18-45	080083292967
FGS60CLMTNW	Single Head High Output Square, Motion	White	270W HID	3000K-6500K	120-277V	2,000-6,000	18-45	080083292950

# HALO OUTDOOR FLOODLIGHTS

## SEC – Single Head

### SECURITY FLOODLIGHT

- Flexibility with field-selectable 5-color CCT (2700/3000K/4000K/5000K/6500K)
- Wide coverage with field-selectable lumens up to 3,500
- Choose from motion, dusk-to-dawn, or motion + dusk-to-dawn modes
- Adjustable heads for targeted coverage
- Ideal for residential applications like backyards, barns, garages, etc




Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC
SEC1HSHWMBLK	Single Head, Motion, D2D (up to 1,500 Lumens)	Black		2700K-5000K	120-277V	360-1,500	3-12	080083303731
SEC1HSHWMWH	Single Head, Motion, D2D (up to 1,500 Lumens)	White		2700K-5000K	120-277V	360-1,500	3-12	080083304325

## SEC – Twin Head

### SECURITY FLOODLIGHT

- Flexibility with field-selectable 5-color CCT (2700/3000K/4000K/5000K/6500K)
- Wide coverage with field-selectable lumens up to 3,500
- Choose from motion, dusk-to-dawn, or motion + dusk-to-dawn modes
- Adjustable heads for targeted coverage
- Ideal for residential applications like backyards, barns, garages, etc



Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC
SEC2HSHWMBLK	Twin Head, Motion, D2D (up to 2,500 Lumens)	Black		2700K-5000K	120-277V	560-2,500	5-20	080083304103
SEC2HSHWMWH	Twin Head, Motion, D2D (up to 2,500 Lumens)	White		2700K-5000K	120-277V	560-2,500	5-20	080083304349
SEC2HSPLUGMBLK	Twin Head, Motion, D2D (up to 2,500 Lumens), AC Plug	Black		2700K-5000K	120-277V	560-2,500	5-20	080083304141
SEC2HSPLUGMWH	Twin Head, Motion, D2D (up to 2,500 Lumens), AC Plug	White		2700K-5000K	120-277V	560-2,500	5-20	080083304387

## SEC – Triple Head

### SECURITY FLOODLIGHT

- Flexibility with field-selectable 5-color CCT (2700/3000K/4000K/5000K/6500K)
- Wide coverage with field-selectable lumens up to 3,500
- Choose from motion, dusk-to-dawn, or motion + dusk-to-dawn modes
- Adjustable heads for targeted coverage
- Ideal for residential applications like backyards, barns, garages, etc



Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC
SEC3HSHWMBLK	Triple Head, Motion, D2D (up to 3,500 Lumens)	Black		2700K-5000K	120-277V	1,480-3,500	7-28	080083304127
SEC3HSHWMWH	Triple Head, Motion, D2D (up to 3,500 Lumens)	White		2700K-5000K	120-277V	1,480-3,500	7-28	080083304363

## HALO OUTDOOR WALL MOUNTS

### BKHD

#### WALL/CEILING MOUNT

- Flexibility with field-selectable 5-color CCT (3000K/3500K/4000K/5000K/6500K)
- Wide coverage with field-selectable lumens up to 3,500
- Integrated Photocell for Dusk to Dawn operation with manual switch operation
- IP65 rated against dust and water; Glare-free UV, & impact resistant PC prismatic lens
- Durable die-cast aluminum housing suitable for wet locations



### Wall Cylinder

#### WALL MOUNT

- Flexibility with field-selectable 5-color CCT (3000K/3500K/4000K/5000K/6500K)
- Integrated Photocell for Dusk to Dawn operation with manual switch operation
- IP65 rated against dust and water
- Durable die-cast aluminum housing suitable for wet locations
- Ideal for commercial applications like warehouses, building entrances, etc



### Mini Wall Pack

#### WALL MOUNT

- Flexibility with field-selectable 3-color CCT (3000K/4000K/5000K)
- Two lumen packages available; 2000 and 4000 lumens
- Integrated Photocell for Dusk to Dawn operation with manual switch operation
- Durable die-cast aluminum housing suitable for wet locations
- Glare-free UV, & impact resistant PC prismatic lens



Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
MWP20FSUNVDBZ	Mini LED Wall Pack, D2D	Bronze	70W INC	3000K-5000K	120-277V	2,000	15	080083260805	Pending
MWP40FSUNVDBZ	Mini LED Wall Pack, D2D	Bronze	150W INC	3000K-5000K	120-277V	4,000	30	080083260782	Pending

## HALO OUTDOOR WALL MOUNTS

### FE Series

#### WALL MOUNT

- Replaces up to 60W/75W Incandescent or 13W/26W CFL fixtures
- Three lumen packages available; 800, 1000 and 1200 lumens in 2 color finishes
- Highly durable & corrosion resistant polycarbonate construction
- Built in, switch operated photocontrol for Dusk-to-Dawn operation & motion sensor
- Perfect security lighting for residential and light commercial applications



Catalog Number	Description	Finish	Replaces	CCT	Voltage	Lumens	Watts	UPC
FE08A40FDB	Jelly Jar, D2D	Bronze	60/75W	4000K	120V	800	8	080083265152
FE12S40FDB	Jelly Jar, D2D	Bronze	60/75W	4000K	120V	1,200	11	080083241989
FE12S40FDW	Jelly Jar, D2D	White	60/75W	4000K	120V	1,000	11	080083242009
FE10A35GLMB	Jelly Jar, Motion	Bronze	60/75W	3500K	120V	1,000	13	080083242023
FE10A35GLMW	Jelly Jar, Motion	White	60/75W	3500K	120V	1,000	13	080083242047

### Solar Motion Wedge

#### WALL MOUNT

- Motion sensor with dual light levels: full brightness when motion is detected, and half brightness when no motion is detected
- 4000K Cool White maintenance free LED's with 50,000 hours life
- 3 Adjustable Time Out settings – 30s, 60s, & 90s
- Durable polycarbonate housing with frosted lens for smooth, glare-free lighting



Catalog Number	Description	Finish	Replaces	CCT	Lumens	UPC
SWL0540W	Solar Wedge, motion	White	40W INC	4000K	500	080083242061
SWL0540B	Solar Wedge, motion	Bronze	40W INC	4000K	500	080083242108
SWL0840W	Solar Wedge, motion	White	70W INC	4000K	800	080083242085
SWL0840B	Solar Wedge, motion	Bronze	70W INC	4000K	800	080083242122

## HALO OUTDOOR AREA/SITE

### SBL Solar

#### AREA/SITE

- 5000K bright cool white light is optimal for security lighting
- 3 operating modes: Motion, Dusk to Dawn, and Motion + Dusk to Dawn, with remote control and On/Off functions included
- 3 Adjustable Time Out settings – 30s, 60s, & 90s
- UV & impact resistant prismatic drop lens



Catalog Number	Description	Finish	Replaces	CCT	Lumens	UPC
SBL10A50GY	Solar barn light, Motion, D2D	Gray	80W INC	5000K	1,000	080083260461
SBL15A50GY	Solar barn light, Motion, D2D	Gray	150W INC	5000K	1,500	080083260485
SBL30A50GY	Solar barn light, Motion, D2D	Gray	300W INC	5000K	3,000	080083260508

### VT Series

#### VAPOR PROOF

- LED or incandescent options available
- Durable die-cast aluminum housing and cage provides protection against vandalism
- Vapor tight IP65 rating protects against dust and moisture
- Versatile mounting options – Wall, Ceiling and Post
- Frosted glass lens provides smooth and even light distribution



Catalog Number	Description	Finish	Replaces	CCT	Voltage	Lumens	Watts	UPC
VT100G	100W Incandescent Vapor Tight	Raw	N/A	2700K	120V	1,600	100	080083757879
VT0840L	800 Lumen, 4000K, LED Vapor Tight	Raw	60W INC	4000K	120-277V	800	9	044427550113


# PRISM PORTAL

## Our Central Hub for Distributor Business.

Cooper Lighting Solutions PRISM Portal is a digital hub for authorized partners to self-serve reliable product data, place orders, and manage orders. It offers hassle-free access to price and availability, spec sheets, order tracking, invoices, and more!

- Advanced Product Search at Your Fingertips
- Real-Time Pricing & Availability
- Seamless Online Order Entry
- Comprehensive Order Status Tracking

[CLICK HERE](#) to register for PRISM Portal



Explore the PRISM Portal for Streamlined Business Solutions.