



	HU11	HU30
Lumens/Foot	380	300
CRI/CCT	90 CRI, 3-Color SeleCCTable (2700K, 3000K, 4000K)	90 CRI, 4-Color SeleCCTable (2700K, 3000K, 3500K, 4000K)
Thickness	.9"	.75"
Available Lengths	9", 18", 24", 36", 48"	9", 18", 24", 36", 48"
Dimming	ELV/TRIAC	ELV/TRIAC
Linkable	Yes	Yes
Direct Wire	Yes	Yes
Plug-In Cord Available	Yes	Yes
Finishes	Matte Black, White	Matte Black, White
Dry/Wet/Damp Rating	Damp	Damp
Energy Ratings	Energy Star	Energy Star
Additional Features	Color Selector Lock, Captive Mounting Hardware	USB Charge Option, Energy-Saving Motion Sensor
Plug-In Cord Available	Yes	Yes
Voltage	120V	120V - 277V