



# Metalux


## COMMERCIAL LED LIGHTING

Metalux Commercial features a wide selection of affordable yet aesthetically pleasing fixtures with an expanded offering of selectable color temperatures and lumen options.

## METALUX FLAT PANELS

### CGTS | CGT Series FLAT PANEL

- Affordable contractor LED panel with fixed or selectable configurations
- Fits in shallow plenums with room to spare; Thin 2 1/8 - inch height
- Field Selectable CCT and Lumens
- Ideal for office spaces, education, healthcare and retail merchandising
- Optional: Wireless integrated sensors provide standalone operation that meets code compliance with simple set up via the Wavelinx mobile app
- Optional: 8W emergency battery packs installed



#### MarketPro Essentials Selectable CCT & Lumens

| Catalog Number        | Description          | Replaces         | CCT         | Voltage  | Lumens      | Watts    | UPC          | DLC Product ID |
|-----------------------|----------------------|------------------|-------------|----------|-------------|----------|--------------|----------------|
| <b>ES</b> 14CGTS-L3C3 | 1'x4' Recessed Panel | 2-T8             | 3500K-5000K | 120-277V | 2,600-4,800 | 20/29/34 | 080083282517 | S-3EJHF2       |
| <b>ES</b> 22CGTS-L3C3 | 2'x2' Recessed Panel | 3-T8 17W, 2-U6T8 | 3500K-5000K | 120-277V | 2,800-4,700 | 19/28/32 | 080083194728 | PL74TQBZR6SL   |
| <b>ES</b> 24CGTS-L3C3 | 2'x4' Recessed Panel | 4-T8 32W         | 3500K-5000K | 120-277V | 4,200-7,200 | 29/42/51 | 080083194704 | PL0ULJMKXBCH   |

#### MarketPro Essentials Dedicated CCT & Lumens

| Catalog Number       | Description          | Replaces   | CCT   | Voltage  | Lumens | Watts | UPC          | DLC Product ID |
|----------------------|----------------------|------------|-------|----------|--------|-------|--------------|----------------|
| <b>ES</b> 22CGT3540C | 2'x2' Recessed Panel | 3-T8       | 4000K | 120-277V | 3,582  | 32    | 080083880027 | POYGNM7S       |
| <b>ES</b> 24CGT4540C | 2'x4' Recessed Panel | 2-T8, 3-T8 | 4000K | 120-277V | 4,432  | 38    | 080083880102 | PLTEVMIJ       |

#### CGTS with Wavelinx LITE

| Catalog Number  | Description                             | Replaces         | CCT         | Voltage  | Selectable Lumens | Watts    | UPC          | DLC Product ID  |
|-----------------|---|------------------|-------------|----------|-------------------|----------|--------------|-----------------|
| 14CGTS-L3C3-WLS | 1'x4' Recessed Panel with WaveLinX LITE | 2-T8             | 3500K-5000K | 120-277V | 2,600-4,800       | 20/29/34 | 080083306015 | S-RFBM0G        |
| 22CGTS-L3C3-WLS | 2'x2' Recessed Panel with WaveLinX LITE | 3-T8 17W, 2-U6T8 | 3500K-5000K | 120-277V | 2,800-4,700       | 19/28/32 | 080083306022 | S-KTBZC8        |
| 24CGTS-L3C3-WLS | 2'x4' Recessed Panel with WaveLinX LITE | 4-T8 32W         | 3500K-5000K | 120-277V | 4,200-7,200       | 29/42/51 | 080083306039 | <b>S-6DLPMV</b> |

Note: DLC Premium items are noted in bold.

#### CGTS with Emergency Battery Packs

| Catalog Number   | Description                        | Replaces         | CCT         | Voltage  | Selectable Lumens | Watts    | UPC          | DLC Product ID |
|------------------|------------------------------------|------------------|-------------|----------|-------------------|----------|--------------|----------------|
| 14CGTS-L3C3-EL8W | 1X4 CGTS 8W w/Emer. Battery Backup | 2-T8             | 3500K-5000K | 120-277V | 2,600-4,700       | 20/29/34 | 080083306046 | S-RFBM0G       |
| 22CGTS-L3C3-EL8W | 2X2 CGTS 8W w/Emer. Battery Backup | 3-T8 17W, 2-U6T8 | 3500K-5000K | 120-277V | 2,800-4,600       | 19/28/32 | 080083306053 | S-KTBZC8       |
| 24CGTS-L3C3-EL8W | 2X4 CGTS 8W w/Emer. Battery Backup | 4-T8 32W         | 3500K-5000K | 120-277V | 4,200-7,200       | 29/42/51 | 080083306060 | S-6DLPMV       |

### FPS Series FLAT PANEL

- Ultra-thin LED flat panel; Less than 2-inches height for shallow plenums
- 3 Color Field-Selectable in 30/35/4000K
- Selectable switch to set color temperature, lumens and watts desired for task
- Refined visual optics, superior acrylic light guide; uniform corner to corner illumination
- Ideal for office spaces, schools, healthcare facilities and retail merchandising areas



| Catalog Number | Description          | Replaces   | Selectable CCT | Voltage  | Selectable Lumens | Watts    | UPC          | DLC Product ID |
|----------------|----------------------|------------|----------------|----------|-------------------|----------|--------------|----------------|
| 14FPSL1SCT3    | 1'x4' Recessed Panel | 2-T8       | 3000K-4000K    | 120-277V | 2,000-4,100       | 18/27/36 | 080083889440 | PYJV3ZJZ       |
| 22FPSL2SCT3    | 2'x2' Recessed Panel | 3-T8       | 3000K-4000K    | 120-277V | 1,700-3,500       | 15/22/31 | 080083889402 | PB32RP9H       |
| 24FPSL2SCT3    | 2'x4' Recessed Panel | 2-T8, 3-T8 | 3000K-4000K    | 120-277V | 3,100-6,300       | 27/40/56 | 080083889365 | PZFCMXS        |

# METALUX FLAT PANELS

## Multi-Mount Selectable FLAT PANEL


- Visually comforting panel mounts directly to the ceiling or wall reducing labor and material cost by removing the need for a surface mount kit
- Versatile mounting allows for surface, wall, recessed, or suspended with kit
- Selectable Color Temperatures in 90 CRI Standard:  
2x2/2x4/1x4: 35/40/5000K | 4' x 6": 27/30/35/40/5000K
- Selectable Lumens: Low, Medium, High settings
- Ideal choice for commercial office, school, and healthcare spaces



| Catalog Number | Description               | Replaces | Selectable CCT | Voltage  | Selectable Lumens | Watts    | UPC          | DLC Product ID |
|----------------|---------------------------|----------|----------------|----------|-------------------|----------|--------------|----------------|
| 4MMS6-L3C5-UNV | 4'x6", Direct Mount Panel | 2-T8 32W | 2700K-5000K    | 120-277V | 1,680-3,000       | 19/25/33 | 080083292028 | S-KJX1CZ       |
| 22MMS-L3C3-UNV | 2'x2", Direct Mount Panel | 3-T8 32W | 3500K-5000K    | 120-277V | 2,400-4,800       | 21/28/42 | 080083292042 | S-KJX1CZ       |
| 24MMS-L3C3-UNV | 2'x4", Direct Mount Panel | 4-T8 32W | 3500K-5000K    | 120-277V | 3,500-6,200       | 28/36/48 | 080083292059 | S-V9CG2Y       |
| 14MMS-L3C3-UNV | 1'x4", Direct Mount Panel | 2-T8 32W | 3500K-5000K    | 120-277V | 2,620-5,286       | 18/25/38 | 080083292035 | S-28RRZT       |

## Y-hanger Suspension Cable Kit FLAT PANEL

Y-hanger suspension cable kit with carabiner, SO cord, connectors and round 4" J-box cover plate



| Catalog Number | Description                   | UPC          |
|----------------|-------------------------------|--------------|
| FPSUS24        | Y-hanger suspension cable kit | 080083258895 |

## CGRK Retrofit Kit FLAT PANEL

- Luminaire panels and mounting rails shipped separately for quick installation
- 3 Color Field-Selectable in 35/40/5000K with three lumen options for various retrofit applications
- Micro-optics for uniform illumination, extruded aluminum frame for performance and aesthetics
- DLC Premium options for maximum energy savings and rebates, including WaveLinx Lite for enhanced savings



| Catalog Number      | Description                               | Replaces         | Selectable CCT | Voltage  | Selectable Lumens | Watts    | UPC          | DLC Product ID |
|---------------------|---|------------------|----------------|----------|-------------------|----------|--------------|----------------|
| 14CGRK-L3C3-UNV-MP4 | 1'x4' Backlit Panel Retrofit Kit (4-Pack) | 2-T8             | 3500K-5000K    | 120-277V | 2,000-4,100       | 14/22/29 | 080083312139 | S-XP62Y7       |
| 22CGRK-L3C3-UNV-MP4 | 2'x2' Backlit Panel Retrofit Kit (4-Pack) | 3-T8 17W, 2-U6T8 | 3500K-5000K    | 120-277V | 2,000-4,100       | 15/22/29 | 080083312146 | S-W4YPLT       |
| 24CGRK-L3C3-UNV-MP4 | 2'x4' Backlit Panel Retrofit Kit (4-Pack) | 4-T8 32W         | 3500K-5000K    | 120-277V | 2,800-5,000       | 20/27/35 | 080083312153 | S-871T6V       |

# METALUX TROFFERS

## Surround Frame Selectable ILLUMINATED FRAME

- Architectural 1.5" illuminated modern frame enhances the look of any space
- Versatile mounting in existing T-grid using ceiling tile as the reflector, suspension also available with kit
- 4 Color Field-Selectable in 30/35/40/5000K
- Selectable Lumens - Low, Medium, High settings
- Ideal choice for commercial office, school, and healthcare spaces



| Catalog Number | Description           | Replaces | Selectable CCT | Voltage  | Selectable Lumens | Watts    | UPC          | DLC Product ID  |
|----------------|-----------------------|----------|----------------|----------|-------------------|----------|--------------|-----------------|
| 22SFS-L3C4-UNV | 2'x2', Surround Frame | 3-T8 32W | 3000K-5000K    | 120-277V | 1,900-4,600       | 15/25/36 | 080083293124 | <b>S-6WZ2T</b>  |
| 24SFS-L3C4-UNV | 2'x4', Surround Frame | 4-T8 32W | 3000K-5000K    | 120-277V | 3,000-6,000       | 23/35/47 | 080083293148 | <b>S-TPM2HQ</b> |

Note: DLC Premium items are noted in bold.

## Cruze Selectable CZS | Cruze ST Recessed TROFFER

- Architectural center basket lens troffer with aesthetic appeal
- Latch-less design provides clean architectural look; ribbed, frosted acrylic lens
- 3 Color Field-Selectable in 30/35/4000K and dedicated in 3500K, 4000K
- Ideal choice for commercial, institutional and healthcare facilities



| Catalog Number | Description    | Replaces   | Selectable CCT | Voltage  | Selectable Lumens | Watts | UPC          | DLC Product ID |
|----------------|----------------|------------|----------------|----------|-------------------|-------|--------------|----------------|
| 14CZSCT3-UNV   | 1'x4', Troffer | 2-T8       | 3000K-4000K    | 120-277V | 3,000-4,400       | 20-30 | 080083268443 | S-5LPE0V       |
| 22CZSCT3-UNV   | 2'x2', Troffer | 2-T5, 2-T8 | 3000K-4000K    | 120-277V | 2,700-4,075       | 21-31 | 080083268467 | S-QDP2J8       |
| 24CZSCT3-UNV   | 2'x4', Troffer | 2-T8, 3-T8 | 3000K-4000K    | 120-277V | 3,500-6,500       | 24-47 | 080083268481 | S-MW0TCN       |

## Achieva™ Recessed Selectable TROFFER

- Ultra slim 1.5" center basket design fits into the shallowest of plenums
- 3 Color Field-Selectable in 30/35/4000K in 80+ CRI
- 3 Selectable lumens in standard or HO options up to 8,150
- Ideal choice for commercial, institutional and healthcare facilities



### MarketPro Essentials

| Catalog Number               | Description             | Replaces   | Selectable CCT | Voltage  | Selectable Lumens | Watts    | UPC          | DLC Product ID  |
|------------------------------|-------------------------|------------|----------------|----------|-------------------|----------|--------------|-----------------|
| <b>ES</b> 14ARS-L3C3-UNV     | 1'x4', Troffer          | 2-T8       | 3500K-5000K    | 120-277V | 2,800-4,600       | 20/26/33 | 080083282241 | <b>S-N7LRJL</b> |
| <b>ES</b> 22ARS-L3C3-UNV     | 2'x2', Troffer          | 2-T8, 2-T5 | 3500K-5000K    | 120-277V | 2,750-4,300       | 20/26/33 | 080083282128 | <b>S-N0X10I</b> |
| <b>ES</b> 24ARS-L3C3-UNV     | 2'x4', Troffer          | 2-T8, 3-T8 | 3500K-5000K    | 120-277V | 3,400-6,250       | 24/33/46 | 080083282005 | <b>S-EA9S16</b> |
| <b>ES</b> 24ARS-L3C3-UNV-MP2 | 2'x4', Troffer (2-Pack) | 2-T8, 3-T8 | 3500K-5000K    | 120-277V | 3,400-6,250       | 24/33/46 | 080083282364 | <b>S-EA9S16</b> |

Note: DLC Premium items are noted in bold.