

HALO SURFACE MOUNT DOWNLIGHTING

Suitable for a variety of applications!

- Below the ceiling installation with no plates or clips required
- Designed for square, octagon, pancake or round junction boxes
- Ideal for closets, storage areas, attics and basements

Quick and Easy Installation



HALO SURFACE MOUNT DOWNLIGHT Product Selection Guide

		Good		Better		Best	
		MarketPro Essentials	MarketPro Essentials	FMNL	SMD	SMX	
		HLCE MS	HLC				
FEATURES/PERFORMANCE	Size / Shape	4", 6" Round	4", 6" Round	8", 11", 15" Round	4", 6" Round, Square	4", 6", 8", 14", 18" Round, Square	
	Trim & Lens	Curved Trim & Lens		Full-lensed Flushmount with Night Light	Square-Edge Trim, Flange, & Flat Lens	Thin Frame and Edgeless Luminous Lens	
	Max Lumens (By size @ 3000K)	1035 or 1260	670, 970	980, 1185, 1540	740, 790	Lumen Select 4" - 650/800/1,000 6" - 750/900/1,200 8" - 900/1,200/1,500 14" - 1,200/1,600/2,000 18" - 1,500/2,000/2,500	
	Color Temperatures (CCT)	5 CCT 27/30/35/40/5000K	5 CCT 27/30/35/40/5000K	5 CCT 27/30/35/40/5000K	5 CCT 27/30/35/40/5000K	5 CCT w/ D2W D2W/27/30/35/40/5000K	
CONTROL	Dimming Phase Cut (LE/TE) / 0-10V	5% Phase Cut	10% Phase Cut	10% Phase Cut	5% Phase Cut, 0-10V	5% Phase Cut, 0-10V	
	Estimated Life Hours	50,000	50,000	50,000	50,000	50,000	
	Input Voltage	120V	120V	120V	120V	120V, 120-277V	
HARDWARE	Decorative Overlays ²	✓		✓	✓	✓	

¹ Motion sensing downlights are not dimmable. ² Matte Black, Tuscan Bronze, Satin Nickel, and Paintable Matte White.

HALO SURFACE MOUNT DOWNLIGHTING

HLCE MS Motion Activated Disk Light SURFACE MOUNT DOWNLIGHTS - 4" & 6"

- 10 feet of motion sensing coverage automatically turns OFF after 40 seconds of no motion
- Installs in most 3-1/2" or 4" ceiling junction and pancake boxes (or retrofits into housings)
- 5 Color Field-Selectable in 27/30/35/40/5000K
- Includes LED Downlight, jbox mounting and wiring hardware, and housing retrofit kit in non-California versions
- 10% Dimming (Phase Cut LE/TE), 35,000 hrs, 90+ CRI
- NEW! Decorative overlays are available through MarketPro online



MarketPro Essentials

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
ES HLCEMS410FS1E	4" Disk Light w/ Motion Sensor (Wet-listed)	70W	2700K-5000K	120V	1035	12.2	080083303069	3994257
ES HLCEMS410FS1E-6BP	4" Disk Light w/ Motion Sensor (Wet-listed) (6-Pack)	70W	2700K-5000K	120V	1035	12.2	080083303243	3994256
ES HLCEMS410FS1E-CA	4" Disk Light w/ Motion Sensor (Wet-listed), CA T20	70W	2700K-5000K	120V	1035	12.2	080083303205	3994258
ES HLCEMS612FS1E	6" Disk Light w/ Motion Sensor (Wet-listed)	70W	2700K-5000K	120V	1260	14.8	080083303083	Pending
ES HLCEMS612FS1E-6BP	6" Disk Light w/ Motion Sensor (Wet-listed) (6-Pack)	70W	2700K-5000K	120V	1260	14.8	080083303267	Pending
ES HLCEMS612FS1E-CA	6" Disk Light w/ Motion Sensor (Wet-listed), CA T20	70W	2700K-5000K	120V	1260	14.8	080083303229	Pending

HLC Tapered Disk Light SURFACE MOUNT DOWNLIGHTS - 4" & 6"

- Ultra-fast below-the-ceiling installation; no clips or plates needed
- Installs in most 3-1/2" or 4" ceiling junction and pancake boxes (or retrofits into housings)
- 5 Color Field-Selectable in 27/30/35/40/5000K
- Twist-release lens with keyhole slots for quick install and easy CCT selection
- Available in economical 24-packs
- 10% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI



MarketPro Essentials

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
ES HLC4FS1E-24P	4" Disk Light, Bulk (24-Pack)	70W	2700K-5000K	120V	690	10	080083448104	Pending
ES HLC6FS1E-24P	6" Disk Light, Bulk (24-Pack)	70W	2700K-5000K	120V	970	15	080083448128	Pending

HALO SURFACE MOUNT DOWNLIGHTING

FMNL Flush Mount with Night Light FLUSH MOUNT DOWNLIGHTS - 8", 11", & 15"

- A bright fully luminous lens face and sleek edgeless design blends effortlessly into any ceiling
- Ceiling or wall mounting in compatible junction boxes or recessed housings
- 5-Color Field-SeleCCTable™ (27/30/35/40/5000K); Night Light: 2000K candlelight glow
- Includes 2 trim rings inside the box (paintable white and Matte Black)
- 5% Dimming (Phase Cut or 0-10V), 50,000 hrs, 90+ CRI



Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
FMNL809FS5	8-inch Flush Mount LED Downlight with Night Light*	White	70W	2700K-5000K (Downlight) 2000K (Night Light)	120V	980	10	080083312214	Pending
FMNL1112FS5	11-inch Flush Mount LED Downlight with Night Light*	White	75W	2700K-5000K (Downlight) 2000K (Night Light)	120V	1185	13	080083312238	Pending
FMNL1515FS5	15-inch Flush Mount LED Downlight with Night Light*	White	100W	2700K-5000K (Downlight) 2000K (Night Light)	120V	1540	17	080083312252	Pending

*Paintable Matte White + Matte Black trim included

SMD Square Edge SURFACE MOUNT DOWNLIGHTS - 4" & 6"

- Round or square surface mount downlight with squared edge design
- Ceiling or wall mounting in compatible junction boxes or retrofit into recessed housings
- 5 Color Field-Selectable in 27/30/35/40/5000K
- Includes LED Downlight, jbox mounting and wiring hardware, and housing retrofit kit
- 5% Dimming (Phase Cut), 50,000 hrs, 90+ CRI



Catalog Number	Description	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
SMD4R07FS5	4" Surface Mount, Round	65W	2700K-5000K	120V	737	8	080083305667	3892052
SMD4S07FS5	4" Surface Mount, Square	65W	2700K-5000K	120V	741	8	080083305681	3892050
SMD6R07FS5	6" Surface Mount, Round	75W	2700K-5000K	120V	800	8	080083305742	3892058
SMD6S07FS5	6" Surface Mount, Square	75W	2700K-5000K	120V	710	8	080083305766	3892054
SMD4R07FS5-6PK	4" Surface Mount, Round (6-Pack)	65W	2700K-5000K	120V	737	8	080083305704	3892052
SMD4S07FS5-6PK	4" Surface Mount, Square (6-Pack)	65W	2700K-5000K	120V	741	8	080083305728	3892050
SMD6R07FS5-6PK	6" Surface Mount, Round (6-Pack)	75W	2700K-5000K	120V	800	8	080083305780	3892058
SMD6S07FS5-6PK	6" Surface Mount, Square (6-Pack)	75W	2700K-5000K	120V	710	8	080083305803	3892054

HALO SURFACE MOUNT DOWNLIGHTING

SMX Edgeless SURFACE MOUNT DOWNLIGHTS - 4", 6", 8" 14" & 18"

- A bright fully luminous lens face and sleek edgeless design blends effortlessly into any ceiling
- Ceiling or wall mounting in compatible junction boxes or recessed housings
- 6-Position Switch: 5 Color Field-Selectable (27/30/35/40/5000K) + Dim-to-Warm (3000K dims to 1800K)
- Includes j-box mounting and wiring hardware
- 5% Dimming (Phase Cut or 0-10V), 50,000 hrs, 90+ CRI



Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	Energy Star ID
SMX4RLSFS2W	4" Surface Mount, Round	65-90W	2700K-5000K + D2W	120V	650/800/1000	7/8/11	080083292202	3701850
SMX4SLSFS2W	4" Surface Mount, Square	65-90W	2700K-5000K + D2W	120V	650/800/1000	7/8/11	080083292189	3998744
SMX4RLSFS010	4" Surface Mount, Round (0-10V)	65-90W	2700K-5000K	120-277V	650/800/1000	7/8/11	080083292387	3998256
SMX4SLSFS010	4" Surface Mount, Square (0-10V)	65-90W	2700K-5000K	120-277V	650/800/1000	7/8/11	800083292462	3998746
SMX6RLSFS2W	6" Surface Mount, Round	75-100W	2700K-5000K + D2W	120V	750/900/1200	7/9/13	080083292240	3701854
SMX6SLSFS2W	6" Surface Mount, Square	75-100W	2700K-5000K + D2W	120V	750/900/1200	7/9/13	080083292325	3998745
SMX6RLSFS010	6" Surface Mount, Round (0-10V)	75-100W	2700K-5000K	120-277V	750/900/1200	7/9/13	080083292400	3998257
SMX6SLSFS010	6" Surface Mount, Square (0-10V)	75-100W	2700K-5000K	120-277V	750/900/1200	7/9/13	080083292486	3998747
SMX8RLSFS2W	8" Surface Mount, Round	90-120W	2700K-5000K + D2W	120V	900/1200/1500	10/12/16	080083294039	3701851
SMX8SLSFS2W	8" Surface Mount, Square	90-120W	2700K-5000K + D2W	120V	900/1200/1500	10/12/16	080083294053	N/A
SMX8RLSFS010	8" Surface Mount, Round (0-10V)	90-120W	2700K-5000K	120-277V	900/1200/1500	10/12/16	080083294077	3998259
SMX8SLSFS010	8" Surface Mount, Square (0-10V)	90-120W	2700K-5000K	120-277V	900/1200/1500	10/12/16	080083294091	N/A
SMX14RLSFS2W	14" Surface Mount, Round	90-150W	2700K-5000K + D2W	120V	1200/1600/2000	16/21/26	080083292141	N/A
SMX14SLSFS2W	14" Surface Mount, Square	90-150W	2700K-5000K + D2W	120V	1200/1600/2000	16/21/26	080083292349	N/A
SMX14RLSFS010	14" Surface Mount, Round (0-10V)	90-150W	2700K-5000K	120-277V	1200/1600/2000	16/21/26	080083292424	N/A
SMX14SLSFS010	14" Surface Mount, Square (0-10V)	90-150W	2700K-5000K	120-277V	1200/1600/2000	16/21/26	080083292509	N/A
SMX18RLSFS2W	18" Surface Mount, Round	90-150W	2700K-5000K + D2W	120V	1500/2000/2500	17/24/30	080083292165	N/A
SMX18SLSFS2W	18" Surface Mount, Square	90-150W	2700K-5000K + D2W	120V	1500/2000/2500	17/24/30	080083292363	N/A
SMX18RLSFS010	18" Surface Mount, Round (0-10V)	90-150W	2700K-5000K	120-277V	1500/2000/2500	17/24/30	080083292448	N/A
SMX18SLSFS010	18" Surface Mount, Square (0-10V)	90-150W	2700K-5000K	120-277V	1500/2000/2500	17/24/30	080083292523	N/A

HFL

FLEXIBLE LINEAR TAPE - 24' & 96'

- 24' and 96' spools at 200/400 lm/ft; field cuttable every 2.5"
- High-density LED Spacing for smooth linear illumination (60 LEDs/ft)
- Eliminate dark spots with LED-integrated tape-to-tape connectors; Tape-to-Wire connects
- 5-Color Field-Selectable in 27/30/35/40/5000K
- 5% Dimming (Phase Cut LE/TE); 90+ CRI



HFL Tape (Essential Components)*

Catalog Number	Description	Selectable CCT	Voltage	Lumens	LEDs/ft	Watts/ft	UPC
HFL2001S	24' selectable CCT tape	2700K-5000K	120-277V	200	60	2.13 W/ft	080083445233
HFL4001S	24' selectable CCT tape	2700K-5000K	120-277V	400	60	2.13 W/ft	080083445257
HFL2002S	96' selectable CCT tape	2700K-5000K	120-277V	200	60	4.26 W/ft	080083445271
HFL4002S	96' selectable CCT tape	2700K-5000K	120-277V	400	60	4.26 W/ft	080083445295

*Each roll features an easy-to-apply 3M adhesive backing for quick installation.

Constant Voltage Drivers (Essential Components)

- Phase-cut (leading edge/trailing edge) or 0–10V dimming drivers, both offering smooth dimming down to 5%
- Available in two wattage options



Catalog Number	Description	Output Voltage/Max. Load	Voltage	Max. Run	Max. Run	UPC
HFLP60A	60W Phase Cut (LE/TE) Dimming Driver	24V / 60W	120V	28 ft	14 ft	080083445318
HFLP100A	100W Phase Cut (LE/TE) Dimming Driver	24V / 100W	120V	47 ft	23.5 ft	080083445332
HFLP50B	50W 0–10V Dimming Driver	24V / 50W	120-277V	23.5 ft	11.75 ft	080083445356
HFLP100B	100W 0–10V Dimming Driver	24V / 100W	120-277V	47 ft	23.5 ft	080083445370

HFL Connectors (Essential Components)

- Tape-to-tape and Tape-to-wire connectors available in multiple formats to support different installation requirements
- Tape-to-tape connectors feature integrated LEDs that eliminate dark gaps and maintain continuous illumination



Catalog Number	Description	Usability	UPC
HFL01	60" Tape-Wire+ Connector (1-pack)	Provides a 60" wire extension to connect tape light segments with spacing.	080083445554
HFL02	6" Tape-Wire+ Connector (1-pack)	Provides a 6" wire extension to connect tape light segments with spacing.	080083445578
HFL03	2" Corner+ Connector (5-pack)	Creates a clean 90° turn between tape light segments for inside or outside corners.	080083445592
HFL04	Tape-Tape Connector (5-pack)	Joins two tape light segments for straight, continuous runs.	080083445615
HFL05	Halo HFL Tape-Wire Connector (5-pack)	Connects tape light to 3-conductor low-voltage wire for gap bridging or routing around obstacles. No soldering required.	080083445639
HFL06	Halo HFL 3-Way+ Connector (5-pack)	Creates a T-junction between three tape light segments for illuminated three-direction layouts.	080083445653
HFL07	Halo HFL 4-Way+ Connector (5-pack)	Creates a four-way illuminated junction by connecting four tape light segments.	080083445677

HFL Accessories

HFL Channels

- Aluminum channels with integrated diffuse lenses creates a smooth, uniform line of light
- Enhances durability and protects LED tape
- Ideal for visible or design-forward applications
- Compatible with HFL Mounting Kits
- Mounting Kits Include 2 endcaps, 4 mounting clips, 4 screws and 4 drywall anchors



HFL Shallow Surface Mount Channels

Catalog Number	Description	UPC
HFLESS4	4' Shallow Surface Mount Lensed Channel (Shallow Surface Mount Channel Mounting Kit required)	080083445394
HFLESS8	8' Shallow Surface Mount Lensed Channel (Shallow Surface Mount Channel Mounting Kit required)	080083445417
HFLKSS*	Shallow Surface Mount Channel Mounting Kit	080083445691

*NOTE – Accessory Mounting Kit(s) required for installation – a minimum of 1 kit per 4 feet of channel (sold separately).

HFL 45° Angled Surface Mount Channels

Catalog Number	Description	UPC
HFLESA4	4' 45° Angled Surface Mount Lensed Channel (45° Angled Surface Mount Channel Mounting Kit required)	080083445479
HFLESA8	8' 45° Angled Surface Mount Lensed Channel (45° Angled Surface Mount Channel Mounting Kit required)	080083445493
HFLKA*	45° Angled Surface Mount Channel Mounting Kit	080083445738

*NOTE – Accessory Mounting Kit(s) required for installation – a minimum of 1 kit per 4 feet of channel (sold separately).

HFL Deep Surface Mount Channels

Catalog Number	Description	UPC
HFLESD4	4' Deep Surface Mount Lensed Channel (Deep Surface Mount Channel Mounting Kit required)	080083445431
HFLESD8	8' Deep Surface Mount Lensed Channel (Deep Surface Mount Channel Mounting Kit required)	080083445462
HFLKSD*	Deep Surface Mount Channel Mounting Kit	080083445714

*NOTE – Accessory Mounting Kit(s) required for installation – a minimum of 1 kit per 4 feet of channel (sold separately).

HFL Deep Recessed Lensed Channels

Catalog Number	Description	UPC
HFLERD4	4' Deep Recessed Lensed Channel (Deep Recessed Lensed Channel Mounting Kit required)	080083445516
HFLERD8	8' Deep Recessed Lensed Channel (Deep Recessed Lensed Channel Mounting Kit required)	080083445530
HFLKRD*	Deep Recessed Lensed Channel Mounting Kit	080083445752

*NOTE – Accessory Mounting Kit(s) required for installation – a minimum of 1 kit per 4 feet of channel (sold separately).