



Save Money



Save Time



Peace of Mind

The SLSTP is a commercial grade LED strip light with decorative end caps and toolless lens removal. It is available in 2', 4' or 8' lengths with 3500K, 4000K or 5000K color temperature options and delivers up to 10,500 lumens per 8 feet. SLSTP is ideal for warehouse, retail, office or retrofit applications.



SLSTP

3500K, 4000K and 5000K LED Strip

Metalux



Save Money



Save Time



Peace of Mind

	Features	Benefits	Result
Construction	2', 4' and 8' lengths with single continuous lens (All lengths)	Design flexibility for new construction or retrofit applications	
	Decorative snap-on injection molded end caps	Provides clean lines and aesthetically pleasing appearance	
	Suitable for either single or continuous row application	Add-on length as needed regardless of application or layout	
	Impact resistant polycarbonate lens	Reduced maintenance	
	Surface, suspended or wall mounted capable	Ideal for all indoor LED strip applications	
Performance	Up to 125 lm/W, 10,500 lumens and 3500K, 4000 or 5000K CCT	Multi-application flexibility	
	Frosted lens with linear prisms	Uniform light distribution and wide area coverage	
	UNV (0-10V) or 120V (Phase-cut) dimming	Save over 40% energy over existing LFL strips	
	DLC®, 5-year warranty, 50K life hours at L70	Eligible for energy rebates; certified and guaranteed performance	

CCT	Catalog Number	UPC	Delivered Lumens	Watts	Efficacy (lm/W)	Unit Weight lbs.	Pallet Qty.	Pallet Gross Weight lbs
3500K	4SLSTP4035DD-UNV	080083807765	4695	41	115	4.8	80	501
	4SLSTP5535DD-UNV	080083807802	5620	49	114	4.8	132	501
	8SLSTP11035DD-UNV	080083807703	10464	83	125	9.5	80	908
	8SLSTP8035DD-UNV	080083804368	8064	71	114	9.5	80	908
4000K	2SLSTP2040DD-UNV	080083807826	2510	23	111	2.6	168	549
	4SLSTP2040DD-UNV	080083705818	2410	21	113	4.8	80	501
	4SLSTP4040DD-UNV	080083705825	4760	44	109	4.8	72	501
	4SLSTP5540DD-UNV	080083807789	5845	49	119	4.8	120	501
	8SLSTP11040DD-UNV	080083807680	10322	49	209	9.5	70	908
	8SLSTP8040DD-UNV	080083814787	8176	71	115	10.1	70	908
	4SLSTP4040CS	080083807741	4835	41	118	4.8	132	501
	8SLSTP8040CS	080083807727	8304	72	115	9.5	80	908
5000K	2SLSTP2050DD-UNV	080083158928	2573	22	117	2.6	168	549
	4SLSTP2050DD-UNV	080083158935	2451	21	119	4.8	80	501
	4SLSTP4050D-UNV	080083158942	4846	43	113	4.8	72	501
	4SLSTP5550D-UNV	080083158959	5696	49	117	4.8	120	501
	8SLSTP11050D-UNV	080083158973	10197	83	123	9.5	70	908
	8SLSTP8050D-UNV	080083158966	8324	70	119	10.1	70	908



Cooper Lighting Solutions
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.cooperlighting.com

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2022 Cooper Lighting Solutions
All Rights Reserved
Printed in USA
Publication No. SA502045EN
July 2022