

Project		Catalog #		Type	
Prepared by		Notes		Date	



HALO

CEZ6125 CEZ6126

6" Canless EZ-Trim
Lamp-based direct mount
15W Maximum

Typical Applications

• Residential • Light Commercial

Product Certification



Product Features




Interactive Menu

- Order Information page 2
- Product Specifications page 3
- Product Warranty

Top Product Features

- Baffle trim
- Direct mount – does not require recessed housing or junction box
- Option for GU24 or E26 lamp base, use with compatible LED lamps (sold by others)
- Air-tite, for use in insulated and non-insulated ceilings
- Shallow version suitable for 2x6 residential framing or shallow plenum commercial construction
- Suitable for wet locations when used with lens overlays

Dimensional and Mounting Details



additional product diagrams

Order Information

SAMPLE ORDER NUMBER: CEZ6125E26WBICAT

A complete luminaire consists of a Canless EZ-Trim lamp-based direct mount and a compatible lamp (sold by others).

Model	Lamp Base	Trim Type	Certifications
Model	Lamp Base	Trim Type	Certifications
CEZ6125 = 6-inch Canless EZ-Trim CEZ6126 = 6-inch Shallow Canless EZ-Trim	E26 = E26 base GU24 = GU24 base	WB = White flange, white baffle trim	ICAT = IC rated, air-tite

Accessories (sold separate)

Accessories (sold separate)	
MF6RC = 6" round mounting frame with drywall collar HL6RSMF = 6" new construction round/square mounting frame	CEZ6125LTRMWHWB = 6" lens overlay, white trim, white baffle CEZ6125LTRMWHBB = 6" lens overlay, white trim, black baffle CEZ6125LTRMBKBB = 6" lens overlay, black trim, black baffle CEZ6125LTRMSN = 6" lens overlay, satin nickel CEZ6125LTRMTBZ = 6" lens overlay, tuscan bronze



MF6RC



HL6RSMF



CEZ6125LTRMWHWB Showerlight



CEZ6125LTRMWHBB Showerlight



CEZ6125LTRMBKBB Showerlight



CEZ6125LTRMSN Showerlight



CEZ6125LTRMTBZ Showerlight

Compatible LED Lamps

- A19 LED, E26 base
 - PAR38 LED, E26 base (CEZ6125 only)
 - BR40 LED, E26 base (CEZ6125 only)
 - BR30 LED, E26 base
 - PAR30L LED, E26 base
 - PAR30S LED, E26 base
 - R30 LED, E26 base
- A19 LED, GU24 base
 - PAR38 LED, GU24 base (CEZ6125 only)
 - BR40 LED, GU24 base (CEZ6125 only)
 - BR30 LED, GU24 base
 - PAR30L LED, GU24 base
 - PAR30S LED, GU24 base
 - R30 LED, GU24 base

Product Specifications

Trim

- Durable metal baffle trim

Lamp Compatibility

- For use with maximum 15W LED lamps
- Option for GU24 or E26 lamp base

Installation

- Can be installed in 1/2" to 1-1/4" thick ceilings
- Shallow version suitable for 2x6 residential framing or shallow plenum commercial construction
- Heat treated springs hold fixture fitting securely in the ceiling eliminating light leaks
- Can be removed from below the ceiling for service or replacement
- Can be used with Halo new construction mounting frames

Junction Box

- Compact galvanized steel junction box
- Listed for (10) #12 AWG 90° C splice conductors
- Hinged door is retained and provides easy access to field wiring
- (2) 1/2" conduit pry-outs positioned to allow straight conduit runs
- (2) Slide-N-Side™ non-metallic (NM) wire traps allow wiring outside the box
- Accepts 14-2, 14-3, 12-2, 12-3 U.S. and 14-2, 14-3, 12-2 Canadian NM cable
- (3) 4-port push wire nuts with clear caps for quick and reliable mains voltage connections

Compliance

- Type IC thermally protected, suitable for direct contact to air permeable insulation and cULus listed for damp locations
- Wet location listed and IP44 ingress protection when used with lens overlay
- Not for use in direct contact with spray foam insulation, consult NEMA LSD57-2013
- Air-tite per ASTM-E283
- Can be used for State of California Title 24 high efficacy luminaire compliance with CA JA8-2016-E or JA8-2019-E labeled lamps
- Suitable for use in clothes closets when installed in accordance with the NEC 410.16 spacing requirements
- Contains no mercury or lead and RoHS compliant

Warranty

- One-year limited warranty, consult website for details. www.cooperlighting.com/global/warranty

Dimensional and Mounting Details

