Description

The H7 family of recessed housings are the standard in the industry for both commercial and residential applications. The wide variety of trims available allows a number of different lighting effects to be created with one basic housing. The H7RICAT housing is designed for installation where it will be in direct contact with insulation. The H7RICAT also meets restricted air flow requirements.

Catalog #		**Type**
Project		
Comments		**Date**
Prepared by		

Specification Features

Housing
- Aluminum construction for greater heat dissipation
- For installation from below the finished ceiling.
- Integral flange secures fixture against ceiling.
- Pre-installed Air-Tite ready ceiling contact gasket on flange

Socket Plate
- Rigid socket plate adjusts and locks without tools for various lamp sizes
- Socket plate and bracket may be removed when using socket supporting trims

Junction Box
- Seven 1/2" trade size conduit knockouts with true pry-out slots are positioned to accommodate straight conduit runs
- Four non-metallic (NM) cable pry-outs included
- Air-Tite™ code compliant

Quick Connect™
- Three 4-port push-in "Quick Connect" wire nuts included in junction box
- Speed installation and increase reliability
- No additional wire nuts required
- Simply strip and insert supply wires

Remodel Springs
- Four remodel springs secure housing and accommodate 1/2" and 5/8" ceiling material

Socket
- Porcelain socket with nickel plated brass screw shell
- Snap-in springs secure socket to socket plate, and may be detached when using socket supporting trims
- Overspray protector included

Thermal Protector
- Self resetting thermal protector deactivates fixture if overheating occurs due to improper lamping or misapplied insulation


Trims
- Halo Fit-All concept offers multiple trim options in a variety of design styles, and functional beam distributions to control beam angle and lumen delivery in accommodating various lamp types including Halogen, CFL and LED

Compliance
- cULus Listed 1598 luminaire
- cULus Listed damp location
- cULus Listed for wet location, covered ceiling, with select trims
- cULus Listed for feed through
- cULus Listed for direct contact with insulation and combustible material*
- Air-Tite code compliant. Certified under ASTM E283; not exceeding 2.0 cfm (0.944 L/s) air leakage rate tested at a 1.57 psf (75 Pa) pressure differential
- RoHS compliant

*Not to be used in direct contact with spray foam insulation (Consult NEMA LSD57-2013)

Discontinued 21-10-2025

Dimensions





H7RICAT

6" IC, Remodel , 120V

FOR USE IN INSULATED CEILINGS

FOR DIRECT CONTACT WITH INSULATION*

Ordering Information

Sample Number: H7RICAT 6110WB
Order housing, trim and lamp (by others) separately for a complete luminaire.

Domestic Preferences[1]	Housing
[Blank] = Standard **TAA** = Trade Agreements Act	**H7RICAT =** 6" IC, Air-tite, Remodel, 120V

Trims

Reflectors



30 Reflector, Self-flange
OD: 7-1/4" [184mm]
30HAT=Haze Reflector, White Trim
30RGAT=Residential Gold Reflector, White Trim
30CAT=Clear Specular Reflector, White Trim



30SBAT Reflector, Self-flange
OD: 7-1/4" [184mm]
30SBAT=Black Specular Reflector, Self-flange



404 Specular Reflector
OD: 7-1/4" [184mm]
404C=Clear Specular Reflector, White Trim
404H=Haze Reflector, White Trim
404SN=Satin Nickel Reflector and Trim
404TBZ=Tuscan Bronze Reflector and Trim



426 Reflector Cone
OD: 7-1/4" [184mm]
426=Clear Specular Reflector Cone, White Trim
426MB=Black Specular Reflector Cone, White Trim
426H=Haze Reflector Cone, White Trim
426SN=Satin Nickel Reflector Cone and Trim
426TBZ=Tuscan Bronze Reflector Cone and Trim



429 Dayform White Cone
OD: 7-1/4" [184mm]
429P=White Reflector and Trim



4041 White Reflector, Self-flange
OD: 7-1/4" [184mm]
4041P=White Reflector and Trim



4261 White Reflector Cone, Self-flange
OD: 7-1/4" [184mm]
4261P=White Reflector and Trim



6106 Straight Reflector Cone, Self-flange
OD: 7-3/4" [197mm]
6106SC=Specular Reflector, White Trim



6107 Tapered Reflector, Self-flange
OD: 7-3/4" [197mm]
6107SC=Specular Reflector, White Trim



6120 Full Cone Reflector, Self-flange
OD: 7-3/4" [197mm]
6120WH=White Reflector and Trim
6120SN=Satin Nickel Reflector and Trim
6120TBZ=Tuscan Bronze Reflector and Trim



6121 Shallow Full Cone Reflector, Self-flange
OD: 7-3/4" [197mm]
6121WH=White Reflector and Trim

Baffles




30 Baffle, Self-flange
OD: 7-1/4" [184mm]
30WAT=White Baffle, Reflector and Trim
30WATH=White Baffle, Clear Reflector and White Trim
30PAT=Black Baffle, Clear Reflector and White Trim
30SNAT=Satin Nickel Baffle, Reflector and Trim
30TBZAT=Tuscan Bronze Baffle, Reflector and Trim




310 Coilex® Baffle
OD: 7-1/4" [184mm]
310W=White Coilex Baffle and Trim
310P=Black Coilex Baffle, White Trim
310SN=Black Coilex Baffle, Satin Nickel Trim
310TBZ=Black Coilex Baffle, Tuscan Bronze Trim



353 Metal Baffle
OD: 7-1/4" [184mm]
353SN=Satin Nickel Baffle and Trim
353TBZ=Tuscan Bronze Baffle and Trim



6100 Tapered Metal Baffle with (2) Trim Rings
OD: 7-1/8" [181mm]
6100WB=White Baffle, Narrow and Wide White Trims (included)
6100BB=Black Baffle, Narrow and Wide White Trims (included)



6101 Straight Metal Baffle with (2) Trim Rings
OD: 7-1/8" [181mm]
6101WB=White Baffle, Narrow and Wide White Trims (included)
6101BB=Black Baffle, Narrow and Wide White Trims (included)



6102 Tapered Metal Baffle, Self-flange
OD: 7-3/4" [197mm]
6102WB=White Baffle and Trim
6102BB=Black Baffle, White Trim



6103 Straight Metal Baffle, Self-flange
OD: 7-3/4" [197mm]
6103WB=White Baffle and Trim
6103BB=Black Baffle, White Trim




6108 Coilex® Straight Plastic Baffle, Self-flange
OD: 7-3/4" [197mm]
6108WB=White Plastic Straight Coilex Baffle, White Trim
6108BB=Black Plastic Straight Coilex Baffle, White Trim
6108BKBB=Black Plastic Straight Coilex Baffle, Black Trim




6109 Coilex® Tapered Baffle, Self-flange
OD: 7-3/4" [197mm]
6109WB=White Tapered Coilex Baffle, White Trim
6109BB=Black Tapered Coilex Baffle, White Trim
6109BKBB=Black Tapered Coilex Baffle, Black Trim



6110 Perftex Baffle, Self-flange
OD: 7-3/4" [197mm]
6110WB=White Perftex Baffle and Trim
6110BB=Black Perftex Baffle, White Trim
6110BKBB=Black Perftex Baffle and Trim



6125 Full Cone Baffle, Self-flange
OD: 7-3/4" [197mm]
6125WB=White Baffle and Trim
6125BB=Black Baffle, White Trim
6125BKBB=Black Baffle and Trim



6126 Shallow Full Cone Baffle, Self-flange
OD: 7-3/4" [197mm]
6126WB=White Baffle and Trim
6126BB=Black Baffle, White Trim

Adjustable - Eyeballs & Gimbals



74 PAR30 Eyeball 30° Tilt, Self-flange
OD: 8" [203mm]
74P=White Eyeball and Trim



76 PAR38 Gimbal 30° Tilt, Self-flange
OD: 8" [203mm]
76P=White Gimbal and Trim



78 BR/PAR30 Eyeball 30° Tilt, Self-flange
OD: 8" [203mm]
78P=White Eyeball and Trim
78PAT=White Eyeball and Trim, Air-Tite
78SN=Satin Nickel Eyeball and Trim
78TBZ=Tuscan Bronze Eyeball and Trim



376 PAR30 Regressed Gimbal 30° Tilt, Self-flange
OD: 7-1/4" [184mm]
376W=White Baffle and Trim
376P=Black Baffle and White Trim



378 PAR30 Regressed Gimbal with Splay 25° Tilt, Self-flange
OD: 7-1/4" [184mm]
378P=White Splay and Trim
378=Clear Specular Splay and White Trim



420 BR/PAR30 Regressed Eyeball 30° Tilt, Self-flange
OD: 7-1/4" [184mm]
420W=White Eyeball, Baffle and Trim
420P=White Eyeball, Black Baffle, White Trim



478 PAR38 Adjustable Regressed Gimbal with Splay 25° Tilt, Self-flange
OD: 7-1/4" [184mm]
478P=White Splay and Trim



6130 BR/PAR30 Eyeball 35° Tilt, Self-flange
OD: 7-3/4" [197mm]
6130WH=White Eyeball and Trim



6170 PAR38 Gimbal 25° Tilt, Self-flange
OD: 7-3/4" [197mm]
6170WH=White Gimbal and Trim
6170BK=Black Gimbal and Trim
6170SN=Satin Nickel Gimbal and Trim
6170TBZ=Tuscan Bronze Gimbal and Trim



6215 PAR30 Double Gimbal 35°-50° Tilt, Self-flange
OD: 7-3/4" [197mm]
6215WH=White Gimbal and Trim
6215BK=Black Gimbal and Trim
6215SN=Satin Nickel Gimbal and Trim
6215TBZ=Tuscan Bronze Gimbal and Trim



6222 Regressed PAR30 Adjustable 45° Tilt, Self-flange
OD: 7-3/4" [197mm]
6222WB=White Baffle and Trim
6222BB=Black Baffle and Trim
6222SC=Specular Clear Reflector, White Trim
6222H=Haze Reflector, White Trim

Lenses & Wet Location Showerlights



170 Albalite Lens with Reflector
OD: 8" [203mm]
170P=Frosted Albalite Glass Lens, White Trim
170PS=Frosted Albalite Glass Lens, White Plastic Trim, Showerlight, Air-Tite



171 Drop Opal Lens with Reflector
OD: 8" [203mm]
171P=Drop Opal Glass Lens, White Trim
171PS=Drop Opal Glass Lens, White Plastic Trim, Showerlight, Air-Tite



172 Dome Lens with Reflector
OD: 7-3/4" [197mm]
172PS=Frosted Glass Dome, White Plastic Trim
172SNS=Frosted Glass Dome, Satin Nickel Plastic Trim
172TBZS=Frosted Glass Dome, Tuscan Bronze Plastic Trim

continued

Discontinued 21-10-2025

Notes: (1) Only product configurations with this designated prefix are built to be compliant with the Trade Agreements Act of 1979 (TAA). Please refer to DOMESTIC PREFERENCES website for more information. Components shipped separately may be separately analyzed under domestic preference requirements.Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information.

*Outdoor rated lamp only (purchase separately)

Ordering Information

Sample Number: H7RICAT 6110WB
Order housing, trim and lamp (by others) separately for a complete luminaire.

Domestic Preferences[1]

[Blank] = Standard
TAA = Trade Agreements Act

Housing

H7RICAT = 6" IC, Air-tite, Remodel, 120V

Trims

Lenses & Wet Location Showerlights



173 Fresnel Lens with Reflector
OD: 8" [203mm]
173P=Fresnel Glass Lens, White Trim
173PS=Fresnel Glass Lens, White Plastic Trim, Showerlight, Air-Tite



6145 Open Wet Location, Shallow Reflector, Self-flange - Showerlight*
OD: 7-3/4" [197mm]
6145WH=White Reflector and Trim
6145SN=Satin Nickel Reflector and Trim
6145TBZ=Tuscan Bronze Reflector and Trim



6146 Open Wet Location, Full Reflector, Self-flange - Showerlight*
OD: 7-3/4" [197mm]
6146WH=White Reflector and Trim
6146SN=Satin Nickel Reflector and Trim
6146TBZ=Tuscan Bronze Reflector and Trim



6150 Frost Dome Glass Lens, Self-flange
OD: 7-3/4" [197mm]
6150WH=Frost Dome Glass Lens with Reflector, White Plastic Trim
6150SN=Frost Dome Glass Lens with Reflector, Satin Nickel Plastic Trim
6150TBZ=Frost Dome Glass Lens with Reflector, Tuscan Bronze Plastic Trim



6162 Drop Opal Plastic Lens, Self-flange - Showerlight
OD: 7-3/4" [197mm]
6162WH=Drop Opal Plastic Lens with Reflector, White Plastic Trim



6230 Squircle Frost Glass Lens, Metal Trim - Showerlight
OD: 7-1/4" [183mm]
6230AH=Frost Glass Lens, Aluminum Haze Squircle Trim
6230PN=Frost Glass Lens, Polished Nickel Squircle Trim
6230SN=Frost Glass Lens, Satin Nickel Squircle Trim
6230TBZ=Frost Glass Lens, Tuscan Bronze Squircle Trim



6255 Soft Square, Frost Curve Glass Lens, Self-flange - Showerlight
OD: 7-1/4" [183mm]
6255WH=Frost Curve Glass Lens with Reflector, White Plastic Trim
6255SN=Frost Curve Glass Lens with Reflector, Satin Nickel Plastic Trim
6255TBZ=Frost Curve Glass Lens with Reflector, Tuscan Bronze Plastic Trim

Open, Splay & Wall Wash



300 Open Trim with Fixed Socket Bracket, Self-flange
OD: 7-1/4" [183mm]
300P=Self-flange with White Open Trim
300SN=Self-flange with Satin Nickel Open Trim
300TBZ=Self-flange with Tuscan Bronze Open Trim



327 White Splay Trim with Fixed Socket Bracket, Self-flange
OD: 7-3/4" [197mm]
327P=White Splay Trim with Socket Bracket



328 White Splay Trim
OD: 7-3/4" [197mm]
328P=White Splay Trim



430 Wall Wash with Baffle & Full Reflector
OD: 7-1/4" [183mm]
430W=White Baffle, with Upper Reflector, White Trim
430P=Black Baffle, with Upper Reflector, White Trim

Accessories

Designer Finish Trim Rings
TRM6C=Chrome
TRM6SN=Satin Nickel
TRM6TBZ=Tuscan Bronze
TRM6MB=Black Metal
TRM7MB=Black plastic
Metal 7 1/4" OD. Compatible with 310*, 312*, 376, 378, 400, 404, 405, 410, 416, 419, 420, 424, 425, 426*, 429*, 455CG, 455SC, 456P, 456W, 477, 478, 1412, 1416, 1475.

Oversized Trim Rings
OT400P=6" ID x 9-1/4" OD, Oversized white metal trim ring for designated 6" trims.
OT403P=6" ID x 8" OD, Oversized gloos white plastic trim ring for designated 6" trims.

H930 R/PAR Lamp Aiming Accessory
H930=For H7T, H7RT, H7ICT, H7ICAT, H7RICT, H7RICAT housings with 310 and 426 trims. Allows lamp to be aimed up to 30˚ from vertical and rotated 358˚. See housing-trim selection for lamp listings.

*Originally supplied with TRM6P white metal trim rings. All others are suppied with white plastic trim rings.

Discontinued 11-10-2025

Notes: (1) Only product configurations with this designated prefix are built to be compliant with the Trade Agreements Act of 1979 (TAA). Please refer to DOMESTIC PREFERENCES website for more information. Components shipped separately may be separately analyzed under domestic preference requirements.Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information.

*Outdoor rated lamp only (purchase separately)

COOPER Lighting Solutions

Cooper Lighting Solutions
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.cooperlighting.com

Specifications and dimensions subject to change without notice.

c UL us LISTED
For use in Halo listed housings.

CLASSIFIED c UL us
Select trims are classified for use in others housings.
See www.cooperlighting.com