

Project		Catalog #		Type	
Prepared by		Notes		Date	



Fail-Safe

Vaportite LED

4' Tamper Resistant LED Vaportite

Typical Applications

Cold Storage • Canopy • Warehouse • Food Processing • Manufacturing
• Complex Environments

Interactive Menu

- Order Information [page 2](#)
- Photometric Data [page 2](#)
- Product Warranty

Product Certification





Product Features



Top Product Features

- 4ft Sealed and Gasketed Tamper Resistant Vaportite
- Lumen packages up to 30K lumens
- High-Performance efficacy up to 146 LPW
- LEDs available in 3500K, 4000K and 5000K at 80 CRI
- Rated for -40c to 40c ambient

Dimensional and Mounting Details





Installation Data

SS Latches and Mounting Bail

MOUNTING BAILS

Furnished (standard)
Stainless steel, Two
per 4' Unit



VT4LED-SS-MKB PK—Stainless Steel
Mounting Bracket (2 per fixture)
VT4LED-ZP-MBK PK—Zinc Mounting
Bracket (2 per fixture)

Order Information

SAMPLE ORDER NUMBER: **VRVT4LED-LD5-24-DR-UNV-L850-CD2-WL-U**

Series	Lamp Type	LED Lumens Output	Lens	Voltage	CCT	Options Emergency
Series	Lamp Type	LED Lumen Output ⁽³⁾	Lens	Voltage ^{(1), (2)}	CCT	Options Emergency
VRVT4LED =LED Vaportite	LD5 =LED 5.0	9=9,000 Lumens 12=12,000 Lumens 15=15,000 Lumens 18=18,000 Lumens 24=24,000 Lumens 30=30,000 Lumens	DR =Clear Acrylic High Impact DRF =Frosted Acrylic High Impact PC =Clear Poly Carbonate	120V =120 Volt 277V =277 Volt 347V =347 Volt 480V =480 Volt UNV =Universal 120-277 Volt UNC =Universal 347-480 Volt	L835 =3500K L840 =4000K L850 =5000K LG52 =Green 520nm LED ⁽¹¹⁾ LA59 =Amber 590nm LED LR63 =Red 630nm LED ⁽¹¹⁾	EL10W =10-watt, 120-277V emergency battery pack installed (available in 9,000 and 12,000 lumen fixtures only) ⁽⁸⁾ VT-REM-EL =Emergency Installed, 700 lumens ⁽⁵⁾
		Notes (3) Lumen output will vary depending on dimming or fixed output refer to IES files for delivered lumens.		Notes (1) Voltage must be specified when ordered with plugs. (2) When ordering MS option, specify as UNV (for 120 or 277V), 347 or 480V.	Notes (11) 12000 Lumens not available for the Green and Red LEDs because they are exceeding the max LED current.	Notes (5) Specify 120 to 277V only. (8) EL10W option rated for 0C to 35C ambient.

Driver Type	Number of Drivers	Label	Options	Packaging	Accessories
Driver Type ⁽³⁾	Number of Drivers	Label	Options	Packaging	Accessories (order separately) ⁽⁴⁾
CD =0-10V Dimming Driver	1=1 Driver (9,000 and 12,000) 2=2 Drivers (15,000, 18,000 and 24,000 lumens) 3=3 Drivers (30,000 lumen)	WL =Wet Label	[Blank] =Plastic Latches and (2) End Watertite Hubs (all Watertite Hubs have 1/2" Conduit Entry) C3 =3' Power Cord C6 =6' Power Cord PC3 =3' Power Cord & Plug (Specify Voltage) PC6 =6' Power Cord & Plug (Specify Voltage) MS =Damp listed Motion Sensor ⁽²⁾ MSWL20 =Wet location motion sensor, up to 20ft mounting height ^{(6), (7)} MSWL40 =Wet location motion sensor, up to 40ft mounting height ^{(6), (7)} HBE11 =Wet location PIR Indoor/Outdoor Occupancy Sensor ⁽¹⁰⁾ SSL =Stainless Steel Latches	U =Unit Pack	VT4LED-SS-MBK PK =Stainless Steel Surface Mounting Bracket (2 per fixture) VT4LED-ZP-MBK PK =Zinc Mounting Bracket (2 per fixture)
Notes (3) Lumen output will vary depending on dimming or fixed output refer to IES files for delivered lumens.			Notes (2) When ordering MS option, specify as UNV (for 120 or 277V), 347 or 480V. (6) When ordering MSWL option, specify voltage (120, 277, or 347V). 480V not available. (7) MSWL sensor rated up to IP65. (10) Available for 120V, 277V, and 347V voltage only.		Notes (4) Mounting beam only available for UNV versions at max. ambient temperature 35°C.

Product Specifications

Construction

- Rugged and durable construction
- Reinforced fiberglass housing with high impact diffuser
- Incorporates a full hinged metal gear tray secured by internal latches for toolless driver access.
- Polyurethane gasketing provides a continuous seamless seal for the diffuser lens
- Four sturdy cam latches clamp diffuser tightly for a positive seal between housing, gasketing and diffuser
- Stainless steel latches option
- Torx (R) Tamperproof Screws to prevent unauthorized access

Electrical

- Long-Life LED system coupled with electrical driver for optimal performance
- LED's available in 3500K, 4000K and 5000K with a CRI ≥ 80
- Projected life is 60,000 hours at 70% lumen output
- Electronic drivers are available for 120-277V, 347V and 480V applications
- 0-10V dimming control is available
- Operating temperature of -40°C to 40°C

Lens

- High-impact clear or frosted acrylic or 100% polycarbonate lens options

Mounting

- Surface, chain, cable or stem mounting
- Suspended mount using two stainless steel mounting bails (included)
- Optional Y-hook, Y-toggle or surface/stem mount bracket available and must be ordered separately


Warranty

- Five-year limited warranty


Compliance

- UL/cUL listed for Wet location
- RoHS compliant
- LED modules comply with IESNA LM-79 and LM-80 standards
- NEMA 4X, IP65 and IP67 rated, up to 1500 PSI hosedown
- NSF certified

Photometric Data

[View IES files](#)


4RVVT4LED-LD5-24-DR-UNV-L850-CD2-WL-U
Electronic Driver
Linear LED 5000K
Spacing criterion: (II) 1.28 x mounting height,
(⊥) 1.17 x mounting height
Lumens: 24975
Input Watts: 179.3W
Efficacy: 139.3 lm/W
Test Report:
4RVVT4LED-LD5-24-DR-UNV-L850-CD2-WL-U.IES



VRVT4LED-LD5-24-DRF-UNV-L850-CD2-WL-U
Electronic Driver
Linear LED 5000K
Spacing criterion: (II) 1.25 x mounting height,
(⊥) 1.2 x mounting height
Lumens: 24393
Input Watts: 179.2W
Efficacy: 136.1 lm/W
Test Report:
VRVT4LED-LD5-24-DRF-UNV-L850-CD2-WL-U.IES

Energy and Performance Data by Catalog Number

White LED

Catalog Number	Description	Delivered Lumens			Watts	Efficacy		
		Lensing				Lensing		
		DR	DRF	PC		DR	DRF	PC
VRVT4LED-9-XX-UNV-L835-CD1	4ft, Vaportight, 9000 lumens UNV, 3500K	8822	8599	8605	64	138	134	134
VRVT4LED-9-XX-UNV-L840-CD1	4ft, Vaportight, 9000 lumens UNV, 4000K	9002	8774	8781	64	141	137	137
VRVT4LED-9-XX-UNV-L850-CD1	4ft, Vaportight, 9000 lumens UNV, 5000K	9362	9125	9132	64	146	143	143
VRVT4LED-12-XX-UNV-L835-CD1	4ft, Vaportight, 12000 lumens UNV, 3500K	11662	11367	11376	93	125	122	122
VRVT4LED-12-XX-UNV-L840-CD1	4ft, Vaportight, 12000 lumens UNV, 4000K	11900	11599	11608	93	128	125	125
VRVT4LED-12-XX-UNV-L850-CD1	4ft, Vaportight, 12000 lumens UNV, 5000K	12376	12063	12072	93	133	130	130
VRVT4LED-15-XX-UNV-L835-CD2	4ft, Vaportight, 15000 lumens UNV, 3500K	14924	14537	14602	112	133	130	130
VRVT4LED-15-XX-UNV-L840-CD2	4ft, Vaportight, 15000 lumens UNV, 4000K	15229	14834	14900	112	136	132	133
VRVT4LED-15-XX-UNV-L850-CD2	4ft, Vaportight, 15000 lumens UNV, 5000K	15838	15427	15496	112	141	138	138
VRVT4LED-18-XX-UNV-L835-CD2	4ft, Vaportight, 18000 lumens UNV, 3500K	17991	17555	17625	133	135	132	133
VRVT4LED-18-XX-UNV-L840-CD2	4ft, Vaportight, 18000 lumens UNV, 4000K	18358	17913	17985	133	138	135	135
VRVT4LED-18-XX-UNV-L850-CD2	4ft, Vaportight, 18000 lumens UNV, 5000K	19092	18630	18704	133	144	140	141
VRVT4LED-24-XX-UNV-L835-CD2	4ft, Vaportight, 24000 lumens UNV, 3500K	23534	22986	22867	179	131	128	128
VRVT4LED-24-XX-UNV-L840-CD2	4ft, Vaportight, 24000 lumens UNV, 4000K	24014	23455	23334	179	134	131	130
VRVT4LED-24-XX-UNV-L850-CD2	4ft, Vaportight, 24000 lumens UNV, 5000K	24975	24393	24267	179	140	136	136
VRVT4LED-30-XX-UNV-L835-CD3	4ft, Vaportight, 30000 lumens UNV, 3500K	29937	29139	29350	232	129	126	127
VRVT4LED-30-XX-UNV-L840-CD3	4ft, Vaportight, 30000 lumens UNV, 4000K	30548	29734	29949	232	132	128	129
VRVT4LED-30-XX-UNV-L850-CD3	4ft, Vaportight, 30000 lumens UNV, 5000K	31770	30923	31147	232	137	133	134

Color LED

Catalog Number	Description	Delivered Lumens			Watts	Efficacy		
		Lensing				Lensing		
		DR	DRF	PC		DR	DRF	PC
VRVT4LED-LD5-9-XX-UNV-LR63-CD1-WL-U	4ft, Vaportight, 9000 lumens UNV, Red 630nm	1440	1404	1405	166	9	8	8
VRVT4LED-LD5-9-XX-UNV-LA59-CD1-WL-U	4ft, Vaportight, 9000 lumens UNV, Amber 590nm	2521	2457	2459	98	26	25	25
VRVT4LED-LD5-9-XX-UNV-LG52-CD1-WL-U	4ft, Vaportight, 9000 lumens UNV, Green 520nm	7202	7019	7025	153	47	46	46
VRVT4LED-LD5-12-XX-UNV-LR63-CD1-WL-U	4ft, Vaportight, 12000 lumens UNV, Red 630nm	1904	1856	1857	240	8	8	8
VRVT4LED-LD5-12-XX-UNV-LA59-CD1-WL-U	4ft, Vaportight, 12000 lumens UNV, Amber 590nm	3332	3248	3250	142	24	23	23
VRVT4LED-LD5-12-XX-UNV-LG52-CD1-WL-U	4ft, Vaportight, 12000 lumens UNV, Green 520nm	9520	9279	9286	220	43	42	42
VRVT4LED-LD5-15-XX-UNV-LR63-CD1-WL-U	4ft, Vaportight, 15000 lumens UNV, Red 630nm	2437	2373	2384	291	8	8	8
VRVT4LED-LD5-15-XX-UNV-LA59-CD1-WL-U	4ft, Vaportight, 15000 lumens UNV, Amber 590nm	4264	4153	4172	172	25	24	24
VRVT4LED-LD5-15-XX-UNV-LG52-CD1-WL-U	4ft, Vaportight, 15000 lumens UNV, Green 520nm	12183	11867	11920	268	46	44	45
VRVT4LED-LD5-18-XX-UNV-LR63-CD1-WL-U	4ft, Vaportight, 18000 lumens UNV, Red 630nm	2937	2866	2878	345	9	8	8
VRVT4LED-LD5-18-XX-UNV-LA59-CD1-WL-U	4ft, Vaportight, 18000 lumens UNV, Amber 590nm	5140	5016	5036	204	25	25	25
VRVT4LED-LD5-18-XX-UNV-LG52-CD1-WL-U	4ft, Vaportight, 18000 lumens UNV, Green 520nm	14686	14330	14388	317	46	45	45
VRVT4LED-LD5-24-XX-UNV-LR63-CD1-WL-U	4ft, Vaportight, 24000 lumens UNV, Red 630nm	3842	3753	3733	464	8	8	8
VRVT4LED-LD5-24-XX-UNV-LA59-CD1-WL-U	4ft, Vaportight, 24000 lumens UNV, Amber 590nm	6724	6567	6534	274	25	24	24
VRVT4LED-LD5-24-XX-UNV-LG52-CD1-WL-U	4ft, Vaportight, 24000 lumens UNV, Green 520nm	19211	18764	18667	427	45	44	44
VRVT4LED-LD5-30-XX-UNV-LR63-CD1-WL-U	4ft, Vaportight, 30000 lumens UNV, Red 630nm	4888	4757	4792	602	8	8	8
VRVT4LED-LD5-30-XX-UNV-LA59-CD1-WL-U	4ft, Vaportight, 30000 lumens UNV, Amber 590nm	8553	8326	8386	356	24	23	24
VRVT4LED-LD5-30-XX-UNV-LG52-CD1-WL-U	4ft, Vaportight, 30000 lumens UNV, Green 520nm	24438	23787	23959	553	44	43	43

Energy and Performance Data by Catalog Number

Lumen Maintenance

Ambient Temperature	TM-21 Lumen Maintenance (60,000 hours)	Theoretical L70 (Hours)
25°C	> 92%	> 281,000

Energy Data

Input Watts:
VRVT4LED-LD5-9-DR=64W
VRVT4LED-LD5-12-DR=92W
VRVT4LED-LD5-15-DR=113W
VRVT4LED-LD5-18-DR=133W
VRVT4LED-LD5-24-DR=179W
VRVT4LED-LD5-30-DR=232W

Shipping Data

Catalog No.	Wt.
VRVT4LED-LD5-9-DR	24 lbs.
VRVT4LED-LD5-12-DR	24 lbs.
VRVT4LED-LD5-15-DR	24 lbs.
VRVT4LED-LD5-18-DR	24 lbs.
VRVT4LED-LD5-24-DR	26 lbs.
VRVT4LED-LD5-30-DR	26 lbs.