

## DESCRIPTION

Regressed glass lens adjustable downlight shower trim with reflector is designed for use with IC or Non-IC AIR-TITE™ 3" Halo small aperture line and low voltage housings. Models 3007WHC, 3007PCC and 3007SN are "dead-front" featuring a glass lens with non-conductive and non-corrosive polymer trim rings. Model 3007TBZ has a die-cast trim ring. This wet location listed shower trim uses MR16 low voltage or GU10 line voltage lamps, ideal for accent and task lighting. Regressed lens trim offers 15° tilt with 360° orientation within housing.


<b>Catalog #</b>		<b>Type</b>
<b>Project</b>		
<b>Comments</b>		<b>Date</b>
<b>Prepared by</b>		

## SPECIFICATION FEATURES

Trim combinations include Specular Clear Reflector with Matte White or Polished Chrome trim ring, Satin Nickel reflector and trim ring, and Tuscan Bronze reflector and trim ring. Three pressure springs ensure positive retention in housing.

3007 is designed for use with the following Halo H3 small aperture housings:

- Line Voltage Housing (for 120V GU10 lamps).
  - H36ICAT 50W IC Air-Tite Housing
  - H36TAT 50W Non-IC Air-Tite Housing
  - H36RTAT 50W Non-IC Air-Tite Remodel Housing
- Low Voltage Housing (for 12V MR16 lamps).
  - H36LVICAT 50W IC Air-Tite Housing
  - H36LVTAT 50W Non-IC Air-Tite Housing
  - H36LVRTAT 50W Non-IC Air-Tite Remodel Housing
  - H36LVTAT277 50W Non-IC Air-Tite Housing, 120/277V
  - H36LVRTAT277 50W Non-IC Air-Tite Remodel Housing, 120/277V
- Line Voltage Housing (for 120V GU10 lamps).
  - H38ICAT 50W IC Air-Tite Housing
- Low Voltage Housing (for 12V MR16 lamps).
  - H38LVICAT 37W IC Air-Tite Housing



Lamp Aperture: 2" [51mm]  
 Reflector Diameter: 3" [75mm]  
 Ceiling Opening: 3-3/4" [95mm]  
 Outside Diameter: 4-1/4" [108mm]



**3007WHC**  
White with Specular Clear Reflector



**3007SN**  
Satin Nickel with Satin Nickel Reflector



**3007TBZ**  
Tuscan Bronze with Tuscan Bronze Reflector



**3007PCC**  
Polished Chrome with Specular Clear Reflector

## 3007

### 3" Regressed Lens Showerlight Trim



3" TRIMS

## ORDERING INFORMATION

**SAMPLE NUMBER: 3007PCC**

Order housing and trims separately.

Trim	Finish
<b>3007</b> = 3" Lensed Showerlight Trim	<b>WHC</b> =White with Specular Clear Reflector, Glass Lens, and Polymer Trim Ring "Dead-Front" <b>PCC</b> =Polished Chrome with Specular Clear Reflector, Glass Lens, and Polymer Trim Ring "Dead-Front" <b>SN</b> =Satin Nickel with Satin Nickel Reflector, Glass Lens, and Polymer Trim Ring "Dead-Front" <b>TBZ</b> =Tuscan Bronze with Tuscan Bronze Reflector, Glass Lens, and Die-Cast Trim Ring "Dead-Front"