



GO CANLESS!

Installs Virtually Anywhere!

- Field-Selectable colour temperatures
- Mounts to drywall or suspended ceilings (no housing required)
- Remote driver/junction box included
- Rated for insulation contact (IC) & non-IC ceilings


Quick and Easy Installation



New Construction Mounting Frames and Smash Plate

For Installing Canless Downlights in New Construction

- Use HALO Mounting Frames/Smash Plates on your next new construction project
- Toolless thumbscrews hold remote driver/jbox to the frame during rough in
- **MF Series** - 4" & 6" rounds with 1/2" drywall collar
- **HL Series** - 4" & 6" rounds that convert to squares with corner knockouts
- **Smash Plate** - Our most cost-effective single frame solution that can fit 3", 4", or 6" HALO Canless Fixtures (convert 4" or 6" openings to squares with corner knockouts)



Catalog Number	Description	UPC
MF4RC	4" Round Mounting Frame with 1/2" Drywall Collar	080083268009
MF6RC	6" Round Mounting Frame with 1/2" Drywall Collar	080083268023
HL4RSMF	4" Round/Square Mounting Frame	080083876167
HL6RSMF	6" Round/Square Canless Mounting Frame	080083876181
SP346RS	3"/4"/6" Round/Square Smash Plate	080083288236

SLIM CANLESS DOWNLIGHT Product Selection Guide

Good Better Best

		HLBE & HLBSL	HLBPH	HLB	HLBC/HLBC+
FEATURES/PERFORMANCE	Slim 1/2" Thin	✓	✓	✓	✓
	Size / Shape	4", 6" Round	4", 6" Round	3", 4", 6", 8", 12" Round, Square	4", 6" Round, Square ¹
	Lens	Smooth	Smooth	Low-glare Prismatic	Regressed, Low-glare Prismatic
	Max Lumens (By size @ 3000K)	745, 1,025	805, 1,015	595, 790, 1,020, 2,350, 2,300	975, 1,270 (Lumen Select, Dedicated)
	Colour Temperatures (CCT)	3 CCT 27/30/3500K 30/40/5000K, Dedicated: 3000K	5 CCT 27/30/35/40/5000K	5 CCT 27/30/35/40/5000K	5 CCT w/ D2W D2W/27/30/35/40/5000K
CONTROL	Dimming	10% Phase Cut	5% Phase Cut	5% Phase Cut, 0-10V ²	5% Phase Cut, 0-10V
	Estimated Life Hours	35,000	50,000	50,000	50,000
	Input Voltage	120V	120V	120V, 120-277V	120V, 120-277V
ACCESSORIES	Fits Mounting Frames	✓	✓	✓	✓
	Decorative Overlays ³	✓	✓	✓	✓ ¹
	Slide-in-Side™ Wire Traps ⁴		✓	✓	✓
	Mounting Bar	✓ ⁵	✓	✓	✓

¹ Overlay Trims sold separately. ² Available in QuickLink Low Voltage (Phase Cut or 0-10V) or Smart Wi-Fi® Connected by WiZ Pro versions. ³ Matte Black, Tuscan Bronze, Satin Nickel, and Paintable Matte White. ⁴ Slide-N-Side wire traps eliminate the need to use knockouts in most instances. Pre-wire outside of the jbox, fold down the tab(s), and insert non-metallic sheathed cable into the Slide-N-Side strain relief. ⁵ Mounting Bars are included with HLBSL but are sold separately for the HLBE Bulk Packs (HLBE-MOUNT-12PK).

HLBSL Slim Lite CANLESS DOWNLIGHTS - 4" & 6"

- Matches the HLBPH with simplified features for budget-conscious installers
- **HLBSL:** 5 Colour Field-Selectable in 27/30/35/40/5000K
- Only available in dead-front plastic frame and smooth lens
- Includes LED downlight and remote driver/junction box with mounting bar*
- 10% Phase Cut (LE/TE) Dimming, 35,000 hrs, 90+ CRI



Selectable CCT

Catalog Number	Description	Replaces	CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
HLBSL406FS5	4" Round LED Direct Mount	65W	2700K-5000K	120V	600	8.5	080083297221	3543535
HLBSL406FS5-12PK	4" Round LED Direct Mount, 12 Pack	65W	2700K-5000K	120V	600	8.5	080083302109	3543535
HLBSL609FS5	6" Round LED Direct Mount	65W	2700K-5000K	120V	900	10	080083297245	3543537
HLBSL609FS5-12PK	6" Round LED Direct Mount, 12 Pack	65W	2700K-5000K	120V	900	10	080083302123	3543537

HALO CANLESS DOWNLIGHTING

HLBPH Slim

CANLESS DOWNLIGHTS - 4" & 6"

- An ultra-thin flange and sleek 1/2"-thin downlight design that fits under any obstruction
- Dead-front trim & smooth lens
- 5 Colour Field-Selectable in 27/30/35/40/5000K
- Includes LED downlight and remote driver/junction box
- 5% Dimming (Phase Cut or 0-10V), 50,000 hrs, 90+ CRI



Catalog Number	Description	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
HLBPH4069FS1EMWR-C	4" Downlight, Round	65W	2700K-5000K	120V	805	10	080083252398	2385132
HLBPH6099FS1EMWR-C	6" Downlight, Round	70W	2700K-5000K	120V	1,015	14	080083253517	2385133

HLB Slim

CANLESS DOWNLIGHTS - 3", 4", 6", 8" & 12"

- An ultra-thin flange and sleek 1/2"-thin downlight design that fits under any obstruction
- Die-cast trim & low-glare prismatic lens
- 5 Colour Field-Selectable in 27/30/35/40/5000K
- Includes LED downlight and remote driver/junction box with mounting bar
- 5% Dimming (Phase Cut or 0-10V), 50,000 hrs, 90+ CRI



Available in square

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
HLB4LSFS5-C	4" Downlight, Round	65W	2700K-5000K	120V	700/850/1000 (Lumen Select)	7.8/9.2/11.6	080083297344	3706760
HLB6LSFS5-C	6" Downlight, Round	65W	2700K-5000K	120V	800/1000/1200 (Lumen Select)	8.9/11.2/13.6	080083297368	3706764
HLB6099FSE010MWR	6" Downlight, Round (0-10V)	70W	2700K-5000K	120-277V	1,060	15	080083912285	2351377
HLB8169FS1EMWR	8" Downlight, Round	100W	2700K-5000K	120V	1761	21	080083150601	2358047
HLB8LS9FSE010MWR-C	8" Downlight, Round (0-10V)	90-150W	2700K-5000K	120-277V	1,400/1,900/2,400 (Lumen Select)	17/25/32	080083083367	2358045

Accessories (optional)

Catalog Number	Description	Finish	UPC
HLB4RTRMMB	4" Round HLB Trim	Matte Black	080083268375
HLB6RTRMMB	6" Round HLB Trim	Matte Black	080083268412



HLB4RTRMMB



HLB4RTRMMW



HLB4RTRMSN



HLB4RTRMTBZ

HALO CANLESS DOWNLIGHTING

CANLESS DOWNLIGHT Product Selection Guide



		DOWNLIGHTS			ADJUSTABLES		
		LT-DM	CJB/CJB+	RL-DM, RLFR, RL-DM Night Light	HLA	RA-DM	RL-Slope
FEATURES / PERFORMANCE	Fixture Types	Downlights	Slim Downlight with Attached Jbox + 2-in-1 Canless-to-Can Versions Available	Recessed Downlights, Fire Rated Downlight, & Downlight + Night Light	Gimbal Adjustables (30° Tilt/360° Rotation)	Gimbal Adjustables (35° Tilt/360° Rotation)	Regressed Slope Adjustable (9-45° Tilt)
	Sizes (Round)	3", 4", 6"	4", 6"	4", 6"	3", 4"	4", 6"	4", 6"
	Trim & Lens	Baffle or Smooth Trim w/ Flat Lens	Slim Trim w/ Flat Smooth Lens	Baffle Trim w/ Curved Lens (NL has Transparent Trim)	Low-glare Prismatic or Smooth Lens	Baffle Trim w/ Flat Lens	Deep Baffle Trim w/ Integrated Optic
	Max Lumens (By size @ 3000K)	570, 645, 785	745, 920	955, 1,300 (Lumen Select, Dedicated) (NL: 780, 1,020)	710	790, 775	960, 1,630
	Colour Temperatures (CCT)	5CCT 27/30/35/40/5000K Dedicated: 3000K	5 CCT 27/30/35/40/5000K	5 CCT w/ D2W D2W/27/30/35/40/5000K (NL: 2000K)	5 CCT 27/30/35/40/5000K	5 CCT 27/30/35/40/5000K	5 CCT 27/30/35/40/5000K
CONTROL	Dimming Phase Cut (LE/TE)/0-10V	10% Phase Cut ¹	10% Phase Cut ¹	5% Phase Cut, 0-10V ^{2, 3} (NL: 5% Phase Cut - Both zones)	5% Phase Cut	5% Phase Cut ³	5% Phase Cut
	Estimated Life Hours	35,000	35,000	70,000 (RL & NL: 50,000)	50,000	50,000	50,000
	Input Voltage	120V	120V	120V	120V	120V	120V
HARDWARE	Fits Mounting Frames/Smash Plate	✓	✓	✓	✓	✓	✓
	Decorative Overlays ⁴	✓		✓ (RL-DM only)	✓		
	Slide-in-Side™ Wire Traps ⁵			✓	✓	✓	✓
	Mounting Bar	✓		✓	✓	✓	✓

¹ LT-DMs are also available in QuickLink Low Voltage (Phase Cut) versions. ² Available in QuickLink Low Voltage (0-10V) versions. ³ Available in Smart Wi-Fi® Connected by WiZ Pro versions. ⁴ Matte Black, Tuscan Bronze, Satin Nicke, Paintable Matte White. ⁵ Slide-N-Side wire traps eliminate the need to remove knockouts. Pre-wire outside of the j-box, fold down the tab, and insert non-metallic sheathed cable into the Slide-N-Side strain relief

LT-DM Recessed Baffle & Smooth Splay Trim

CANLESS DOWNLIGHTS - 3", 4", & 6"

- Closely mirrors the RL-DM design with simplified features for maximum savings
- Dead-front plastic trim in either baffle or smooth splay and flat lens
- 5 Colour Field-Selectable in 27/30/35/40/5000K
- Includes LED downlight and remote driver/junction box with mounting bar
- 10% Dimming (Phase Cut LE/TE), 35,000 hrs, 90+ CRI



Available in black

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
LTC305FS5B	3" Baffle	60W	2700K-5000K	120V	550	6.0	080083297047	3557102
LTC305FS5BMB	3" Baffle, Black	60W	2700K-5000K	120V	550	6.5	080083309382	4437375
LTC406FS5B-C	4" Baffle	60W	2700K-5000K	120V	650	7.2	80083304769	3557103
LTC406FS5BMB	4" Baffle, Black	60W	2700K-5000K	120V	650	7.5	080083309405	4437376
LTC608FS5B-C	6" Baffle	60W	2700K-5000K	120V	750	8.5	080083304783	3943235
LTC608FS5BMB	6" Baffle, Black	60W	2700K-5000K	120V	750	9.0	080083309429	4437377

Accessories (optional)

Catalog Number	Description	Finish	UPC
LT30MW	3" Smooth Splay Overlay	Matte White	080083297528
LT40MW	4" Smooth Splay Overlay	Matte White	080083297542
LT60MW	6" Smooth Splay Overlay	Matte White	080083297566



Paintable
Matte White

RL-DM Recessed Baffle Trim

CANLESS DOWNLIGHTS - 4" & 6"

- The perfect balance of value and visual comfort, available as a canless direct mount
- Die-cast aluminum baffle trim with curved lens and selectable lumen options
- 6-Position Switch: 5 Colour Field-Selectable (27/30/35/40/5000K) + Dim-to-Warm (3000K dims to 1800K)
- LED downlight with remote driver/junction box
- 5% Phase Cut (LE/TE) Dimming, 70,000 hrs, 90+ CRI





Catalog Number	Description	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
RL4LS9FSD2W1EWHDM-C	4" Baffle Downlight	60-70W	2700K-5000K+D2W	120V	600/900	7.5/11.5	080083259045	2403141
RL6LS9FSD2W1EWHDM-C	6" Baffle Downlight	70-75W	2700K-5000K+D2W	120V	900/1,200	10/14	080083259120	2403144

RLFR Fire-rated Recessed Baffle Trim

CANLESS DOWNLIGHTS - 4" & 6"

- Prevent the passage of flames & toxic gases for up to 2 hours
- Die-cast aluminum baffle trim and curved lens
- 5 Colour Field-Selectable in 27/30/35/40/5000K
- Includes LED downlight and remote driver/junction box with mounting bar
- 5% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI



Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
RLFR4FS	4" Fire Rated Baffle Downlight, white	White	70W	2700K-5000K	120V	1,000	11	080083295838	3549872
RLFR6FS	6" Fire Rated Baffle Downlight, white	White	75W	2700K-5000K	120V	1,400	13	080083295852	3549873

HLBFR Fire Rated Slim

CANLESS DOWNLIGHTS - 4" & 6"

- Prevent the passage of flames & toxic gases for up to 2 hours
- Sleek 5/8"-thin downlight design fits under any obstruction in fire rated ceilings
- Die-cast trim & low-glare prismatic lens
- 5 Colour Field-Selectable in 27/30/35/40/5000K
- Includes LED downlight and remote driver/junction box with mounting bar
- 5% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI



Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
HLBFR407FS5	4" Fire Rated Downlight, Round	White	65W	2700K-5000K	120V	690	10	080083304950	4005521
HLBFR407FS5MB	4" Fire Rated Downlight, Round	Black	65W	2700K-5000K	120V	690	10	080083304998	4005519
HLBFR609FS5	6" Fire Rated Downlight, Round	White	70W	2700K-5000K	120V	1035	14	080083304974	4005518
HLBFR609FS5MB	6" Fire Rated Downlight, Round	Black	70W	2700K-5000K	120V	995	14	080083305117	4005520

HLA Super Adjustable Gimbal

CANLESS DOWNLIGHTS - 3", 4" & 6"

- Aim lighting where you want it with 360° of rotation and 90° of tilt!
- NEW! Flip-N-Klip Canless Locking Springs - No more pinched fingers!
- Ideal for shallow plenum spaces - requires only 1-1/2" above the ceiling
- 5 Colour Field-Selectable in 27/30/35/40/5000K
- Includes LED downlight and remote driver/junction box with mounting bar
- 5% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI



Catalog Number	Description	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
HLA305FS5	3" Super Adjustable	65W	2700K-6500K	120V	610	7.0	080083301201	4020741
HLA406FS5	4" Super Adjustable	65W	2700K-6500K	120V	660	7.0	080083301225	4020742
HLA609FS5	6" Super Adjustable	65W	2700K-6500K	120V	990	10.5W	080083301249	4020743

LCR Light Commercial Downlight

CANLESS DOWNLIGHTS

- Light commercial LED downlight in 2, 4, 6 and 8-inch sizes
- Installs into drywall/suspended ceiling (no j-box or housing required)
- 5 field-selectable CCT: 2700K, 3000K, 3500K, 4000K, 5000K; 90 CRI
- Regressed lens and smooth baffle provide high optical cutoff
- Wide distribution pattern is ideal for general area illumination; Airtight
- 120-277V input, 0-10V dimming to 5%



Catalog Number	Description	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
LCR208RD9FSE020	2" LCR Direct Mount, White	65W	2700K-6500K	120-277V	800	10	080083259144	2405806
LCR408RD9FSE020	4" LCR Direct Mount, White	65W	2700K-6500K	120-277V	800	10.7	080083261505	2405430
LCR412RD9FSE020	4" LCR Direct Mount, White	75W	2700K-6500K	120-277V	1200	14.5	080083261567	2405436
LCR615RD9FSE020	6" LCR Direct Mount, White	75W	2700K-6500K	120-277V	1500	17.7	080083261628	2405442
LCR621RD9FSE020	6" LCR Direct Mount, White	150W, 2-26W CFL	2700K-6500K	120-277V	2100	23	080083261680	2405603
LCR630RD9FSE010	6" LCR Direct Mount, White	150W, 2-26W CFL	2700K-6500K	120-277V	3000	32.4	080083261741	2405609

Accessories (optional)

Catalog Number	Description	UPC
LCR6TRMSC	6" Accessory Skin, Specular	080083890361

HALO RECESSED LED TRIMS

Maximum energy savings with easy installation!

- Compatible with most recessed housings and sizes
- Suitable for new construction and remodel
- Replaces traditional incandescent lighting

Quick and Easy Installation



HALO RECESSED LED TRIM Product Selection Guide



		DOWNLIGHTS			ADJUSTABLES	
		HLBT	LT	RL & RL Night Light	LA	RA
FEATURES / PERFORMANCE	LED Trim Type	Downlights	Downlights	Downlights	Gimbal Adjustables (35° Tilt/360° Rotation)	Gimbal Adjustables (35° Tilt/360° Rotation)
	Size & Shape	4" & 6" Round	4", 5"/6" Round	3", 4", 5"/6" Round	4", 5"/6" Round	3", 4", 5"/6" Round
	Trim & Lens	Smooth w/ Flat Lens	Baffle or Smooth w/ Flat Lens	Baffle w/ Curved Lens (NL has Transparent Trim)	Baffle w/ Flat Lens	Baffle w/ Flat Lens
	Max Lumens (By size @ 3000K)	705, 965	570, 645, 785	610, 900, 1,200 (Lumen Select, Dedicated) (NL: 775, 1065)	610, 635	500 (3"), 600/900 (4" & 5"/6")
	Colour Temperatures (CCT)	5 CCT 27/30/35/40/5000K	5 CCT 27/30/35/40/5000K Dedicated: 3000K	5 CCT w/ D2W D2W/27/30/35/40/5000K (NL: 2000K)	Dedicated 3000K	5 CCT w/ D2W D2W/27/30/35/40/5000K
CONTROL	Dimming Phase Cut (LE/TE)	10%	10%	5% ¹	10%	5%
	Estimated Life Hours	50,000	50,000	70,000 (NL: 50,000)	35,000	50,000
	Input Voltage	120V	120V	120V, 120-277V	120V	120V
HARDWARE	Decorative Overlays ²	✓	✓ (Baffle Overlays for Baffle LT/LTEs)	✓ Smooth & Baffle Overlays for Standard RLs)		

¹ Available in Smart Wi-Fi® Connected by WiZ Pro versions.

² Matte Black, Tuscan Bronze, Satin Nickel, Paintable Matte White.

HALO RECESSED LED TRIMS

LT Recessed Baffle or Smooth Splay

LED TRIMS - 4" & 5"/6"

- The LT LED trims offer a cost-saving alternative to the RL Series
- Dead-front plastic fixture with either baffle or smooth splay trims and smooth flat lens
- **LT** - 5 Colour Field-Selectable in 27/30/35/40/5000K; **LT/LTE** - Dedicated in 3000K
- Includes LED Trim, E26 medium socket adapter, and mounting hardware (4" - friction blades; 5"/6" - torsion springs - only fits housings with spring receivers)
- 10% Dimming (Phase Cut LE/TE), 35,000 hrs, 90+ CRI



Selectable 5-CCT

Catalog Number	Description	Replaces	CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
LT4069FS1EWHR	4" Baffle Trim, White	60W	2700K-5000K	120V	680	7W	080083283965	2508121
LT56079FS1EWHR	5"/6" Baffle Trim, White	60W	2700K-5000K	120V	805	7W	080083284047	2508241
LTT4069FSMBSS	4" Retrofit Baffle-Trim, Black	60W	2700K-5000K	120V	685	8W	080083309481	4437369
LTT5607FSMBSS	6" Retrofit Baffle-Trim, Black	60W	2700K-5000K	120V	750	9W	080083309504	4437372

RL Recessed Baffle

LED TRIMS - 3", 4", & 5"/6"

- Delivers long life, exceptional performance, selectable lumens, and installs into almost any recessed housing
- Die-cast aluminum baffle trim and curved lens reduces glare and provides a traditional downlight appearance
- 6-Position Switch: 5 Colour Field-Selectable (27/30/35/40/5000K) + Dim-to-Warm (3000K dims to 1800K)
- Includes LED Trim, E26 medium socket adapter, and mounting hardware (3" & 4" - friction blades and 5"/6" - torsion springs & friction blades)
- 5% Dimming (Phase Cut LE/TE), 70,000 hrs, 90+ CRI



Catalog Number	Description	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
RL4LS9FSD2W1EWH-C	4" Baffle Trim	60-70W	2700K-5000K+D2W	120V	600/900 (Lumen Select)	7/11	080083259021	2402941
RL56069FSD2W1EWH-C	5"/6" Baffle Trim	60W	2700K-5000K+D2W	120V	700	8	080083259069	2402950
RL56LS9FSD2W1EWH-C	5"/6" Baffle Trim	70-75W	2700K-5000K+D2W	120V	900/1,200 (Lumen Select)	8.5/14	080083259083	2402953

H Series Housings

The industry standard recessed housing for commercial and residential applications.

- Ideal for commercial and residential applications
- Compatible with recessed LED trims.
- For installation in insulated contact (IC) and non-IC rated ceilings.




LED Housings

Catalog Number	Description	Connection	Lamp Source	Voltage	UPC
H245ICAT	4" LED Ultra-Shallow New Construction (No Socket)	LED Quick Connect	LED Modules	120-277V	080083770717

Accessories


Catalog Number	Description	Finish	Lamp Source	UPC
H347	Stepdown Transformer from 347V to 120V, 75VA	Accessory	Accessory	662400151289



HALO is now available with WiZ and Matter!

Illuminate spaces with the perfect lighting. Set the mood with 16 million colours + white tuning using the WiZ App or preferred compatible voice assistant.

Introducing Matter, which allows you to control your WiZ fixtures from more than one smart platform, providing ultimate flexibility and an Open Platform.



RL Smart Wi-Fi Dual Zone Direct Mount

DUAL ZONE CANLESS DOWNLIGHTS - 4" & 6"

- Round 4" & 6" Dual Zone Smart Wi-Fi® Canless LED Downlight
- Canless mounting for remodel or new construction installations
- White tuning (2200K - 6500K) + 16 million colours
- Wireless dimming to 5% (120V input) Set schedules, scenes, static/dynamic lighting modes rhythms, music sync all via the WiZ App
- SpaceSense™ technology that turns your lights into motion sensors, so they turn on with movement



Catalog Number	Description	Finish	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
RLWZDZC4	4" Smart Wi-Fi Canless Downlight	White	Full Colour (RGB) & Tunable White (2200K-6500K)	120V	730	9.1W	080083296897	3892085
RLWZDZC6	6" Smart Wi-Fi Canless Downlight	White	Full Colour (RGB) & Tunable White (2200K-6500K)	120V	985	10.4W	080083297115	3892086

HLB Smart Wi-Fi Slim

CANLESS LED DOWNLIGHTS (Connected by WiZ Pro) - 4" & 6"

- Set up with the WiZ app to wirelessly control lighting via WiZ app
- Fixtures provide 16 million colours and tunable white light from 2200-6500K
- Dead-front plastic frame and smooth lens
- Includes LED downlight and remote driver/junction box with mounting bar
- Wi-Fi® Control & Dimming to 5% via WiZ app, 50,000 hrs, 90+ CRI



Catalog Number	Description	Finish	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
HLB4069WZRGBWMWR-C	4" Smart Slim Canless Downlight (WiZ Pro)	White	Full Colour & Tunable White (2200-6500K)	120V	600	9	080083256563	2408244
HLB6099WZRGBWMWR-C	6" Smart Slim Canless Downlight (WiZ Pro)	White	Full Colour & Tunable White (2200-6500K)	120V	974	11.2	080083256549	2408245

RL Smart Wi-Fi Recessed Baffle

LED TRIMS (Connected by WiZ Pro) - 4" & 5"/6"

- Set up with the WiZ app to wirelessly control lighting via WiZ app
- Fixtures provide 16 million colours and tunable white light from 2200-6500K
- Die-cast aluminum baffle trim reduces glare
- Includes LED Trim, E26 medium socket adapter, and mounting hardware
(4" - friction blades and 5"/6" - torsion springs & friction blades)
- Wi-Fi® Control & Dimming to 5% via WiZ app, 50,000 hrs, 90+ CRI



WIZ
PRO



Catalog Number	Description	Finish	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
RL4069WZRGBWWHR-C	4" Smart Baffle LED Trim (WiZ Pro)	White	Full Colour & Tunable White (2200-6500K)	120V	615	8	080083256525	3891057
RL56069WZRGBWWHR-C	5"/6" Smart Slim Canless Downlight (WiZ Pro)	White	Full Colour & Tunable White (2200-6500K)	120V	690	8	080083256501	3891055



works with **Hey Google**

works with **alexa**

works with **Siri Shortcuts**



Works with **IFTTT**

Works with **SmartThings**

Just say "Hey..."

Need to illuminate the kitchen while you're carrying in groceries but don't have a free hand? Use your smart speaker to turn on the lights with your voice.

HC Downlight Series

HALO COMMERCIAL DOWNLIGHTS - 4" & 6"

- 4" & 6" aperture new construction/remodel downlights
- Retrofit downlighting kit installs from below ceiling for LED upgrades
- 5 Colour Field-Selectable in 27/30/35/40/5000K; 80 or 90CRI
- 2 light engines; Lumens: 1,000, 1,500, 2,000 or 3,000, 4,000
- Distributions: Precision-formed reflectors in Narrow, Medium and Wide
- Universal voltage, 0-10V dimming down to 1%
- L70 at 60,000 hours



Housing

Catalog Number	Description	Voltage	Lumens	Watts	UPC	Energy Star ID
HC410D010	4" Housing, Round, 0-10V	120-277V	1000	10.1W	080083860586	3943323
HC415D010	4" Housing, Round, 0-10V	120-277V	1500	14.5W	080083860609	3943324
HC420D010	4" Housing, Round, 0-10V	120-277V	2000	20.9W	080083860623	3943144
HC430D010	4" Housing, Round, 0-10V	120-277V	3000	28.6W	080083860654	3943145
HC610D010	6" Housing, Round, 0-10V	120-277V	1000	10W	080083883646	3984079
HC615D010	6" Housing, Round, 0-10V	120-277V	1500	14.5W	080083883660	3984080
HC620D010	6" Housing, Round, 0-10V	120-277V	2000	20.9W	080083883684	3984081

Power Module

Catalog Number	Description	Replaces	CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
HM40525830	4" LED Module	150W INC, 2-26W CFL	3000K	120-277V	500-2500	6/10/15/21/28W	080083213924	3943144
HM40525835	4" LED Module	150W INC, 2-26W CFL	3500K	120-277V	500-2500	6/10/15/21/28W	080083213948	3943144
HM40525840	4" LED Module	150W INC, 2-26W CFL	4000K	120-277V	500-2500	6/10/15/21/28W	080083213962	3943144
HM40525935	4" LED Module	150W INC, 2-26W CFL	3500K	120-277V	500-2500	6/10/15/21/28W	080083214044	3943324
HM60525830	6" LED Module	150W INC, 2-26W CFL	3000K	120-277V	500-2500	6/10/15/21/28W	080083214648	3994162
HM60525835	6" LED Module	150W INC, 2-26W CFL	3500K	120-277V	500-2500	6/10/15/21/28W	080083214662	3994162
HM60525840	6" LED Module	150W INC, 2-26W CFL	4000K	120-277V	500-2500	6/10/15/21/28W	080083214686	3984081

Trim

Catalog Number	Description	UPC
41MDC	4" Trim Conical Reflector, Medium 60° Beam Angle, Specular Clear, Polished Flange	080083850167
41MDCWF	4" Trim Conical Reflector, Medium 60° Beam Angle, Specular Clear, White Flange	080083850228
41MDH	4" Trim Conical Reflector, Medium 60° Beam Angle, Semi-Specular Clear, Polished Flange	080083850181
41MDHWF	4" Trim Conical Reflector, Medium 60° Beam Angle, Semi-Specular Clear, White Flange	080083850242
41MDW	4" Trim Conical Reflector, Medium 60° Beam Angle, White, White Flange	080083850204
41WDC	4" Trim Conical Reflector, Wide 75° Beam Angle, Specular Clear, Polished Flange	080083850266
41WDH	4" Trim Conical Reflector, Wide 75° Beam Angle, Haze Semi-Specular, Polished Flange	080083850280
61MDC	6" Trim Conical Reflector, Medium 60° Beam Angle, Specular Clear, Polished Flange	080083850969
61MDCWF	6" Trim Conical Reflector, Medium 60° Beam Angle, Specular Clear, White Flange	080083851027
61MDH	6" Trim Conical Reflector, Medium 60° Beam Angle, Semi-Specular Clear, Polished Flange	080083850983
61MDHWF	6" Trim Conical Reflector, Medium 60° Beam Angle, Semi-Specular Clear, White Flange	080083851041
61MDW	6" Trim Conical Reflector, Medium 60° Beam Angle, White, White Flange	080083851003
61WDC	6" Trim Conical Reflector, Wide 65° Beam Angle, Specular Clear, Polished Flange	080083851065
61WDH	6" Trim Conical Reflector, Wide 65° Beam Angle, Semi-Specular Clear, Polished Flange	080083851089

HCD468 Pro Direct Mount Downlight System

HALO COMMERCIAL DOWNLIGHTS - 4", 6" & 8"

- 4", 6", and 8" install-from-below retrofit/remodel/new construction downlighting
- All LED fixture kits fit any size, shape, or beam distribution of HCD reflector
- 5-colour Field-SeleCCTable or dedicated: 27/30/35/40/5000K CCT; 90 CRI
- Selectable or fixed lumens: Options from 500 to 5,000 lms (nominal)
- 0-10V dimming down to 1% (dim-to-off with WaveLinX)
- L80 at 60,000 hours (80% lumen maintenance at 60,000 hours)



Selectable 5-CCT

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
HCDJBS10CSD	Fixture Kit	150W INC, 2-26W CFL	2700K-5000K	120-277V	500-1,000	6/10/13	080083297962	3554154
HCDJBS1525CSD	Fixture Kit	150W INC, 2-26W CFL	2700K-5000K	120-227V	1,500-2,500	16/21/26	080083297979	3554155
HCDJBS3040CSD	Fixture Kit	250W INC, 4-26W CFL	2700K-5000K	120-277V	3,000-5,000	31/36/41	080083297986	3554156

Accessories

Catalog Number	Description	UPC
HCD41TRC	4" Reflector Round Wide (Shallow), Specular Clear	080083279470
HCD41TRMW	4" Reflector Round Wide (Shallow), Matte White	080083279517
HCD4TRC	4" Reflector Round Medium, Specular Clear	080083278039
HCD4TRMW	4" Reflector Round Medium, Matte White	080083278077
HCD4TSQC	4" Reflector Square Medium, Specular Clear	080083278275
HCD4TSQMW	4" Reflector Square Medium, Matte White	080083278312
HCD61TRC	6" Reflector Round Wide (Shallow), Specular Clear	080083279593
HCD61TRMW	6" Reflector Round Wide (Shallow), Matte White	080083279630
HCD6TRC	6" Reflector Round Medium, Specular Clear	080083278510
HCD6TRMW	6" Reflector Round Medium, Matte White	080083278558
HCD81TRC	8" Reflector Round Wide (Shallow), Specular Clear	080083277674
HCD81TRMW	8" Reflector Round Wide (Shallow), Matte White	080083279814
HCD8TRC	8" Reflector Round Medium, Specular Clear	080083278992
HCD8TRMW	8" Reflector Round Medium, Matte White	080083279036
HCD41TRLWW	4" Round Wide Lensed Wall Wash Kit	080083280667
HCD4TRLWW	4" Round Medium Lensed Wall Wash Kit	080083280544
HCD4TSQLWW	4" Square Medium Lensed Wall Wash Kit	080083280568
HCD61TRLWW	6" Round Wide Lensed Wall Wash Kit	080083280681
HCD6TRLWW	6" Round Medium Lensed Wall Wash Kit	080083280582
HCD81TRLWW	8" Round Wide Lensed Wall Wash Kit	080083280704
HCD8TRLWW	8" Round Medium Lensed Wall Wash Kit	080083280629




HCD4TRC

HCD41TRC



HCD Round Wall Wash Kit



HCD Round Wall Wash Kit in Reflector