

METALUX STRIPS LIGHTS

SLSTP Series

STRIP LIGHT

- LED strip light with decorative end caps and toolless lens removal
- Suitable for either single or continuous row application
- Auto-Sensing 120-347V (NUV) driver standard on selectable models
- 3 Colour Field-Selectable in 35/40/5000K and dedicated in 4000K
- Field-Selectable lumens 2,400 - 11,200 or dedicated up to 9300
- Impact resistant polycarbonate lens reduces maintenance



Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
4SLSTP4040DD-UNV	4' Single Lens	2-T8 32W, 1-T5HO 54W	4000K (Dedicated)	120-277V	5,200 (Dedicated)	43	080083705825	PXZQGN9C
4SLSTPSLC-NUV	4' Single Lens	2-T8 32W, 1-T5HO 54W	3500K-5000K	120-347V	2,400-6,000	18/31/48W	080083305070	S-54WT1B
8SLSTPSLC-NUV	8' Single Lens	4-T8 32W, 2-T12 75W	3500K-5000K	120-347V	4500-11000	32/62/84W	080083305087	S-B8FSB7

Sensor Kits

Catalog Number	Description	PIR Sensor	UPC
SLSTP MS00 KIT	SLSTP Field Installable Sensor KIT	100%/50% / OFF	080083254200
SLSTP MS25 KIT	SLSTP Field Installable Sensor KIT	100%/50% / Low (~30%)	080083254224

Accessories (Optional)

Catalog Number	Description	UPC
WG-SLSTP-4	4' Wireguard	080083296330

ST Series

STRIP LIGHT

- Full-length LED strip light ideal for replacing fluorescent strips
- Superior performance with lumens up to 9,300 and 129 lumens per watt
- Continuous row mount aligner included to add-on length as needed
- Low voltage 0-10V dimming to 10%



Catalog Number	Description	Replaces	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
4ST1L2040R	4' Single Lens, Non-Dimming	1-T8 32W	4000K	120-277V	4,800	41	080083838189	2382010
4ST2L4040R	4' Dual Lens, Non-Dimming	2-T8 32W, 1-T5HO 54W	4000K	120-277V	4200	40	080083838196	N/A
8ST2L8040R	8' Dual Lens, Non-Dimming	4-T8 32W, 2-T12 75W	4000K	120-277V	8867	78	080083838202	2382033

Accessories

Catalog Number	Description	UPC
WG/SSF-4FT-B	4' Wireguard for Use with ST Series	662400106647

METALUX STRIP LIGHTS | WRAPS

SNX Series STRIP LIGHT

- Contemporary single frosted radial lens LED strip light
- Replaces two or four lamp fluorescents up to 150W
- 3 Colour Field-Selectable in 35/40/5000K and dedicated in 4000K
- 3 Field-Selectable lumens: Low, Medium or High settings
- Single or continuous row via surface or suspended mount



Rapid Response



Selectable CCT & Lumens

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
4SNX-SL3-LW-UNV-CC83-CD1-U	4' Single Lens	2-T8 32W, 1-T5HO 54W	3500K-5000K	120-277V	2,000-6,100	17-51	080083265107	S-9ZYMUK
8TSNX-SL3-LW-UNV-CC83-CD2-U	8' Single Lens	4-T8 32W, 2-T12 75W	3500K-5000K	120-277V	4,100-12,000	34-101	080083265114	S-Q7H6AT

Accessories

Catalog Number	Description	UPC
WG-SNX/SN-4FT-B	4' Wiregaurd for Use with SNX/SN Series	080083265268

WP Series WRAP

- Compact LED wrap light delivers value and energy savings
- Perfect retrofit solution for replacing single or 2-lamp fluorescent wraparounds
- Low-profile, highly versatile design; Post-painted die-formed channel
- Prismatic lens ensures even, glare-free light distribution



Catalog Number	Description	Replaces	CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
4WP3040R	4' Utility Wrap	2-T8 32W	4000K	120-277V	4010	34	080083847167	2326235

Achieva™ Surface Selectable WRAP

- Ideal for replacing up to four lamp and low-bay linear fluorescents
- 3 Colour Field-Selectable in 35/40/5000K, Field-Selectable lumens: 2,250 - 12,500
- Designed for single or continuous row mount
- Suitable for ceiling, wall, or suspension mounting



Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
4AWWS-L3C3-NUV	4' Wide Modern Wrap, Dimming	2-T8 32W	3500K-5000K	120-347V	4,500-6,500	32/40/50	080083289974	S-DFLKJS

NWS Series

WRAP

- Ideal for replacing two or three lamp fluorescents up to 96W
- 3 Colour Field-Selectable in 35/40/5000K
- Field-Selectable lumens: 2,000 - 5,272
- Surface (wall or ceiling) mount via junction box or direct to surface
- UNV 0-10V dimming to 10%



Catalog Number	Description	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
4NW35C3R	4' Wrap, Dimming	2-T8 32W	3000K-4000K	120V	3500	35	080083257447	2398236
4NWS3C3-NUV	4' Wrap, Dimming	2-T8 32W	3500K-5000K	120-347V	3,300-4,800 (Selectable)	28/34/42	080083257546	S-YJTA0N

