
Project		**Catalog #**		**Type**	
Prepared by		**Notes**		**Date**	



Connected by

Metalux WiZ PRO

WiZ 1x4 MMS LED Panel

Full color & tunable white LED 1x4 Backlit Panel with WiZ Pro smart control

Typical Applications

Entertainment Room, Theatre Room, Kitchen, Garage, Basement, Lounge, Cafes, Salons, Boutiques, Education, Offices

Interactive Menu

- Order Information page 2
- Product Specifications page 2
- Product Warranty

Top Product Features

- Delivers 4000 lumens at 50,000 life-hours using long life LEDs
- Versatile mounting: Surface (no surface mount kit needed), recessed, suspended (with kit) or wall mount
- Smart Wi-Fi downlight with white tuning (2700K - 6500K) + 16 million of colors + wireless dimming via the WiZ App
- Configure and control lighting quickly over Wi-Fi with the WiZ App
- Professional Installers can use the WiZ Pro Setup App to manage multiple projects, pair over Bluetooth, and access advanced features in the WiZ Pro Dashboard
- Create Schedules, Group Fixtures together, Control with your voice or App from anywhere
- Matter certified to work with Google Home and Amazon Alexa
- Acrylic micro-optics provide uniform illumination across the entire lens
- Contemporary white trim provides a clean, non-descript appearance
- 120VAC input, Dims to 5%


Product Certification

CERTIFIED · RoHS COMPLIANT · damp location · matter

Product Integrations

Connected by WiZ PRO · WiZ · WiZ PRO · works with Hey Google · works with alexa · works with Siri Shortcuts · Works with IFTTT · Works with SmartThings

Dimensions



Ordering Information/Performance


Catalog Number	Voltage (V)	Wattage (W)	Delivered lumens	Efficacy (lumen/watt)	CCT (K)	CRI	Control
14MMS-WZ-RGBW	120V	45W	4000	>80	2700K-6500K	>80	WiZ App

Accessories

Suspension Kit (Sold Separately)

Catalog	UPC	Description
FPSUS24	080083258895	Y-hanger suspension cable kit carabiner, SO cord, connectors and round 4" J-box cover plate
Mounting height from ceiling **Min.**=7-1/4" [184mm] **Max**.=27" [286mm]		

FPSUS24



Shipping Data

Model Number	14MMS-WZ-RGBW
UPC	080083307371
Weight	8.73 lbs
Units per Pallet	44
Gross weight per Pallet	418.6 lbs

Accessory WiZ Controls (sold separately)

Catalog number	Module	Type	Power	Finish	Packaging
CWR-TW-SCENE-WH	Controller, WiZ Pro connected remote	ON/OFF/DIM, Tunable White + Scenes	Battery (4 AAA by others)	White	Plastic-free & fully recyclable
CWW-TW-SCENE-WH	Controller, Wall Mount, WiZ Pro connected	ON/OFF/DIM, Tunable White + Scenes	Mains Power	White	Plastic-free & fully recyclable

Product Specifications

Construction
- Rigid cold rolled steel housing
- No holes in the housing prevents dust, debris or bug intrusion
- Equipped with steel bracket for easy surface or recessed mounting

Mounting
- Surface mount bracket included for seamless installation to wall or ceiling
- Safety fasteners included to allow hands free wiring and safe installation
- Integral grid clips secure fixture to the T-Grid

Wireless System
- MMS products can be set up using either the WiZ App or WiZ PRO Setup App.
- Compatible with all WiZ-enabled products.
- Max Devices/Account: 200

WiZ App Setup & Control
- For standard applications, use the WiZ app and claim over Bluetooth/Wi-Fi®
- These products can be claimed and controlled directly within the WiZ app
- The WiZ app allows for wireless control of lighting from home or away via Wi-Fi®
- Wirelessly control on/off, white tuning (incandescent 2700K to true daylight 6500K), full color (16-million options), and dimming (100% to 5%) via the WiZ app
- The WiZ app and WiZ Pro Setup app are Android or Apple iOS compatible with most smartphones and tablets
- Setup homes, rooms, groups, scenes, schedules, rhtyhms, music sync, and SpaceSense™ motion detection to automate your smart home lighting
- Integrates with Matter, Amazon Alexa, Hey Google, Apple HomeKit, Siri Shortcuts, IFTTT, and SmartThings
- **Learn more at** wizconnected.com

WiZ PRO Control
- Metalux with WiZ PRO also has claiming and account management features designed for the pro installer
- Pros can use the WiZ Pro Setup App to claim products quickly using pre-Wi-Fi® commissioning and manage multiple jobsites including transferring account ownership
- The WiZ Pro Dashboard gives professional installers:
  - A clear overview to monitor lighting over a mapped location
  - Full range of configurations and remote control
  - Comprehensive reporting on device status & energy usage
- **Learn more about WiZ Pro features and functionality at** pro.wizconnected.com

Controls & Dimming
- Standard 120V, FCC Class B, driver with dimming capability down to 5%
- Wireless flicker-free dimming from 100%-5% via the WiZ App
- Do not connect to line voltage dimmer
- Fixtures can be controlled with standard ON/OFF switches. (Do not use with any dimmers)
- Fixtures can be controlled using WiZ Click Feature a secondary option using your main light switch:
  - Toggle the switch on once to activate Favorite Mode 1
  - Toggle twice for Favorite Mode 2
- Wireless flicker-free dimming from 100%-5% via the WiZ App
- Only compatible with other WiZ-enabled products (Not compatible with HALO Home or any other controls)

Power Cycle Behavior
- Unpaired WiZ fixtures will operate like a standard fixture until claimed into an account
- **IMPORTANT:** If fixtures are hardwired with constant power or a user plans to always control them wirelessly instead of with a standard ON/OFF switch, use the Power Outage Recovery setting to prevent devices from turning back ON after a power outage

Electrical
- MMS projected lumen maintenance based on TM21 testing standards is >L82@60,000 hours
- Driver rated for FCC part 15 Class B for use in residential or commercial applications
- Junction box constructed of code gauge galvanized steel with access plate
- Multiple 7/8" KO's provided, suitable for up to 12AWG wiring
- LEDs are 80 CRI (minimum)

Optical Shielding
- Acrylic micro-optics covers LEDs and control distribution
- Smooth, frosted lens delivers uniform illumination across the entire lens
- Durable lens with surface texture to minimize scratch and impact damage

Certifications
- cULus listed for 25C ambient environments, indoor applications
- IC rated for direct insulation contact
- UL damp location listed
- IESNA LM-79 and LM-80 standards compliant
- Qualifies as State of California Title 24 high efficiency luminaire
- FCC part 15 class B (residential) compliant
- Suitable for use in clothes closets when installed in accordance with the NEC 410.16 spacing requirements
- Contains no mercury or lead and RoHS compliant
- Lumen maintenance projections in accordance with IES LM-80-08 and TM-21-11

Warranty
- Five year limited standard warranty

Cooper Lighting Solutions
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.cooperlighting.com

© 2025 Cooper Lighting Solutions
All Rights Reserved.

Specifications and dimensions subject to change without notice.