

Shaper

DESCRIPTION

605-W and 605-WP Luminous Wall Sconce features 6 standard finishes, 3 decorative trim bar options and ADA compliant.

- Interior Wall Luminous Vanity Luminaire
- Painted solid aluminum w/ extruded white acrylic panel
- Universal circular strap for a standard 4" J-box or plaster ring
- UL and CUL approved for interior and damp locations

Catalog #	Type
Project	
Comments	Date
Prepared by	

SPECIFICATION FEATURES

Material

Painted solid aluminum with a 1/8" matte white extruded acrylic panel and solid aluminum end caps closed end.

Finishes

ALP (Aluminum Paint)
MW (Matte White)
MB (Matte Black)
GRM (Graphite Metallic)
DP (Dark Platinum)
BM (Bronze Metallic)
CC (Custom Color – Specify

For Custom Color contact factory for quotation.

LED

25" L3:2000 (nominal lumens at

max) 20W

37" L4:3000 (nominal lumens at max) 29W

49" L5:4000 (nominal lumens at max) 38W

Driver

Standard integral class 2 driver 38W max., 0-10V dimming. LED system coupled with electrical driver to deliver optimal performance. Electronic drivers are available for 120-277V applications. A 0-10V dimming control is standard on all models.

Installation

Supplied with a universal circle strap for a standard 4" J-box or round or octagonal plaster ring.

Horizontal or vertical mount. Shaper 605-W luminaires are designed for interior installations only. Shaper 605-WP are listed for wet location. Battery must be remote mounted in an interior location at a 5ft max distance.

Compliance

For W mounting, U.L. and C.U.L. approved for indoor and damp location. For WP mounting, U.L. and C.U.L. listed for wet location, ADA compliant, except with proud trim options.


Warranty

5 year limited warranty on LED components.



605-W Series 605-WP Series

DIMENSIONS



25"

- Lumen Output Source Lumens: L3:2000 nominal lumens at max
- Wattage: 20W
- Color Rendering: CRI 83+
- Correlated Color Temperature: 4000K, 3500K, 3000K, 2700K
- Rated Life of Lamp (hrs): 50,000
- Dimming: 0-10V

37"

- Lumen Output Source Lumens: L4:3000 nominal lumens at max
- Wattage: 29W
- Color Rendering: CRI 83+
- Correlated Color Temperature: 4000K, 3500K, 3000K, 2700K
- Rated Life of Lamp (hrs): 50,000
- Dimming: 0-10V

49"

- Lumen Output Source Lumens: L5:4000 nominal lumens at max
- Wattage: 38W
- Color Rendering: CRI 83+
- Correlated Color Temperature: 4000K, 3500K, 3000K, 2700K
- Rated Life of L amp
- Dimming: 0-10V

ORDERING INFORMATION

Sample Number: 605-37-W-L4/827-UNV-ALP-2VTB

Series	Size	Mounting Type	LED Lamp			LED Voltage	Finish	Options
			25"	37"	49"			
605 = Luminous Sconce	25 = 25" 37 = 37" 49 = 49"	W = Interior Wall WP = Exterior Wall	L3/827	L4/827	L5/827	UNV = (120-277V)	ALP=Aluminum Paint MW=Matte White MB =Matte Black DP = Dark Platinum GRM=Graphite Metallic BM=Bronze Metallic CC =Custom Color - Contact factory for quotation	2VTB=Two Vertical Trim Bars 2HTB=Two Horizontal Trim Bars 2VTB/2HTB=Two Vertical Trim Bars/Two Horizontal Trim Bars RBP =Remote Battery Pack PC = Perf Center
			L3/830	L4/830	L5/830			
			L3/835	L4/835	L5/835			
			L3/840	L4/840	L5/840			