

DESCRIPTION

The RF LED Surface Heads Series provides remote heads (no battery) manufactured in high impact, mar-resistant engineering grade thermoplastic. A highly polished reflector located behind the lamp provides abundant emergency light to the floor when connected to an emergency battery source. Several finishes and lamp styles are available.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

Electrical

LED Remote Heads

Lampholder/Mounting Plate

Construction


- Choose single, or double
- Adjustable 359° swivel
- White finish standard
- Mounts to standard 4" round junction box

Lamp Data


- High lumen output equal to 9W incandescent

Environmental Information


- WP versions below are weather proof and are UL wet location listed




RFLED401



RFLED402



RFLED401WP



RFLED402WP



ORDERING INFORMATION

Catalog No. Prefix	No. of Heads	Ship Wt.
RFLED401	1	2
RFLED402	2	4
RFLED401WP	1	2
RFLED402WP	2	4

RIVAL LED REMOTE HEADS

SURFACE MOUNT HEAD
LESS BATTERY
THERMO PLASTIC
LED LAMPS
EMERGENCY LIGHTING