



FIRE SAFE

HALO[®]

Fire Safe Fire Rated Housings

UL263 Listed for up to 2 hours



COOPER
Lighting Solutions



Product Features


- Available in 3-inch (H350FR2ICAT), 4-inch (H450FR2ICATD010), 5-inch (H550FR2ICATD010) and 6-inch (H750FR2ICATD010) new construction LED housings
- For use with LED integrated trims or modules
- No need to build additional boxes anymore
- Suitable for use in multi-family and mixed use applications requiring up to 2 hours of protection

**FIRE
RATED** 
**UP TO
2 HOURS**

HALO Fire Rated Housings can prevent the passage of flames and toxic gases for up to two hours in accordance to UL 263.

**No need to build
additional boxes
anymore!**


Save Time And Money



H350FR2ICAT

3-inch Fire Safe new construction housing, 2-hour fire rated, 10W LED, ICAT

Material Number	UPC	Compatible LED modules
13393480	080083130481	RL3, RA3




H450FR2ICATD010

4-inch Fire Safe new construction housing, 2-hour fire rated, 15W LED, ICAT, 120V-277V, Phase & 0-10V Dimming

120V - 277V; compatible with both phase-cut dimming and 0-10V dimming retrofit modules

Material Number	UPC	Compatible LED modules
13393481	080083130504	BLD4, LT4, LA4, ML4, RA4, RL4, RLD4, RSQ4, SLD4, SMD4




H550FR2ICATD010

5-inch Fire Safe new construction housing, 2-hour fire rated, 20W LED, ICAT, 120V-277V, Phase & 0-10V Dimming

120V - 277V; compatible with both phase-cut dimming and 0-10V dimming retrofit modules

Material Number	UPC	Compatible LED modules
13393482	080083130528	LT56, LA56, ML56, RL56, RA56, RSQ5, SLD6, SMD6



H750FR2ICATD010

6-inch Fire Safe new construction housing, 2-hour fire rated, 20W LED, ICAT, 120V-277V, Phase & 0-10V Dimming

Material Number	UPC	Compatible LED modules
13565550	080083130542	BLD6, LT56, LA56, ML56, RL56, RA56, RSQ6, SLD6, SMD6