

DESCRIPTION

Stadium Pro brings the dynamics of the game to life with consistent, precisely-delivered light that meets the stringent demands of international HDTV broadcasting, digital photography and slow-motion recording. Controlled intensity and uniformity removes the need for supplemental sports lighting while eliminating shadows, improving the appearance of moving objects and the ease with which camera operators can follow the action of the game. Color temperature tuning allows you to adjust for different events or more closely match the outdoor lighting conditions if desired. Advanced controls allow the creation of dynamic scenes and fan experience effects. Stadium Pro is the ultimate light for versatility and the best player, fan and broadcast experience.

SPECIFICATION FEATURES

Construction

Solid-state design means no moving parts and nothing to wear out or replace, providing maintenance-free operation for hundreds of thousands of hours.

Optics

Custom-engineered optics direct light precisely where needed while minimizing glare.

Precision Aiming

Integrated laser mount provides ability to precisely aim the fixture.

Customization

Control options available to provide operational flexibility, create dynamic lighting scenes and control color temperature tuning.

Catalog #

Type

Project

Comments

Date


Prepared by



STADIUM PRO

SPORTS LIGHTING

DIMENSIONS



CERTIFICATION DATA

IP66 Rated

EPA

Effective Projected Area (Sq. Ft.): 2.2

SHIPPING DATA

Approximate Net Weight:
55 lbs. (24.9 kgs.)

ORDERING INFORMATION

Sample Number: SD-1000-2-CT-BLK

Model	Wattage	Optics	CCT	Fixture Color
SD=Stadium	1000=1000	2B=NEMA2B 2=NEMA2 3=NEMA3 4=NEMA4 5=NEMA5	CT=Color Tuning	BLK=Black

ENERGY AND PERFORMANCE DATA

	Stadium Pro
Lumen Output	115,000
System Wattage	1000
Input Voltage	240VAC, 277VAC, 347VAC, 480VAC
L70 Hours	>225,000
Color Temperature Tuning Range	4000K - 6500K
Operating Temperature Range	-40°C to 50°C
Surge (Common Mode / Differential Mode)	1560VAC/Internal MOV protection 460J 10 KA Surge
NEMA Rating	NEMA 4X
Effective Projected Area (EPA)	2.2 (sq. ft.)
Approximate Weight	55 lbs. (24.9 kgs.)

NOTES:

1. The specifications listed were obtained under optimal testing conditions. Changes in options, features and conditions may result in slightly different performance specifications among fixtures.
2. Weight may vary depending on mounting bracket selection.
3. Fixtures are wired for DMX control.

Discontinued
05-07-19