



FEATURES

- Heavy-duty, 20-gauge steel housing
- White powder coat finish
- Dual voltage input 120/277 VAC, 60Hz
- Available in both 6 volt and 12 volt models
- Powerful incandescent lamping
- Dependable sealed lead calcium batteries

ENERGY DATA

See Specification Sheet for Energy Data

Compliances may not apply to all product configurations. Please consult the product spec sheet for compliance details.

COMPLIANCES: UL924 Listed; Damp Location, NYC Code Compliant

REL - STEEL EMERGENCY LIGHT

ORDERING INFORMATION

SAMPLE NUMBER: 6REL18


Voltage	Family	Capacity
6=6 Volt	REL =Rival Emergency Light	18=18 Watts (with (2) 9 Watt Heads) 27=27 Watts (with (2) 12 Watt Heads)

ORDERING INFORMATION

SAMPLE NUMBER: 12REL503

Voltage	Family	Capacity	Number of Heads
12=12 Volt	REL =Rival Emergency Light	50=50 Watts	3=(3) 12 Watt Heads

6REL18 / 6REL27



12REL50-3

