

Lumark

WP Wall Pack LED

Features and Benefits

Traditional style. Modern efficiency.

The Lumark WP Wall Pack LED wall luminaire provides traditional architectural style with high performance energy efficient illumination across three housing sizes. Rugged die-cast aluminum construction, stainless steel hardware along with a sealed and gasketed optical compartment make the luminaire virtually impenetrable to contaminants. IP66 Rated. UL/cUL wet location listed. Replaces up to 450W metal halide equivalent. The WP wall luminaire is ideal for pathway illumination, building entrances, vehicle ramps, schools, tunnels, stairways and loading docks.

PRODUCT FEATURES

- Durable die-cast aluminum construction and borosilicate refractive glass lens
- Removable door allows for easy installation
- Superior efficacy of up to 128 lumens per watt provides maximum energy efficiency
- Save up to 89% in energy and maintenance costs when replacing traditional HID sources

STOCK ORDERING INFORMATION

Catalog Number	HID Equivalent	Housing Size	Lumens	Input Watts	Efficacy (LPW)	UPC
WPSLED10	100W	Small	4,733	39	121	080083885664
WPMLED10	100W	Medium	4,700	39	121	080083885688
WPMLED15	150W	Medium	6,203	49	127	080083885701
WPMLED25	250W	Medium	10,227	81	126	080083885725
WPLLED15	150W	Large	6,075	49	124	080083885749
WPLLED25	250W	Large	10,198	81	126	080083885763
WPLLED45	450W	Large	15,523	121	128	080083885787



QUICK FACTS

- Replaces up to 100-450W equivalent HID
- 4,700 up to 15,500 lumens
- 89% lumen maintenance at 50,000 hours at 40°C
- Universal voltage (120-277V 50/60 Hz)
- Operates at -40°C to 40°C (-40°F to 104°F)
- Five-year warranty