

Project		Catalog #		Type	
Prepared by		Notes		Date	



Greengate

QuickConnect Cable

Cables are pre-terminated with industry standard RJ45 connectors

Typical Applications

Office • Education • Healthcare • Hospitality • Retail • Industrial • Manufacturing

Interactive Menu

- Order Information page 2
- Additional Resources page 2
- Connected Systems page 2
- Product Warranty

Product Certification



Top Product Features

- The QuickConnect cables, couplers and splitters connect the Room Controller or DLVP system and devices simplifying the Click & Go connection enabling automatic functionality upon power up
- Cables are preterminated with industry standard RJ45 connectors.
- Lengths up to 100 feet
- Available in plenum and non-plenum rated
- Automatically included as part of the Room Controller Quickkit

Order Information

SAMPLE ORDER NUMBER: **ATW-SW4-30HE-UNV-EL7W-L830**

additional text about ordering - if needed

Catalog Number

Catalog Number	Description
GGRC-COUPLER	RJ45 Coupler
GGRC-SPLITTER	RJ45 Splitter
GGRJ45-006-G	RJ45 cables 6 inches
GGRJ45-03-G	RJ45 cables 3 feet
GGRJ45-10-G	RJ45 cables 10 feet
GGRJ45-25-G	RJ45 cables 25 feet
GGRJ45-50-G	RJ45 cables 50 feet
GGRJ45-100-G	RJ45 cables 100 feet
GGRJ45-10P-G	RJ45 cables 10 feet plenum rated
GGRJ45-25P-G	RJ45 cables 25 feet plenum rated
GGRJ45-50P-G	RJ45 cables 50 feet plenum rated
GGRJ45-100P-G	RJ45 cables 100 feet plenum rated
Notes *The Room Controller QuickKit automatically includes recommended cable quantities and lengths based on the installed room type and number of devices.	

Product Specifications

Key Features

- QuickConnect cables are plugged into ports on the Room Controller or DLVP Power Distribution Module and low voltage devices creating a local room based network that works out-of-the-box providing a superior energy savings control sequence with intuitively engraved wallstations
- Low voltage devices are connected to the Room Controller or DLVP Power Distribution Module using provided QuickConnect cables

Mechanical

Size: 6" up to 100'

Environment:

- Temperature: 32°F to 104°F (0°C to 40°C)
- Relative Humidity: Less than 95%, non-condensing
- For indoor use only

Electrical

Voltage: 24 VDC supplied from Room Controller

Rating: Class 2, LPS

Standards/Ratings

- cULus Listed
- UL 508 Listed

Warranty

Consult website for warranty information

Control Systems

- Greengate
- DLVP