

A modern cafe interior featuring a series of long, rectangular wooden tables and black chairs with wooden legs. The ceiling is made of concrete and has several large, green, cylindrical track lighting fixtures mounted on it. The walls are made of red brick, and there are large windows on the left side. A bar area with a white brick backsplash and various bottles is visible in the background. The overall atmosphere is bright and contemporary.

HALO[®]


Stasis LED Track Luminaires



COOPER


Lighting Solutions

a Signify business



STASIS

Spaces that Inspire with Stasis



The right accent lighting can inspire awe among customers and patrons. With sleek simple lines, numerous beam widths and color temperatures, and all-encompassing light output levels, Stasis gives lighting designers the flexibility desired to create spaces that draw clout, foot traffic, sales, and good reviews.

The Collection

With sleek, simple geometric profiles and high-performance optics, and a full range of beam angles in 3 different sizes, Stasis gives lighting designers superior flexibility to create accent lighting on any layout.

L815SML Small



MB
Matte Black

P
White

L815MED Medium



MB
Matte Black

P
White

L815SQ Square



MB
Matte Black

P
White

All-metal housing + simple contours = no distraction

The simple, timeless, durable all-metal housing design of Stasis gives a premium look and feel to everyday spaces so that customers experience the space, not the lighting fixtures themselves.

Sleak Form Factor

Concealed heat sink keeps audiences' attention away from the fixture and on the object of interest.

Interchangeable Optics and Media Accommodation

Customers can order replacement optics if the application needs change. On the medium and small cylinders, Stasis accommodates up to 2 pieces of PAR30 and PAR20 media, respectively.



On/Off Switch

Aiming


Full aiming capability. The Stasis luminaire can pivot $\pm 90^\circ$ vertically and horizontally without adjusting track position.





Indentations every 15° for precise and repeatable tilt aiming.



Coffee Shop / Café

The Stasis Small is used in this urban-industrial café to create an inviting, casual environment for catching up with friends. Narrow floods provide focused light to tabletops, while floods provide general fill light to the café space. Wall Washes bring out the texture of the brick walls in this not-so-posh post-industrial gathering spot.




	L815SML05NF930MB - 500 lumen, narrow flood, 90 CRI, 3000K
	L815SML05SP930MB - 500 lumen, spot, 90 CRI, 3000K
	L815SML10WW930MB - 1000 lumen, wall wash, 90 CRI, 3000K
	L815SML10FL930MB - 1000 lumen, flood, 90 CRI, 3000K





Furniture Gallery


The Stasis Square makes upholstery of most sizes look plush and brings out the texture in wood grain. A customer can feel comfy looking at a sofa across the store without even sitting in it.




 L815SQ20FL930MB
- 2000 lumen, flood, 90 CRI, 3000K

 L815SQ10SP930MB
- 1000 lumen, spot, 90 CRI, 3000K

 L815SQ40FL930MB
- 4000 lumen, flood, 90 CRI, 3000K

 L815SQ20NF930MB
- 2000 lumen, narrow flood, 90 CRI, 3000K

 L815SQ20WW930MB
- 2000 lumen, wall wash, 90 CRI, 3000K




HUMAN
INTEREST
PAINTINGS
FROM THE
PRIVATE
COLLECTION

Human Interest is a collection of paintings from the private collection of the artist. The collection features a variety of subjects, including portraits, landscapes, and still lifes. The paintings are characterized by their vibrant colors and bold, expressive brushstrokes. The collection is a testament to the artist's skill and creativity, and it is a valuable addition to any art collection.

Art Gallery

Stasis creates impactful contours to store goods and artwork. In this art gallery, Stasis spots give life to some abstract sculptures. Whether highlighting a student's capstone project in a school or a motor boat in a showroom, the stark contrasts of shadows and light provided by Stasis invite patrons and customers to have a closer look.



L815MED20SP930MB
- 500 lumen, narrow spot, 90 CRI, 3000K



L815MED30SP930MB
- 500 lumen, spot, 90 CRI, 3000K



L815MED20NS930MB
- 1000 lumen, narrow spot, 90 CRI, 3000K



L815MED30NF930MB
- 3000 lumen, wall wash, 90 CRI, 3000K







L815MED30WW930MB
- 1000 lumen, narrow flood, 90 CRI, 3000K






Clothing Store

Stasis cylinders nail contrast on a variety of wares. A combination of Stasis smalls and mediums are used to highlight the various articles of clothing available. The intense, narrow spots bring three dimensionality with strong contrast lines to the shoes and suit displays, while narrow floods create a grazing effect to the coat racks.




	L815SML05NS930MB - 500 lumen, narrow spot, 90 CRI, 3000K
	L815SML05SP930MB - 500 lumen, spot, 90 CRI, 3000K
	L815SML10NS930MB - 1000 lumen, narrow spot, 90 CRI, 3000K


	L815MED30WW930MB - 3000 lumen, wall wash, 90 CRI, 3000K
	L815MED10NF930MB - 1000 lumen, narrow flood, 90 CRI, 3000K
	L815MED10SP930MB - 1000 lumen, flood, 90 CRI, 3000K



L815 Stasis Small



Adapter for Global
TEK / HTEK track



Ordering Information

Track

L=Halo Power Trac
L2G=Global TEK/HTEK®
LJ=Juno Track®

LL=Lightolier®
M=Monopoint

Size

815SML

Output

05=500 Lumens
10=1000 Lumens
18=1800 Lumens

Optic

NS=8 degrees
SP=15 degrees
NF=25 degrees

FL=45 degrees
WW=Wall Wash

CRI & CCT

927=2700K / 90 CRI
930=3000K / 90 CRI

935=3500K / 90 CRI
940=4000K / 90 CRI

Finish

MB=Matte Black
P=White

Voltage

Blank=120V
277=277V

Accessories

Media Holder

LM11520MB=Small Media Holder, Black
LM11520P=Small Media Holder, White
LM11520SL=Small Media Holder, Silver

815MA115SML=Small Media Adapter (includes white and black)

Media

815SMLSFL=Soft Focus Lens, Stasis Small
815SMLLSL=Linear Spread Lens, Stasis Small
815SMLPDL=Prismatic Diffuse Lens, Stasis Small
815SMLLHC=Hexcell Louver, Stasis Small

Snoot

LS115SMLMB=Small snoot, Black
LS115SMLP=Small snoot, White
LS115SMLSL=Small snoot, Silver

Bezel

LB115SMLMB=Small Bezel Accessory, Black
LB115SMLP=Small Bezel Accessory, White
LB115SMLSL=Small Bezel Accessory, Silver

Optics

815SMLFLOPK=Small Flood Optic Accessory
815SMLNFOPK=Small Narrow Flood Optic Accessory
815SMLNSOPK=Small Narrow Spot Optic Accessory
815SMLSPOPK=Small Spot Optic Accessory

Wall Wash Optic

(includes optic and wall wash bezel)

815SMLWWOPKMB=Small Wall Wash Optic Accessory, Black
815SMLWWOPKP=Small Wall Wash Optic Accessory, White
815SMLWWOPKSL=Small Wall Wash Optic Accessory, Silver



[View spec sheet](#)

REFER TO SPECIFICATION SHEETS FOR ALL TECHNICAL NOTES, EXCEPTIONS, AND THE LATEST INFORMATION.


Global® is a registered trademark of Nordic Aluminum.

Juno® T single circuit and 2-circuit track contact. Juno® is a registered trademark of Juno® Lighting.


Lightolier® Lyfespán 6000 single circuit and 2 circuit track contact. Lightolier® is a registered trademark of Philips Lighting.



L815 Stasis Medium



Adapter for Global
TEK / HTEK track



Ordering Information

Track

L=Halo Power Trac
L2G=Global TEK/HTEK®
LJ=Juno Track®

LL=Lightolier®
M=Monopoint

Size

815MED

Output

10=1000 Lumens
20=2000 Lumens
30=3000 Lumens

Optic

NS=8 degrees
SP=15 degrees
NF=25 degrees

FL=45 degrees
WF=60 degrees
WW=Wall Wash

CRI & CCT

927=2700K / 90 CRI
930=3000K / 90 CRI

935=3500K / 90 CRI
940=4000K / 90 CRI

Finish

MB=Matte Black
P=White

Voltage

Blank=120V
277=277V

Accessories

Media Holder

LM11530MB=Medium Media Holder, Black
LM11530P=Medium Media Holder, White
LM11530SL=Medium Media Holder, Silver

815MA115MED=Medium Media Adapter (includes white and black)

Media

815MEDSFL=Soft Focus Lens, Stasis Medium
815MEDLSL=Linear Spread Lens, Stasis Medium
815MEDPDL=Prismatic Diffuse Lens, Stasis Medium
815MEDLHC=Hex Cell Louver, Stasis Medium

Snoot

LS115MEDMB=Medium snoot, Black
LS115MEDP=Medium snoot, White
LS115MEDSL=Medium snoot, Silver

Bezel

LB115MEDMB=Medium Bezel Accessory, Black
LB115MEDP=Medium Bezel Accessory, White
LB115MEDSL=Medium Bezel Accessory, Silver

Optics

815MEDFLOPK=Medium Flood Optic Accessory
815MEDNFOPK=Medium Narrow Flood Optic Accessory
815MEDNSOPK=Medium Narrow Spot Optic Accessory
815MEDSOPK=Medium Spot Optic Accessory

Wall Wash Optic

(includes optic and wall wash bezel)

815MEDWWOPKMB=Medium Wall Wash Optic Accessory, Black
815MEDWWOPKP=Medium Wall Wash Optic Accessory, White
815MEDWWOPKSL=Medium Wall Wash Optic Accessory, Silver



[View spec sheet](#)

REFER TO SPECIFICATION SHEETS FOR ALL TECHNICAL NOTES, EXCEPTIONS, AND THE LATEST INFORMATION.


Global® is a registered trademark of Nordic Aluminum.

Juno® T single circuit and 2-circuit track contact. Juno® is a registered trademark of Juno® Lighting.


Lightolier® Lyfspan 6000 single circuit and 2 circuit track contact. Lightolier® is a registered trademark of Philips Lighting.



L815 Stasis Square



Adapter for Global
TEK / HTEK track



Ordering Information

Track

L=Halo Power Trac
L2G=Global TEK/HTEK®
LJ=Juno Track®

LL=Lightolier®
M=Monopoint

Size

815SQ

Output

10=1000 Lumens
20=2000 Lumens

30=3000 Lumens
40=4000 Lumens

Optic

SP=15 degrees
NF=25 degrees
FL=45 degrees

WF=60 degrees
WW=Wall Wash

CRI & CCT

927=2700K / 90 CRI
930=3000K / 90 CRI

935=3500K / 90 CRI
940=4000K / 90 CRI

Finish

MB=Matte Black
P=White

Voltage

Blank=120V
277=277V

Accessories

Back Cover

815LRGCVPKMB=Square back cover, Black
815LRGCVPKP=Square back cover, White
815LRGCVPKSL=Square back cover, Silver

Media

815SQFRL=Frosted Lens, Stasis Square
LB115HEXSQ=Square hex cell louver

Optics - 1000 & 2000 Lumen

815SQSP130PK=Square Spot Optic Accessory
815SQNF130PK=Square Narrow Flood Optic Accessory
815SQFL130PK=Square Flood Optic Accessory
815SQWF130PK=Square Wide Flood Optic Accessory
815SQWW130PK=Square Wall Wash Optic Accessory

Optics - 3000 & 4000 Lumen

815SQSP260PK=Square Spot Optic Accessory
815SQNF260PK=Square Narrow Flood Optic Accessory
815SQFL260PK=Square Flood Optic Accessory
815SQWF260PK=Square Wide Flood Optic Accessory
815SQWW260PK=Square Wall Wash Optic Accessory



[View spec sheet](#)

REFER TO SPECIFICATION SHEETS FOR ALL TECHNICAL NOTES, EXCEPTIONS, AND THE LATEST INFORMATION.

Global® is a registered trademark of Nordic Aluminum.

Juno® T single circuit and 2-circuit track contact. Juno® is a registered trademark of Juno® Lighting.

Lightolier® Lyfespas 6000 single circuit and 2 circuit track contact. Lightolier® is a registered trademark of Philips Lighting.

Stasis Accessories & Halo Track Systems

REFER TO SPECIFICATION SHEETS FOR ALL TECHNICAL NOTES, EXCEPTIONS, AND THE LATEST INFORMATION.



Media Holders

For use with color filters and other media on the L815SML and L815MED. Hold standard PAR20 and PAR30 media for small and medium sizes respectively.



Snoot


For cutoff and for use with color filters and other media on the L815SML and L815MED.



Optics

Wide range of interchangeable optics available for the Stasis series.

8° (narrow spot) | 15° (spot) | 25° (narrow flood) | 45° (flood) | 60° (wide flood)



Single Circuit Track

Miniature track provides versatility for every lighting need.


Decorator finishes, push-in connectors and economy all combine to make single-circuit track perfect for residential or commercial use.



Two Circuit Power-Trac

Halo-2 Power-Trac has two circuits for greater system flexibility.


Halo-2 Power-Trac system provides two separate 20 AMP circuits. Each circuit can be independently switched. Suitable for commercial, merchandising and residential applications.



Lazer Track

Lazer track offers economy and convenience.


The Lazer Two-Conductor track is available in two finishes and 4 lengths. The overall height is only 9/16" with a decorative reveal at the ceiling line.



TEK

Halo TEK track system for 120V installations has two isolated circuits for greater power handling and dimming capability.

The Halo TEK track system provides two isolated circuits each with its own neutral. Each circuit can be independently switched. Suitable for commercial, merchandising and residential applications.



HTEK

Halo HTEK track system for 277V installations has two isolated circuits for longer runs, greater power handling and dimming capability.

The Halo HTEK track system provides two isolated circuits each with its own neutral. Each circuit can be independently switched. Suitable large retail and institutional applications.

Lighting Product Lines

Ametrix
AtLite
Corelite
Ephesus
Fail-Safe
HALO
HALO Commercial
Invue
io
IRiS
Lumark
Lumière
McGraw-Edison
Metalux
MWS
Neo-Ray
Portfolio
RSA
Shaper
Streetworks
Sure-Lites

Controls Product Lines

Fifth Light Technology
Greengate
iLight (International Only)
iLumin
Zero 88

Connected Lighting Systems

Distributed Low-Voltage Power
HALO Home
iLumin Plus
LumaWatt Pro
WaveLinx



Cooper Lighting Solutions
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.halolighting.com

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2025 Cooper Lighting Solutions
All Rights Reserved
Printed in USA
Publication No. BR518073EN
January 7, 2025 9:12 AM

All other trademarks are property
of their respective owners.

Product availability, specifications,
and compliances are subject to
change without notice.