

**Caretaker**  
Area / Site Luminaire





# Security made easy by design.

Superior illumination.  
Low maintenance. Built to last.

The Caretaker LED area luminaire combines high performance, low maintenance and easy installation in a simple, extremely economic package that has been designed for years of worry-free operation. The Caretaker luminaire is ideal for pole or wall mounted security lighting, residential street lighting, perimeter area lighting, parking areas, loading platforms, boat docks, access drives or pathways.

## Features and benefits

- Single heavy-duty die-cast housing for durability and low maintenance in security lighting applications
- Universal wall and wood pole mount bracket for ease of installation and numerous applications
- Integral slipfitter for mounting to pipe arm for versatility in mounting configuration
- High performance LED delivers up to 9,700 lumens and replaces up to 250W HID equivalents
- Precision molded optic designed to shape the distribution allowing maximum efficiency and application coverage
- Integrated light shield for full cutoff compliance to eliminate light pollution
- 3-PIN NEMA twist-lock photocontrol (included) provides automatic dusk-to-dawn operation for maximum energy savings
- 6kV integral surge protection device protects drivers and LED components



Standard

Energy and maintenance savings up to **89%** compared to HID

High-performance efficacy up to **155** lumens per watt




Small acrylic refractor


## Design features



Wall / square pole mount



Wood pole mount



Pipe arm mount



Zero uplight shield





Single-point access



3-PIN NEMA receptacle

## Photometrics



## Technical specifications

### STOCK SKUs

CTKRV1B  
CTKRV2B  
CTKRV3B

### PERFORMANCE

**Distributions:** Type V symmetric round  
**Color temperature:** 4000K / 70 CRI  
**Lumens:** 4,515 / 7,110 / 9,741  
**Wattage:** 29W / 50W / 71W  
**Efficacy:** Up to 155 lm/W

### ENERGY DATA

**Minimum temperature:** -40°C  
**Ambient temperature rating:** 40°C  
**Operation:** 120-277V 50/60Hz  
**Controls:** 0-10V dimmable

### WEIGHT

7 lbs. (3.2 kgs.)

### ADDITIONAL INFORMATION


**Warranty:** 5 year  
**Vibration rated:** 3G  
**UL/cUL listed:** Wet location  
**IP rated:** Yes (Optic)  
**ISO 9001:** Certified  
**LM79/LM80:** Compliant  
**RoHS:** Compliant

### ENERGY / MAINTENANCE SAVINGS


**Annual savings:** Up to 89% (compared to HID)

### Dimensions

#### Full Cutoff (Standard)



#### Small Acrylic Refractor




Product specifications subject to change without notice.  
Visit [cooperlighting.com](http://cooperlighting.com) to find the most up to date information.




# Decorative Shield Options Hillbrook Hoods


## Available Colors:




Raw Aluminum (A)




Black (BK)




Bronze (BZ)



White (WH)



Grey (AP)



## Unlit Fixtures:



 Raw Aluminum (A)



 Black (BK)



 Bronze (BZ)



 Grey (AP)



 White (WH)

## Lit Fixtures:



 Raw Aluminum (A)



 Black (BK)



 Bronze (BZ)




 Grey (AP)




 White (WH)

# Decorative Shield Options RadioWave Hoods


## Available Colors:




Raw Aluminum (A)




Black (BK)




Bronze (BZ)



White (WH)



Grey (AP)



## Unlit Fixtures:



 Raw Aluminum (A)



 Black (BK)



 Bronze (BZ)



 Grey (AP)



 White (WH)

## Lit Fixtures:



 Raw Aluminum (A)



 Black (BK)



 Bronze (BZ)



 Grey (AP)



 White (WH)

## Lighting Product Lines

Ametrix  
AtLite  
Corelite  
Ephesus  
Fail-Safe  
HALO  
HALO Commercial  
Invue  
iO  
Iris  
Lumark  
Lumark AP  
Lumière  
McGraw-Edison  
Metalux  
MWS  
Neo-Ray  
Portfolio  
Pentalux - 3D Printed Lighting  
RSA  
Shaper  
Streetworks  
Sure-Lites

## Controls Product Lines

Greengate  
Fifth Light  
Intelligent Lighting Controls

## Connected Lighting Systems and Smart Spaces Platform

WaveLinx  
Trellix Infrastructure



**Cooper Lighting Solutions**  
1121 Highway 74 South  
Peachtree City, GA 30269  
P: 770-486-4800  
[www.cooperlighting.com](http://www.cooperlighting.com)

**Canada Sales**  
5925 McLaughlin Road  
Mississauga, Ontario L5R 1B8  
P: 905-501-3000  
F: 905-501-3172

© 2025 Cooper Lighting Solutions  
All Rights Reserved  
Printed in USA  
Publication No. BR500012EN  
June 10, 2025 1:49 PM

Cooper Lighting Solutions is a registered trademark.  
All other trademarks are property of their respective owners.  
Product availability, specifications, and compliances are  
subject to change without notice.