

13 WATT FLUORESCENT ENTRY LIGHT WITH PHOTO CONTROL



FE13PC SERIES

FEATURES

- High impact, weather-resistant housing and lens
- Nighttime ON/Daytime OFF
- Built-in photo control
- Electronic ballast design provides reliable starting in cold weather
- Perfect for patio or entrance lighting
- 13W (maximum) fluorescent bulb included
- Available in bronze (FE13PC) and white (FE13PCW)

Compliances may not apply to all product configurations. Please consult the product spec sheet for compliance details.

COMPLIANCES: UL/cUL Listed, RoHS Compliant



ALTERNATE COLOR



FE13PCW White

13W FLUORESCENT BULB



ORDERING INFORMATION

Model	Description	Unit Carton Dimension (Inches)	Unit Carton Weight (Pounds)	Master Carton Dimension (Inches)	Master Carton Weight (Pounds)	Master Carton Quantity
FE13PC	13W Fluorescent - Bronze	9.5H x 6.3W x 4.8D	1.50	10.0H x 10.0W x 6.8D	3.25	2
FE13PCW	13W Fluorescent - White	9.5H x 6.3W x 4.8D	1.50	10.0H x 10.0W x 6.8D	3.25	2

23 WATT FLUORESCENT GU24 FLOODLIGHT WITH PHOTO CONTROL



FFL23PC-T24 SERIES

FEATURES

- Frosted high-impact protective lens
- Perfect for wall-mount or eave-mount applications
- Self-diagnostic LED (Title 24) indicator light
- Will accept 13W-23W GU24 bulb
- Fluorescent bulb lasts 5 times longer than standard incandescent bulbs
- Photo control provides convenient nighttime ON/daytime OFF
- Heavy-duty, die-cast aluminum housing
- 120 Volts (standard household supply)
- Available in black (FFL23PC-T24) and white (FFL23PCW-T24)

Compliances may not apply to all product configurations. Please consult the product spec sheet for compliance details.

COMPLIANCES: UL/cUL Listed, RoHS Compliant, California Title 24




ALTERNATE COLOR



FFL23PCW-T24 White

23W GU24 FLUORESCENT BULB



ORDERING INFORMATION

Model	Description	Unit Carton Dimension (Inches)	Unit Carton Weight (Pounds)	Master Carton Dimension (Inches)	Master Carton Weight (Pounds)	Master Carton Quantity
FFL23PC-T24	23W Fluorescent GU24 Floodlight - Black	6.8H x 7.1W x 6.9D	1.94	7.5H x 13.4W x 7.6D	5.07	2
FFL23PCW-T24	23W Fluorescent GU24 Floodlight - White	6.8H x 7.1W x 6.9D	1.94	7.5H x 13.4W x 7.6D	5.07	2

23 WATT FLUORESCENT GU24 PATIO LIGHT WITH PHOTO CONTROL



PFL23PC-T24 SERIES

FEATURES

- Frosted high-impact protective lens
- Self diagnostic LED (Title 24) indicator light
- Will accept 13W-27W GU24 bulb
- Fluorescent bulb lasts 5 times longer than standard incandescent bulbs
- Photo control provides convenient nighttime ON/daytime OFF
- Heavy-duty, die-cast aluminum housing
- 120 Volts (standard household supply)
- Available in black (PFL23PC-T24) and white (PFL23PCW-T24)

Compliances may not apply to all product configurations. Please consult the product spec sheet for compliance details.

COMPLIANCES: UL/cUL Listed, RoHS Compliant, California Title 24




ALTERNATE COLOR



PFL23PCW-T24 White

23W GU24 FLUORESCENT BULB



ORDERING INFORMATION

Model	Description	Unit Carton Dimension (Inches)	Unit Carton Weight (Pounds)	Master Carton Dimension (Inches)	Master Carton Weight (Pounds)	Master Carton Quantity
PFL23PC-T24	23W Fluorescent GU24 Patio Light - Black	8.8H x 7.1W x 5.4D	2.2	9.4H x 11.7W x 7.5D	5.5	2
PFL23PCW-T24	23W Fluorescent GU24 Patio Light - White	8.8H x 7.1W x 5.4D	2.2	9.4H x 11.7W x 7.5D	5.5	2

NOTE: Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Solutions Representative or visit our website at www.cooperlighting.com for available options, accessories and ordering information.