



## H3 A new dimension in recessed lighting

Recessed lighting has always been popular for its ability to deliver effective lighting while maintaining an unobtrusive ceiling appearance. The H3 is designed for small aperture lamps in low voltage MR16 and line voltage GU10. The Halo H3 trims deliver effective illumination yet do not intrude on the main decorating elements in a space. The trims feature meticulous die-cast or machined detailing and they accommodate either low voltage or line voltage MR16 lamps depending on the housing used.

## **Finishes**



White/Black Baffle



White/White Baffle



Black/Black Baffle



Tuscan Bronze



Satin Nickel



Polished Chrome



Frost (Glass)

## **Round Trims**























## **Square Trims**











H3 housings are offered in ten models designed for MR16 type lamps. Insulated Ceiling (IC) Air-Tite™, Non-IC Air-Tite™, low voltage (12V), line voltage (120V), new construction, remodel and commercial 277-volt. Housings have all the Halo contractor friendly features such as Got Nail™, Pass-N-Thru™ bar hangers and Slide-N-Side™ junction boxes that save installation time and money.





All H3 trims accept either 12V MR16 lamps or 120V GU10 lamps. Most trims allow lamp to tilt 15° to 35° for precise aiming. The 3010 Super-Adjustable allows 0° up to 80° tilt for aiming in even tight distances.



Locking screw on adjustable trims keeps aiming angle secure even during lamp replacements.



Die-cast adjustable gimbals with positive and negative aiming.



Precision machined baffles with solid die-cast rings.



Select wet location listed shower lights offered in die-cast or non-conductive and non-corrosive polymer trim rings with frosted glass edged lenses or regressed glass clear lenses.





### H36TAT

#### Fits Halo Trim Models:

3001, 3002, 3003, 3004, 3006, 3007, 3008, 3009, 3010, 3011, 3012, 3013, 3017, 3020

120V 50W GU10

cutout: 3-3/4" [95mm]

**H x W x L:** 5"x 5-1/4" x 8" [127mm x 133mm x 203mm]



### **H36LVTAT**

#### Fits Halo Trim Models:

3001, 3002, 3003, 3004, 3006, 3007, 3008, 3009, 3010, 3011, 3012, 3013, 3017, 3020

12V 50W MR16

Non-IC

cutout: 3-3/4" [95mm]

**H x W x L:** 5"x 5-1/4" x 10" [127mm x 133mm x 254mm]



## H36LVTAT277

#### Fits Halo Trim Models:

3001, 3002, 3003, 3004, 3006, 3007, 3008, 3009, 3010, 3011, 3012, 3013, 3017, 3020

12V 50W MR16

cutout: 3-3/4" [95mm]

**H x W x L:** 5"x 5-1/4" x 10" [127mm x 133mm x 254mm]



#### H38ICAT

Fits Halo Trim Models:

3001, 3002, 3003, 3004, 3006, 3007, 3008, 3009, 3010, 3011, 3012, 3013, 3017, 3020

120V 50W GU10

cutout: 3-3/4" [95mm]

**H x W x L**: 7-1/4" x 9-1/8" x 12-3/4" [184mm x 231mm x 324mm]



#### **H38LVICAT**

#### Fits Halo Trim Models:

3003, 3004, 3009, 3010, 3017 3017 3008, 3011, 3012, 3013, 3020

12V 50W MR16 | 12V 37W MR16

**cutout:** 3-3/4" [95mm]

**H x W x L:** 7-1/4" x 9-1/8" x 12-3/4" [184mm x 231mm x 324mm]



IC

#### H36ICAT

#### Fits Halo Trim Models:

3001, 3002, 3003, 3004, 3006, 3007, 3008, 3009, 3010, 3011, 3013, 3017, 3030

3012, 3013, 3017, 3020

120V 50W GU10

cutout: 3-3/4" [95mm]

**H x W x L:** 5-1/4"x 13-1/2" x 13" [133mm x 343mm x 330mm]



### **H36LVICAT**

#### Fits Halo Trim Models:

3001, 3002, 3003, 3004, 3006, 3007, 3008, 3009, 3010, 3011, 3012, 3013, 3017, 3020

12V 50W MR16

IC

cutout: 3-3/4" [95mm]

**H x W x L:** 5-1/4" x 13-1/2" x 13" [133mm x 343mm x 330mm]



Non-IC

# H36RTAT

#### Fits Halo Trim Models:

3001, 3002, 3003, 3004, 3006, 3007, 3008, 3009, 3010, 3011, 3012, 3013, 3017, 3020

120V 50W GU10

cutout: 3-3/4" [95mm]

**H x W x L:** 5"x 3-5/8" x 7-1/2" [127mm x 92mm x 190mm]



#### **H36LVRTAT**

#### Fits Halo Trim Models:

3001, 3002, 3003, 3004, 3006, 3007, 3008, 3009, 3010, 3011, 3012, 3013, 3017, 3020

12V 50W MR16

cutout: 3-3/4" [95mm]

**H x W x L:** 5"x 3-5/8" x 9-7/8" [127mm x 92mm x 251mm]



#### H36LVRTAT277

#### Fits Halo Trim Models:

3001, 3002, 3003, 3004, 3006, 3007, 3008, 3009, 3010, 3011, 3012, 3013, 3017, 3020

12V 50W MR16

Non-IC

cutout: 3-3/4" [95mm]

**H x W x L:** 5"x 3-5/8" x 9-7/8" [127mm x 92mm x 251mm]



**O.D.:** 4-1/4" [108mm] I.D.: 1-3/4" [45mm]

## 3001

## Adjustable Pinhole Baffle

#### Finishes:

White (WHWB, WHBB), Black (BKBB), Satin Nickel (SNBB), Tuscan Bronze (TBZBB)



## 3002

## Adjustable Pinhole Clear Reflector

Finishes: White (WHC)

O.D.: 4-1/4" [108mm] I.D.: 1-3/4" [45mm]



#### 3003

### Adjustable Baffle

#### Finishes:

White (WHWB, WHBB), Black (BKBB), Satin Nickel (SNB), Tuscan Bronze (TBZB)

**O.D.:** 4-1/4" [108mm] Baffle I.D.: 3" [75mm] I.D.: 2" [51mm]



#### 3004

#### Adjustable Reflector

#### Finishes:

White (WHC), Satin Nickel (SN), Tuscan Bronze (TBZ)

O.D.: 4-1/4" [108mm] Reflector I.D.: 3" [75mm]

I.D.: 2" [51mm]



## Adjustable Slot Aperture

#### Finishes:

White (WHBB), Black (BKBB), Satin Nickel (SNBB),

Tuscan Bronze (TBZBB)




## **O.D.:** 4-1/4" [108mm]

**I.D.:** 1-1/4" x 2" [32mm x 51mm]

#### 3007





Satin Nickel (SN), Tuscan Bronze (TBZ), Polished Chrome (PCC)



### Reflector I.D.: 3" [75mm] I.D.: 2" [51mm]

## 3008



Frosted Glass Showerlight Finishes:

White (FG)





O.D.: 4-1/4" [108mm] Gimbal: 2-3/4" [70mm] I.D.: 1-3/4" [45mm]



O.D.: 4-1/4" [108mm] **Gimbal:** 2-1/2" [64mm] I.D.: 1-3/4" [45mm]

## 3009

## Adjustable Gimbal

#### Finishes:

White (WHWB, WHBB), Black (BKBB), Satin Nickel (SNBB), Tuscan Bronze (TBZBB)

#### 3010

#### Super-Adjustable

#### Finishes:

White (WH), Satin Nickel (SN), Tuscan Bronze (TBZ)

#### 3011



**O.D.:** 4-1/4" square [108mm] Baffle I.D.: 2-1/4" [57mm]

I.D.: 2" [51mm]

I.D.: 2" [51mm]

## Adjustable Square Baffle

#### Finishes:

White (WHBB, WHWB), Black (BKBB), Satin Nickel (SNBB), Tuscan Bronze (TBZBB)

#### 3012



#### Adjustable Square Baffle Showerlight

#### Finishes:

White (WHBB, WHWB), Black (BKBB), Satin Nickel (SNBB), Tuscan Bronze (TBZBB)

#### 3013



O.D.: 4-1/4" square [108mm] Gimbal: 2-1/4" [57mm] I.D.: 2" [51mm]

**O.D.:** 4-1/4" square [108mm]

**Baffle I.D.:** 2-1/4" [57mm]

**Adjustable Square Gimbal** Finishes:

White (WH), Black (BK), Satin Nickel (SN), Tuscan Bronze (TBZ)



Low Profile Glass Curve Showerlight Finishes: Frost (FGS)

# **O.D.:** 4-1/4" [108mm]

# I.D.: 1-5/8" [41mm]

#### 3020



Wall Wash Downlight Finishes: White (WW)

O.D.: 4-1/4" [108mm] I.D.: 1-3/4" [45mm]

#### **Cooper Lighting Solutions**

1121 Highway 74 South Peachtree City, GA 30269 P: 770-486-4800 www.cooperlighting.com

Canada Sales 5925 McLaughlin Road Mississauga, Ontario L5R 1B8 P: 905-501-3000

F: 905-501-3172

#### **Lighting Product Lines**

Ametrix AtLite

Corelite

**Ephesus** 

Fail-Safe

HALO

HALO Commercial

Invue

io

IRiS Lumark

Lumière

McGraw-Edison

Metalux

MWS

Neo-Ray

Portfolio

**RSA** 

Shaper Streetworks

Sure-Lites

#### **Controls Product Lines**

Greengate

#### **Connected Lighting Systems**

Fifth Light (Canada Only) HALO Home

## IoT Platform

WaveLinx

Trellix





© 2021 Cooper Lighting Solutions All Rights Reserved Printed in USA Publication No. BR518006EN May 2021

Products, specifications and compliances are subject to change without notice.

Cooper Lighting Solutions is a registered trademark.
All other trademarks are property of their respective owners.

