MARKETPRO
Stock Lighting Solutions

2024
VOL. 3

RESIDENTIAL | COMMERCIAL | INDUSTRIAL

SELECTABLE LIGHTING

PRODUCT GUIDE

seleCCTable colors

selectable lumens

HALO | HALO COMMERCIAL | METALUX COMMERCIAL | METALUX INDUSTRIAL | LUMARK

COOPER Lighting Solutions

Multiple Light Choices, One Fixture.

At Cooper Lighting Solutions, we deliver industry-leading indoor and outdoor lighting products, lighting controls, smart lighting systems, programs and services.

VISIT OUR

MARKETPRO WEBSITE

Your one-stop shop for tools and resources designed to help grow your business

- Product Guide
- E-Commerce Tools
- Find Utility Rebates
- Sample Before You Buy
- Marketing & Training

READILY-AVAILABLE SOLUTIONS FROM OUR TRUSTED BRANDS

The MarketPro program provides our customers with top selling lighting and controls products from industry-preferred brands for their trusted performance, reliability and quality. These products are in-stock and ready to ship to meet your project needs.

In-Stock

Our essential products are in stock and readily-available to ship

Top Brands

Trusted products from HALO, Metalux, Greengate, Sure-Lites and Lumark

Proven Best Sellers

Contractor preferred top selling lighting and controls products

Sample Before You Buy

Try new products risk free

Innovation

State-of-the-art product innovation, direct mount installation, selectable technology and integrated controls

Utility Incentives

Products qualify for ENERGY STAR® and DLC®, saving money and adding value

Quick Solutions

Easily access our most popular, readily available products through our Quick Spec program

Training & Education

Online and instructor-led classes to expand your lighting and controls knowledge

Visit the MarketPro website to download the product guide

COOPERLIGHTING.COM/MARKETPRO

OUR BRANDS AND THE MARKETS WE SERVE

RESIDENTIAL

Residential lighting fixtures for single and multi-family construction and remodel projects.

COMMERCIAL

Lighting and control solutions for healthcare, education, hospitality, retail and office.

INDUSTRIAL

Lighting and control solutions for warehouses, distribution centers and logistic facilities.

OUTDOOR

Lighting that provides easy installation, area safety, and energy savings in commercial and industrial spaces.

We deliver a range of innovative and reliable indoor and outdoor lighting and controls product solutions specifically designed to maximize performance, energy efficiency and cost savings.

8 **HALO**
Recessed & Surface Downlights
Commercial Downlights

33 **METALUX**
Ambient Commercial & Industrial

45 **ARCHITECTURAL**
Commercial Lighting

48 **LUMARK & HALO OUTDOOR**
Outdoor Commercial & Industrial

SELECTABLE TECHNOLOGY

Multiple Light Choices, One Fixture.

Explore 250+ selectable products from HALO, Metalux and Lumark

Field-Selectable technology empowers you to take control. Go selectable to choose your way, every time. Adjust color temperatures (CCT) and lumen outputs with the flip of a switch!

SELECTABLE COLORS (CCT)

Choose from a wide range of color temperatures to set the ideal lighting scene.

SELECTABLE LUMENS

Select between the preset lumen outputs to create your optimal lighting experience.

For details visit:
cooperlighting.com/selectable to download the latest Selectable Lighting Product Guide.



Product Spotlight

HALO RLFR Fire-rated Recessed Baffle Trim

Canless Downlights

The RLFR Fire-rated canless downlight prevents the passage of flames & toxic gases for up to 2 hours. Die-cast aluminum baffle trim with curved lens.

PAGE **19**

HALO JBox Housing

The HALO 4" junction box housing is the solution for new construction fire-rated ceilings. Designed to work seamlessly with all 4" HALO Recessed LED Trims and any HALO Surface Mount Fixture. Its quick and easy new construction installation process is especially ideal for shallow plenum applications.

Page **25**

HALO Commercial HCD Pro System

Commercial Downlights

The HCD Series is a completely modular LED down-lighting system built on a set of fixture kits that easily interchange any size, shape, or distribution of HCD reflectors. Available in direct mount for retrofit/remodel with mounting frames for new construction.

Page **31**

At Cooper Lighting Solutions, we build forward-thinking lighting solutions that make people's lives safer, while making buildings, homes and cities smarter and more sustainable. Learn about our latest lighting solutions and new MarketPro products.

Metalux Regress Mount & Uplift Kit

Flat Panel Accessory

The Metalux Ambient Regress kit adds 2" deep regress solution to create visual excitement to any stock panel that installs on a ceiling grid. The metal bevel design provides clean edges, depth and glare control.

PAGE **35**

Metalux Multi-Mount Selectable

Flat Panels

The Multi-mount is a visually comforting flat panel that can be mounted directly to the ceiling or wall reducing labor and material cost by removing the need for a surface mount kit.

selectable lumens

seleCCTable colors

PAGE **35**

Metalux Surround Frame Selectable

Flat Panels

The Surround Frame offers an architectural illuminated modern frame that can enhance the look of any space. Versatile mounting in existing T-grid using ceiling tile as the reflector.

selectable lumens

seleCCTable colors

PAGE **36**

Canless Downlighting p. 9-19

Surface Mount Downlighting p. 20-25

Recessed LED and Traditional Trims p. 26-28

Under Cabinets p. 29

HALO®

RECESSED LED DOWNLIGHTS

HALO is the industry leader in high-quality recessed downlighting, offering the widest selection of innovative and flexible solutions for your application needs.

HALO® CANLESS DOWNLIGHTING

GO CANLESS!

Installs Virtually Anywhere!

- Field-Selectable color temperatures
- Mounts to drywall or suspended ceilings (no housing required)
- Remote driver/junction box included
- Rated for insulation contact (IC) & non-IC ceilings

MORE FLEXIBILITY!

SAVE TIME AND MONEY!

NO HOUSING NEEDED!



Quick and Easy Installation

New Construction Mounting Frames and Smash Plate

For Installing Canless Downlights in New Construction

- Use HALO Mounting Frames/Smash Plates on your next new construction project
- Toolless thumbscrews hold remote driver/jboxes to the frame during rough in
- **MF Series** - 4" & 6" rounds with 1/2" drywall collar
- **HL Series** - 3", 4", 6", & 8" rounds that convert to squares with corner knockouts
- **Smash Plate** - our most cost-effective single frame solution that can fit 3", 4", or 6" HALO Canless Fixtures (convert 4" or 6" openings to squares with corner knockouts)

Canless Fixture | Mounting Frame | Easy Install



MF Series

HL Series

No hanger bars



Smash Plate

Catalog Number	Description	UPC
MF4RC	4" Round Mounting Frame with 1/2" Drywall Collar	080083268009
MF6RC	6" Round Mounting Frame with 1/2" Drywall Collar	080083268023
HL3RSMF	3" Round/Square Mounting Frame	080083876143
HL4RSMF	4" Round/Square Mounting Frame	080083876167
HL6RSMF	6" Round/Square Canless Mounting Frame	080083876181
HL8RSMF	8" Round/Square Canless Mounting Frame	080083890460
SP346RS	3"/4"/6" Round/Square Smash Plate	080083288236

HALO SLIM CANLESS DOWNLIGHT PRODUCT SELECTION GUIDE

Good | Better | Best

		HLBE & HLBSL	HLBPH	HLB	HLBC/HLBC+
FEATURES/PERFORMANCE	Slim 1/2" Thin	✔	✔	✔	✔ with regressed lens + 2-in-1 (Canless-to-Can) Install Option
	Size / Shape	4", 6" Round	4", 6" Round	3", 4", 6", 8", 12" Round, Square	4", 6" Round, Square[1]
	Lens	Smooth	Smooth	Low-glare Prismatic	Low-glare Prismatic
	Max Lumens (By size @ 3000K)	745, 1,025	805, 1,015	595, 790, 1,020, 2,350, 2,300	975, 1,270 (Lumen Select, Dedicated)
	Color Temperatures (CCT)	**3 CCT** 27/30/3500K | 30/40/5000K, **Dedicated:** 3000K	**5 CCT** 27/30/35/40/5000K	**5 CCT** 27/30/35/40/5000K	**5 CCT w/ D2W** D2W/27/30/35/40/5000K
CONTROL	Dimming Phase Cut (LE/TE) / 0-10V	10% Phase Cut	5% Phase Cut	5% Phase Cut, 0-10V[2]	5% Phase Cut, 0-10V
	Estimated Life Hours	35,000	50,000	50,000	50,000
	Input Voltage	120V	120V	120V, 120-277V	120V, 120-277V
ACCESSORIES	Fits Mounting Frames & Smash Plate	✔	✔	✔	✔
	Decorative Overlays[3]	✔	✔	✔	✔[1]
	Slide-in-Side™ Wire Traps[4]		✔	✔	✔
	Mounting Bar	✔[5]	✔	✔	✔

[1] Round and Round-to-Square Designer Overlay Trims sold separately. [2] HLBs are also available in QuickLink Low Voltage (Phase Cut or 0-10V) or Smart Wi-Fi Connected by WiZ Pro versions. [3] Matte Black, Tuscan Bronze, Satin Nickel, Paintable Matte White. [4] Slide-N-Side wire traps eliminate the need to use knockouts in most instances. Pre-wire outside of the j-box, fold down the tab(s), and insert non-metallic sheathed cable into the Slide-N-Side strain relief. [5] Mounting Bars are included with HLBSL but are sold separately for the HLBE Bulk Packs (HLBEMOUNT-12PK).

HLBC/HLBC+ Slim Regressed

CANLESS DOWNLIGHTS - 4" & 6"

- Standard HLBC is canless with dedicated lumens while the HLBC+ features Lumen Select and 2-in-1 installation for fast Canless-to-Can conversion!
- Regressed baffle die-cast aluminum trim and prismatic lens improve visual comfort while maintaining 1/2"-thin recess into the ceiling!
- 6-Position Switch: 5 Color Field-Selectable (27/30/35/40/5000K) + Dim-to-Warm (3000K dims to 1800K)
- Includes LED downlight and remote driver/junction box with mounting bar
- 5% Dimming (Phase Cut or 0-10V), 50,000 hrs, 90+ CRI

dim-to-warm option included | seleCCTable colors | selectable lumens | 2 in 1 installation

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
HLBC4LS9FSD2W1EMWR	4" Downlight, 2-in-1 Install	White	60-70W	2700K-5000K+D2W	120V	Lumen Select 600-900	9/13	080083263097	2406536
HLBC4LS9FSD2W1EMWR-CA	4" Downlight, 2-in-1 Install, CA T20	White	60-70W	2700K-5000K+D2W	120V	Lumen Select 600-900	9/13	080083267927	2406535
HLBC4LS9FSD2WE010MWR	4" Downlight, 2-in-1 Install (0-10V)	White	60-70W	2700K-5000K+D2W	120-277V	Lumen Select 600-900	8.5/13	080083263233	2406530
HLBC4LS9FSD2WE010MWR-CA	4" Downlight, 2-in-1 Install, CA T20, (0-10V)	White	60-70W	2700K-5000K+D2W	120-277V	Lumen Select 600-900	8.5/13	080083267965	2406529
HLBC6LS9FSD2W1EMWR	6" Downlight, 2-in-1 Install	White	70-75W	2700K-5000K+D2W	120V	Lumen Select 900-1,200	11/16	080083263219	2406539
HLBC6LS9FSD2W1EMWR-CA	6" Downlight, 2-in-1 Install, CA T20	White	70-75W	2700K-5000K+D2W	120V	Lumen Select 900-1,200	11/16	080083267941	2406538
HLBC6LS9FSD2WE010MWR	6" Downlight, 2-in-1 Install (0-10V)	White	70-75W	2700K-5000K+D2W	120-277V	Lumen Select 900-1,200	11.5/16.5	080083263257	2406534
HLBC6LS9FSD2WE010MWR-CA	6" Downlight, 2-in-1 Install, CA T20 (0-10V)	White	70-75W	2700K-5000K+D2W	120-277V	Lumen Select 900-1,200	11.5/16.5	080083267989	2406532
HLBC4069FSD2W1EMW	4" Downlight, Canless Only	White	60W	2700K-5000K+D2W	120V	675	8	080083263059	2406524
HLBC6099FSD2W1EMW	6" Downlight, Canless Only	White	70W	2700K-5000K+D2W	120V	1,010	12	080083263073	2406527

HLB & HLBPH Slim

CANLESS DOWNLIGHTS - 3", 4", & 6"

- An ultra-thin flange and sleek 1/2"-thin downlight design that fits under any obstruction.
- **HLB** - die-cast aluminum with low-glare prismatic lens; **HLBPH** - dead-front plastic frame with smooth lens
- 5 Color Field-Selectable in 27/30/35/40/5000K
- Includes LED downlight and remote driver/junction box with mounting bar
- 5% Dimming (Phase Cut or 0-10V), 50,000 hrs, 90+ CRI

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
HLB3059FS1EMWR	3" Downlight, Round	White	40W	2700K-5000K	120V	575	9	080083151301	2370657
HLB3S059FS1EMWR	3" Downlight, Square	White	40W	2700K-5000K	120V	595	9	080083151325	N/A
HLB4069FS1EMWR	4" Downlight, Round	White	65W	2700K-5000K	120V	790	12	080083848140	2322243
HLB4SP069FS1EMWR	4" Downlight, Square (Rnd Hole)	White	65W	2700K-5000K	120V	650	10	080083909667	2347583
HLB6099FS1EMWR	6" Downlight, Round	White	70W	2700K-5000K	120V	1,020	16	080083848164	2322242
HLB6S099FS1EMWR	6" Downlight, Square	White	70W	2700K-5000K	120V	975	12	080083863389	2331663
HLB8169FS1EMWR	8" Downlight, Round	White	100W	2700K-5000K	120V	1,760	21	080083150601	2358047
HLB4069FSE010MWR	4" Downlight, Round (0-10V)	White	65W	2700K-5000K	120-277V	790	11	080083912261	2351376
HLB4S069FSE010MWR	4" Downlight, Square (0-10V)	White	65W	2700K-5000K	120-277V	725	11	080083912308	N/A
HLB6099FSE010MWR	6" Downlight, Round (0-10V)	White	70W	2700K-5000K	120-277V	1,060	15	080083912285	2351377
HLB6S099FSE010MWR	6" Downlight, Square (0-10V)	White	70W	2700K-5000K	120-277V	975	15	080083912322	N/A
HLB8LS9FSE010MWR	8" Downlight, Round (0-10V)	White	90-150W	2700K-5000K	120-277V	Lumen Select 1,400/1,900/2,400	17/25/32	080083083367	2358045
HLB12LS9FSE010MWR	12" Downlight, Round (0-10V)	White	90-150W	2700K-5000K	120- 277V	Lumen Select 1,300/1,900/2,300	17/25/32	080083088782	N/A
HLBPH4069FS1EMWR	4" Downlight, Round	White	65W	2700K-5000K	120V	805	10	080083190003	2385132
HLBPH6099FS1EMWR	6" Downlight, Round	White	70W	2700K-5000K	120V	1,015	14	080083190027	2385133

HLBSL & HLBE Slim Lite

CANLESS DOWNLIGHTS - 4" & 6"

- Matches the HLBPH with simplified features for budget-conscious installers
- **HLBSL** - 3 Color Field-Selectable in 27/30/3500K or 30/40/5000K; **HLBE** - dedicated in 3000K
- Only available in dead-front plastic frame and smooth lens
- Includes LED downlight and remote driver/junction box with mounting bar*
- 10% Phase Cut (LE/TE) Dimming, 35,000 hrs, 90+ CRI

Catalog Number	Description	Finish	Replaces	CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
HLBSL4069FS231EMWR	4" Downlight	White	65W	2700K-3500K	120V	753	10	080083912346	2349484
HLBSL4069FS351EMWR	4" Downlight	White	65W	3000K-5000K	120V	735	10	080083916368	2349485
HLBSL6099FS231EMWR	6" Downlight	White	70W	2700K-3500K	120V	955	13	080083912360	2349475, 2349476, 2349477
HLBSL6099FS351EMWR	6" Downlight	White	70W	3000K-5000K	120V	950	13	080083916382	2349478, 2349479, 2349480
HLBE4069301EMWR-12PK*	4" Downlight (12-Pack)	White	65W	3000K	120V	740	10	080083265503	2405484
HLBE4069301EMWR-24PK*	4" Downlight (24-Pack)	White	65W	3000K	120V	740	10	080083265527	2405484
HLBE6099301EMWR-12PK*	6" Downlight (12-Pack)	White	70W	3000K	120V	1,025	13	080083265541	2405486
HLBE6099301EMWR-24PK*	6" Downlight (24-Pack)	White	70W	3000K	120V	1,025	13	080083265565	2405486

*HLBE: mounting bar 12 packs sold separately (HLBEMOUNT-12PK).

HALO CANLESS DOWNLIGHT PRODUCT SELECTION GUIDE

Good — Better — Best

		DOWNLIGHTS				ADJUSTABLES		
		LT-DM	CJB/CJB+	RL-DM, RLFR, RL-DM Night Light	LCR	HLA	RA-DM	RL-Slope
FEATURES / PERFORMANCE	**Fixture Types**	Downlights	Slim Downlight with Attached J-box + 2-in-1 Canless-to-Can Versions Available	Recessed Downlights, Fire Rated Downlight, & Downlight + Night Light	Recessed Downlights/ Wall Washers, + Emergency Battery Backup options	Gimbal Adjustables (30° Tilt/360° Rotation)	Gimbal Adjustables (35° Tilt/360° Rotation)	Regressed Slope Adjustable (9-45° Tilt)
	Sizes (Round)	3", 4", 6"	4", 6"	4", 6"	2", 4", 6", 8"	3", 4"	4", 6"	4", 6"
	Trim & Lens	Baffle or Smooth Trim w/ Flat Lens	Slim Trim w/ Flat Smooth Lens	Baffle Trim w/ Curved Lens (**NL** has Transparent Trim)	Smooth Trim w/ Flat Lens	Low-glare Prismatic or Smooth Lens	Baffle Trim w/ Flat Lens	Deep Baffle Trim w/ Integrated Optic
	Max Lumens (By size @ 3000K)	570, 645, 785	745, 920	955, 1,300 (Lumen Select, Dedicated) (**NL:** 780, 1,020)	835, 1,295, 3,100, 8,155	710	790, 775	960, 1,630
	Color Temperatures (CCT)	**3 CCT** 27/30/3500K, 30/40/5000K, **Dedicated:** 3000K	**5 CCT** 27/30/35/40/ 5000K	**5 CCT w/ D2W** D2W/27/30/35/40/ 5000K (**NL**: 2000K)	**6 CCT** 27/30/35/40/50/ 6500K	**5 CCT** 27/30/35/40/ 5000K	**5 CCT** 27/30/35/40/ 5000K	**5 CCT** 27/30/35/40/ 5000K
CONTROL	**Dimming Phase Cut (LE/TE)/0-10V**	10% Phase Cut[1]	10% Phase Cut[1]	5% Phase Cut, 0-10V[2] (**NL**: 5% Phase Cut - Both zones)	5% Dual-Dim (Phase Cut + 0-10V), 0-10V	5% Phase Cut	5% Phase Cut	5% Phase Cut
	Estimated Life Hours	35,000	35,000	70,000 52 (**RL & NL**: 50,000)	50,000	50,000	50,000	50,000
	Input Voltage	120V	120V	120V	120-277V	120V	120V	120V
HARDWARE	**Fits Mounting Frames/Smash Plate**	✔	✔	✔	✔	✔	✔	✔
	Decorative Overlays[3]			✔ (RL-DM only)	✔	✔		
	Slide-in-Side™ Wire Traps[4]			✔	✔	✔	✔	✔
	Mounting Bar	✔		✔	✔	✔	✔	✔

[1] LT-DMs are also available in QuickLink Low Voltage (Phase Cut) versions.
[2] RL-DMs are also available in QuickLink Low Voltage (0-10V) versions.
[3] Matte Black, Tuscan Bronze, Satin Nickel, Paintable Matte White.
[4] Slide-N-Side wire traps eliminate the need to remove knockouts. Pre-wire outside of the j-box, fold down the tab, and insert non-metallic sheathed cable into the Slide-N-Side strain relief.

RL-DM Recessed Baffle Trim

CANLESS DOWNLIGHTS - 4" & 6"

- The perfect balance of value and visual comfort, available as a canless direct mount
- Die-cast aluminum baffle trim with curved lens and selectable lumen options
- 6-Position Switch: 5 Color Field-Selectable (27/30/35/40/5000K) + Dim-to-Warm (3000K dims to 1800K)
- LED downlight with remote driver/junction box
- 5% Phase Cut (LE/TE) Dimming, 70,000 hrs, 90+ CRI

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
RL4LS9FSD2W1EWHDM	4" Baffle Downlight	White	60-70W	2700K-5000K+D2W	120V	Lumen Select 600/900	7.5/11.5	080083258901	2403141
RL6069FSD2W1EWHDM	6" Baffle Downlight	White	60W	2700K-5000K+D2W	120V	750	7	080083258963	2402947
RL6LS9FSD2W1EWHDM	6" Baffle Downlight	White	70-75W	2700K-5000K+D2W	120V	Lumen Select 900/1,200	10/14	080083258987	2403144

LT-DM Recessed Baffle & Smooth Splay Trim

CANLESS DOWNLIGHTS - 3", 4", & 6"



- Closely mirrors the RL-DM design with simplified features for maximum savings
- Dead-front plastic trim in either baffle or smooth splay and flat lens
- 3 Color Field-Selectable in 27/30/3500K or 30/40/5000K; dedicated in 3000K
- Includes LED downlight and remote driver/junction box with mounting bar
- 10% Dimming (Phase Cut LE/TE), 35,000 hrs, 90+ CRI

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
LT3059FS231EWHDMR	3" Smooth Splay Downlight	White	60W	2700K-5000K	120V	550	7	080083159680	2389367
LT3059FS351EWHDMR	3" Smooth Splay Downlight	White	60W	3000K-5000K	120V	570	7	080083159628	N/A
LTB4069FS351EWHDMR	4" Baffle Downlight	White	60W	3000K-5000K	120V	625	8	080083253456	2398167
LT4069FS231EWHDMR	4" Smooth Splay Downlight	White	60W	2700K-5000K	120V	620	7	080083159925	2374009
LT4069FS351EWHDMR	4" Smooth Splay Downlight	White	60W	3000K-5000K	120V	645	7	080083159642	2374012
LTB6089FS351EWHDMR	6" Baffle Downlight	White	65W	3000K-5000K	120V	745	9	080083253470	2398173
LT6089FS231EWHDMR	6" Smooth Splay Downlight	White	65W	2700K-5000K	120V	765	8	080083159963	2374019
LT6089FS351EWHDMR	6" Smooth Splay Downlight	White	65W	3000K-5000K	120V	785	9	080083159666	2374021

RLS Slope Recessed Baffle Trim Adjustable

CANLESS DOWNLIGHTS - 4" & 6"

- Tilt the adjustment mechanism from 9° to 45° to match ceiling pitches from 2/12 to 12/12
- Better lighting and improved visual comfort with its integrated optic and regressed light engine
- 5 Color Field-Selectable in 27/30/35/40/5000K
- Includes LED downlight and remote driver/junction box with mounting bar
- 5% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
RLS4099FS1EWHDMR	4" Slope Ceiling Recessed Downlight	White	70W	2700K-5000K	120V	960	9	080083190300	2382794
RLS6159FS1EWHDMR	6" Slope Ceiling Recessed Downlight	White	150W	2700K-5000K	120V	1,630	9	080083190324	2382795

RA-DM Baffle Trim Adjustable Gimbal

CANLESS DOWNLIGHTS - 4" & 6"

- Aim lighting where you want it with 360° of rotations and 35° of tilt
- Regressed baffle for increased cutoff
- 6-Position Switch: 5-Color Field-Selectable (27/30/35/40/5000K) + Dim-to-Warm (3000K dims to 1800K)
- Includes LED downlight and remote driver/junction box with mounting bar
- 5% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	Energy Star ID
RA4LS9FSD2W1EWHDM	4" Adjustable Baffle Downlight	White	65W	2700K-5000K + D2W	120V	600-900	9	080083283019	2351865
RA6LS9FSD2W1EWHDM	6" Adjustable Baffle Downlight	White	65W	2700K-5000K + D2W	120V	600-900	9	080083283033	2351876

HLA Adjustable Gimbal

CANLESS DOWNLIGHTS - 4"

- Aim lighting where you want it with 360° of rotations and 35° of tilt
- Ideal for shallow plenum spaces - requires only 1-1/2" above the ceiling
- 5 Color Field-Selectable in 27/30/35/40/5000K
- Includes LED downlight and remote driver/junction box with mounting bar
- 5% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI

Catalog Number	Description	Finish	Replaces Up To	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
HLA406FL9FS1EMWR	4" Adjustable Direct Mount	White	60W	2700K-5000K	120V	710	11	080083882960	2341271
HLA406VWFL9FS1EMWR	4" Adjustable Direct Mount	White	60W	2700K-5000K	120V	710	11	080083863600	2333844

Canless LED Downlights

RL-DM/RL Night Light

CANLESS DOWNLIGHTS & RECESSED LED TRIMS - 4" & 6"

- 2 Modes: Downlight for general illumination and Night Light with gentle glow (2000K)
- Dead-front plastic trim with smooth splay and curved lens
- 6-Position Switch: 5 Color Field-Selectable (27/30/35/40/5000K) + Dim-to-Warm (3000K dims to 1800K); Night Light CCT: Warm glow 2000K
- 5% Dimming (Phase Cut LE/TE), 70,000 hrs, 90+ CRI

Recessed LED Trims

Canless LED Downlights with remote/driver/junction box

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
RLNL4079FSD2W1EWHDM	4" Night Light + Downlight	White	65W	2700K-5000K + D2W + Night Light (2000K)	120V	780	9	080083265039	2403400
RLNL6109FSD2W1EWHDM	6" Night Light + Downlight	White	70W	2700K-5000K + D2W + Night Light (2000K)	120V	1,020	12	080083265053	2403403

Recessed LED Trims with E26 medium socket adapter, and mounting hardware (4"-friction blades and 5"/6"-torsion springs & friction blades)

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
RLNL4079FSD2W1EWH	4" Night Light + Downlight Trim	White	65W	2700K-5000K + D2W + Night Light (2000K)	120V	775	8	080083268047	2409525
RLNL56109FSD2W1EWH	5"/6" Night Light + Downlight Trim	White	75W	2700K-5000K + D2W + Night Light (2000K)	120V	1,065	11	080083268061	2409524

Installing downlights has never been faster.

Power multiple fixtures on the single power supply for easy and efficient lighting installation.

SAVE UP TO 85% WIRING TIME

QuickLink Low Voltage System

HLB QuickLink Low Voltage (Phase Cut Dimming)

SLIM CANLESS DOWNLIGHTS - 4" & 6"

- Fixtures twist-connect to low voltage cable, powered by the single remote driver/j-box
- Die-cast aluminum with low-glare prismatic lens
- 5 Color Field-Selectable in 27/30/35/40/5000K
- (1) 72W remote power supply & 35-ft of low voltage cable + (4) downlights*
- 5% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI

seleCCTable colors

QuickLink Low Voltage System

Catalog Number	Description	Max Fixtures	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts Per	UPC	Energy Star ID
HLBQL4069FS1E-4PK	Kit: (1) Remote Power Supply & 35-ft of cable + (4) 4" HLBQL Fixtures*	7	White	60W	2700K-5000K	Driver: 120V Lights: QL LowV	640	8	080083190102	2388203
HLBQL6099FS1E-4PK	Kit: (1) Remote Power Supply & 35-ft of cable + (4) 6" HLBQL Fixtures*	6	White	60W	2700K-5000K	Driver: 120V Lights: QL LowV	975	12	080083190126	2388204
HLBQL4069FS1E	(1) 4" HLBQL Fixture**	-	White	60W	2700K-5000K	QL Low Voltage	600	8	080083190188	N/A
HLBQL6099FS1E	(1) 6" HLBQL Fixture**	-	White	60W	2700K-5000K	QL Low Voltage	975	12	080083190218	N/A

*Additional lights sold separately. **Driver not included. Only compatible with the HALO QuickLink 120V phase cut system.

LT-DM QuickLink Low Voltage (Phase Cut Dimming)

RECESSED SMOOTH TRIM CANLESS DOWNLIGHTS - 4" & 6"

- Fixtures twist-connect to low voltage cable, powered by the single remote driver/j-box
- Dead-front plastic trim in smooth splay and flat lens
- 5 Color Field-Selectable in 27/30/35/40/5000K
- (1) 72W remote power supply & 35-ft of low voltage cable + (4) downlights*
- 10% Dimming (Phase Cut LE/TE), 35,000 hrs, 90+ CRI

seleCCTable colors

QuickLink Low Voltage System

Catalog Number	Description	Max Fixtures	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts Per	UPC	Energy Star ID
LTQL4069S1EDM-4PK	Kit: (1) Remote Power Supply & 35-ft of cable + (4) 4" LTQL Fixtures*	8	White	60W	2700K-5000K	Driver: 120V Lights: QL LowV	675	8	080083190140	2388205
LTQL6069S1EDM-4PK	Kit: (1) Remote Power Supply & 35-ft of cable + (4) 6" LTQL Fixtures*	8	White	60W	2700K-5000K	Driver: 120V Lights: QL LowV	825	8	080083190164	2388206
LTQL4069S1EDM	(1) 4" LTQL Fixture**	-	White	60W	2700K-5000K	QL Low Voltage	675	8	080083190232	N/A
LTQL6069S1EDM	(1) 6" LTQL Fixture**	-	White	60W	2700K-5000K	QL Low Voltage	825	8	080083190256	N/A

*Additional lights sold separately. **Driver not included. Only compatible with the HALO QuickLink 120V phase cut system.

HALO CANLESS LOW VOLTAGE DOWNLIGHTING

HALO canless commercial downlights with a 120-277V remote driver/ junction box positioned as HALO's light commercial solution for new construction and remodel applications.

HLB QuickLink Low Voltage (0-10V Dimming)

SLIM CANLESS DOWNLIGHTS - 4" & 6"

- Fixtures twist-connect to low voltage cable, powered by the single remote driver/j-box
- Die-cast aluminum with low-glare prismatic lens
- 5 Color Field-Selectable in 27/30/35/40/5000K
- (1) 90W remote power supply & 40-ft of low voltage cable + (6) downlights*
- 5% Dimming (0-10V), 50,000 hrs, 90+ CRI

Catalog Number	Description	Max Fixtures	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts Per	UPC	Energy Star ID
HLBQL4069FSE010-6PK	Kit: (1) Remote Power Supply + 40-ft of cable; (6) 4" HLBQL Downlights (0-10V)*	11	White	60W	2700K-5000K	Driver: 120-277V Lights: QL LowV	605	8	080083182206	2388712
HLBQL6099FSE010-6PK	Kit: (1) 0-10V Remote Power Supply + 40-ft of cable; (6) 6" HLBQL Downlights (0-10V)*	7	White	60W	2700K-5000K	Driver: 120-277V Lights: QL LowV	935	12	080083182220	2388713
HLBQL4069FSE010	4" HLBQL Additional Fixture (0-10V)**	-	White	60W	2700K-5000K	QL Low Voltage	605	8	080083182367	N/A
HLBQL6099FSE010	6" HLBQL Additional Fixture (0-10V)**	-	White	60W	2700K-5000K	QL Low Voltage	935	12	080083182381	N/A

*Additional lights sold separately. **Driver not included. Only compatible with the HALO QuickLink 120-277V system.

RL-DM QuickLink Low Voltage (0-10V Dimming)

RECESSED BAFFLE TRIM CANLESS DOWNLIGHTS - 4" & 6"

- Fixtures twist-connect to low voltage cable, powered by the single remote driver/j-box
- Die-cast aluminum baffle trim and curved lens
- 5 Color Field-Selectable in 27/30/35/40/5000K
- (1) 90W remote power supply & 50-ft of low voltage cable + (8) downlights*
- 5% Dimming (0-10V), 70,000 hrs, 90+ CRI

Catalog Number	Description	Max Fixtures	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts Per	UPC	Energy Star ID
RLQL4069SE010DM-8PK	Kit: (1) 0-10V Remote Power Supply + 50-ft of cable; (8) 4" RLQL Downlights (0-10V)*	13	White	60W	2700K-5000K	Driver: 120-277V Lights: QL LowV	620	7	080083182282	2388378
RLQL6069SE010DM-8PK	Kit: (1) Remote Power Supply + 50-ft of cable; (8) 6" RLQL Downlights (0-10V)*	13	White	60W	2700K-5000K	Driver: 120-277V Lights: QL LowV	665	7	080083182305	2388389
RLQL4069SE010DM	4" RLQL Additional Fixture (0-10V)**	-	White	60W	2700K-5000K	QL Low Voltage	620	7	080083182442	N/A
RLQL6069SE010DM	6" RLQL Additional Fixture (0-10V)**	-	White	60W	2700K-5000K	QL Low Voltage	665	7	080083182466	N/A

*Additional lights sold separately. **Driver not included. Only compatible with the HALO QuickLink 120-277V system.

LCR Light Commercial Recessed

CANLESS DOWNLIGHTS - 2", 4", 6", & 8"

- Redesigned with dual-dimming and additional CCT selectability and lumen packages, decorative trim options, and new wall wash or emergency battery backup versions
- Die-cast aluminum smooth splay trim and flat lens (downlight and wall wash versions)
- 6 Color Field-Selectable in 27/30/35/40/50/6500K
- Includes LED downlight and remote driver/junction box with mounting bar
- 5% Dual Dim: 0-10V or Phase Cut (LE/TE), 50,000 hrs, 90+ CRI

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
LCR208RD9FSE020	2" Downlight	White	70W	2700K-6500K	120-277V	835	10	080083259144	2405806
LCR408RD9FSE020	4" Downlight	White	70W	2700K-6500K	120-277V	890	11	080083261505	2405430
LCR412RD9FSE020	4" Downlight	White	75W	2700K-6500K	120-277V	1,295	14	080083261567	2405436
LCR615RD9FSE020	6" Downlight	White	75W	2700K-6500K	120-277V	1,610	18	080083261628	2405442
LCR621RD9FSE020	6" Downlight	White	150W	2700K-6500K	120-277V	2,100	23	080083261680	2405603
LCR630RD9FSE010	6" Downlight	White	150W	2700K-6500K	120-277V	3,100	30	080083261741	2405609
LCR810RD9FSE020	8" Downlight	White	75W	2700K-6500K	120-277V	1,090	12	080083261789	2405807
LCR830RD9FSE010	8" Downlight	White	150W	2700K-6500K	120-277V	3,150	35	080083261826	2405809
LCR850RD9FSE010	8" Downlight	White	150W	2700K-6500K	120-277V	5,180	55	080083261864	2405810
LCR880RD9FSE010	8" Downlight	White	200W	2700K-6500K	120-277V	8,155	92	080083261901	2405812

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
LCR408WW9FSE020	4" Wall Wash (Damp-listed)	White	70W	2700K-6500K	120-277V	835	10	080083259182	2405431
LCR412WW9FSE020	4" Wall Wash (Damp-listed)	White	75W	2700K-6500K	120-277V	1,255	14	080083261543	2405437
LCR615WW9FSE020	6" Wall Wash (Damp-listed)	White	75W	2700K-6500K	120-277V	1,520	18	080083261604	2405598
LCR621WW9FSE020	6" Wall Wash (Damp-listed)	White	150W	2700K-6500K	120-277V	2,125	23	080083261666	2405601
LCR630WW9FSE010	6" Wall Wash (Damp-listed)	White	150W	2700K-6500K	120-277V	2,970	32	080083261727	2405611

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
LCR408RD9FSE040	4" Downlight + Emergency Batt.	White	70W	2700K-6500K	120-277V	890	10.7	080083259168	2405429
LCR412RD9FSE040	4" Downlight + Emergency Batt.	White	75W	2700K-6500K	120-277V	1,295	14.4	080083261529	2405434
LCR615RD9FSE040	6" Downlight + Emergency Batt.	White	75W	2700K-6500K	120-277V	1,610	17.5	080083261581	2405442
LCR621RD9FSE040	6" Downlight + Emergency Batt.	White	150W	2700K-6500K	120-277V	2,100	23	080083261642	2405601
LCR630RD9FSE040	6" Downlight + Emergency Batt.	White	150W	2700K-6500K	120-277V	3,100	31.6	080083261703	2405607
LCR810RD9FSE040	8" Downlight + Emergency Batt.	White	75W	2700K-6500K	120-277V	1,090	12	080083261765	2405800
LCR830RD9FSE040	8" Downlight + Emergency Batt.	White	150W	2700K-6500K	120-277V	3,150	33	080083261802	2405809
LCR850RD9FSE040	8" Downlight + Emergency Batt.	White	150W	2700K-6500K	120-277V	5,180	50	080083261840	2405802
LCR880RD9FSE040	8" Downlight + Emergency Batt.	White	200W	2700K-6500K	120-277V	8,155	92	080083261888	2405812

CJB/CJB+ Integrated JBox

CANLESS DOWNLIGHTS - 4" & 6"

- Standard CJB is canless while the CJB+ features 2-in-1 installation for fast Canless-to-Can conversion!
- Slim flat trim and smooth lens
- 5 Color Field-Selectable in 27/30/35/40/5000K
- 10% Dimming (Phase Cut LE/TE), 35,000 hrs, 90+ CRI

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
CJB4069FS1EMWR	4" Downlight, 2-in-1 Install	White	60W	2700K-5000K	120V	745	8	080083266470	2508445
CJB6099FS1EMWR	6" Downlight, 2-in-1 Install	White	70W	2700K-5000K	120V	920	9	080083266494	2508446
CJB4069FS1EMWR-6PK	4" Downlight, 2-in-1 Install (6-Pack)	White	60W	2700K-5000K	120V	745	8	080083266517	2508445
CJB6099FS1EMWR-6PK	6" Downlight, 2-in-1 Install (6-Pack)	White	70W	2700K-5000K	120V	920	9	080083266531	2508446
CJB4069FS1EMWR-12P	4" Downlight, 2-in-1 Install (12-Pack)	White	60W	2700K-6500K	120V	745	8	080083266555	2508445
CJB6099FS1EMWR-12P	6" Downlight, 2-in-1 Install (12-Pack)	White	70W	2700K-6500K	120V	920	9	080083266579	2508446
CJB4069FS1EMW	4" Downlight, Canless Only	White	60W	2700K-5000K	120V	745	8	080083266234	2508445
CJB6099FS1EMW	6" Downlight, Canless Only	White	70W	2700K-5000K	120V	920	9	080083266258	2508446
CJB4069FS1EMW-6PK	4" Downlight (6-Pack), Canless Only	White	60W	2700K-5000K	120V	745	8	080083266272	2508445
CJB6099FS1EMW-6PK	6" Downlight (6-Pack), Canless Only	White	70W	2700K-5000K	120V	920	9	080083266296	2508446
CJB4069FS1EMW-12PK	4" Downlight (12-Pack), Canless Only	White	60W	2700K-5000K	120V	745	8	080083266418	2508445
CJB6099FS1EMW-12PK	6" Downlight (12-Pack), Canless Only	White	70W	2700K-5000K	120V	920	9	080083266432	2508446

RLFR Fire-rated Recessed Baffle Trim

CANLESS DOWNLIGHTS - 4" & 6"

- Prevent the passage of flames & toxic gases for up to 2 hours
- Die-cast aluminum baffle trim and curved lens
- 5 Color Field-Selectable in 27/30/35/40/5000K
- Includes LED downlight and remote driver/junction box with mounting bar
- 5% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI

New! Available in August

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
RLFRC4FS	4" Fire Rated Baffle Downlight	White	70W	2700K-5000K	120V	1,000	11	080083295838	Pending
RLFRC4FSMBB	4" Fire Rated Baffle Downlight	Black	70W	2700K-5000K	120V	900	11	080083295876	Pending
RLFRC6FS	6" Fire Rated Baffle Downlight	White	75W	2700K-5000K	120V	1,300	13	080083295852	Pending
RLFRC6FSMBB	6" Fire Rated Baffle Downlight	Black	75W	2700K-5000K	120V	1,300	13	080083295890	Pending

HALO® SURFACE MOUNT DOWNLIGHTING

Suitable for a variety of applications!

- Below the ceiling installation with no plates or clips required
- Designed for square, octagon, pancake or round junction boxes
- Ideal for closets, storage areas, attics and basements

Quick and Easy Installation



HALO SURFACE MOUNT DOWNLIGHT PRODUCT SELECTION GUIDE

Good — Better — Best

		HLCE	HLS	JBD	SMD	SLD
FEATURES/PERFORMANCE	**Size / Shape**	4", 6" Round	4", 6", 9" Motion Round	4" Round, Square	4", 6", 12" Round, Square	4", 6" Round
	Trim & Lens	Curved Trim & Lens	Curved Trim with chamfered edge & Curved Lens	Interchangeable Flat/Baffle, Round/Square Trims or Full Lens Diffuser	Square-Edge Trim & Flat Lens	Beveled Trim & Flat Low-glare Prismatic Lens
	Max Lumens (By size @ 3000K)	820, 965	945, 1,330	715	740, 790, 2,240	635, 1,300
	Color Temperatures (CCT)	**5 CCT** 27/30/35/40/5000K **Dedicated:** 3000K, 4000K, 5000K	**5 CCT** 27/30/35/40/5000K **Dedicated:** 3000K, 4000K, 5000K	**5 CCT** 27/30/35/ 40/5000K	**5 CCT** 27/30/35/ 40/5000K	**5 CCT** 27/30/35/ 40/5000K
CONTROL	**Dimming Phase Cut (LE/TE) / 0-10V**	10% Phase Cut	10% Phase Cut	5% Phase Cut	5% Phase Cut, 0-10V	5% Phase Cut, 0-10V
	Estimated Life Hours	35,000	35,000	50,000	50,000	50,000
	Input Voltage	120V	120V	120V	120V, 120-277V	120V, 120-277V
HARDWARE	**Decorative Overlays[1]**	✔	✔	✔	✔	✔

[1] Matte Black, Tuscan Bronze, Satin Nickel, Paintable Matte White.

SLD Beveled Edge

SURFACE MOUNT DOWNLIGHTS - 4" & 6"

- Low profile surface mount downlight with sleek beveled edge and glare-reducing flat lens
- Ceiling or wall mounting in compatible junction boxes or retrofit into recessed housings
- 5 Color Field-Selectable in 27/30/35/40/5000K
- Includes LED Downlight and j-box mounting and wiring hardware (6" includes housing retrofit kit)
- 5% Dimming (Phase Cut or 0-10V), 50,000 hrs, 90+ CRI

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
SLDSL4069S1EMWR	4" Surface Downlight	White	60W	2700K-5000K	120V	635	9	080083153107	2366149
SLDSL6069S1EMWR	6" Surface Downlight	White	60W	2700K-5000K	120V	635	9	080083153121	2366163
SLD6129S1EMWR	6" Surface Downlight	White	75W	2700K-5000K	120V	1,300	15	080083153145	2373952
SLD6129SE010MWR	6" Surface Downlight (0-10V)	White	75W	2700K-5000K	120-277V	1,300	15	080083153169	2373954
SLDACCKIT	4" and 6" SLD Accessory Kit	N/A	N/A	N/A	N/A	N/A	N/A	080083159819	2373954

SMD Square Edge

SURFACE MOUNT DOWNLIGHTS - 4", 6", & 12"

- Round or square surface mount downlight with squared edge design
- Ceiling or wall mounting in compatible junction boxes or retrofit into recessed housings
- 5 Color Field-Selectable in 27/30/35/40/5000K
- Includes LED Downlight, j-box mounting and wiring hardware, and housing retrofit kit
- 5% Dimming (Phase Cut or 0-10V), 50,000 hrs, 90+ CRI

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
SMD4R69SWH	4" Surface Mount, Round	White	65W	2700K-5000K	120V	735	9	080083020904	2365919
SMD4S69SWH	4" Surface Mount, Square	White	65W	2700K-5000K	120V	740	9	080083020928	2365921
SMD6R69SWH	6" Surface Mount, Round	White	65W	2700K-5000K	120V	755	9	080083020942	2365923
SMD6S69SWH	6" Surface Mount, Square	White	65W	2700K-5000K	120V	790	9	080083020966	2366348
SMD12R209SWHE	12" Surface Mount, Round (0-10V)	White	150W	2700K-5000K	120-277V	2,240	27	080083138005	N/A

JBD Slim

SURFACE MOUNT DOWNLIGHTS - 4"

- Ultra-thin surface mount downlight with smooth flat lens
- Ceiling or wall mounting in compatible 4" junction boxes or recessed housings
- Interchangeable round, square, and full-lensed designer trims in multiple finishes
- 5 Color Field-Selectable in 27/30/35/40/5000K
- Includes LED Downlight, j-box mounting and wiring hardware, and housing retrofit kit in non-California versions
- 5% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
JBD4079FS1EWH	4" Slim Light w/ Matte White Trim	White	65W	2700K-5000K	120V	715	10	080083283514	2567962
JBD4079FS1EWH-CA	4" Slim Light w/ Matte White Trim, CA T20	White	65W	2700K-5000K	120V	715	10	080083285631	2567961

Accessories (optional)

Catalog Number	Description	Finish	UPC
JBD4TRMMW	4" Round Flat Trim	Matte White	080083283538
JBD4TRMMB	4" Round Flat Trim	Matte Black	080083283590
JBD4TRMSN	4" Round Flat Trim	Satin Nickel	080083283552
JBD4TRMTBZ	4" Round Flat Trim	Tuscan Bronze	080083283576
JBD4STRMMW	4" Square Flat Trim	Matte White	080083285679
JBD4STRMMB	4" Square Flat Trim	Matte Black	080083285730
JBD4STRMSN	4" Square Flat Trim	Satin Nickel	080083285693
JBD4STRMTBZ	4" Square Flat Trim	Tuscan Bronze	080083285716
JBD4TRMMWB	4" Round Baffle Trim	Matte White	080083291311
JBD4TRMMBB	4" Round Baffle Trim	Matte Black	080083291373
JBD4TRMSNB	4" Round Baffle Trim	Satin Nickel	080083291335
JBD4TRMTBZB	4" Round Baffle Trim	Tuscan Bronze	080083291359
JBD4STRMMWB	4" Square Baffle Trim	Matte White	080083291397
JBD4STRMMBB	4" Square Baffle Trim	Matte Black	080083291458
JBD4STRMSNB	4" Square Baffle Trim	Satin Nickel	080083291410
JBD4STRMTBZB	4" Square Baffle Trim	Tuscan Bronze	080083291434
JBD4DIFF	4" Full Lens Diffuser	Diffuser	080083283613

HLS Disk Lights

SURFACE MOUNT DOWNLIGHTS - 4", 6", & 9"

- Wet-rated ultra-thin disk light with chamfered rim (9" motion sensing version available)
- Installs in most 3-1/2" or 4" ceiling junction and pancake boxes (or retrofits into housings)
- 5 Color Field-Selectable in 27/30/35/40/5000K; dedicated in 3000K, 4000K, or 5000K
- Includes LED Downlight, j-box mounting and wiring hardware, and housing retrofit kit in non-California versions
- 10% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI
- NEW! Decorative overlays are available through MarketPro online

Selectable 5-CCT (Available in August, 2024)

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
HLS4079FS1E-6BP	4" Disk Light (6-Pk)	White	65W	2700K-5000K	120V	750	9	080083286980	3531006
HLS4079FS1E-12BP	4" Disk Light (12-Pk)	White	65W	2700K-5000K	120V	750	9	080083287000	3531006
HLS6099FS1E-6BP	6" Disk Light (6-Pk)	White	70W	2700K-5000K	120V	900	10.6	080083287024	3531008
HLS6099FS1E-12BP	6" Disk Light (12-Pk)	White	70W	2700K-5000K	120V	900	10.6	080083287048	3531008
HLS9129FS1E	9" Disk Light	White	75W	2700K-5000K	120V	1,200	16.1	080083287062	N/A
HLS9129FS1E-CA	9" Disk Light, CA T20	White	75W	2700K-5000K	120V	1,200	16.1	080083287086	N/A
HLSMS9129FS1E	9" Disk Light with Motion Sensor	White	75W	2700K-5000K	120V	1,200	16	080083287109	N/A
HLSMS9129FS1E-CA	9" Disk Light with Motion Sensor, CA T20	White	75W	2700K-5000K	120V	1,200	16	080083287123	N/A

Dedicated CCT & Lumens

Catalog Number	Description	Finish	Replaces	CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
HLS4079301EWH-6BP	4" Disk Light (6-Pk)	White	70W	3000K	120V	765	12	080083256662	2401097
HLS4079301EWH-12BP	4" Disk Light (12-Pk)	White	70W	3000K	120V	765	12	080083256723	2401097
HLS4079301EWH-6BP-CA	4" Disk Light (6-Pk), CA T20	White	70W	3000K	120V	765	12	080083257041	2401093
HLS4079301EWH-12BP-CA	4" Disk Light (12-Pk), CA T20	White	70W	3000K	120V	765	12	080083257102	2401093
HLS4079401EWH-6BP	4" Disk Light (6-Pk)	White	75W	4000K	120V	765	12	080083256686	2401095
HLS4079401EWH-6BP-CA	4" Disk Light (6-Pk), CA T20	White	75W	4000K	120V	765	12	080083257065	2401096
HLS4079501EWH-6BP	4" Disc Light (6-Pack)	White	70W	5000K	120V	790	12	080083256709	2401094
HLS4079501EWH-6BP-CA	4" Disk Light (6-Pk), CA T20	White	70W	5000K	120V	790	12	080083257089	2401094
HLS6099301EWH-6BP	6" Disc Light (6-Pack)	White	70W	3000K	120V	925	15.4	080083256785	2401101
HLS6099301EWH-12BP	6" Disc Light (12-Pack)	White	70W	3000K	120V	925	15.4	080083256846	2401101
HLS6099301EWH-6BP-CA	6" Disk Light (6-Pk), CA T20	White	70W	3000K	120V	925	15.4	080083257164	2401103
HLS6099301EWH-12BP-CA	6" Disk Light (12-Pk), CA T20	White	70W	3000K	120V	925	15.4	080083257225	2401103
HLS6099401EWH-6BP	6" Disc Light (6-Pack)	White	75W	4000K	120V	945	15.4	080083256808	2401102
HLS6099401EWH-6BP-CA	6" Disk Light (6-Pk), CA T20	White	75W	4000K	120V	945	15.4	080083896462	2401102
HLS6099501EWH-6BP	6" Disc Light (6-Pack)	White	75W	5000K	120V	970	15.6	080083256822	2401103
HLS9129301EWH	9" Disc Light	White	75W	3000K	120V	1,245	18	080083256907	2401113
HLS9129401EWH	9" Disc Light	White	75W	4000K	120V	1,295	18	080083256921	2401111
HLS9129301EWH-CA	9" Disk Light, CA T20	White	75W	3000K	120V	1,245	18	080083257287	2401110
HLS9129401EWH-CA	9" Disk Light, CA T20	White	75W	4000K	120V	1,295	18	080083257300	2401112
HLSMS9129301EWH	9" Disk Light with Motion Sensor	White	75W	3000K	120V	1,265	18	080083256969	2401115
HLSMS9129401EWH	9" Disk Light with Motion Sensor	White	75W	4000K	120V	1,330	18	080083256983	2401119
HLSMS9129301EWH-CA	9" Disk Light with Motion Sensor, CA T20	White	75W	3000K	120V	1,265	18	080083257348	2401120
HLSMS9129401EWH-CA	9" Disk Light with Motion Sensor, CA T20	White	75W	4000K	120V	1,330	18	080083257362	2401117

HLCE Disk Lights

SURFACE MOUNT DOWNLIGHTS - 4" & 6"

- Damp-rated ultra-thin surface mount disk downlight with fast installation
- Installs in most 3-1/2" or 4" ceiling junction and pancake boxes (or retrofits into housings)
- 5 Color Field-Selectable in 27/30/35/40/5000K; dedicated in 3000K, 4000K, or 5000K
- Includes LED Downlight, j-box mounting and wiring hardware, and housing retrofit kit in non-California versions
- 10% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI
- NEW! Decorative overlays are available through MarketPro online

seleCCTable colors

Selectable 5-CCT (Available in August, 2024)

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
HLCE4079FS1E	4" Disk Light (Damp-listed)	White	70W	2700K-5000K	120V	1040	9	80083286904	3477929
HLCE4079FS1E-12P	4" Disk Light (Damp-listed) (12-Pk)	White	70W	2700K-5000K	120V	1040	9	80083286706	3477930
HLCE4079FS1E-18P	4" Disk Light (Damp-listed) (18-Pk)	White	70W	2700K-5000K	120V	1040	9	80083286744	3477930
HLCE4079FS1E-CA	4" Disk Light (Damp-listed), CA T20	White	70W	2700K-5000K	120V	1040	9	80083286942	3477931
HLCE4079FS-12P-CA	4" Disk Light (Damp-listed) (12-Pk), CA T20	White	70W	2700K-5000K	120V	1040	9	80083286782	3477931
HLCE4079FS-18P-CA	4" Disk Light (Damp-listed) (18-Pk), CA T20	White	70W	2700K-5000K	120V	1040	9	80083286829	3477931
HLCE6129FS1E	6" Disk Light (Damp-listed)	White	75W	2700K-5000K	120V	1220	10	80083286928	3477933
HLCE6129FS1E-12P	6" Disk Light (Damp-listed) (12-Pk)	White	75W	2700K-5000K	120V	1220	10	80083286720	3477934
HLCE6129FS1E-18P	6" Disk Light (Damp-listed) (18-Pk)	White	75W	2700K-5000K	120V	1220	10	80083286768	3477934
HLCE6129FS1E-CA	6" Disk Light (Damp-listed), CA T20	White	75W	2700K-5000K	120V	1220	10	80083286966	3477932
HLCE6129FS-12P-CA	6" Disk Light (Damp-listed) (12-Pk), CA T20	White	75W	2700K-5000K	120V	1220	10	80083286805	3477932
HLCE6129FS-18P-CA	6" Disk Light (Damp-listed) (18-Pk), CA T20	White	75W	2700K-5000K	120V	1220	10	80083286843	3477932

Dedicated CCT & Lumens

Catalog Number	Description	Finish	Replaces	CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
HLCE4079301EWH-12P	4" Disc Light (Damp-listed) (12-Pack)	White	70W	3000K	120V	815	10.8	080083276806	2470915
HLCE4079301EWH-18P	4" Disc Light (Damp-listed) (18-Pack)	White	70W	3000K	120V	815	10.8	080083276844	2470915
HLCE407930-12P-CA	4" Disk Light (Damp-listed) (12-Pk), CA T20	White	70W	3000K	120V	815	10.8	080083276882	2470916
HLCE407930-18P-CA	4" Disk Light (Damp-listed) (18-Pk), CA T20	White	70W	3000K	120V	815	10.8	080083276929	2470916
HLCE4079401EWH-12P	4" Disc Light (Damp-listed) (12-Pack)	White	70W	4000K	120V	810	10.3	080083287208	2839424
HLCE4079401EWH-18P	4" Disc Light (Damp-listed) (18-Pack)	White	70W	4000K	120V	810	10.3	080083287246	2839424
HLCE407940-12P-CA	4" Disk Light (Damp-listed) (12-Pk), CA T20	White	70W	4000K	120V	810	10.3	080083287284	2839423
HLCE407940-18P-CA	4" Disk Light (Damp-listed) (18-Pk), CA T20	White	70W	4000K	120V	810	10.3	080083287321	2839423
HLCE4079501EWH-12P	4" Disc Light (Damp-listed) (12-Pack)	White	70W	5000K	120V	820	10.4	080083287369	2839422
HLCE4079501EWH-18P	4" Disc Light (Damp-listed) (18-Pack)	White	70W	5000K	120V	820	10.4	080083287406	2839422
HLCE6099301EWH-12P	6" Disc Light (Damp-listed) (12-Pack)	White	75W	3000K	120V	940	13.6	080083276820	2470917
HLCE6099301EWH-18P	6" Disc Light (Damp-listed) (18-Pack)	White	75W	3000K	120V	940	13.6	080083276868	2470917
HLCE609930-12P-CA	6" Disk Light (Damp-listed) (12-Pk), CA T20	White	75W	3000K	120V	940	13.6	080083276905	2470918
HLCE609930-18P-CA	6" Disk Light (Damp-listed) (18-Pk), CA T20	White	75W	3000K	120V	940	13.6	080083276943	2470918
HLCE6099401EWH-12P	6" Disc Light (Damp-listed) (12-Pack)	White	70W	4000K	120V	990	13.2	080083287222	2839426
HLCE6099401EWH-18P	6" Disc Light (Damp-listed) (18-Pack)	White	70W	4000K	120V	990	13.2	800083287260	2839426
HLCE609940-12P-CA	6" Disk Light (Damp-listed) (12-Pk), CA T20	White	70W	4000K	120V	990	13.2	080083287307	2839425
HLCE609940-18P-CA	6" Disk Light (Damp-listed) (18-Pk), CA T20	White	70W	4000K	120V	990	13.2	080083287345	2839425
HLCE6099501EWH-12P	6" Disk Light (Damp-listed) (12-Pk)	White	70W	5000K	120V	985	13.1	080083287383	2839427
HLCE6099501EWH-18P	6" Disk Light (Damp-listed) (18-Pk)	White	70W	5000K	120V	985	13.1	080083287420	2839427

FM Full-lensed

FLUSHMOUNTS - 8", 11", & 15"

- LED flushmount installs in most 3-1/2" or 4" junction boxes or retrofits 5" and 6" recessed housings
- Round die-formed lens design with 360-degrees of light distribution
- 3 Color Field-Selectable in 30/40/5000K (8" fixture) or 5 Color Field-Selectable in 27/30/35/40/5000K (11" & 15" fixtures)
- Includes LED Downlight, j-box mounting and wiring hardware, and housing retrofit kit
- 10% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
FM89S1EWHR	8" Flushmount	White	70W	3000K-5000K	120V	920	10	080083256587	2399871
FM119S1EWHR	11" Flushmount	White	75W	2700K-5000K	120V	1,250	18	080083257706	2399874
FM159S1EWHR	15" Flushmount	White	100W	2700K-5000K	120V	1,510	14	080083257720	2399877

HALO® 4" Junction Box Housing

The solution for new construction fire-rated ceilings

Suitable for use in fire-rated ceiling construction that requires up to 2-hour protection per International Building Code Section 714.

Compatable with all 4" HALO LED Trims

Compatable with any HALO Surface Mount Fixture

Scan for details

JBox Housing - 4"

- For use with all 4" HALO Recessed LED Trims and any HALO Surface Mount Fixture
- Meets UL514A Metallic Outlet Box
- Pass-N-Thru™ hangar bars allow for toolless shortening in tight spaces (7" to 24")
- For installation in insulated contact (IC) and non-IC ceilings
- All-Nail!™ preinstalled nail and integral T-grid clips allow for easy single-person installation

Catalog Number	Description	Voltage	UPC
JB4FR2	4" Junction Box Housing for use in standard or fire-rated ceilings	120-277V	080083290307

1. Use with T24-listed LED trims or surface mount fixtures.
2. Can be used to meet requirement when used with AIR-TITE or wet location-listed LED trim or surface mount fixture.

HALO® RECESSED LED TRIMS

Maximum energy savings with easy installation

- Compatible with most recessed housings and sizes
- Suitable for new construction and remodel
- Replaces traditional incandescent lighting

Quick and Easy Installation

HALO RECESSED LED TRIM PRODUCT SELECTION GUIDE

Good | Better | Best

		DOWNLIGHTS			Adjustables
		LT	RL & RL Night Light	RSQ	RA
FEATURES / PERFORMANCE	LED Trim Type	Downlights	Downlights	Square Downlights	Gimbal Adjustables (35° Tilt/360° Rotation)
	Size & Shape	4", 5"/6" Round	3", 4", 5"/6" Round	4", 5", 6" Square	3", 4", 5"/6" Round
	Trim & Lens	Baffle or Smooth w/ Flat Lens	Baffle w/ Curved Lens (**NL** has Transparent Trim)	Baffle w/ Flat Lens	Baffle w/ Flat Lens
	Max Lumens (By size @ 3000K)	570, 645, 785	610, 900, 1,200 (Lumen Select, Dedicated) (**NL**: 775, 1065)	790, 775	710
	Color Temperatures (CCT)	**5 CCT** 27/30/35/40/5000K **Dedicated:** 3000K	**5 CCT w/ D2W** D2W/27/30/35/ 40/5000K (**NL**: 2000K)	**5 CCT w/ D2W** D2W/27/30/35/ 40/5000K	**5 CCT w/ D2W** D2W/27/30/35/ 40/5000K
CONTROL	Dimming Phase Cut (LE/TE)	10%	5%[1]	5%	5%
	Estimated Life Hours	50,000	70,000 (**NL**: 50,000)	50,000	50,000
	Input Voltage	120V	120V, 120-277V	120V	120V
HARDWARE	Decorative Overlays[2]		✔	✔	

[1] RL LED Trims are also available in Smart Wi-Fi Connected by WiZ Pro versions.
[2] Matte Black, Tuscan Bronze, Satin Nickel, Paintable Matte White.

RL Recessed Baffle

LED TRIMS - 3", 4", & 5"/6"

- Delivers long life, exceptional performance, selectable lumens, and installs into almost any recessed housing
- Die-cast aluminum baffle trim and curved lens reduces glare and provides a traditional downlight appearance
- 6-Position Switch: 5 Color Field-Selectable (27/30/35/40/5000K) + Dim-to-Warm (3000K dims to 1800K)
- Includes LED Trim, E26 medium socket adapter, and mounting hardware (3" & 4" - friction blades and 5"/6" - torsion springs & friction blades)
- 5% Dimming (Phase Cut LE/TE), 70,000 hrs, 90+ CRI

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
RL3059FSD2W1EWH	3" Baffle Trim	White	60W	2700K-5000K+D2W	120V	610	6.4W	080083257669	2402944
RL4LS9FSD2W1EWH	4" Baffle Trim	White	60-70W	2700K-5000K+D2W	120V	Lumen Select 600-900	7/11	080083257683	2402940
RL56069FSD2W1EWH	5"/6" Baffle Trim	White	60W	2700K-5000K+D2W	120V	700	8	080083818525	2356074
RL56LS9FSD2W1EWH	5"/6" Baffle Trim	White	70-75W	2700K-5000K+D2W	120V	Lumen Select 900-1,200	8.5/14	080083818549	2354587

LT Recessed Baffle or Smooth Splay

LED TRIMS - 4" & 5"/6"

- The LT LED trims offer a cost-saving alternative to the RL Series
- Dead-front plastic fixture with either baffle or smooth splay trims and smooth flat lens
- **LT** - 5 Color Field-Selectable in 27/30/35/40/5000K; **LT/LTE** - dedicated in 3000K
- Includes LED Trim, E26 medium socket adapter, and mounting hardware (4" - friction blades; 5"/6" - torsion springs - only fits housings with spring receivers)
- 10% Dimming (Phase Cut LE/TE), 35,000 hrs, 90+ CRI

Selectable 5-CCT

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
LTSS4069FS1EWHR	4" Smooth Splay Trim	White	60W	2700K-5000K	120V	650	7.2	080083283989	3462891
LT4069FS1EWHR	4" Baffle Trim	White	60W	2700K-5000K	120V	680	7	080083283965	2508121
LT4099FS1EWHR	4" Baffle Trim	White	70W	2700K-5000K	120V	1030	9	080083284009	2508243
LTSS56079FS1EWHR	5"/6" Smooth Splay Trim	White	65W	2700K-5000K	120V	750	8.3	080083284061	3462894
LT56079FS1EWHR	5"/6" Baffle Trim	White	60W	2700K-5000K	120V	805	7	080083284047	2508127
LT56129FS1EWHR	5"/6" Baffle Trim	White	75W	2700K-5000K	120V	1345	12	080083284085	2508244

Dedicated CCT & Lumens

Catalog Number	Description	Finish	Replaces	CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
LT460WH6930R	4" Baffle Trim	White	60W	3000K	120V	620	8	080083746163	2309297
LT460WH6930R-CA	4" Baffle Trim, CA T20	White	60W	3000K	120V	665	7	080083900893	2257770, 2277227
LT560WH6930R	5"/6" Baffle Trim	White	60W	3000K	120V	750	10	080083746187	2309300
LT560WH6930R-CA	5"/6" Baffle Trim, CA T20	White	60W	3000K	120V	745	8	080083900954	2252183, 2277232
LTE46930-12PK	4" Baffle Trim (12-Pk)	White	60W	3000K	120V	620	8	080083285761	2856270
LTE46930-18PK	4" Baffle Trim (18-Pk)	White	60W	3000K	120V	620	8	080083285785	2856270
LTE566930-12PK	5"/6" Baffle Trim (12-Pk)	White	60W	3000K	120V	700	10	080083285808	2856271
LTE566930-18PK	5"/6" Baffle Trim (18-Pk)	White	60W	3000K	120V	700	10	080083285822	2856271

RA Recessed Adjustable Gimbal Baffle

LED TRIMS - 3", 4", & 5"/6"

- Adjustable retrofit aims lighting where you want it with 360° of rotations and 35° of tilt and installs in almost any recessed housing
- Regressed die-cast aluminum baffle trim reduces glare and improves cutoff
- 6-Position Switch: 5 Color Field-Selectable (27/30/35/40/5000K) + Dim-to-Warm (3000K dims to 1800K)
- Included: Adjustable LED Trim, E26 medium socket adapter, and mounting hardware (4" - friction blades; 5"/6" - torsion springs & friction blades)
- 5% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
RA3059FSD2W1EWH	3" Adjustable Gimbal Trim	White	60W	2700K-5000K + D2W	120V	570	6	080083900954	2252183, 2277232
RA4LS9FSD2W1EWH	4" Adjustable Gimbal Trim	White	60W	2700K-5000K + D2W	120V	Lumens Select 600-900	6/9	080083282975	2567964
RA56LS9FSD2W1EWH	5"/6" Adjustable Gimbal Trim	White	60W	2700K-5000K + D2W	120V	Lumens Select 600-900	6/9	080083282999	2567965

RSQ Square Recessed Baffle

LED TRIMS - 4", 5", & 6"



- Elegant integrated LED trims with a square dead-front baffle trim and flat lens
- The rotatable trim makes installation and fixture alignment a breeze
- 6-Position Switch: 5 Color Field-Selectable (27/30/35/40/5000K) + Dim-to-Warm (3000K dims to 1800K)
- Includes LED Trim, E26 medium socket adapter, and mounting hardware
- 5% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	Energy Star ID
RSQ4LS9FSD2W1EWH	4" Square Baffle Trim	White	60W-70W	2700K-5000K + D2W	120V	830-1,000	6.5/10	080083282531	2333094
RSQ5LS9FSD2W1EWH	5" Square Baffle Trim	White	60W-70W	2700K-5000K + D2W	120V	830-1,000	6.5/10	080083282555	2333267
RSQ6LS9FSD2W1EWH	6" Square Baffle Trim	White	60W-70W	2700K-5000K + D2W	120V	830-1,000	7/11	080083282579	2333093

Accessories (optional)

Catalog Number	Description	Finish	UPC
RSQ4TRMWH	4" Square Trim	Matte White	080083282593
RSQ4TRMMB	4" Square Trim	Matte Black	080083282753
RSQ4TRMSN	4" Square Trim	Satin Nickel	080083282715
RSQ4TRMTBZ	4" Square Trim	Tuscan Bronze	080083282739
RSQ5TRMWH	5" Square Trim	Matte White	080083282777
RSQ5TRMMB	5" Square Trim	Matte Black	080083282838
RSQ5TRMSN	5" Square Trim	Satin Nickel	080083282791
RSQ5TRMTBZ	5" Square Trim	Tuscan Bronze	080083282814
RSQ6TRMWH	6" Square Trim	Matte White	080083282852
RSQ6TRMMB	6" Square Trim	Matte Black	080083282913
RSQ6TRMSN	6" Square Trim	Satin Nickel	080083282876
RSQ6TRMTBZ	6" Square Trim	Tuscan Bronze	080083282890

Paintable Matte White

Matte Black

Satin Nickel



Tuscan Bronze

HALO UNDER CABINET

Sleek and Seamless

This low-profile design remains invisible to the eye while providing uniform illumination on the task. With maximum energy savings and contractor friendly installation features, the HU11 series is ideal for commercial and residential projects.

HU11 LED Under Cabinet

Selectable CCT

3 seleCCTable™ colors



2700K

3000K

4000K

With a simple slide of the SeleCCTable color temperature switch, users have the flexibility to choose between 2700K, 3000K and 4000K CCT to customize the color temperature to suit their specific lighting need.

HU11 LED Under Cabinet

9", 18", 24", & 36"

- Sleek, low-profile LED under cabinet with less than 1" profile
- 3 Color Field-Selectable in 27/30/4000K
- 5% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI

seleCCTable colors

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
HU1109D9SP	9" Under Cabinet	White	17W INC	2700K-4000K	120V	300	5	080083875788	2341224
HU1118D9SP	18" Under Cabinet	White	33W INC	2700K-4000K	120V	560	8	080083875863	2341217
HU1124D9SP	24" Under Cabinet	White	44W INC	2700K-4000K	120V	785	11	080083875948	2341218
HU1136D9SP	36" Under Cabinet	White	56W INC	2700K-4000K	120V	1,125	16	080083876020	2341219

PR Series Downlights
p. 31

HCD Pro System Downlights
p. 31

HALO®
COMMERCIAL
LED DOWNLIGHTS

Commercial LED Lighting provides the right balance of visual comfort and energy efficiency, with proven and tested products that always meet commercial code and never break the budget.

PR SeleCCTable™ Series

COMMERCIAL DOWNLIGHTS - 4", 6", & 8"

- 4", 6", & 8" self-flanged, lensed recessed LED downlights
- Available in new construction and retrofit
- Field-Selectable Lumens: 1,000/1,500/2,000
- 3 Color Selectable in 30/35/4000K; 80 CRI
- Universal input 120V-277V with 0-10V 1% dimming

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
PR4FS12D010	4" Housing	N/A	18W-32W CFL	N/A	120-277V	Lumen Select 1,000-2,000	20	080083131839	2353549
PR4M12MD8FSMW	4" LED Module	Matte White	18W-32W CFL	3000K-4000K	120-277V	Lumen Select 1,000-2,000	N/A	080083060795	2353549
PR4RFS12D010	4" Retrofit Kit	N/A	18W-32W CFL	N/A	120-277V	Lumen Select 1,000-2,000	22	080083132683	2353549
PR6FS12D010	6" Housing	N/A	18W-32W CFL	N/A	120/277V	Lumen Select 1,000-2,000	21	080083892174	2328770
PR6M12MD8FSMW	6" LED Module	Matte White	18W-32W CFL	3000K-4000K	N/A	Lumen Select 1,000-2,000	N/A	080083891122	2345484
PR6RFS12D010	6" Retrofit Kit	N/A	18W-32W CFL	N/A	120V-277V	Lumen Select 1,000-2,000	22	080083891726	2345457, 2345484
PR820D010	8" Housing	N/A	18W-32W CFL	N/A	120-277V	Lumen Select 1,000-2,000	22	080083771769	2289673
PR8M12MDMW	8" LED Module	Matte Finish	18W-32W CFL	3000K-4000K	120-277V	Lumen Select 1,000-2,000	N/A	080083772926	2289581
PR8R20D010	8" Retrofit Kit	N/A	18W-32W CFL	N/A	120-277V	Lumen Select 1,000-2,000	22	080083772179	2289681

A complete downlight includes housing or retrofit kit + LED Module.
The MarketPro program offers our most popular product configurations. For additional configurations visit cooperlighting.com.

HCD Pro Direct Mount System

COMMERCIAL DOWNLIGHTS - 4", 6", & 8"

Kit includes interchangeable round or square reflector

- A completely modular LED downlighting system built on a set of fixture kits that fit any size, shape, or distribution of HCD reflector
- 4", 6", & 8" install-from-below self-flanged, lensed LED downlights
- Available in direct mount for retrofit/remodel with mounting frames for new construction
- Field-Selectable Lumens: 500/750/1,000 or 1,500/2,000/2,500
- 5 Color Field-Selectable in 27/30/35/40/5000K; 90 CRI

JBox LED Fixture Kits (New! Available in August)

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	Energy Star ID
HCDJBLS510CSD	J-Box LED Fixture Kit (0-10V)	White	60-75W INC, 13-26W CFL	2700K-5000K	120-277V	500-1,000	12.5W at 120V 12.6W at 277V	080083297962	Pending
HCDJBLS1525CSD	J-Box LED Fixture Kit (0-10V)	White	100-150W INC, 26-42W CFL	2700K-5000K	120-277V	1,500-2,500	25.9W at 120V 25.9W at 277V	080083297979	Pending

Interchangeable Reflectors

Catalog Number	Description	UPC
HCD4TRH	4" Round Reflector	080083278053
HCD4TSQH	4" Square Reflector	080083278299
HCD6TRH	6" Round Reflector	080083278534
HCD6TSQH	6" Square Reflector	080083278770
HCD8TRH	8" Round Reflector	080083279012
HCD8TSQH	8" Square Reflector	080083279258

Accessory New Construction Mounting Frames

Catalog Number	Description	UPC
HCD4MFR	4" Round Basic New Construction Mounting Frame	080083298440
HCD6MFR	6" Round Basic New Construction Mounting Frame	080083298600
HCD8MFR	8" Round Basic New Construction Mounting Frame	080083298761
HCD4MFS	4" Square Basic New Construction Mounting Frame	080083298525
HCD6MFS	6" Square Basic New Construction Mounting Frame	080083298686
HCD8MFS	8" Square Basic New Construction Mounting Frame	080083298846

A complete downlight includes LED Fixture Kit + Round/Square Reflector. Include a mounting frame for new construction applications.
The MarketPro program offers our most popular product configurations. For additional configurations visit cooperlighting.com.

QUICK SPEC

Stay ahead of demanding **project schedules**

We've consolidated all legacy quick shipment programs (i.e. Rapid Response, Quick Ship, Rapid Ship) into one program. Quick Spec is your solution for fast-moving construction projects that require quick access to information, a broad portfolio of lighting and control products plus **shipping in 10 days or less.**

QUICK **INFORMATION**

Save time finding important information, assets, and tools for your projects.

QUICK **SOLUTIONS**

Tap into a broad portfolio of spec grade products in one location.

QUICK **SHIPPING**

The 10-day lead time on select products caters to fast-moving construction projects.

Look for the Quick Spec logo above the MarketPro product tables identifying qualified products.



Catalog Number	Description	Replaces Up To	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
LHBS-1218-UNV-L84050-U	Lensed HB Select, Medium Distr	4-T8, 3-T5HO, 175W MH	4000K-5000K	120-277V	13,000-18,000	85-124	080083274741	S-J1KSFT
LHBS-1824-UNV-L84050-U	Lensed HB Select, Medium Distr	6-T5HO, 8-T8, 400W MH	4000K-5000K	120-277V	18,800-24,000	119-156	080083275625	S-24YMLJ
LHBS-2436-UNV-L84050-U	Lensed HB Select, Medium Distr	8-T5HO, 10-T8, 750W MH	4000K-5000K	120-277V	24,388-36,000	155-246	080083276141	S-EUKB89

CLICK HERE to learn more about Quick Spec.

Flat Panels
p. 34-36

Troffers
p. 36-37

Strip Lights
p. 37-39

Wraps
p. 39-40

METALUX

COMMERCIAL LED LIGHTING

Metalux Commercial features a wide selection of affordable yet aesthetically pleasing fixtures with an expanded offering of selectable color temperatures and lumen options.

CGT | CGTS Series

FLAT PANEL



- Affordable contractor LED panel with fixed or selectable configurations
- Fits in shallow plenums with room to spare; Thin 2 1/8 -inch height
- 3 Color Field-Selectable in 35/40/5000K and dedicated in 3500K, 4000K, 5000K
- 3 Field-Selectable lumens: Low, Medium or High settings
- Ideal for office spaces, education, healthcare and retail merchandising

Selectable CCT & Lumens

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
14CGTS-L3C3	1'x4' Recessed Panel	2-T8	3500K-5000K	120-277V	3,200-5,100	21/31/36	080083282517	S-3EJHF2
22CGTS-L3C3	2'x2' Recessed Panel	3-T8 17W, 2-U6T8	3500K-5000K	120-277V	2,500-4,900	21/29/39	080083194728	PL74TQBZR6SL
24CGTS-L3C3	2'x4' Recessed Panel	4-T8 32W	3500K-5000K	120-277V	3,700-6,800	27/39/51	080083194704	PL0ULJMKXBCH

Dedicated CCT & Lumens

Catalog Number	Description	Replaces	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
22CGT3535C	2'x2' Recessed Panel	3-T8	3500K	120-277V	3,449	32	080083880003	P6WE1HNZ
22CGT3540C	2'x2' Recessed Panel	3-T8	4000K	120-277V	3,582	32	080083880027	P0YGNM7S
24CGT4535C	2'x4' Recessed Panel	2-T8, 3-T8	3500K	120-277V	4,268	38	080083880089	P28JP113
24CGT4540C	2'x4' Recessed Panel	2-T8, 3-T8	4000K	120-277V	4,432	38	080083880102	PLTEVMIJ
24CGT5540C	2'x4' Recessed Panel	2-T8, 4-T8	4000K	120-277V	5,337	47	080083880188	P5F04P82

FP | FPS Series

FLAT PANEL

- Ultra-thin LED flat panel; Less than 2-inches height for shallow plenums
- 3 Color Field-Selectable in 30/35/4000K and dedicated in 3500K, 4000K
- Selectable switch to set color temperature, lumens and watts desired for task
- Refined visual optics, superior acrylic light guide; uniform corner to corner illumination
- Ideal for office spaces, schools, healthcare facilities and retail merchandising areas

Selectable CCT & Lumens

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
14FPSL1SCT3	1'x4' Recessed Panel	2-T8	3000K-4000K	120-277V	2,000-4,100	18/27/36	080083889440	PYJV3ZJZ
22FPSL2SCT3	2'x2' Recessed Panel	3-T8	3000K-4000K	120-277V	1,700-3,500	15/22/31	080083889402	PB32RP9H
24FPSL2SCT3	2'x4' Recessed Panel	2-T8, 3-T8	3000K-4000K	120-277V	3,100-6,300	27/40/56	080083889365	PZFJCMXS

Dedicated CCT & Lumens

Catalog Number	Description	Replaces	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
22FP3235C	2'x2' Recessed Panel	3-T8	3500K	120-277V	3,307	29	080083833528	PQC9IUIC
22FP3240C	2'x2' Recessed Panel	3-T8	4000K	120-277V	3,560	30	080083833542	PUOIG6S2
22FP4235C	2'x2' Recessed Panel	2-U6T8	3500K	120-277V	4,641	39	080083833580	P8HIK308
22FP4240C	2'x2' Recessed Panel	3-U6T8	4000K	120-277V	4,567	39	080083833603	PELH4PNQ
24FP4735C	2'x4' Recessed Panel	2-T8, 3-T8	3500K	120-277V	4,990	40	080083833641	PRZ2RGDY
24FP4740C	2'x4' Recessed Panel	2-T8, 3-T8	4000K	120-277V	4,858	40	080083833665	PGY6ID6B
24FP6440C	2'x4' Recessed Panel	3-T8, 4-T8	4000K	120-277V	6,611	59	080083833726	PIBWK9P9

Regress Mount & Uplift Kit

FLAT PANEL ACCESSORY

- 2" uplift kit with clean edges, powder coated white finish elevate the look of any space
- Soft bevel design for depth and improved glare control
- Compatible with all stocked Metalux panels and configurations (CGT/CGTS/FP/FPS)
- Flat Panel sold seperately

damp locatic

Catalog Number	Description	Compatible With	UPC
RMK2-22-W	2' x 2' Regress Kit	CGT/CGTS/FP/FPS Flat Panels	080083287185
RMK2-24-W	2' x 4' Regress Kit	CGT/CGTS/FP/FPS Flat Panels	080083288007

RBG Series

FLAT PANEL

- Architectural elegant 6-inch grid, 4-inch aperture fixture
- Recessed, surface or suspension mounting
- 3 Color Field-Selectable in 30/35/4000K; 80 CRI
- Lumen selectable: 500, 750 or 1,000 lumens per foot

damp location

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
2RBG6-SL1-L8SCT3	2' Length	2- F17T8, 2-F14T5	3000K-4000K	120-277V	500/750/1,000*	11/16/19	080083865826	N/A
4RBG6-SL1-L8SCT3	4' Length	2-F32T8, 1-F54T5HO, 2-F28T5	3000K-4000K	120-277V	500/750/1,000*	18/28/36	080083866465	S-30ZJ8K
8RBG6-SL1-L8SCT3	8' Length	2-F60T8, 2-F75T12	3000K-4000K	120-277V	500/750/1,000*	42/61/75	080083866502	N/A

*Lumens per ft.

Multi-Mount Selectable

FLAT PANEL

- Visually comforting panel mounts directly to the ceiling or wall reducing labor and material cost by removing the need for a surface mount kit
- Versatile mounting allows for surface, wall, recessed, or suspended with kit
- Selectable Color Temperatures in 90 CRI Standard: 2x2/2x4: 35/40/5000K I 6x4: 27/30/35/40/5000K
- Selectable Lumens: Low, Medium, High settings
- Ideal choice for commercial office, school, and healthcare spaces

damp location

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
4MMS6-L3C5-UNV	4'x6', Direct Mount Panel	2-T8 32W	2700K-5000K	120-277V	1,680-3,000	19/25/33	080083292028	Pending
22MMS-L3C3-UNV	2'x2', Direct Mount Panel	3-T8 32W	3500K-5000K	120-277V	2,400-4,800	21/28/42	080083292042	Pending
24MMS-L3C3-UNV	2'x4', Direct Mount Panel	4-T8 32W	3500K-5000K	120-277V	3,500-6,200	28/36/48	080083292059	Pending

Surround Frame Selectable

ILLUMINATED FRAME

- Architectural 1.5" illuminated modern frame enhances the look of any space
- Versatile mounting in existing T-grid using ceiling tile as the reflector, suspension also available with kit
- 4 Color Field-Selectable in 30/35/40/5000K
- Selectable Lumens- Low, Medium, High settings
- Ideal choice for commercial office, school, and healthcare spaces

Center of frame is open

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
22SFS-L3C4-UNV	2'x2', Surround Frame	3-T8 32W	3000K-5000K	120-277V	1,900-4,600	15/25/36	080083293124	Pending
24SFS-L3C4-UNV	2'x4', Surround Frame	4-T8 32W	3000K-5000K	120-277V	3,000-6,000	23/35/47	080083293148	Pending

Cruze ST Recessed | CZS Series

TROFFER

- Architectural center basket lens troffer with aesthetic appeal
- Latch-less design provides clean architectural look; Ribbed, frosted acrylic lens
- 3 Color Field-Selectable in 30/35/4000K and dedicated in 3500K, 4000K
- Ideal choice for commercial, institutional and healthcare facilities

Selectable CCT & Lumens

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
14CZSCT3-UNV	1'x4', Troffer	2-T8	3000K-4000K	120-277V	3,000-4,400	20-30	080083268443	S-5LPE0V
22CZSCT3-UNV	2'x2', Troffer	2-T5, 2-T8	3000K-4000K	120-277V	2,700-4,075	21-31	080083268467	S-QDP2J8
24CZSCT3-UNV	2'x4', Troffer	2-T8, 3-T8	3000K-4000K	120-277V	3,500-6,500	24-47	080083268481	S-MW0TCN

Dedicated CCT & Lumens

Catalog Number	Description	Replaces	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
22CZ2-32-UNV-L835-CD1-U	2'x2', Troffer	2-T5, 2-T8	3500K	120-277V	3,280	26	080083881185	**PL057CFW**
22CZ2-32-UNV-L840-CD1-U	2'x2', Troffer	2-T5, 2-T8	4000K	120-277V	3,280	26	080083881208	**PO3ODW27**
22CZ2-39-UNV-L835-CD1-U	2'x2', Troffer	3-T8, 4-T8, 2-T5HO	3500K	120-277V	3,943	34	080083881284	**P0AXJUK1**
22CZ2-39-UNV-L840-CD1-U	2'x2', Troffer	3- T8, 4-T8, 2-T5HO	4000K	120-277V	3,943	34	080083881307	**PU7UA6BJ**
24CZ2-40-UNV-L835-CD1-U	2'x4', Troffer	2-T8, 3-T8	3500K	120-277V	4,196	36	080083881505	**PUDYNNME**
24CZ2-40-UNV-L840-CD1-U	2'x4', Troffer	2-T8, 3-T8h	4000K	120-277V	4,196	36	080083881529	**PHYY5ZSG**
24CZ2-50-UNV-L835-CD1-U	2'x4', Troffer	2-T8, 2-T5	3500K	120-277V	5,015	48	080083881628	**POK3FN8Z**
24CZ2-50-UNV-L840-CD1-U	2'x4', Troffer	2-T8, 2-T5	4000K	120-277V	5,015	48	080083881642	**PI0YCHQ9**

Note: DLC Premium items are noted in bold.

Achieva™ Recessed

TROFFER

- Ultra slim 1.5" center basket design fits into the shallowest of plenums
- 3 Color Field-Selectable in 30/35/4000K in 80+ CRI
- 3 Selectable lumens in standard or HO options up to 8,150
- Ideal choice for commercial, institutional and healthcare facilities

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
14ARS-L3C3-UNV	1'x4', Troffer	2-T8	3500K-5000K	120-277V	2,800-4,600	20/26/33	080083282241	**S-N7LRJL**
22ARS-L3C3-UNV	2'x2', Troffer	2-T8, 2-T5	3500K-5000K	120-277V	2,750-4,300	20/26/33	080083282128	**S-N0X1OI**
22ARS-L3C3-HO-UNV	2'x2', Troffer, High Output	3-T5, 3-T8	3500K-5000K	120-277V	5,000-6,350	37/41/45	080083282203	S-Q6A8TB
24ARS-L3C3-UNV	2'x4', Troffer	2-T8, 3-T8	3500K-5000K	120-277V	3,400-6,250	24/33/46	080083282005	**S-EA9S16**
24ARS-L3C3-HO-UNV	2'x4', Troffer, High Output	3-T8, 2-T5HO	3500K-5000K	120-277V	6,300-8,150	46/52/58	080083282081	**S-SHLC4F**
22ARS-L3C3-UNV-MP4	2'x2', Troffer (4-Pack)	2-T5, 2-T8	3500K-5000K	120-277V	2,750-4,300	20/26/33	080083282388	**S-N0X1OI**
24ARS-L3C3-UNV-MP2	2'x4', Troffer (2-Pack)	2-T8, 3-T8	3500K-5000K	120-277V	3,400-6,250	24/33/46	080083282364	**S-EA9S16**

Note: DLC Premium items are noted in bold.

SLSTP Series

STRIP LIGHT

- LED strip light with decorative end caps and toolless lens removal
- Suitable for either single or continuous row application
- 3 Color Field-Selectable in 35/40/5000K and dedicated in 4000K
- Field-Selectable lumens 2,400 - 11,200 or dedicated up to 9300
- Impact resistant polycarbonate lens reduces maintenance

Selectable CCT & Lumens

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
4SLSTPSLC-UNV	4' Single Lens	2-T8 32W, 1-T5HO 54W	3500K-5000K	120/277V	2,400-6,000	18-46	080083174416	S-OICHU8
8SLSTPSLC-UNV	8' Single Lens	4-T8 32W, 2-T12 75W	3500K-5000K	120/277V	4,300-11,200	33-85	080083174423	S-7SKGJW

Dedicated CCT & Lumens

Catalog Number	Description	Replaces	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
4SLSTP4040DD-UNV	4' Single Lens	2-T8 32W, 1-T5HO 54W	4000K	120/277V	4,927	41	080083705825	PXZQGPN9C
8SLSTP8040DD-UNV	8' Single Lens	4-T8 32W, 2-T12 75W	4000K	120/277V	9,304	79	080083814787	P0K8WFD1

Sensor Kits

Catalog Number	Description	PIR Sensor	UPC
SLSTP MS00 KIT	SLSTP Field Installable Sensor KIT	100% / 50% / OFF	080083254200
SLSTP MS25 KIT	SLSTP Field Installable Sensor KIT	100% / 50% / Low (~30%)	080083254224

SNX Series

STRIP LIGHT

- Contemporary single frosted radial lens LED strip light
- Replaces two or four lamp fluorescents up to 150W
- 3 Color Field-Selectable in 35/40/5000K and dedicated in 4000K
- 3 Field-Selectable lumens: Low, Medium or High settings
- Single or continuous row via surface or suspended mount

damp location

DIMMABLE

selectable lumens

seleCCTable colors

Selectable CCT & Lumens

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
4SNX-SL3-LW-UNV-CC83-CD1-U	4' Single Lens	2-T8 32W, 1-T5HO 54W	3500K-5000K	120-277V	2,000-6,100	17-51	080083265107	S-VF0RKS
8TSNX-SL3-LW-UNV-CC83-CD2-U	8' Single Lens	4-T8 32W, 2-T12 75W	3500K-5000K	120-277V	4,100-12,000	34-101	080083265114	S-7FC8RS

Dedicated CCT & Lumens

Catalog Number	Description	Replaces	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
4SNX-45SL-LW-UNV-L840-CD1-U	4' Single Lens	2-T8 32W	4000K	120-277V	4,300	30	080083277605	S-CSWH9R
8TSNX-82SL-LW-UNV-L840-CD1-U	8' Single Lens	4-T8 32W	4000K	120-277V	7,700	53	080083277612	S-825EGL

ST Series

STRIP LIGHT

- Full-length LED strip light ideal for replacing fluorescent strips
- Superior performance with lumens up to 9,200 and 115 lumens per watt
- 3 Color Field-Selectable in 35/40/5000K
- Continuous row mount aligner included to add-on length as needed
- Low voltage 0-10V dimming to 10%

Dimming and Selectable CCT

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
2ST2L20SC3	2' Dual Lens, Dimming	2-T8 17W	3500K-5000K	120-277V	2,258	19	080083241569	S-UQO28D
4ST2L40SC3	4' Dual Lens, Dimming	2-T8 32W, 1-T5HO 54W	3500K-5000K	120-277V	4,653	40	080083241583	S-TSP41D
8ST2L80SC3	8' Dual Lens, Dimming	4-T8 32W, 2-T12 75W	3500K-5000K	120-277V	9,060	78	080083242207	S-5J2ZA0

Achieva™ Surface

WRAP

- Ideal for replacing up to four lamp and low-bay linear fluorescents
- 3 Color Field-Selectable in 35/40/5000K, Field-Selectable lumens: 2,250 - 12,500
- Designed for single or continuous row mount
- Suitable for ceiling, wall, or suspension mounting

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
2AWS-L3C3-UNV	2' Narrow Modern Wrap, Dimming	2-T8 17W	3500K-5000K	120-277V	2,250-3,084	18/21/25	080083281244	S-LXMBTS
4AWS-L3C3-UNV	4' Narrow Modern Wrap, Dimming	2-T8 32W	3500K-5000K	120-277V	4,095-5,916	31/38/46	080083281602	S-QV8V88
8AWS-L3C3-UNV	8' Narrow Modern Wrap, Dimming	2-T8 96W, 4-T8 32W	3500K-5000K	120-277V	7,845-12,019	54/71/83	080083281800	S-864B60
2AWWS-L3C3-UNV	2' Wide Modern Wrap, Dimming	3-T8 17W	3500K-5000K	120-277V	2,313-3,170	18/21/25	080083281541	S-8BS41V
4AWWS-L3C3-UNV	4' Wide Modern Wrap, Dimming	3-T8 32W	3500K-5000K	120-277V	4,254-6,013	31/38/47	080083281701	S-2PPZXM
8AWWS-L3C3-UNV	8' Wide Modern Wrap, Dimming	3-T8 96W, 6-T8 32W	3500K-5000K	120-277V	8,296-12,554	57/74/85	080083281909	S-0R1G6X

NWS Series

WRAP

- Ideal for replacing two or three lamp fluorescents up to 96W
- 3 Color Field-Selectable in 35/40/5000K
- Field-Selectable lumens: 2,000 - 5,272
- Surface (wall or ceiling) mount via junction box or direct to surface, UNV 0-10V dimming to 10%

damp location

DIMMABLE

selectable lumens

seleCCTable colors

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
2NWS3C3-UNV	2' Wrap, Dimming	2-T8 17W	3500K-5000K	120-277V	2,009-2,679	15/18/21	080083257485	S-PKU0E2
4NWS3C3-UNV	4' Wrap, Dimming	3-T8 32W	3500K-5000K	120-277V	3,300-4,800	28/32/39	080083257522	S-YJTA0N
4NWS3C3MS-UNV	4' Wrap, Dimming, Sensor *	3-T8 32W	3500K-5000K	120-277V	3,675-5,016	28/32/38	080083257607	S-2V0NL5

* Includes integrated microwave motion sensor (MS) option.

High Bays
p. 42-43

Vaportites
p. 43

METALUX

INDUSTRIAL LIGHTING

Metalux Industrial offers a selection of economical and energy-efficient high-bay and vaportite lighting solutions designed for a wide variety of applications.

UHBS Selectable Series

HIGH BAY

- Compact, 13" and 15" round die cast aluminum housing
- Up to 36,000 selectable lumens and 4000K/5000K selectable CCT
- Sensor ready port for quick plug and play install
- 120-347 volt operating range

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
UHBS-1218-MV-L84050-U	Round, White*	320W Halide, 4-T5HO 54W	4000K-5000K	120-347V	12,000-18,000	81-120	080083256471	**S-PEIA6S**
UHBS-2436-MV-L84050-U	Round, White*	750W Halide, 8-T5HO 54W	4000K-5000K	120-347V	24,000-36,000	145-238	080083256488	**S-Z5HGE1**
UHBS-1218-MV-L84050-BLK	Round, Black*	320W Halide, 4-T5HO 54W	4000K-5000K	120-347V	12,000-18,000	81-120	080083272341	**S-PEIA6S**
UHBS-2436-MV-L84050-BLK	Round, Black*	750W Halide, 8-T5HO 54W	4000K-5000K	120-347V	24,000-36,000	145-238	080083272365	**S-Z5HGE1**

* Medium Distribution. Note: DLC Premium items are noted in bold.

Accessories

Catalog Number	Description	UPC
UHBS-CLR13	UHBS 13" Dia. Clear PC Reflector	080083273300
UHBS-CLR15	UHBS 15" Dia. Clear PC Reflector	080083273317
UHBS-ALR13	UHBS 13" Dia. Aluminum Reflector	080083273324
UHBS-ALR15	UHBS 15" Dia. Aluminum Reflector	080083273331
UHBS-WG13	UHBS 13" Dia. Wire Guard	080083273348
UHBS-WG15	UHBS 15" Dia. Wire Guard	080083273355

Accessories (cont.)

Catalog Number	Description	UPC
Y-TOGGLE-10-2PK	Mounting Toggle and 10' Cable	080083259557
Y-TOGGLE-30-2PK	Mounting Toggle and 30' Cable	080083259571

PIR Sensor

Catalog Number	Description	UPC
UHBS-SENSOR PK	PIR Sensor, 360 Lens	080083257898

SPHB Selectable Series

HIGH BAY

- 2 Compact, lightweight designs for easy install
- Up to 36,000 selectable lumens and 4000K/5000K selectable CCT
- Sensor Ready port for quick plug and play install
- Great for Industrial, manufacturing, gymnasium, and warehouse

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
SPHB-1224SE-M-UNV-L84050-CD-SP1-U	Med. Distr	6-T5HO, 8-T8, 400W MH	4000K-5000K	120-277V	12,000-24,000	82/123/166	080083289264	Pending
SPHB-2436SE-M-UNV-L84050-CD-SP1-U	Med. Distr	8-T5HO, 10-T8, 750W MH	4000K-5000K	120-277V	24,000-36,000	162/209/251	080083289288	Pending

LHBS Series

HIGH BAY

- Economical industrial high bay/low bay LED linear luminaire
- CCT (4000/5000K) and lumen select for greater flexibility
- Standard diffused lens provides added protection and glare control
- Energy-efficient, one-for-one replacement of linear fluorescent and HID fixtures
- Perfect for industrial, manufacturing, gymnasium and warehouse applications

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
LHBS-1218-UNV-L84050-U	Lensed HB Select*	4-T8, 3-T5HO, 175W MH	4000K-5000K	120-277V	13,000-18,000	85-124	080083274741	**S-J1KSFT**
LHBS-1824-UNV-L84050-U	Lensed HB Select*	6-T5HO, 8-T8, 400W MH	4000K-5000K	120-277V	18,800-24,000	119-156	080083275625	**S-24YMLJ**
LHBS-2436-UNV-L84050-U	Lensed HB Select*	8-T5HO, 10-T8, 750W MH	4000K-5000K	120-277V	24,388-36,000	155-246	080083276141	**S-EUK8B9**

* Medium Distribution. Note: DLC Premium items are noted in bold.

VHB Series

HIGH BAY

- Designed for a wide variety of applications and mounting heights
- Precision designed optics; High impact polycarbonate optical LED lens
- Compact, lightweight design for ease of installation
- Solution for spaces utilizing traditional linear fluorescent and HID high bay
- Ideal for industrial, commercial, manufacturing and gymnasium applications

Selectable Lumens

Catalog Number	Description	Replaces	CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
VHB-1215-W-UNV-L840-CD-U	Wide Distr.	4-T8, 3-T5HO, 175W MH	4000K	120/277V	12,000-15,000	110	080083192304	PJHJOBPH
VHB-1215-W-UNV-L850-CD-U	Wide Distr.	4-T8, 3-T5HO, 175W MH	5000K	120/277V	12,000-15,000	110	080083192311	PQX68N7B
VHB-1824-W-UNV-L840-CD-U	Wide Distr.	4-T5HO, 6-T8 320W MH, 6-T5HO, 8-T8, 400W MH	4000K	120/277V	18,000-24,000	158	080083192328	PKWWO6XP
VHB-1824-W-UNV-L850-CD-U	Wide Distr.	4-T5HO, 6-T8 320W MH, 6-T5HO, 8-T8, 400W MH	5000K	120/277V	18,000-24,000	158	080083192335	PMKN6560

Dedicated CCT & Lumens

Catalog Number	Description	Replaces	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
VHB-18-W-UNV-L840-CD-U	Wide Distr.	4-T5HO, 6-T8 320W MH	5000K	120/277V	18,647	134	080083785919	P75UEXLK
VHB-18-W-UNV-L850-CD-U	Wide Distr.	4-T5HO, 6-T8 320W MH	4000K	120/277V	19,160	134	080083785902	PIIJDELY
VHB-24-W-UNV-L840-CD-U	Wide Distr.	6-T5HO, 8-T8, 400W MH	5000K	120/277V	23,057	174	080083815708	PJ92YFP9
VHB-24-W-UNV-L850-CD-U	Wide Distr.	6-T5HO, 8-T8, 400W MH	4000K	120/277V	23,692	174	080083818365	PH575GE1

APVT Series

VAPORTITE

- Durable polycarbonate housing with integral metal gear tray
- 4ft and 8ft sizes with CCT and lumen select capability
- UL Wet location, IP65 and Operating temp -20C to 40C
- Stainless steel latches, single conduit hub, and mounting included

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
4APVTLD-SL3C3	4' Selectable Output	3-T8 32W, 2-T5HO 54W	3500K-5000K	120-277V	3,000-6,000	21-46	080083264216	S-M39BJL
8APVTLD-SL3C3	8' Selectable Output	4-T8 32W, 3-T5HO 54W	3500K-5000K	120-277V	8,500-12,000	59-94	080083266333	S-3EH2VC

METALUX VAPORTITES

Good | Better | Best

		LHBS	VHB	SPHB	UHBS
APPLICABILITY[1]	Big Box Retail	★	★	★★	★★
	Sports / Recreation	★★	★★	★★	★★
	Warehouses	★★★	★★★	★★★	★★
	Manufacturing	★★	★★	★★★	★★
	Cold Storage	★	★★★	★★★	★
	Complex Environments		★	★	★★
FEATURES / PERFORMANCE	Lumen Range	12,000 - 36,000	9,000 - 24,000	12,000 - 36,000	12,000-36,000
	Selectable Lumens	12,000-18,000 or 18,000-24,000 or 24,000-36,000	12,000 - 15,000 or 18,000 - 24,000	12,000 - 24,000 or 24,000 - 36,000	12,000-18,000 or 24,000-36,000
	Efficacy (Max)	160 lm/W	147 lm/W	158 lm/W	137 lm/W
	CRI	80	70, 80, 90	80	80
	Distribution	M	N, W	M	M
	Sizes	13" x 2' & 4'	< 2'	12" x 18" or 12" x 36"	13" & 15"
	Housing [2]	CRS	CRS / Extruded	CRS	Diecast
	Lensing	Acrylic	Polycarbonate	Polycarbonate	Polycarbonate
	Uplight	None	None	None	None
	Life (@ 60K hrs)	L84	L83	L86	L91
	Ambient Range	-20C to 50C	-40C to 40C	-40C to 45C	-40C to 45C
	Emergency	None	Remote	Optional	None
	Ratings	Damp	Damp	Damp, IP5X	IP65, NSF, Wet Location
	DLC	Premium	Standard, Premium	Premium	Standard
INTEGRATED CONTROLS	Basic Occupancy		✓	✓	
	Stand Alone Daylight / Occupancy		✓	✓	✓
	WaveLinx		✓	✓	

Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable
2. CRS=Cold-rolled Steel, Extruded= Extruded Aluminum, Diecast=Diecast Aluminum.

IO
p. 46

ARCHITECTURAL
COMMERCIAL LIGHTING

iO and Corelite delight architects by offering simple designs that create comfort with a perfect balance of beautiful aesthetics, superior performance and ease of installation.

CovSelect Architectural Cove Light

iO

- Cove lighting fixture with integral driver for interior applications
- Field-Selectable CCTs: 2700K, 3000K, 3500K, 4000K; 80 CRI
- Field-Selectable lumen output: 350 lumens/ft and 700 lumens/ft
- Up to 200 ft run from a single power drop
- Rated for interior / damp installations
- Simplifies install by eliminating remote drivers and field assembly needed for tape light

damp location

No QS prefix needed for stock or Quick Spec orders

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	Energy Star ID
CS-SL-8SCT-120-ID-UNV-W-SA-STD-4F	4' Linear Fixture	32W T8, 40W T12	2700K-4000K	120-277V	350 lm/ft, 700 lm/ft	21	080083267095	2401210
CS-SL-8SCT-120-ID-UNV-W-SA-STD-1F	1' Linear Fixture	32W T8, 40W T13	2700K-4000K	120-277V	350 lm/ft, 700 lm/ft	6	080083267507	2401209

Power Harness/Control Modules (1 required for each power drop)

Catalog Number	Description	UPC
CS-10V-STD	Standard Power Harness	080083267088

Accessories (optional)

Catalog Number	Description	UPC
CS-JHARN02-006	6" Jumper accessory	080083267071
CS-JHARN02-012	12" Jumper accessory	080083267064
CS-JHARN02-036	36" Jumper accessory	080083267057
CS-JHARN02-144	144" Jumper accessory	080083267040

DREAM. EXPERIMENT. PLAN.

A more powerful way to design.

Light ARchitect™

See your space in a new light with augmented reality

We've taken the guesswork out of lighting design with Light ARchitect, an augmented reality mobile app that lets you instantly visualize light fixtures in your space.

- Browse state-of-the-art light LED fixtures and choose the ones you want to see in your space
- Adjust the fixture's finish, lumen output, mounting height, color temperature and more
- Virtually turn lights on to get the full effect
- Take screenshots to share and email to clients or colleagues



Light ARchitect is free and available for iOS and Android devices

Download **Light ARchitect**

Download on the App Store

GET IT ON Google Play

To learn how Light ARchitect has changed our customers' way of working, visit cooperlighting.com/lightarchitect

Wall Mounts
p. 49 & 52

Floodlight
p. 50, 53-55

Ceiling Mount
p. 50

Area/Site
p. 51

LUMARK & LUMARK AP

OUTDOOR LED LUMINAIRES

Lumark brands offer a wide selection of high-quality product solutions that provide market-leading ease of installation, superior area safety, and maximum energy savings in commercial and industrial spaces.

LUMARK AP WALL MOUNTS

Lumark AP provides high-value outdoor lighting products that are in stock and supported with decades of experience and expertise in the industry.

ASWP Adjustable Slim Wall Pack Luminaire

WALL MOUNT

- Adjustable slim wall pack available in small and medium sizes
- 3-color selectable CCT: 3000K, 4000K, 5000K; 70CRI
- Lumen packages range from 2,100-10,200 lumens
- Internal toggle switches to easily adjust luminaire CCT and lumens
- Integrated button type photocontrol for dusk-to-dawn operation

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
ASWPLED1S	Small LED Wall Pack	Bronze	155W HID	3000K-5000K	120-347V	2,000-4,000	15-30W	080083265169	**S-YWC5DG**
ASWPLED2S	Medium LED Wall Pack	Bronze	375W HID	3000K-5000K	120-347V	5,000-10,000	40-75W	080083265183	**S-9DIVKW**

Note: DLC Premium items are noted in bold.

WPM Wall Pack Luminaire

WALL MOUNT

- LED wall pack available with selectable configurations
- Die-cast aluminum housing with hinged, removable die-cast aluminum door
- Heat and impact resistant borosilicate glass lens
- Energy and maintenance savings up to 89%
- Ideal for pathway illumination, building entrances, vehicle ramps, schools, tunnels, stairways and loading docks

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
WPMLED15S	Medium LED Wall Pack	Bronze	150W HID	3000K-5000K	120-347V	3,977-7,535	29-59	080083176144	PLAP4BWH9V52
WPMLED25S	Medium LED Wall Pack	Bronze	250W HID	3000K-5000K	120-347V	9,779-12,829	72-101	080083176168	PLCDOB65Z8EN

LSF Selectable Flood Luminaire

FLOODLIGHT

- Available in 3 housing sizes and multiple lumen packages
- 3-color selectable CCT: 3000K, 4000K, 5000K; 70CRI
- Lumen packages ranging from 1,700-20,000 lumens
- Knuckle, slipfitter, trunnion and yoke mounting types
- Integrated button type photocontrol for dusk-to-dawn operation

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
LSF25-KN-PC	Knuckle Mount, Photocontrol	Bronze	155W HID	3000K-5000K	120-347V	1,700-4,000	11-25W	080083267705	**S-W43YTM**
LSF65-KN-PC	Knuckle Mount, Photocontrol	Bronze	375W HID	3000K-5000K	120-347V	5,000-10,000	25-65W	080083267729	**S-5HK1XN**
LSF120-SF-PC	Slipfitter Mount, Photocontrol	Bronze	450W HID	3000K-5000K	120-347V	9,000-20,000	50-120W	080083267743	**S-M4YHAF**
LSF25-YK-PC	Yoke Mount, Photocontrol	Bronze	155W HID	3000K-5000K	120-347V	1,700-4,000	11-25W	080083267767	**S-W43YTM**
LSF65-YK-PC	Yoke Mount, Photocontrol	Bronze	375W HID	3000K-5000K	120-347V	5,000-10,000	25-65W	080083267781	**S-5HK1XN**
LSF120-TR-PC	Trunnion Mount, Photocontrol	Bronze	450W HID	3000K-5000K	120-347V	9,000-20,000	50-120W	080083267804	**S-M4YHAF**

Note: DLC Premium items are noted in bold.

CLCS Canopy Luminaire

CEILING MOUNT

- LED canopy available with fixed output or selectable configurations
- 3-color selectable CCT: 3000K, 4000K, 5000K
- High-performance, energy-efficient illumination
- Energy and maintenance savings up to 86% versus HID solutions
- Ideal for new or existing spaces including bank, retail, drive-thru, covered sidewalks and hospital entryways

Selectable CCT & Lumens

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
CLCS17S	Small LED Canopy	Bronze	175W HID	3000K-5000K	120-277V	5,323-7,939	39-56	080083160006	P5MUAJIY, P5S4B75K
CLCS17S-PC	Small LED Canopy	Bronze	175W HID	3000K-5000K	120-277V	5,323-7,939	39-56	080083159727	P5MUAJIY
CLCS40S	Large LED Canopy	Bronze	400W HID	3000K-5000K	120-277V	12,614-17,427	91-123	080083160020	PUT8OLSK, PPEWK64B

Dedicated CCT & Lumens

Catalog Number	Description	Finish	Replaces	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
CLCS15	Small LED Canopy	Bronze	150W HID	4000K	120-277V	5,671	39	080083161003	PAVO9EAO
CLCS17	Small LED Canopy	Bronze	175W HID	4000K	120-277V	7,956	56	080083161041	P3KXJQWI

LAS Luminaire

AREA/SITE

- Automatic dusk-to-dawn area lighting with included twistlock photocontrol
- 10-position, Field-Selectable lumens across 2 die-cast aluminum housing sizes
- Energy and maintenance savings up to 79% versus HID solutions up to 79%
- Pole mount arm or adjustable slipfitter mounting arm included
- Ideal parking lots, walkways, building areas and other outdoor areas

selectable lumens

Catalog Number	Description	Finish	Replaces	CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
LAS45S-T3	T3 Distr., Adjustable Slipfitter Arm	Bronze	450W HID	4000K	120-277V	4,900-20,000	30-153	080083155804	**P1T4HG08**
LAS45P-T3	T3 Distr., Pole Mount Arm	Bronze	450W HID	4000K	120-277V	4,900-20,000	30-153	080083248360	**P1T4HG08**
LAS45S-T4	T4 Distr., Adjustable Slipfitter Arm	Bronze	450W HID	4000K	120-277V	4,900-20,000	30-153	080083155828	**PJZTZ423**
LAS45P-T4	T4 Distr., Pole Mount Arm	Bronze	450W HID	4000K	120-277V	4,900-20,000	30-153	080083248384	**PJZTZ423**
LAS45S-T5	T5 Distr., Adjustable Slipfitter Arm	Bronze	450W HID	4000K	120-277V	4,900-20,000	30-153	080083155842	**PW39PQB3**
LAS45P-T5	T5 Distr., Pole Mount Arm	Bronze	450W HID	4000K	120-277V	4,900-20,000	30-153	080083248704	**PW39PQB3**
LAS100S-T3	T3 Distr., Adjustable Slipfitter Arm	Bronze	1,000W HID	4000K	120-277V	8,200-34,000	48-251	080083155866	**PP8AW4F5**
LAS100P-T3	T3 Distr., Pole Mount Arm	Bronze	1,000W HID	4000K	120-277V	8,200-34,000	48-251	080083248780	**PP8AW4F5**
LAS100S-T4	T4 Distr., Adjustable Slipfitter Arm	Bronze	1,000W HID	4000K	120-277V	8,200-34,000	48-251	080083155880	**P0CHU9AS**
LAS100P-T4	T4 Distr., Pole Mount Arm	Bronze	1,000W HID	4000K	120-277V	8,200-34,000	48-251	080083248803	**P0CHU9AS**
LAS100S-T5	T5 Distr., Adjustable Slipfitter Arm	Bronze	1,000W HID	4000K	120-277V	8,200-34,000	48-251	080083155903	**PMUFIF4F**
LAS100P-T5	T5 Distr., Pole Mount Arm	Bronze	1,000W HID	4000K	120-277V	8,200-34,000	48-251	080083248827	**PMUFIF4F**

Note: DLC Premium items are noted in bold.

LUMARK WALL MOUNTS

Lumark combines value-engineered, specification-grade lighting features with market-leading retrofit installation solutions, to enable contractors to get on and off the job quickly and deliver superior illumination coverage.



AXC Axcent Luminaire

WALL MOUNT

- Full cutoff and refractive LED lens models available in small or large
- Hook-N-Lock mechanism for quick, easy installation
- Die-cast aluminum construction with energy-efficient illumination
- Gasketed housing and sealed optical compartment making impervious to contaminants
- Ideal for pathway illumination and floodlighting applications

Catalog Number	Description	Finish	Replaces	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
AXCS1A	Small Full Cutoff	Carbon Bronze	70W HID	4000K	120-277V	1,806	14	080083887965	**S-3SJYCL**
AXCS2A	Small Full Cutoff	Carbon Bronze	100W HID	4000K	120-277V	2,561	21	080083887989	**S-0YO8BE**
AXCS3A	Small Full Cutoff	Carbon Bronze	150W HID	4000K	120-277V	3,537	27	080083888009	**S-H712OV**
AXCS4A	Small Full Cutoff	Carbon Bronze	250W HID	4000K	120-277V	5,520	44	080083888023	**PI16J9UO**
AXCS4ARL	Small Refractive Lens	Carbon Bronze	250W HID	4000K	120-277V	5,858	44	080083888030	**PPXSGJ9K, PCFKRFBV**
AXCS5A	Small Full Cutoff	Carbon Bronze	320W HID	4000K	120-277V	6,300	52	080083888047	**PCPDYSZM**
AXCL6A	Large Full Cutoff	Carbon Bronze	320W HID	4000K	120-277V	7,594	56	080083811564	**PLXS8Y3B**
AXCL6ARL	Large Refractive Lens	Carbon Bronze	320W HID	4000K	120-277V	7,809	56	080083811649	**PZXNXUOI**
AXCL8A	Large Full Cutoff	Carbon Bronze	400W HID	4000K	120-277V	9,696	72	080083811588	**PG4TJNY3**
AXCL8ARL	Large Refractive Lens	Carbon Bronze	400W HID	4000K	120-277V	9,970	72	080083811663	**PBA84MB6**
AXCL10A	Large Full Cutoff	Carbon Bronze	400W HID	4000K	120-277V	13,283	102	080083811601	**P5XO6GE7**
AXCL12A	Large Full Cutoff	Carbon Bronze	450W HID	4000K	120-277V	16,823	123	080083811625	**PD1N4D39**

Note: DLC Premium items are noted in bold.

AXC Back Box Accessory

Catalog Number	Description	Finish	UPC
BB/AXC	Back Box	Carbon Bronze	080083160709
BB/AXC-PC	Back Box with Photocontrol	Carbon Bronze	080083160723

Features
Lumen Select pack allows installer to reduce the light output to 75 or 50%
Integrated photocontrol provides maximum energy savings while leveraging
Four 1/2" NPT conduit entry points for surface mounted conduit
Single die-cast aluminum back box to simultaneously accommodate Axcent Small and Large housings

NHR Night Harrier

FLOODLIGHT

- Cutting edge innovated design offering years of maintenance-free service
- 3-color selectable CCT: 3000K, 4000K, 5000K
- Lumen packages ranging from 5,500-22,000 lumens
- Slipfitter and trunnion mounting types
- Ideal for area lighting such as facade, wall washing, building and sign lighting

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
NHRS50UT	Trunnion Mount	Bronze	70W to 500W HID	3000K-5000K	120-277V	5,500-22,000	40-155W	080083283903	Pending
NHRS50US	Slipfitter Mount	Bronze	70W to 500W HID	3000K-5000K	120-277V	5,500-22,000	40-155W	080083283910	Pending
NHRS50HT	Trunnion Mount	Bronze	70W to 500W HID	3000K-5000K	347-480V	5,500-22,000	40-155W	080083283927	Pending
NHRS50HS	Slipfitter Mount	Bronze	70W to 500W HID	3000K-5000K	347-480V	5,500-22,000	40-155W	080083283934	Pending
NHRS50UT-BPC	Trunnion Mount, Photocontrol	Bronze	70W to 500W HID	3000K-5000K	120-277V	5,500-22,000	40-155W	080083283941	Pending
NHRS50US-BPC	Slipfitter Mount, Photocontrol	Bronze	70W to 500W HID	3000K-5000K	120-277V	NHRS50UT-BPC	40-155W	080083283958	Pending

TGS Series – Single Head

SECURITY FLOODLIGHT

- Three different brightness levels using Lumen Select Technology
- Durable die-cast aluminum square head with UV resistant lens
- Easy install to wall or eave mounting, with integrated easy connector
- Switch activated, Dusk-to-Dawn, and motion activated models available
- Ideal for security lighting in residential and commercial applications

Dusk-To-Dawn models available

with sensor

Catalog Number	Description	Finish	Replaces	CCT	Voltage	Selectable Lumens	Watts	UPC	Energy Star ID
TGS3S401FSRB	Single Head Square	Bronze	180W INC	4000K	120V	1,700-3,500	27	080083913169	Pending
TGS3S401FSRW	Single Head Square	White	180W INC	4000K	120V	1,700-3,500	27	080083912971	Pending
TGS3S401DSRB	Single Head Square, D2D	Bronze	180W INC	4000K	120V	1,700-3,500	27	080083913268	Pending
TGS3S401DSRW	Single Head Square, D2D	White	180W INC	4000K	120V	1,700-3,500	27	080083912995	Pending
TGS3S401MSRB	Single Head Square, Motion	Bronze	180W INC	4000K	120V	1,700-3,500	27	080083913015	Pending
TGS3S401MSRW	Single Head Square, Motion	White	180W INC	4000K	120V	1,700-3,500	27	080083260089	Pending

TGS Series – Twin Head

SECURITY FLOODLIGHT

- Three different brightness levels using Lumen Select Technology
- Durable die-cast aluminum square head with UV resistant lens
- Easy install to wall or eave mounting, with integrated easy connector
- Switch activated, Dusk-to-Dawn, and motion activated models available
- Ideal for security lighting in residential and commercial applications

Dusk-To-Dawn models available

with sensor

also available in square head

Catalog Number	Description	Finish	Replaces	CCT	Voltage	Selectable Lumens	Watts	UPC	Energy Star ID
TGS2S402FRRB	Twin Head Round	Bronze	180W INC	4000K	120V	1,500-2,500	22	080083913053	Pending
TGS2S402FRRW	Twin Head Round	White	180W INC	4000K	120V	1,500-2,500	22	080083913374	Pending
TGS2S402DRRB	Twin Head Round, D2D	Bronze	180W INC	4000K	120V	1,500-2,500	22	080083913435	Pending
TGS2S402DRRW	Twin Head Round, D2D	White	180W INC	4000K	120V	1,500-2,500	22	080083913459	Pending
TGS2S402MRRB	Twin Head Round, Motion	Bronze	180W INC	4000K	120V	1,500-2,500	22	080083913510	Pending
TGS2S402MRRW	Twin Head Round, Motion	White	180W INC	4000K	120V	1,500-2,500	22	080083913534	Pending
TGS2S402MSRB	Twin Head Square, Motion	Bronze	180W INC	4000K	120V	1,500-2,500	22	080083913558	Pending
TGS2S402MSRW	Twin Head Square, Motion	White	180W INC	4000K	120V	1,500-2,500	22	080083913572	Pending

TGS Series – Triple Head

SECURITY FLOODLIGHT

- Three different brightness levels using Lumen Select Technology
- Durable die-cast aluminum square head with UV resistant lens
- Easy install to wall or eave mounting, with integrated easy connector
- Switch activated, Dusk-to-Dawn, and motion activated models available
- Ideal for security lighting in residential and commercial applications

Dusk-To-Dawn models available

with sensor

selectable lumens

Catalog Number	Description	Finish	Replaces	CCT	Voltage	Selectable Lumens	Watts	UPC	Energy Star ID
TGS3S403FRRB	Triple Head Round	Bronze	270W INC	4000K	120V	2,000-3,000	27	080083913596	Pending
TGS3S403FRRW	Triple Head Round	White	270W INC	4000K	120V	2,000-3,000	27	080083913619	Pending
TGS3S403DRRB	Triple Head Round, D2D	Bronze	270W INC	4000K	120V	2,000-3,000	27	080083913671	Pending
TGS3S403DRRW	Triple Head Round, D2D	White	270W INC	4000K	120V	2,000-3,000	27	080083913695	Pending
TGS3S403MRRB	Triple Head Round, Motion	Bronze	270W INC	4000K	120V	2,000-3,000	27	080083256105	Pending
TGS3S403MRRW	Triple Head Round, Motion	White	270W INC	4000K	120V	2,000-3,000	27	080083256129	Pending

TGS Series – Single Head High Output

SECURITY FLOODLIGHT

- Three different brightness levels using Lumen Select Technology
- Durable die-cast aluminum square head with UV resistant lens
- Easy install to wall or eave mounting, with integrated easy connector
- Switch activated, Dusk-to-Dawn, and motion activated models available
- Ideal for security lighting in residential and commercial applications

Dusk-To-Dawn models available

with sensor

selectable lumens

Catalog Number	Description	Finish	Replaces	CCT	Voltage	Selectable Lumens	Watts	UPC	Energy Star ID
TGS5S401DSCB	Single Head High Output Square, D2D	Bronze	175W Metal halide	4000K	120-277V	2,700-5,800	50	080083256013	Pending
TGS5S401MSCB	Single Head High Output Square, Motion	Bronze	175W Metal halide	4000K	120-277V	2,700-5,800	50	080083260041	Pending
TGS5S401MSCW	Single Head High Output Square, Motion	White	175W Metal halide	4000K	120-277V	2,700-5,800	50	080083260065	Pending

Maximize Savings with Utility Rebates

Cooper Lighting Solutions Exclusive Utility Rebate Incentive Finder

Cooper Lighting Solutions has the largest portfolio of **ENERGY STAR®**-certified recessed downlights and **DesignLights® Consortium (DLC)** - qualified commercial luminaires, meeting high-quality, energy-efficient standards. See below for more information about the compliance codes and standards which identify products that qualify for utility rebates.

For details visit:
cooperlighting.com/global/resources/incentive-finder

Look for the DLC, ENERGY STAR and T20 icons that identifies qualified products.

By using our Online Incentive Finder, you can search by state and zip code to find local rebates that save money and add value for your customers. For your convenience, we've identified and included the ENERGY STAR® and DLC® product ID numbers within the MarketPro catalog.



DLC Product ID
S-PKU0E2

DLC Premium items are denoted in bold

ENERGY STAR ID
2326235

Efficiency Standards
T20 California Title 20 Certified LED Tier 2 Lamp

T20 icon located under the product description

This non-profit organization drives the adoption of energy, efficiency and high-performing commercial lighting and controls products. Our products represent the broadest portfolio available.

To find which Cooper Lighting Solutions products are listed, visit **www.designlights.org/QPL.**

ENERGY STAR® is the trusted, government-backed symbol for energy efficiency helping us save money and protect the environment through energy-efficient products and practices.

Visit **www.energystar.gov** for more information.

Efficiency Standards
T20 California Title 20 Certified LED Tier 2 Lamp

Title 20 is a set of energy efficiency regulations established by the California Energy Commission governing various products and appliances. Products with this logo meet the energy efficiency standards set by the California Energy Commission.

For more information on Title 20, visit **www.energy.ca.gov.**

Resource Center

Cooperlighting.com > Resources

Literature, product photography, videos, case studies, logos & more!

Visit Cooperlighting.com and click on the Resources tab. The Resource Center is a central location of supportive product selection tools, inspirational images and downloadable digital resources.

Product Resources

- Brochures & Guides
- Spec sheets
- Installation sheets and guides

Inspiration

- Application Photography
- Product Photography & Videos
- Case studies
- Logos

Tools

- Energy Incentive Finder
- Photometric IES
- Revit Models
- Calculators & Audit Tools

Programs

- MarketPro
- Quick Spec
- Overstock

Education

- Instructor-led Classes
- Free online courses
- Continuing education

Learn. Grow. Visualize.

Explore our one-stop-shop for Cooper Lighting Solutions digital tools.

Explore Our Video Library!

Visit Cooper Lighting Solutions' YouTube page to explore our ever-expanding product video library! Everything you need to know about our innovative product offering can be found here. Get the facts on newly introduced solutions, discover product benefits and watch videos on how to install them. Explore our curated playlists to easily find informative videos by industry-leading brand, market and product category.

youtube.com/cooperlightingsolutions

Source Lighting Education Center

The benchmark for lighting educational facilities and programs for 30 years.

Expand Your Knowledge!

The SOURCE is an excellent resource for training and professional development.
As the industry's leading lighting educational facility, the SOURCE offers numerous online and instructor-led courses and workshops for those wanting to expand their lighting and controls knowledge.

- Instructor-led Classes
- Free Online Courses
- Continuing Education
- reSource Articles

To start learning today, visit:

cooperlighting.com/global/resources/source-lighting-education

Lighting & Controls
STOCK PRODUCT GUIDE

LIGHTING BRANDS
Ametrix
AtLite
Corelite
Ephesus
Fail-Safe
HALO
HALO Commercial
Invue
iO
Iris
Lumark
LumarkAP
Lumière
McGraw-Edison
Metalux
MWS
NeoRay
Portfolio
PrentaLux - 3D Printed Lighting
RSA
Shaper
Streetworks
Sure-Lites

CONTROLS BRANDS
Greengate
Fifth Light
Intelligent Lighting Controls

CONNECTED LIGHTING SYSTEMS AND SMART SPACES PLATFORM
WaveLinx
Trellix Infrastructure

COOPER Lighting Solutions

Cooper Lighting Solutions
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.cooperlighting.com

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2024 Cooper Lighting Solutions
All Rights Reserved
Printed in USA
Publication No. CA525919
July 2024

Cooper Lighting Solutions is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.