




Use what you already know and complete projects and open schools faster while reducing cost with the WaveLinx PRO system, for LED lighting and controls.

Wire integrated luminaire or retrofit kit




Wire for power not load switching




Easy programming with mobile application
(Wireless Area Controller required)



Go from this...



To this!



How to Videos



Now simple standard wiring provides so much more. Here's what you get:

Lighting

- Continuous dimming
- Individual control

Occupancy

- Auto On to 50% or Vacancy
- Auto Off of lighting and plug loads

Daylighting

- Continuous dimming to OFF
- Open or closed loop

Scheduling

Security

- IEC 62443-4-1 and IEC 62443-4-2 certified
- UL924
- DLC NLC V5 qualified



WaveLinx PRO devices are IEC 62443-4-1 and IEC 62443-4-2 certified.
Independent certifications have been performed by certified labs.



Stay secure with unparalleled 7-tier network security features

Satisfy your customer and your bottom line.
Get off the job faster and at a lower installation cost with WaveLinx PRO components.

WaveLinx Pro products

CATALOG NUMBER	DESCRIPTION	VOLTAGE	UPC	MSRP
WAC2-POE	Wireless Area Controller 1 required per 49 rooms	WPOE-120	080083763818	
WPOE2-120	PoE power supply for WAC	120V	080083763825	
WSP-UV-010	Wireless Dimming Switchpack 20A relay and 0-10V output	120-347VAC 16A LED	080083840816	
W4S-RL-S4-*	4 small button field programmable wallstation with Raise/Lower (W, V, G, B)	120/277VAC Not load switching, for radio power only	080083866809	
WB5-S3-W	White 3 small 1 large button with Raise/Lower field programmable wallstation (Scene 1, Scene 2, Scene 3, Off, v, ^)	Qty 4 AAA batteries	080083865505	
WB6-S3D-W	White 6 small button field programmable wallstation (Scene 1, Scene 2, Scene 3, Raise, Lower, Off)		080083865604	
WB6-S5-W	White 6 small button field programmable wallstation (Scene 1, Scene 2, Scene 3, Scene 4, Scene 5, Off)		080083865628	
WOLC-7P-010	Outdoor Lighting Control Module	120/347VAC 10A LED	080083837540	
WR-20	Wireless 20A Receptacle	120V 20A	080083763788	
WR-15	Wireless 15A Receptacle	120V 15A	080083763771	
CWPD-1500	Wireless PIR 1500 sq ft Ceiling Sensor	Qty 2 AA batteries	080083763795	

Reduce installation time by 60% with MWS products

CATALOG NUMBER	DESCRIPTION	UPC	MSRP
12EC12/2G11	120V 12AWG Extender Cable 11' long	622697307677	
12EC12/2G15	120V 12AWG Extender Cable 15' long	622697308094	
12FC12/2G11	120V 12AWG Fixture Cable 11' long	622697362317	
12ST12/2G	120V 12AWG Circuit Starter Cable	622697277376	
27EC12/2G11	277V 12AWG Extender Cable 11' long	622697310127	
27EC12/2G15	277V 12AWG Extender Cable 15' long	622697310172	
27FC12/2G11	277V 12AWG Fixture Cable 11' long	622697362690	
27ST12/2G	277V 12AWG Circuit Starter Cable	622697277604	
27ST12/2G	277V 12AWG Circuit Starter Cable	080083837540	

Save time and money with stock fixtures with integrated sensors

CATALOG NUMBER	DESCRIPTION	LUMEN PACKAGE & CCT	UPC	MSRP
22CZRK-LD4-34-UNV-L840-CD1-SWPD1-U	2x2 Cruze retrofit kit w/integrated sensor	3400 Lumen, 4000K CCT	080083809103	
24CZ-LD5-40-UNV-L840-CD1-SWPD1-U	2x4 Cruze luminaire w/integrated sensor	4000 Lumen, 4000K CCT	080083809080	
22CZ2-34HE-UNV-L840-CD1-SWPD1-U	2x2 Cruze ST High Efficiency luminaire w/integrated sensor	3400 Lumen, 4000K CCT	080083881246	
24CZ2-40HE-UNV-L840-CD1-SWPD1-U	2x4 Cruze ST High Efficiency luminaire w/integrated sensor	4000 Lumen, 4000K CCT	080083881468	