UHBS2 High Performance LED

HIGH BAY

- Compact, 12" and 14" round die cast aluminum housing
- Field selectable distribution - Narrow, Medium, or Wide
- Up to 36,000 selectable lumens with 5 Colour Selectable CCT - 30/35/40/50/6500K
- IP65, NSF, NEMA 4X and Wet Location rated
- Sensor ready port for quick plug and play install
- 120-347 input, 0-10V dimming with 6KV surge protection



Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
UHBS2-1218-MV-L8C5-U	Round, White	400W HID, 6-T5HO 54W	3000K-6500K	120-347V	12,000-18,000	81-120	080083301836	**S-DVZ2KB**
UHBS2-2436-MV-L8C5-U	Round, White	400W HID, 6-T5HO 54W	3000K-6500K	120-347V	24,000-36,000	150-240	080083301843	**S-JVQHNC**

Note: DLC Premium items are noted in bold.

SPHB Selectable Series

HIGH BAY

- 2 Compact, lightweight designs for easy install
- Up to 36,000 selectable lumens and 4000K/5000K selectable CCT
- Sensor Ready port for quick plug and play install
- Great for industrial, manufacturing, gymnasium, and warehouse

Selectable lumen output and colour temperature with an easy to access toggle switch.



Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
SPHB-1224SE-M-UNV-L84050-CD-SP1-U	Med. Distr	6-T5HO, 8-T8, 400W MH	4000K-5000K	120-277V	12,000-24,000	82/123/166	080083289264	S-01PR4D
SPHB-2436SE-M-UNV-L84050-CD-SP1-U	Med. Distr	8-T5HO, 10-T8, 750W MH	4000K-5000K	120-277V	24,000-36,000	162/209/251	080083289288	S-7V2YTC

* Medium Distribution. Note: DLC Premium items are noted in bold.

Standalone Sensor

HIGH BAY

- Works with UHBS2, EZBY and SPHB highbays
- Simple in-field plug and play installation; Occupancy control with 4 preset modes
- Passive Infra-Red (PIR) and daylight sensor with detection at mounting heights up to 50FT
- Remote control capability using separate accessory (HBS Sensor Remote)



Catalog Number	Description	UPC
HBS1	PIR Sensor 360 Lensn50FT MH Kit	080083471171
HBS SENSOR REMOTE	HBS Sensor Remote Control	080083471188

* To meet provincial and local codes, EBP cannot be used with UHBS with sensor or with UHBS sensor accessory.



WaveLinx Sensor

HIGH BAY

- Models suitable for High bay (up to 40ft) applications
- Out of the box functionality: Occupied to Full, Unoccupied to off, daylighting disabled
- Passive Infra-Red (PIR) motion sensor; Integrated photocell for daylight harvesting



The WaveLinx LITE App can be downloaded via the Apple Store® or Google Play and is an accessory to the WaveLink LITE Wireless system.

Catalog Number	Description	UPC
WLS4-HB2	WaveLinx LITE Industrial Fixture Mount High Bay Sensor, White, 15-40FT (4.5 - 12.2M)	080083446315

EZBY Series

HIGH BAY

- Up to 30,000 selectable lumens and 3000/4000/5000K selectable CCT
- Sensor ready port for quick plug and play install
- Mounting ring included for rapid install
- 120-347V input, 0-10V dimming



Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
EZBY-1830C3-MV-BLK	Round, Black	8 T8 or 6 T5HO lamps or 400W MH	3000K-5000K	120-347V	18,000-30,000	122/156/191	080083305889	S-WK156D

VHB Series

HIGH BAY

- Designed for a wide variety of applications and mounting heights
- Precision designed optics; High impact polycarbonate optical LED lens
- Compact, lightweight design for ease of installation
- Lumen selectable models available
- Solution for spaces utilizing traditional linear fluorescent and HID high bay
- Ideal for industrial, commercial, manufacturing and gymnasium applications



Catalog Number	Description	Replaces	CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
VHB-1824-W-UNC-L840-CD-MP-U	Compact Linear, WD Distr, Selectable Lumens	400W HID, 6-T5HO 54W	4000K	347-480V	18,000-24,000	126-158	080083191611	**PKWWO6XP**
VHB-1824-W-UNV-L840-CD-MP-U	Compact Linear, WD Distr, Selectable Lumens	400W HID, 6-T5HO 54W	4000K	120-277V	18,000-24,000	126-158	080083191390	**PKWWO6XP**
VHB-24-W-UNC-L840-CD-MP-U	Compact Linear, WD Distr	400W HID, 6-T5HO 54W	4000K	347-480V	24,000 (Dedicated)	174	080083827282	**PJ92YFP9**
VHB-24-W-UNV-L840-CD-MP-U	Compact Linear, WD Distr	400W HID, 6-T5HO 54W	4000K	120-277V	24,000(Dedicated)	174	080083827299	**PJ92YFP9**

Note: DLC Premium items are noted in bold.

F-Bay Accessories

Catalog Number	Description	UPC
AYC-CHAIN/SET-U	V Hooks & 36" Chain Set	080083545704
HBAYC-CHAIN/SET-U	Hook-style V-Hangers	080083575756
Y-TOGGLE-10-2PK	Aircraft Cable Y-Toggle 120"	080083259557
MC12	Modular Cord & Plug	080083552498
MC6	Modular Cord & Plug	623961368455

APVT Series

VAPOURTITE

- Durable polycarbonate housing with integral metal gear tray
- 4ft and 8ft sizes with CCT and lumen select capability
- UL Wet location, IP65 and operating temp -20C to 40C
- Stainless steel latches, single conduit hub, and mounting included



Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
4APVTLD-SL3C3	4' Selectable Output	3-T8 32W, 2-T5HO 54W	3500K-5000K	120-277V	3,000-6,000	21-46	080083264216	S-C8E2SZ

METALUX HIGH BAYS

Good | Better | Best



		EZBY	SPHB	UHBS
APPLICABILITY[1]	Big Box Retail	★	★★	★★
	Sports / Recreation	★★	★★	★★
	Warehouses	★★★	★★★	★★
	Manufacturing	★★	★★★	★★
	Cold Storage	★	★★★	★
	Complex Environments	★	★	★★
FEATURES / PERFORMANCE	Lumen Range	18,000 - 28,000	12,000 - 36,000	12,000-36,000
	Selectable Lumens	18,000-28,000	12,000 - 24,000 or 24,000 - 36,000	12,000-18,000 or 24,000-36,000
	Efficacy (Max)	150 lm/W	158 lm/W	137 lm/W
	CRI	80	80	80
	Distribution	Medium (100-deg)	M	M
	Sizes	13.4	12" x 18" or 12" x 36"	12" & 14"
	Housing [2]	Diecast	CRS	Diecast
	Lensing	Polycarbonate	Polycarbonate	Polycarbonate
	Uplight	None	None	None
	Life (@ 60K hrs)	L91	L86	L91
	Ambient Range	-20C to 50C	-40C to 45C	-40C to 45C
	Emergency	Remote	Optional	Remote
	Ratings	IP65	Damp, IP5X	IP65, NSF, NEMA 4X, Wet Location
	DLC	Premium	Premium	Premium
INTEGRATED CONTROLS	Basic Occupancy		✓	
	Stand Alone Daylight / Occupancy	✓	✓	✓
	WaveLinx	✓	✓	✓

Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable
2. CRS=Cold-rolled Steel, Extruded= Extruded Aluminum, Diecast=Diecast Aluminum.