

To assist with sales acceleration of Cruze ST, we have prepared a cross over to clarify the differences in catalog nomenclature to Cruze SB. The **Cruze ST standard efficiency version has no suffix** after the lumens while the original Cruze SB has the "SE" suffix. The **Cruze ST high efficiency versions have the "HE" suffix** after the lumens and the original Cruze SB does not have a suffix. The list below is a reference when comparing Cruze SB to the Cruze ST.

Cruze ST specs

Cruze family 2x4



	Cruze SB	Cruze ST	Lumens	Wattage	Efficacy
STANDARD	24CZ-LD5-30SE-UNV-L840-CD1-U	24CZ2-30-UNV-L840-CD1-U	3032	24.2	125.3
	24CZ-LD5-35SE-UNV-L840-CD1-U	24CZ2-35-UNV-L840-CD1-U	3638	30.1	120.9
	24CZ-LD5-40SE-UNV-L840-CD1-U	24CZ2-40-UNV-L840-CD1-U	4196	36.2	115.9
	24CZ-LD5-45SE-UNV-L840-CD1-U	24CZ2-45-UNV-L840-CD1-U	4618	42.9	107.6
	24CZ-LD5-50SE-UNV-L840-CD1-U	24CZ2-50-UNV-L840-CD1-U	5015	48.6	103.2
	24CZ-LD5-55SE-UNV-L840-CD1-U	24CZ2-55-UNV-L840-CD1-U	5571	50.5	110.3
	24CZ-LD5-60SE-UNV-L840-CD1-U	24CZ2-60-UNV-L840-CD1-U	6042	55.6	108.7
	24CZ-LD5-65SE-UNV-L840-CD1-U	24CZ2-65-UNV-L840-CD1-U	6572	62.8	104.7
HIGH	24CZ-LD5-30-UNV-L840-CD1-U	24CZ2-30HE-UNV-L840-CD1-U	3014	22.4	134.5
	24CZ-LD5-35-UNV-L840-CD1-U	24CZ2-35HE-UNV-L840-CD1-U	3583	26.9	133.2
	24CZ-LD5-40-UNV-L840-CD1-U	24CZ2-40HE-UNV-L840-CD1-U	4029	30.6	131.7
	24CZ-LD5-45-UNV-L840-CD1-U	24CZ2-45HE-UNV-L840-CD1-U	4582	35.3	129.8

Cruze family 2x2



STANDARD	22CZ-LD5-20SE-UNV-L840-CD1-U	22CZ2-20-UNV-L840-CD1-U	2101	17.9	117.4
	22CZ-LD5-24SE-UNV-L840-CD1-U	22CZ2-24-UNV-L840-CD1-U	2450	21.9	111.9
	22CZ-LD5-32SE-UNV-L840-CD1-U	22CZ2-32-UNV-L840-CD1-U	3280	36.7	122.9
	22CZ-LD5-39SE-UNV-L840-CD1-U	22CZ2-39-UNV-L840-CD1-U	3943	34.5	114.3
	22CZ-LD5-44SE-UNV-L840-CD1-U	22CZ2-44-UNV-L840-CD1-U	4424	42.7	103.6
HIGH	22CZ-LD5-20-UNV-L840-CD1-U	22CZ2-20HE-UNV-L840-CD1-U	2044	16.0	127.7
	22CZ-LD5-24-UNV-L840-CD1-U	22CZ2-24HE-UNV-L840-CD1-U	2416	19.2	125.8
	22CZ-LD5-29-UNV-L840-CD1-U	22CZ2-29HE-UNV-L840-CD1-U	2942	22.2	132.5
	22CZ-LD5-34-UNV-L840-CD1-U	22CZ2-34HE-UNV-L840-CD1-U	3386	25.8	131.2
	22CZ-LD5-39-UNV-L840-CD1-U	22CZ2-39HE-UNV-L840-CD1-U	3930	30.3	129.7
	22CZ-LD5-44-UNV-L840-CD1-U	22CZ2-44HE-UNV-L840-CD1-U	4464	35.0	127.5

Cruze family 1x4



STANDARD	14CZ-LD5-20-UNV-L840-CD1-U	14CZ2-20-UNV-L840-CD1-U	2008	16.3	123.2
	14CZ-LD5-25-UNV-L840-CD1-U	14CZ2-25-UNV-L840-CD1-U	2473	20.5	120.7
	14CZ-LD5-29-UNV-L840-CD1-U	14CZ2-29-UNV-L840-CD1-U	2879	24.3	118.5
	14CZ-LD5-35-UNV-L840-CD1-U	14CZ2-35-UNV-L840-CD1-U	3545	31.2	113.6
	14CZ-LD5-39-UNV-L840-CD1-U	14CZ2-39-UNV-L840-CD1-U	3941	32.3	121.7
	14CZ-LD544-UNV-L840-CD1-U	14CZ2-44-UNV-L840-CD1-U	4511	38.3	117.8
HIGH		14CZ2-39HE-UNV-L840-CD1-U	3965	29.3	135.3
		14CZ2-48HE-UNV-L840-CD1-U	4823	36.9	130.7
		14CZ2-60HE-UNV-L840-CD1-U	6021	48.3	124.7