

# Architectural Linear LED


Lines of Light

# Metalux | Corelite | Neo-Ray

**M**arket focused portfolio with products designed for broad applications

**V**alue - competitive prices with industry leading DLC listings

**P**erformance - market leading performance with connected sensors options delivering value beyond lumens per watt



Whether lighting contemporary architectural spaces or general area lighting, **Cooper Lighting Solutions' architectural linear LED** products offer a complete family of innovative, affordable, and energy saving LED solutions for your next project.

|                            |                                        | Good        |                             | Better      |                           | Best        |                                |
|----------------------------|----------------------------------------|-------------|-----------------------------|-------------|---------------------------|-------------|--------------------------------|
|                            |                                        |             |                             |             |                           |             |                                |
|                            |                                        |             |                             |             |                           |             |                                |
| APPLICABILITY <sup>1</sup> | Office                                 | Metalux RBG | ★★                          | Metalux RCG | ★★                        | Corelite CL | ★★                             |
|                            | Secondary Education                    |             | ★★                          |             | ★★                        |             | ★★★                            |
|                            | Primary Education                      |             | ★★★                         |             | ★★★                       |             | ★★                             |
|                            | Healthcare                             |             | ★★                          |             | ★                         |             | ★★★                            |
|                            | Tenant Improvement                     |             | ★★★                         |             | ★★★                       |             | ★                              |
|                            |                                        |             |                             |             |                           |             |                                |
| FEATURES / PERFORMANCE     | Apertures                              |             | 4"                          |             | 3"                        |             | 2", 4"                         |
|                            | Sizes                                  |             | Fixed 2', 4', 8'            |             | 4', 8'                    |             | 4', 8' + Continuous Runs       |
|                            | Length Resolution                      |             | Fixed                       |             | Fixed                     |             | 4' Increments                  |
|                            | Installation Type                      |             | Ceiling, Wall               |             | Ceiling                   |             | Ceiling                        |
|                            | Configuration Geometry                 |             | Straight                    |             | Straight                  |             | Straight                       |
|                            | Compatible Family Fixtures             |             | Surface/Susp & Drywall Kits |             | N/A                       |             | N/A                            |
|                            | lm/W (Max)                             |             | 115                         |             | 121                       |             | 124                            |
|                            | Lms/ft (Max)                           |             | 1,000                       |             | 1,000                     |             | 1,200                          |
|                            | Standard Lumen Levels                  |             | 3                           |             | 4                         |             | 5                              |
|                            | Lens                                   |             | Flush Frosted               |             | Flush Frosted, Asymmetric |             | Flush Frosted, Asymmetric      |
|                            | Emergency                              |             | Integrated, Remote Switch   |             | Integrated                |             | Integrated                     |
|                            | CRI                                    |             | 80+                         |             | 80 Standard, 90 Optional  |             | 80 Standard, 90 Optional       |
|                            | Ceiling Integration / Flange Type      |             | Standard T-Grid, Gypsum     |             | Standard T-Grid, Gypsum   |             | 6 Common Architectural Systems |
|                            | DLC                                    |             | Standard                    |             | Standard                  |             | Standard & Premium             |
|                            | VividTune™                             |             | No                          |             | No                        |             | No                             |
| INTEGRATED CONTROLS        | WaveLinx, Enlighted, DLVP, Stand Alone |             | Integrated or Tile Mount    |             | Integrated                |             | Integrated                     |
|                            | Integral Downlights                    |             | N/A                         |             | N/A                       |             | N/A                            |
|                            |                                        |             |                             |             |                           |             |                                |
|                            |                                        |             |                             |             |                           |             |                                |
|                            |                                        |             |                             |             |                           |             |                                |
|                            |                                        |             |                             |             |                           |             |                                |
|                            |                                        |             |                             |             |                           |             |                                |
|                            |                                        |             |                             |             |                           |             |                                |
|                            |                                        |             |                             |             |                           |             |                                |
|                            |                                        |             |                             |             |                           |             |                                |
|                            |                                        |             |                             |             |                           |             |                                |
|                            |                                        |             |                             |             |                           |             |                                |
|                            |                                        |             |                             |             |                           |             |                                |

Notes: 1. ★★ = high applicability, ★ = medium applicability, ★ = low applicability, blank = non-applicable



**Cooper Lighting Solutions**  
1121 Highway 74 South  
Peachtree City, GA 30269  
P: 770-486-4800  
www.cooperlighting.com

**Canada Sales**  
5925 McLaughlin Road  
Mississauga, Ontario L5R 1B8  
P: 905-501-3000  
F: 905-501-3172

© 2021 Cooper Lighting Solutions  
All Rights Reserved  
Publication No. SA519058EN-web  
November 2, 2021 11:52 AM

Cooper Lighting Solutions is a registered trademark.  
All other trademarks are property of their respective owners.  
Product availability, specifications, and compliances are subject to change without notice.