

Good

Better

Best

Click on products to learn more



		GRW	GRV	FSP	FCB	FCZ	ENW/ENC	ENV	CLM	CLP	FSN
Applicability ¹	Vandal Resistant	●	●●●	●●	●●	●●●	●	●●●	●	●	●●●
	High Abuse	●	●●●	●●●	●●	●●●	●●	●●●	●●	●	●●●
	Healthcare	●	●	●●●	●●●	●●●	●●●	●●	●	●	●●●
	Behavioral Health	●	●●●	●●	●●	●●●	●	●●●	●	●	●●●
	Cleanroom	●		●●●		●●	●●●	●●	●●●	●●●	●●
	Pharmaceuticals	●●		●●●	●	●●	●●●	●●	●●●	●●●	●●
	Vivariums					●			●●●	●●●	
	Hosedown	●●		●●●	●	●●	●●●	●●●	●●●	●●●	●●●
	Food Prep			●●●		●●●	●●●	●●	●●●	●●●	●●●
Features	Size	1' x 4', 2' x 2', 2' x 4'	1' x 4', 2' x 2', 2' x 4'	1' x 4', 2' x 2', 2' x 4'	1' x 4', 2' x 2', 2' x 4'	1' x 4', 2' x 2', 2' x 4'	1' x 4', 2' x 2', 2' x 4'	1' x 4', 2' x 2', 2' x 4'	1' x 4', 2' x 2', 2' x 4'	1' x 4', 2' x 2', 2' x 4'	Fixed 2', 4', 8'
	Mounting	Grid	Grid	Grid	Grid	Grid	Grid	Grid	Grid	Grid/Flange/Surface	Surface
	Max Lumens	18,000	18,000	6,400	7,500	7,500	7,000	7,000	24,000	24,000	4,121 (4ft)
	Sevice from Below	✓	✓		✓				✓	✓	
Ratings	Wet Location	Standard	Standard	Standard	Optional	Standard	Optional (ENW) Standard (ENC)	Standard	Standard	Standard	Standard
	IP	-	-	IP66 Optional	-	IP65 Optional	IP66	IP66	IP65	IP66	IP66
	NSF	-	-	Standard	-	Standard	Standard	Standard	Standard	Standard	Standard
	ISO Cleanroom ²	-	-	5	-	5	5	5	5	5	5

Notes: 1. ●●●= high applicability, ●●= medium applicability, ●= low applicability, blank = non-applicable
 2. Fixtures rated ISO 5 are compatible with cleanrooms rated ISO 5 or higher.