

A modern office hallway with a large wall of vertical garden modules and wood slats. The wall is composed of horizontal wooden slats of various shades of brown, interspersed with rectangular panels of vibrant green moss or small plants. The ceiling features exposed ductwork, pipes, and several cylindrical pendant lights. Two women are walking in the distance on the left side of the hallway.

Portfolio

Surface Mount

2-inch, 4-inch, 6-inch & 8-inch
Surface & Wall Mount Cylinders

Portfolio

architectural downlighting



Illuminate your creativity



Designed to complement any architectural space, the 2, 4, 6, and 8" LED round and square, standard or shallow height cylinders complement any space with wall, ceiling, pendant-mount, or aircraft cable options. A two-stage system produces smooth distribution with excellent light control and low aperture brightness. The cylinders are available in multiple lumen packages, color temperatures and a variety of finishes with custom options. Standard 0-10V driver dims to 1% and a multitude of optional drivers are available. Creating the perfect atmosphere is easy with these sleek cylinders that offer a variety of color control and connected options.



LSR2B, LSSQ2B
2" Round and Square Cylinders



LER4C/LESQ4C
LER4D/LESQ4D
4" Round and Square Cylinders



LER6C/LESQ6C
LER6D/LESQ6D
6" Round and Square Cylinders



- Available lumens
 - 2" = 500, 1000, 1500, and 2000 lumens
 - 4" = 250-5000 lumens
 - 6" = 250-6500 lumens
 - 8" = 1000-15,000 lumens
- Standard and shallow heights
- Round or square
- Ceiling mount, pendant mount, aircraft cable, cord, power over cable, wall mount, up/down versions, yoke mount or internal adjustment
- Ceiling mount wet location with covered ceiling, Wall mount wet location listed
 - Optional lens kit for up/down wet locations
- Emergency battery backup
- Remote or integral drivers with multiple options



Multiple installation options




Wall



Surface



Yoke Mount



48" White or Black
120" White or Black

Aircraft Cable



Pendant or Cord Mount

36" Pendant Kit
SP* Special lengths available
(made to order - see ordering information)

Finishes:
MW Matte White
MB Matte Black
SL Silver
BZ Bronze

60" Cord Kit
120" Cord Kit

Finishes:
MW Matte White
MB Matte Black



LuxWire™ Aircraft Cable

120" White or Black



Advanced LuxWire™ technology.

Low-voltage power is elegantly delivered to the cylinder via aircraft cables. Drivers and bulky power cords are tucked above the ceiling, allowing the luminaire to float beautifully in space.

Standard or custom finishes



P

Matte White



MB

Matte Black



SL

Silver



BZ

Bronze



Custom finishes available
to compliment a design.
Consult our factory for details.

Reflector finishes



LI

Specular



H

Semi Specular Clear



WMH

Warm Haze



WH

Wheat



GPH

Graphite Haze



B

Specular Black

Painted Reflector finishes



MW

Matte White



MB

Matte Black



MMS

Matte Metallic Silver



Color Control



Fine Tuning of Light

Whether you're looking to optimize productivity or simply add dramatic flair, VividTune's tunable white technology allows you to adjust the color temperature from warm white to cool white, creating an environment that fosters productivity and concentration.





light intensity



D2W™ Dim-to-Warm Solution

Bring the warm, dim glow reminiscent of traditional incandescent and halogen sources into your space, for a fraction of the energy consumption, with our dim-to-warm solution.




dim-to-warm



The Importance of Light on Performance


Light has a visual impact (see better), an emotional impact (feel better), and a biological impact (function better).



Spectrally Enhanced Tunable and Static White

WaveLinx

- Digital Lighting
Control
Solutions



SCAN for
WaveLinx Brand

SIMPLE. SCALABLE. INSIGHTFUL.

WaveLinx LITE



WaveLinx LITE is a cost effective, wireless digital lighting control system, with out-of-the-box functionality, that saves energy and meets code. Customize installations using the secure, simple WaveLinx mobile app.



SCAN for
WaveLinx LITE

WaveLinx PRO



WaveLinx PRO is a wireless lighting control solution, for connected spaces, that significantly reduces a building's energy consumption. From a single floor to an entire campus, WaveLinx PRO connects more than lighting assets; it shares aggregated sensor data with the WaveLinx CORE platform and other building systems, so building owners can improve operations, spaces environment, and tenants' experience using a desktop or mobile app.



SCAN for
WaveLinx PRO



LITE Tilemount Sensor

The WLST tilemount sensor kit provides occupancy/vacancy sensing and daylight dimming capabilities as part of the innovative WaveLinx Bluetooth enabled system.



LITE Node

The WaveLinx LITE Node (OEM-WLN) is a wireless to 0-10V control module designed to be integrated into the luminaire. The LITE Node offers two continuous 0-10V output channels that can be used to control dim-to-off 0-10V LED drivers with auxiliary power.



PRO Tilemount Sensor

The WPST tilemount sensor kit provides occupancy/vacancy sensing and daylight dimming capabilities as part of the innovative WaveLinx Bluetooth enabled system.



PRO Node

The WaveLinx PRO Node (OEM-WPN) is a wireless to 0-10V control module designed to be integrated into the luminaire. The adapter offers two continuous 0-10V output channels that can be used to control dim-to-off 0-10V LED drivers with auxiliary power.



Lighting Brands

Ametrix
AtLite
Corelite
Ephesus
Fail-Safe
HALO
HALO Commercial
Invue
iO
Iris
Lumark
LumarkAP
Lumière
McGraw-Edison
Metalux
MWS
NeoRay
Portfolio
PrentaLux - 3D Printed Lighting
RSA
Shaper
Streetworks
Sure-Lites

Controls Brands

Greengate
Fifth Light
Intelligent Lighting Controls

Connected Lighting Systems and Smart Spaces Platform

WaveLinx
Trellix Infrastructure



SCAN
for more
Portfolio
information