

# Industrial LED Vaportite

## Selection Guide

# Metalux

**M**arket focused portfolio with products designed for broad applications

**V**alue - competitive prices with industry leading DLC listings

**P**erformance - market leading performance with connected sensors options delivering value beyond lumens per watt



Metalux's sealed and gasketed products deliver maximum operation and reliability in complex environments where the elements require more than just a standard light fixture.

Click on products to learn more

Good

Better

Best

		APVT	VT2	VT3	VT4S	VT4
<b>APPLICABILITY<sup>1</sup></b>	Canopy	★★	★★	★★		
	Storage	★★★	★★★	★★		
	Parking Garage		★★	★★★		
	Warehouse	★	★★★	★★★	★	★
	Food Processing		★★	★★★	★★	★★
	Manufacturing		★★	★★	★★★	★★★
	Complex Environments		★	★★★	★★★	★★★
<b>FEATURES / PERFORMANCE</b>	Lumen Range	2,000 - 4,000	2,000 - 22,000	2,000 - 8,000	9,000 - 18,000	9,000 - 30,000
	Efficacy (Max)	132 lm/W	150 lm/W	154 lm/W	165 lm/W	146 lm/W
	Distribution <sup>2</sup>	G	G, W	G, W, P	G	G
	Sizes	2', 4'	2', 4', 8'	2', 4'	2'	4'
	Housing	Polycarbonate	Fiberglass/Polyester	Fiberglass/Polyester	Fiberglass	Fiberglass
	Lensing	Polycarbonate	DR Acrylic or Polycarb	DR Acrylic or Polycarb	DR Acrylic or Polycarb	DR Acrylic or Polycarb
	Wet Location	Yes	Yes	Yes	Yes	Yes
	IP Rating	None	None	IP65, 66, 67	IP65, 66, 67, 69	IP65, 67
	NSF	None	Yes	Yes	Yes	Yes
	NEMA 4X	None	None	None	Yes	Yes
	Life (@60K hrs)	L70 at 54K	L91	L91	L91	L92
	Ambient Range	-20C to 30C	-40C to 35C	-40C to 50C	-40C to 40C	-40C to 40C
	Emergency	None	Yes	Yes	Yes	Yes
Vandal Resistant	None	Optional	Optional	Optional	Optional	
DLC	Standard	Premium	Premium	Premium	Premium	
<b>INTEGRATED CONTROLS</b>	Basic Occupancy		✓	✓	✓	✓
	Stand Alone Daylight / Occupancy		✓	✓	✓	✓
	WaveLinx					
	LumaWatt Pro <sup>3</sup>					

Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable  
 2. G=General, W=Wide, P=Parking Garage.  
 3. Location data for asset tracking.



**Cooper Lighting Solutions**  
 1121 Highway 74 South  
 Peachtree City, GA 30269  
 P: 770-486-4800  
 www.cooperlighting.com

**Canada Sales**  
 5925 McLaughlin Road  
 Mississauga, Ontario L5R 1B8  
 P: 905-501-3000  
 F: 905-501-3172

© 2021 Cooper Lighting Solutions  
 All Rights Reserved  
 Publication No. SA507007EN-web  
 May 18, 2021 9:00 AM

Cooper Lighting Solutions is a registered trademark.  
 All other trademarks are property of their respective owners.  
 Product availability, specifications, and compliances are subject to change without notice.