



Refined
Square Design



The RSQ Series is the perfect lighting solution for low to medium-height ceilings. A shallow square lens and rotatable baffle trim make installation and alignment a breeze.

With the Lumen Select Switch and flicker-free 5% dimming, you can easily customize the lighting levels to fit your needs. And the 6-position CCT switch offers a range of 5 color temperatures, plus Dim-to-Warm, allowing you to create your own amazing ambiance.

These LED trims are suitable for new construction, remodel, and retrofit installation in most IC (insulation contact) or non-IC housings. The integral gasket ensures it's AIR-TITE, code-compliant, and provides additional energy savings.

Upgrade your lighting with the RSQ Square Recessed LED Trims today.

Product Features


- Square 4", 5", and 6" sizes available
- Installs into most recessed housings
- 6-position CCT switch, 5-color SeleCCTable (27/30/35/40/5000K) + Dim-to-Warm (3000K dims to 1800K); 90+ CRI
- Square rotatable dead-front baffle trim and shallow square diffuse lens
- Lumen Select Switch - 600/900 or 600/1000 lms (nominal)
- Dims to 5% (phase cut LE/TE) with compatible dimmers; 120V input
- Mounting hardware, orange LED Quick Connect and E26 adapter included
- AIR-TITE, wet location-listed, IC-rated, and ENERGY STAR® certified
- 50,000 hrs of maintenance-free operation
- 5-year warranty



LEARN MORE



RSQ4LS9FSD2W1EWH



RSQ5LS9FSD2W1EWH



RSQ6LS9FSD2W1EWH

EASY INSTALLATION

Fits most recessed housings*



* See website for list of compatible housings.




RSQ Series trims are rotatable, making the challenge of aligning square fixtures a breeze.





Personalize Your Lighting




Selectable technology to help you get the perfect light. Adjust color temperature with the SeleCCTable switch or increase the overall brightness with a Lumen Select fixture.




Bright White (3000K) dims to Candlelight (1800K)

Dim-to-warm is a stunning lighting effect that is built into many preferred and premium HALO product series.


Catalog Number	Material Number	Description	UPC	Accessories
				Decorative Baffle Trim Overlays
RSQ4LS9FSD2W1EWH	13644856	4" Square Recessed LED Trim, 600/900 Lumen Select, 6-position Color SeleCCTable (5CCT+D2W) 90 CRI, 120V 60Hz, 5% Phase Cut LE/TE Dimming, Matte White	080083282531	RSQ4TRMWH Paintable Matte White RSQ4TRMSN Satin Nickel RSQ4TRMTBZ Tuscan Bronze RSQ4TRMMB Matte Black
RSQ5LS9FSD2W1EWH	13644857	5" Square Recessed LED Trim, 600/900 Lumen Select, 6-position Color SeleCCTable (5CCT+D2W) 90 CRI, 120V 60Hz, 5% Phase Cut LE/TE Dimming, Matte White	080083282555	RSQ5TRMWH Paintable Matte White RSQ5TRMSN Satin Nickel RSQ5TRMTBZ Tuscan Bronze RSQ5TRMMB Matte Black
RSQ6LS9FSD2W1EWH	13644858	6" Square Recessed LED Trim, 600/900 Lumen Select, 6-position Color SeleCCTable (5CCT+D2W) 90 CRI, 120V 60Hz, 5% Phase Cut LE/TE Dimming, Matte White	080083282579	RSQ6TRMWH Paintable Matte White RSQ6TRMSN Satin Nickel RSQ6TRMTBZ Tuscan Bronze RSQ6TRMMB Matte Black




Paintable
Matte White



Satin Nickel



Tuscan Bronze



Matte Black



Refer to ENERGY STAR® Certified Products List. Can be used to comply with California Title 24 High Efficacy requirements. Certified to California Appliance Efficiency Database under JAB.

NOTE: Due to T20 changes as of July 1st 2019 consult factory for current catalog number and availability for T20 compliant products.

Lighting Brands

Ametrix
AtLite
Corelite
Ephesus
Fail-Safe
HALO
HALO Commercial
Invue
iO
Iris
Lumark
LumarkAP
Lumière
McGraw-Edison
Metalux
MWS
NeoRay
Portfolio
PrentaLux - 3D Printed Lighting
RSA
Shaper
Streetworks
Sure-Lites

Controls Brands

Greengate
Fifth Light
Intelligent Lighting Controls

Connected Lighting Systems and Smart Spaces Platform

WaveLinx
Trellix Infrastructure



SCAN
for more
HALO
information



Cooper Lighting Solutions
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.cooperlighting.com

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2024 Cooper Lighting Solutions
All Rights Reserved
Printed in USA
Publication No. BR51844424
April 2024

Cooper Lighting Solutions is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.