

E26 6" Trim Series


DESCRIPTION

Air-Tite™ frosted dome lens with reflector 6" trim family for use in recessed downlighting. Compatible for use in Halo and other housings.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

- Frosted glass dome
- Non-conductive, non-corrosive gasketed polymer (plastic) trim ring
- Features "dead-front" construction and is wet location listed for use in showers
- Torsion spring retention
- Air-Tite trim makes any installation Air-Tite



Dimensions:

H: 2-1/8"[54mm]

OD: 7-3/4"[197mm]

Housings		Max Lamp Compatibility
H7ICT	H7ICAT	60W A19, 50W PAR30S
H7RICT	H7RICAT	
E7ICAT	E7RICAT	172PS: 53W A19, 50W PAR30S 172SNS, 172TBZS: 43W A19, 50W PAR30S
H7UICAT		75W A19, 75W PAR30
H7ICTNB		60W A19
H7ICATNB		
E7ICATNB		172PS: 53W A19, 50W PAR30S 172SNS, 172TBZS: 43W A19, 50W PAR30S
H27ICAT		60W A19, 50W PAR30S
H27RICAT		
E27ICAT		43W A19
E27RICAT		
H7T	E7TAT	100W A19, 75W PAR30S
H7RT	E7RTAT	60W A19, 50W PAR30S
H7TNB	E7TATNB	100W A19, 75W PAR30S
H27T	E27TAT	100W A19, 75W PAR30S
H27RT	E27RTAT	72W A19, 75W PAR30S

Compatible with Halogen, Incandescent, LED* or CFL* lamps.



172PS
White Trim, Dome Lens
with Reflector



172SNS
Satin Nickel Trim,
Dome Lens with Reflector



172TBZS
Tuscan Bronze Trim,
Dome Lens with Reflector

172
6-Inch Frosted Glass
Dome with Reflector,
Wet Location Listed

"Dead Front"
Non-Conductive
trim ring and glass lens



For use in Halo listed housings.



Select trims are classified for use in
others housings.
See www.cooperlighting.com.



ORDERING INFORMATION

SAMPLE NUMBER: 172PS

Trim	Finish
172PS= 6" Frosted Glass Dome, White Polymer Trim	WH=White
172SNS= 6" Frosted Glass Dome, Satin Nickel Polymer Trim	SN=Satin Nickel
172TBZS= 6" Frosted Glass Dome, Tuscan Bronze Polymer Trim	TBZ=Tuscan Bronze

HALO HOUSING COMPATIBILITY

Trim #	Style	H7ICT	H7ICAT	H7RICT	H7RICAT	E7ICAT	E7RICAT	H7UICAT	H7ICTNB
172PS 172SNS 172TBZS	Showerlight	•	•	•	•	•	•	•	•
		H7ICATNB	E7ICATNB	H27ICAT	H27RICAT	E27ICAT	E27RICAT		
		•	•	•	•	•	•		
		H7T	H7TCP	H7RT	E7TAT	E7RTAT	H7TNB	E7TATNB	H27T
		•		•	•	•	•	•	•
		H27RT	E27TAT	E27RTAT					
•	•	•							

For use in select other's housings, refer to U.L. classification list at www.cooperlighting.com

*UL1993 listed LED & CFL equivalent lamps permitted. Consult lamp manufacturer for conditions of use. Cooper Lighting Solutions does not warranty the lamp.