



**Meet energy codes.
Reduce cost.
Save time.**



OSW-D-010 / VSW-D-010
0-10V Dual Tech Sensor Dimmer
Occupancy / Vacancy




OSW-P-010 / VSW-P-010
0-10V PIR Sensor Dimmer
Occupancy/Vacancy


3 Devices in one

Eaton's 0-10V Dual Tech Sensor Dimmer is a 3-in-1 solution that combines functionality of a switchpack, a sensor and a 0-10V dimmer into one wallbox device to help customers save labor costs, reduce installation time as well as meet the latest energy codes and standards.

Typical 0-10V Dimming & Sensing



0-10V Dimming & Sensing




One device replaces three!

Eaton's 0-10V Dual Tech Sensor Dimmer solution offers a convenient and cost effective way for users to satisfy commercial energy codes like ASHRAE 90.1 and California Title 20 that require designs that enable energy savings for Commercial facilities.

Design features

- 0-10V Dimming
- Occupancy sensing
- Integrated photocontrol for daylight harvesting*
- Title 20 compliant
- Easily configurable for application specific operation
- Surge and zero cross protection
- Universal input (120-277V)
- cULus, NOM and ANCE certified

*Available only on Dual Tech Models





Catalog No.	Description	Compatible Lamp Types	Rating		Colors
			Watt	V/AC	
OSW-D-010-	0-10V Dual Tech Sensor Dimmer - Occupancy with LED Single pole/3-Way preset	0-10VDC LED/FLR	960 2200	120 277	White (W) Black (BK) Gray (G) Light Almond (LA)
VSW-D-010-	0-10V Dual Tech Sensor Dimmer - Vacancy with LED Single pole/3-Way preset	0-10VDC LED/FLR	960 2200	120 277	Ivory (V) Red (R)

For ordering devices, include Catalog no. followed by the Color suffix:
W (White), B (Black), G (Gray), LA (Light Almond), V (Ivory), R (Red)

Note: Not all colors are available in stock and some color options may have extended lead times.

W	B	G	LA	V	R
(White)	(Black)	(Gray)	(Light Almond)	(Ivory)	(Red)



Catalog No.	Description	Compatible Lamp Types	Rating		Colors
			Watt	V/AC	
OSW-P-010-	0-10V Occupancy Dimmer Sensor	0-10VDC LED/FLR	1200 2200	120 277	White (W) Black (BK) Gray (G) Light Almond (LA)
VSW-P-010-	0-10V Vacancy Dimmer Sensor	0-10VDC LED/FLR	1200 2200	120 277	Ivory (V)

For ordering devices, include Catalog no. followed by the Color suffix:
W (White), B (Black), G (Gray), LA (Light Almond), V (Ivory)

Note: Not all colors are available in stock and some color options may have extended lead times.

W	B	G	LA	V
(White)	(Black)	(Gray)	(Light Almond)	(Ivory)

Lighting Brands

Ametrix
AtLite
Corelite
Ephesus
Fail-Safe
Halo
Halo Commercial
Invue
io
Iris
Lumark
Lumière
McGraw-Edison
Metalux
MWS
Neo-Ray
Portfolio
RSA
Shaper
Streetworks
Sure-Lites

Controls Brands

Greengate
Fifth Light

Connected Lighting Systems

HALO Home
WaveLinx

IoT Platforms

Trellix

Cooper Lighting Solutions

1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.cooperlighting.com

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2021 Cooper Lighting Solutions
All Rights Reserved
Printed in USA
Publication No. BR503058EN
March2021

Cooper Lighting Solutions is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.

