

F-Bay Mounting Accessories<sup>(1)</sup>

Mounting Accessories		Designation	Description	
<b>Single Point Mount</b> 		<b>HB</b> <b>HBL</b> <b>I5/I8</b> <b>OHB</b> <b>VHB</b>	<b>-SPM</b> =Galvanized Single Monopoint Hanging Kit with Hub	
		<b>HB</b> <b>HBL</b> <b>I5/I8</b>	<b>-SPM-S</b> =Galvanized Surface Mount Hanging Kit with Hub	
		<b>ILED</b>	<b>-SPM</b> =Galvanized Single Monopoint Hanging Kit with Hub	
Mounting Methods		Designation	Description	
<b>Hook and Safety Hook</b> 		<b>FH-1</b> =Fixture Hook	Fixture Hook (must be used with -SPM accessory)	
		<b>FL-1</b> =Fixture Loop	Fixture Loop (must be used with -SPM accessory)	
<b>SHK</b> 		<b>SHK</b> =Fixture Hook	Fixture Hook (must be used with -SPM accessory)	

Notes: (1) Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information.

Fixture Series	AYC	HB/AYC	SPM	SHK	Single Toggle	"Y" Toggle	Loop Hanger	Mounting Hardware Included
<b>HBI/HBL</b>		X	X	X		X		
<b>ILED</b>	X		X	X	X		X	
<b>CZL</b>	X			X	X	X	X	
<b>BMK</b>				X			X	
<b>LHBS</b>							X	V-hanger and chain
<b>OHB</b>		X	X	X		X		V-hanger
<b>VHB/VHBS</b>		X		X		X		V-hanger
<b>SNX</b>	X				X	X <sup>(2)</sup>		
<b>SLSTP</b>	X					X <sup>(2)</sup>		J-box cover plate w/ screws
<b>ST</b>		X			X	X <sup>(2)</sup>		
<b>Steeler</b>			X					hook
<b>UHBS</b>				X				Hook
<b>VT2 LED</b>						X		
<b>VT3</b>							X	
<b>VT4/VT4S</b>						X		V-hanger only
<b>APVTS</b>								Surface Mnt Bracket and V-clip

Notes: (2) Continuous row mount only between fixtures.

F-Bay Mounting Accessories<sup>(1)</sup>

Mounting Methods	Catalog Logic	Description
HBAYC-CHAIN/SET-U=Hook style V-hanger w/chain set		Two (2) Hook style V-hangers, thirty-six Inch (36") Chain Sets with S-hooks
AYC-CHAIN/SET-U=V-hanger w/chain set		Standard V-hanger and thirty-six Inch (36") Chain Sets with S-hooks
"Y" Toggle	Y-Toggle-10-2PK=Mounting Toggle and Ten Foot (10') Cable	(2) Y-Toggle #2 Cables at 10FT long
	Y-Toggle-30-2PK=Mounting Toggle and Thirty (30') Cable	(2) Y-Toggle #2 Cables at 30FT long
Loop Hanger	Loop-10	Ten Foot (10') Loop Hanger #2 Cable
	Loop-30	Thirty Foot (30') Loop Hanger #2 Cable
Single Toggle	Toggle-10	Ten Foot (10') Single Toggle #2 Cable
	Toggle-30	Thirty Foot (30') Single Toggle #2 Cable

Notes: (1) Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information.