WSNLED and **WNLED**

Premium and utility commercial LED wraparound

Metalux







WNLED/WSNLED Commercial LED wraparounds

These two product lines offer traditionally styled wraparound with Cooper Lighting Solutions' latest market leading LED and energy efficiency driver technologies. Offered in multiple lumen packages, color temperatures and driver options, the **WSNLED** and **WNLED** series enables customers to have the ideal balance with aesthetics, performance and energy efficiency. Additionally, the WSNLED series utilizes premium optical material which enhances the visual aesthetics providing customers with even, clean illumination eliminating lamp image commonly associated with traditional fluorescent solutions.



Performance

- · 4 ft. and 2 ft. product configurations
- Lumen package WSNLED (15) and WNLED (4)
- Evenly illuminated lens (WSNLED) for premium aesthetic or frost prismatic lens (WNLED)
- Multiple CCT: 3000K, 3500K, 4000K, 5000K at 82+ CRI
- Excellent performance, up to 145 lm/W
- Powered by Fifth Light. 0-10V dimming driver is standard
- · Ideal for surface and suspended
- · Suitable for use in clothes closets
- · L88 at 60,000 hours
- Five-year limited warranty

Controls

- WNLED and WSNLED luminaires include 0-10V dimming drivers for control using wall dimmers (10% - 100%), daylighting sensors and room controllers from Cooper Lighting Solutions. Optional 1% dimming available.
- WNLED and WSNLED luminaires are available with native DALI drivers for complete digital energy management using Fifth Light addressable controls.

Compliance

- LED modules comply with IESNA LM-79 and LM-80 standards
- DesignLights Consortium® Qualified and classified for both DLC Standard and DLC Premium, refer to www.designlights.org for details.
- cULus listed 1598 for damp locations
- · RoHS compliant

Compliance and approvals









LM79 / LM80 Compliant







fifthlight









Energy and performance

WNLED Utility LED wraparound								
Lumen type	Length	Catalog number	Nominal 3500K lumens	Wattage	lm/W			
Standard	2 ft.	2WNLED-LD4-28SL-F-UNV-L835-CD1-U	2786	27.5	101			
Standard	4 ft.	4WNLED-LD4-32SL-F-UNV-L835-CD1-U	3298	28.0	118			
Standard	4 ft.	4WNLED-LD4-40SL-F-UNV-L835-CD1-U	4062	36.0	113			
Standard	4 ft.	4WNLED-LD4-50SL-F-UNV-L835-CD1-U	4966	46.6	107			

WSNLED Premium LED wraparound							
Lumen type	Length	Catalog number	Nominal 3500K lumens	Wattage	lm/W		
Standard	2 ft.	2WSNLED-LD4-20SL-F-UNV-L835-CD1-U	1978	14.3	138		
Standard	2 ft.	2WSNLED-LD4-24SL-F-UNV-L835-CD1-U	2507	18.4	136		
Standard	2 ft.	2WSNLED-LD4-28SL-F-UNV-L835-CD1-U	3037	22.4	136		
Standard	4 ft.	4WSNLED-LD4-20SL-F-UNV-L835-CD1-U	1983	14.3	139		
Standard	4 ft.	4WSNLED-LD4-24SL-F-UNV-L835-CD1-U	2525	17.4	145		
Standard	4 ft.	4WSNLED-LD4-28SL-F-UNV-L835-CD1-U	2795	20.4	137		
Standard	4 ft.	4WSNLED-LD4-32SL-F-UNV-L835-CD1-U	3064	21.6	142		
Standard	4 ft.	4WSNLED-LD4-36SL-F-UNV-L835-CD1-U	3600	25.6	141		
Standard	4 ft.	4WSNLED-LD4-40SL-F-UNV-L835-CD1-U	4044	28.9	140		
Standard	4 ft.	4WSNLED-LD4-44SL-F-UNV-L835-CD1-U	4486	32.2	139		
High	4 ft.	4WSNLED-LD4-48HL-F-UNV-L835-CD1-U	4750	34.3	139		
High	4 ft.	4WSNLED-LD4-52HL-F-UNV-L835-CD1-U	5276	38.3	138		
High	4 ft.	4WSNLED-LD4-56HL-F-UNV-L835-CD1-U	5712	41.8	137		
High	4 ft.	4WSNLED-LD4-60HL-F-UNV-L835-CD1-U	6059	45.0	135		
High	4 ft.	4WSNLED-LD4-64HL-F-UNV-L835-CD1-U	6405	48.0	133		

Lighting Brands

Ametrix AtLite Corelite **Ephesus** Fail-Safe HALO

HALO Commercial

Invue iΟ Iris Lumark LumarkAP Lumière

McGraw-Edison

Metalux MWS NeoRay Portfolio

PrentaLux - 3D Printed Lighting

RSA Shaper Streetworks Sure-Lites

Controls Brands

Greengate Fifth Light

Intelligent Lighting Controls

Connected Lighting Systems and Smart Spaces Platform

WaveLinx

Trellix Infrastructure



Cooper Lighting Solutions 1121 Highway 74 South Peachtree City, GA 30269 P: 770-486-4800 www.cooperlighting.com

Canada Sales 5925 McLaughlin Road Mississauga, Ontario L5R 1B8 P: 905-501-3000 F: 905-501-3172

Cooper Lighting Solutions is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.

© 2024 Cooper Lighting Solutions All Rights Reserved Printed in USA Publication No. BR519017EN November 19, 2024 12:49 PM