

Metalux

SNX Performance Strip

Versatile Luminaire for any space

Offered in multiple sizes and configurations, the SNX is the perfect linear solution for a variety of applications. The streamline, narrow housing can be installed as a continuous row or as a stand alone fixture delivering from 2,000 up to 21,000 lumens.



Scan for more.



Save Money

Compact, narrow design delivers performance with less material, reducing initial project costs



Save Time

Encapsulated LED lens assembly with tool-less, snap-in design for quicker install



Peace of Mind

Certified and guaranteed performance backed by CLS 5-year warranty

Office • Schools • Data Centers • Retail • Warehouse/Distribution
• Manufacturing • Commercial and Industrial




Lens Options




Integral Sensor



Base




Accessories



Contractor friendly installation

- One piece Encapsulated LED/Lens assembly for easy installation
- Multiple mounting options for different applications
- CRS channel rated for thru-branch wiring

Click for animation



	Features	Benefits	Result
Construction	2', 4' and 8' lengths with single continuous lens	Design flexibility for new construction or retrofit applications	\$ ⏱️ ✓
	Encapsulated LED Lens assembly	Toolless access and quicker installation	\$ ⏱️
	Flat, round and square lens options	Design and application flexibility	⏱️ ✓
Performance	Selectable lumens and 3500, 4000 or 5000K selectable CCT options	Multi-application flexibility	\$ ⏱️
	General, narrow and wide distributions options	More choices to address mounting heights and application needs for all markets	✓
	DLC®, 5-year warranty, 60K life hours at L87	Eligible for energy rebates; certified and guaranteed performance	\$ ✓

Stock is available in the following catalog numbers:

Catalog Number	Description	Replaces Up To	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
4SNX-SL3-LW-UNV-CC83-CD1-U	4' Single Lens	2-T8 32W, 1-T5HO 54W	3500K-5000K	120-277V	2000-6100	17/33/51	080083265107	S-Z5CGBY
8TSNX-SL3-LW-UNV-CC83-CD2-U	8' Single Lens	4-T8 32W, 2-T12 75W	3500K-5000K	120-277V	4100-12000	34/67/101	080083265114	S-V503E2

