
Project	Catalog #	Туре	
Prepared by	Notes	Date	



HALO

SMD6 Surface Mount LED Downlight

The HALO SMD Surface Mount Downlight combines modern style with high performance, suitable for new construction, remodel, and retrofit projects. Its sleek design remains unchanged, but the installation process is now easier thanks to a new twist and lock mounting bracket. This bracket ensures a secure, gap-free fit, providing a flawless finish. The SMD series can be installed directly to a junction box or recessed housings, making it versatile for any lighting project. Enjoy the perfect blend of style and functionality with a hassle-free installation.

Typical Applications Residential



Interactive Menu

- Order Information page 2
- Product Specifications page 3
- Photometric Data page 4
- Product Warranty




























Top Product Features

- 6" Surface Mount Downlight
- · Redesigned Mounting Bracket for faster installation
- Installs in many 3-1/2" and 4" (30/40) square, octagonal, or round junction boxes
- 5-color Field-SeleCCTable (27/30/35/40/5000K); 90+ CRI
- Brightness (@3000K): 800 lm (Round); 710 lm (Square)
- Dimming: Dims to 5% (phase cut LE/TE) with compatible dimmers; 120V input
- · Mounting hardware, orange LED Quick Connect and E26 adapter included
- Decorative Overlays (sold separately)
- AIR-TITE, wet location-listed, IC-rated, and ENERGY STAR® certified
- · 50,000 hrs of maintenance-free operation
- 5-year warranty

Dimensional and Mounting Details









Order Information

Catalog Number	Description	Lumens (@3000K)	сст	Finish	Driver Compatibilty	Packaging
SMD6R07FS5	6" Round Surface Mount LED Downlight	800 lm	90+ CRI, Field Selectable CCT: 2700/3000/3500/4000/5000K	Matte White	120V 60Hz, LE & TE phase cut 100–5% dimming	Plastic-free recyclable
SMD6S07FS5	6" Square Surface Mount LED Downlight	710 lm	90+ CRI, Field Selectable CCT: 2700/3000/3500/4000/5000K	Matte White	120V 60Hz, LE & TE phase cut 100–5% dimming	Plastic-free recyclable

Multi-packs

Catalog Number	Description	Lumens (@3000K)	сст	Finish	Driver Compatibilty	Packaging
SMD6R07FS5-6PK	6" Round Surface Mount LED Downlight 6 Pack	800 lm	90+ CRI, Field Selectable CCT: 2700/3000/3500/4000/5000K	Matte White	120V 60Hz, LE & TE phase cut 100–5% dimming	6 Pack Plastic-free recyclable
SMD6S07FS5-6PK	6" Square Surface Mount LED Downlight 6 Pack	710 lm	90+ CRI, Field Selectable CCT: 2700/3000/3500/4000/5000K	Matte White	120V 60Hz, LE & TE phase cut 100–5% dimming	6 Pack Plastic-free recyclable

Accessories						
Catalog Number	Finish					
SMD6RTRMWH	6" Round Decorative Overlay	Paintable Matte White				
SMD6RTRMMB	6" Round Decorative Overlay	Matte Black				
SMD6RTRMSN	6" Round Decorative Overlay	Satin Nickel				
SMD6RTRMTBZ	6" Round Decorative Overlay	Tuscan Bronze				
SMD6STRMWH	6" Square Decorative Overlay	Paintable Matte White				
SMD6STRMMB	6" Square Decorative Overlay	Matte Black				
SMD6STRMSN	6" Square Decorative Overlay	Satin Nickel				
SMD6STRMTBZ	6" Square Decorative Overlay	Tuscan Bronze				

Decorative Overlays









SMD6RTRMWH Paintable Matte White

SMD6RTRMMB Matte Black

SMD6RTRMSN Satin Nickel

SMD6RTRMTB7 Tuscan Bronze









SMD6STRMWH

SMD6STRMMB

SMD6STRMSN

SMD6STRMTBZ

Compatible Junction Boxes²



Octagon Steel Light Fixture w/Fan Box



Square Steel Deep Box



Round New Work Fixture Box (Plastic) 4" Diameter x 2-3/16"



New Work Ceiling Box (Plastic) 3-1/2" Diameter x 2-3/4"



Old Work Box (Plastic) 4-1/4" Diameter flange (3-1/2" I.D.) x 2-5/8"



New Work Fixture Box (Plastic) w/Bar Hanger



For non-metallic cable 4" x 4" x 2-1/8'



TP317 For metal clad cable 4" x 4" x 2-1/8"



Cat #: JB4FR2 4" NC JBox for Fire Rated Ceilings 4" diameter x 5-1/2" (102mm x 140mm)

2. This is a representative list of compatible junction boxes only. Information contained in this literature about other manufacturers' products is from published information made available by the manufacturer and is deemed to be reliable, but has not been verified. Cooper Lighting Solutions makes no specific recommendation on product selection and there are no warranties of performance or compatibility implied. Installer must determine that site conditions are suitable to allow proper installation of the mounting bracket in the box.

Compatible Housings

HALO - 4" Housings 3

Standard Housing	H99ICAT, H99RTAT, H99TAT, E4ICATSB, E4RTATSB
LED Housing H995ICAT, H995RICAT, H245ICAT	
Shallow Housing	H245ICAT, H245RICAT

HALO - 5" Housings 4

HALO LED Housings	O LED Housings H550ICAT, H550RICAT, E550ICAT, E550RICAT	
Standard Housings	H5ICAT, H5ICATNB, H5RICAT, H5T, H5TNB, H5RT, E5ICAT, E5ICATNB, E5RICAT, E5RTAT, E5TAT, E5TATNB	
Shallow Housings	H25ICAT, H25RICAT, H25ICATNB, H2550ICAT	
Fire Rated Housings	H550FR2ICAT	

HALO - 6" Housings 5

HALO LED	H750ICAT, H750RICAT, H750TCP, H2750ICAT, H2750RICAT, E750ICAT, E750RICAT
Standard Housing H7ICAT, H7ICATNB, H7ICTNB, H7INB, H7UICAT, H7TCP, H7RICAT, H7RICT, E7ICAT, E7ICATNB, E7RICAT, E7RTAT E7TATNB, H7ICATNB, H7ICATNB, H7INB	
Shallow Housing	H27ICAT, H27RICAT, H27ICT, H27RICT, H27T, H27RT, E27ICAT, E27RICAT, E27TAT, E27RTAT, H2750ICAT
Fire Rated Housing	H750FR2ICAT

- 3. This fixture is UL Certified for use with any 4" diameter recessed housing constructed of steel or aluminum with an internal volume that exceeds 62.3 in³ addition to those noted above.
- 4. This fixture is UL Certified for use with any 5" diameter recessed housing constructed of steel or aluminum with an internal volume that exceeds 107.9" in addition to those noted below and does not exceed the input rating of the housing.
- 5. The fixutre is UL Certified for use with any 6" diameter recessed luminaire constructed of steel or aluminum with an internal volume that exceeds 97.4 in³ addition to those noted below and does not exceed the input rating of the luminaire.

Product Specifications

Module

- · Non-electrically conductive polycarbonate frame.
- Stamped aluminum heat sink provides passive thermal cooling achieving L70 at 50,000 hrs in IC (insulation contact) and non-IC applications

Selectable System

- Use the CCT select switch to choose between 5 color temperatures.
- Color Temperature: Selectable color temperature (2700K, 3000K, 3500K, 4000K, 5000K)
- Factory default is set to 3000K

LED Array

- · Color Quality: 90+ CRI minimum, R9 greater than 50
- Color Accuracy within 4 SDCM at the CCT endpoints provides excellent color quality and uniformity
- Factory default color temperature (CCT) is set to bright white (3000K)
- Mid power led array provide a uniform source with high efficiency and long life
- Expected Life: L70 at 50,000 hours projected in accordance with TM-21

Optical Assembly

 Precision engineered optic provides uniform luminance from a low-profile convex lens

Driver & Dimming

- Integral 120V 60Hz constant current driver provides noise-free, high-efficiency operation
- Dimmable: Continuous, flicker-free phase cut (leading-edge/trailing-edge - LE/TE) dimming from 100% to 5% output with compatible dimmers
- See this fixture's Dimming Guide for compatible dimmers

- Tip: For optimal dimming performance, consider dimmers with low-end trim adjustment; note that some dimmers require a neutral wire in the box
- Wiring: Includes electrical orange LED Quick Connect and E26 medium socket adapter provides mains connections for recessed housing installations. (Reference installation instructions for complete mounting steps.)

Electrical Junction Box Mounting

- Installs from below the ceiling in most 30 (3-1/2") and 40 (4") standard square/round/octagonal junction boxes
- May be used in compatible electrical junction boxes in direct contact with insulation, including spray foam insulation
- Installer must ensure compatibility of fit, wiring, and proper mounting in the electrical junction box. This includes all applicable national and local electrical and building coded NEMA LSD 57-2013
- Reference installation instructions for complete mounting steps

Recessed Housing Mounting

- Installs from below the ceiling to HALO 6" recessed housings with included extension springs (non-California product only)
- Not for use in recessed housings in direct contact with spray foam insulation refer to NEMA LSD 57-2013
- The included wire nuts, LED connector, and E26 medium socket adapter provide easy mounting to recessed housings (non-California product only)
- Reference installation instructions for complete mounting steps

Compliance

- · cULus certified for US and Canada
- Wet location listed
- · Airtight per ASTM-E283 (no gasket necessary)
- Suitable for use in clothes closets when installed in accordance with the NEC 410.16 spacing requirements
- EMI/RFI emissions per FCC 47CFR Part 15 consumer limits
- · Contains no mercury or lead and RoHS compliant1
- Photometric testing in accordance with IES LM-79-08
- Lumen maintenance projections in accordance with IES LM-80-08 and TM-21-11
- ENERGY STAR® certified, reference Certified Light Fixtures database
- Certified to State of California Title 20, State regulated LED Lamp; reference Modernized Appliance Efficiency Database System (MAEDBS) for State-regulate d LED Lamp
- Can be used for State of California Title 24 high efficacy LED compliance under JA8¹, reference Modernized Appliance Efficiency Database System (MAEDBS) for 2022 JA8 High Efficacy Lighting

Warranty

 Five year limited warranty, consult website for details. <u>www.cooperlighting.com/warranty</u>




Energy Data

	120V	(Triac)
	Round	Square
	SMD6R07FS5	SMD6S07FS5
Lumens	715	715
Input Voltage (V)	120V	120V
Input Current (A)	74mA	74mA
Input Power (W)	7.9W	7.9W
Efficiency	80%	80%
Inrush (A)	2.08A @ 16usec	2.08A @ 16usec
THDi (%)	<20	<20
PF	>0.9	>0.9
T Ambient	-30 to +40 °C	-30 to +40 °C
Sound Rating	<22db @1feet	<22db @1feet
Efficacy(LPW)	>90	>90

SMD6R07FS5 (Equivalent to 60W Incandescent)					
CCT	Watts	Lumens	LPW	CRI	
2700K	7.9	790	100	93	
3000K	8.10	800	98.8	93	
3500K	8.1	790	97.5	93	
4000K	8.1	790	97.5	93	
5000K	8.0	770	96.3	93	

SMD6S07FS5 (Equivalent to 60W Incandescent)				
CCT	Watts	Lumens	LPW	CRI
2700K	8.1	705	86.8	93
3000K	7.90	710	90	93
3500K	8.2	720	84.7	93
4000K	8.2	730	96.3	93
5000K	8.1	720	85.7	93

Photometric Data



SMD6R07FS5-3000K

Spacing criterion: (0-180) 1.26 | (90-270) 1.24 (Diagonal) 1.38 Beam Angle: 113° Field Angle: 164° Lumens: 800 Input Watts: 8.1 W Efficacy: 98.8 LPW


UGR: 27.5 Test Report: P991384

Zonal Lumen	Lumens	% Lumens
0-30	214.9	27
0-40	352	44
0-60	624	78
0-90	799.6	100

CCT: Range of 2700K - 5000K



113°



SMD6S07FS5-3000K

Spacing criterion: (0-180) 1.26 | (90-270) 1.25

(Diagonal) 1.37 Beam Angle: 114° Field Angle: 165° Lumens: 710 Input Watts: 7.9 W Efficacy: 89.9 LPW UGR: 27.5

Test Report: P991379

Zonal Lumen	Lumens	% Lumens
0-30	189	27
0-40	309.5	44
0-60	549.4	77
0-90	709.9	100

CCT: Range of 2700K - 5000K



